

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644506

Luminaire Tested: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644506
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7626.5 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 67.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644506

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644506

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																			
1	101	97	94	91	94	91	88	86	79	77	75	67	66	65	57	56	55	51																			
2	94	87	82	78	87	82	77	74	71	68	65	62	59	57	53	51	50	46																			
3	87	79	73	68	81	74	69	64	65	61	58	57	54	51	49	47	45	41																			
4	81	71	64	59	75	67	61	57	59	55	51	52	49	46	45	43	41	37																			
5	75	65	58	52	70	61	55	50	54	49	46	48	44	41	42	39	37	34																			
6	70	59	52	47	65	56	49	45	50	45	41	44	40	37	39	36	34	31																			
7	65	54	47	42	61	51	45	40	46	41	37	41	37	34	36	33	31	28																			
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	33	30	28	26																			
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24																			
10	53	42	36	31	50	40	34	30	36	31	28	33	29	26	29	26	24	22																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	33886	33886	33886
5°	33630	34092	34757
10°	34175	34848	35418
15°	35028	35504	35740
20°	35218	35544	35137
25°	34544	34630	34206
30°	33028	32940	32145
35°	30152	29903	29280
40°	25048	24682	24215
45°	15733	17898	15012
50°	6034	10598	5596
55°	2846	4448	2892
60°	1377	2245	1225
65°	1268	1330	1146
70°	1269	1269	1118
75°	1283	1283	1083
80°	1324	1175	1027
85°	1467	1171	874

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17898 cd/sqm



TEST NUMBER: P644506

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.7	3.3
10°-20°	747.4	9.8
20°-30°	1110.2	14.6
30°-40°	1162.0	15.2
40°-50°	703.8	9.2
50°-60°	162.4	2.1
60°-70°	44.6	0.6
70°-80°	26.1	0.3
80°-90°	10.5	0.1
90°-100°	78.0	1.0
100°-110°	555.6	7.3
110°-120°	754.3	9.9
120°-130°	613.9	8.1
130°-140°	493.8	6.5
140°-150°	389.3	5.1
150°-160°	284.7	3.7
160°-170°	176.8	2.3
170°-180°	60.3	0.8
0°-30°	2110.3	27.7
0°-40°	3272.3	42.9
0°-60°	4138.5	54.3
0°-90°	4219.8	55.3
90°-120°	1387.9	18.2
90°-150°	2884.9	37.8
90°-180°	3407.0	44.7
0°-180°	7626.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2623	2623	2623	2623	2623	
5°	2594	2654	2629	2640	2681	248
15°	2619	2699	2655	2634	2673	737
25°	2424	2495	2430	2367	2400	1110
35°	1912	1941	1896	1853	1857	1175
45°	861	979	980	945	822	661
55°	126	144	198	136	128	131
65°	42	43	44	40	38	42
75°	26	26	26	24	22	27
85°	10	10	8	8	6	10
90°	0	4	8	12	12	2
95°	32	59	32	36	44	36
105°	124	190	722	922	610	130
115°	219	266	622	1293	1512	218
125°	315	358	586	1025	1212	280
135°	391	434	590	844	969	301
145°	463	502	594	736	814	291
155°	542	562	606	667	698	249
165°	602	610	622	638	650	169
175°	634	638	634	630	626	60
180°	634	634	634	634	634	



TEST NUMBER: P644506

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2623.4	2623.4	2623.4	2623.4	2623.4
2.5°	2598.1	2644.4	2618.6	2620.7	2642.3
5°	2593.7	2653.6	2629.3	2640.1	2680.6
7.5°	2600.8	2663.4	2649.0	2652.8	2697.2
10°	2605.6	2671.2	2656.9	2656.0	2700.4
12.5°	2616.6	2685.4	2658.5	2652.8	2695.7
15°	2619.4	2698.6	2655.0	2634.1	2672.7
17.5°	2593.7	2681.0	2622.2	2579.0	2609.9
20°	2562.1	2651.0	2585.8	2525.3	2556.2
22.5°	2513.1	2600.4	2530.5	2465.3	2497.7
25°	2423.8	2495.3	2429.8	2367.3	2400.1
27.5°	2310.8	2361.1	2304.9	2245.7	2264.2
30°	2214.4	2264.7	2208.5	2147.5	2155.2
32.5°	2107.0	2149.5	2094.7	2040.0	2046.1
35°	1912.2	1941.2	1896.4	1853.0	1856.9
37.5°	1675.2	1679.0	1648.7	1609.2	1610.0
40°	1485.5	1497.1	1463.8	1432.3	1436.1
42.5°	1259.5	1305.1	1272.6	1244.1	1244.9
45°	861.3	979.1	979.8	945.4	821.8
47.5°	475.7	612.0	699.7	542.6	409.7
50°	300.3	387.2	527.4	317.2	278.5
52.5°	214.9	253.9	385.2	224.3	204.3
55°	126.4	143.8	197.5	136.1	128.4
57.5°	77.0	92.1	115.4	91.0	77.4
60°	53.3	66.9	86.9	60.9	47.4
62.5°	47.0	51.3	68.0	48.5	44.2
65°	41.5	43.4	43.5	39.5	37.5
67.5°	36.7	38.7	36.7	34.7	32.8
70°	33.6	35.5	33.6	31.6	29.6
72.5°	30.4	32.4	30.4	28.4	26.5
75°	25.7	25.7	25.7	23.7	21.7
77.5°	20.9	20.9	20.5	18.9	17.0
80°	17.8	17.8	15.8	15.8	13.8
82.5°	14.6	14.6	12.6	12.6	10.7
85°	9.9	9.9	7.9	7.9	5.9
87.5°	4.7	5.5	4.8	5.5	4.0
90°	0.0	3.9	8.0	12.0	12.0
92.5°	9.6	13.5	17.5	24.8	27.9
95°	31.9	59.2	31.9	36.1	43.9
97.5°	56.6	113.6	234.5	69.2	59.8
100°	75.8	142.1	470.7	138.5	91.7
102.5°	94.9	164.3	636.6	365.6	200.2
105°	123.6	189.9	721.9	922.3	610.3
107.5°	152.4	202.3	689.2	1342.2	1257.2
110°	171.5	218.3	670.1	1410.4	1515.7



TEST NUMBER: P644506

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.7	237.5	650.9	1370.5	1547.6
115°	219.4	266.2	622.2	1293.3	1511.7
117.5°	248.9	294.9	615.0	1209.7	1434.3
120°	271.2	314.1	602.3	1146.1	1380.1
122.5°	287.2	333.2	586.3	1091.4	1306.7
125°	315.1	358.0	586.3	1025.3	1212.5
127.5°	338.2	381.9	587.1	948.7	1133.6
130°	351.0	397.8	590.3	897.4	1072.9
132.5°	367.0	413.8	590.3	874.4	1018.7
135°	390.9	433.8	590.3	844.4	969.2
137.5°	410.8	456.8	590.3	811.3	918.2
140°	426.8	469.7	590.3	792.0	889.5
142.5°	442.7	482.5	593.5	769.5	860.7
145°	462.7	501.7	594.3	735.7	813.7
147.5°	486.6	520.9	599.1	711.3	771.4
150°	502.6	533.8	602.3	695.2	745.9
152.5°	518.5	546.6	602.3	682.2	723.5
155°	542.5	562.0	606.3	666.8	698.0
157.5°	561.6	580.3	611.1	657.0	679.7
160°	574.4	590.0	614.2	650.6	670.1
162.5°	583.9	599.5	617.4	647.3	660.5
165°	602.3	610.1	622.2	638.4	650.1
167.5°	612.7	619.7	626.2	634.4	641.4
170°	622.2	626.1	626.2	634.3	638.2
172.5°	625.4	632.4	629.4	631.1	635.0
175°	634.2	638.1	634.2	630.1	626.2
177.5°	634.2	637.3	634.2	634.1	631.0
180°	634.2	634.2	634.2	634.2	634.2

(END OF REPORT)