

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331553-830

Luminaire Tested: **S122DIW-S675D1440U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331553-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D1440U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7979.5 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.1	1.2
10°-20°	264.8	3.3
20°-30°	389.2	4.9
30°-40°	452.1	5.7
40°-50°	451.6	5.7
50°-60°	393.8	4.9
60°-70°	291.2	3.6
70°-80°	164.9	2.1
80°-90°	48.9	0.6
90°-100°	61.8	0.8
100°-110°	226.6	2.8
110°-120°	605.8	7.6
120°-130°	1000.0	12.5
130°-140°	1063.4	13.3
140°-150°	988.4	12.4
150°-160°	794.7	10.0
160°-170°	512.1	6.4
170°-180°	176.3	2.2
0°-30°	748.0	9.4
0°-40°	1200.1	15.0
0°-60°	2045.4	25.6
0°-90°	2550.4	32.0
90°-120°	894.2	11.2
90°-150°	3946.0	49.5
90°-180°	5429.0	68.0
0°-180°	7979.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	16	27	33	36	6
95°	87	46	52	58	58	107
105°	408	425	82	96	102	435
115°	771	794	827	236	110	759
125°	1090	1108	1133	1142	1146	971
135°	1349	1369	1382	1395	1393	1041
145°	1564	1564	1586	1594	1589	978
155°	1723	1712	1726	1734	1724	793
165°	1815	1808	1811	1819	1811	513
175°	1857	1848	1850	1858	1846	177
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.1	14.4	14.7	15.1	15.4	15.6	15.7	15.8	16.0	16.1	15.9
90°	1.3	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3
92.5°	27.1	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9
95°	87.1	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7
97.5°	173.0	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2
100°	237.2	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8
102.5°	308.0	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6
105°	407.6	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0
107.5°	520.9	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1
110°	593.9	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8



TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	662.5	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1
115°	770.8	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2
117.5°	867.6	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8
120°	938.4	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2
122.5°	998.4	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0
125°	1089.9	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8
127.5°	1172.7	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1
130°	1225.2	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7
132.5°	1278.8	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7
135°	1348.6	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1
137.5°	1419.1	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7
140°	1465.2	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4
142.5°	1503.8	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8
145°	1564.4	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9
147.5°	1617.2	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2
150°	1651.5	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4
152.5°	1680.5	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1
155°	1722.6	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3
157.5°	1755.6	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7
160°	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6
162.5°	1792.0	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0
165°	1815.1	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2
167.5°	1832.2	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0
170°	1841.9	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6
172.5°	1848.3	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0
175°	1856.6	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0
177.5°	1857.9	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	15.7	15.5	15.3	15.2	15.1	15.1	15.0	14.9
90°	29.8	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	32.6	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	55.2	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	72.4	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	81.2	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	84.7	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	88.3	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	107.8	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	175.0	145.2	115.5	101.1	102.4	103.5	104.7	105.9





TEST NUMBER: P331553-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	374.4	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	551.3	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	849.4	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	989.8	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1050.2	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1136.9	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1217.1	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1268.0	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1317.4	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1388.0	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1453.6	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1496.0	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1535.2	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1590.0	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1637.8	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1667.2	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1693.9	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1730.1	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1760.7	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1778.4	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1795.0	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1832.1	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1840.7	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1847.1	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1854.1	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1854.8	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)