

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331554-830

Luminaire Tested: **S122DIW-S675D1440U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331554-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D1440U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7260.8 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.1	1.3
10°-20°	264.8	3.6
20°-30°	389.2	5.4
30°-40°	452.1	6.2
40°-50°	451.6	6.2
50°-60°	393.8	5.4
60°-70°	291.2	4.0
70°-80°	164.9	2.3
80°-90°	51.1	0.7
90°-100°	106.7	1.5
100°-110°	331.4	4.6
110°-120°	566.4	7.8
120°-130°	744.9	10.3
130°-140°	836.1	11.5
140°-150°	819.8	11.3
150°-160°	687.6	9.5
160°-170°	456.0	6.3
170°-180°	159.4	2.2
0°-30°	748.0	10.3
0°-40°	1200.1	16.5
0°-60°	2045.4	28.2
0°-90°	2552.6	35.2
90°-120°	1004.5	13.8
90°-150°	3405.2	46.9
90°-180°	4708.0	64.8
0°-180°	7260.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	19	50	47	48	6
95°	74	87	91	91	88	85
105°	306	310	313	315	316	323
115°	568	576	574	572	568	562
125°	827	839	836	831	830	739
135°	1070	1085	1088	1087	1083	826
145°	1299	1309	1317	1318	1313	811
155°	1485	1489	1493	1500	1496	683
165°	1616	1614	1614	1623	1617	455
175°	1681	1677	1674	1683	1675	160
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.1	14.5	15.0	15.4	15.8	16.5	17.6	18.7	19.7	20.7	20.1
90°	1.4	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1
92.5°	25.3	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3
95°	73.9	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0
97.5°	135.0	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9
100°	180.5	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0
102.5°	228.2	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0
105°	305.5	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2
107.5°	383.3	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8
110°	433.4	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.0	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6
115°	568.4	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7
117.5°	648.6	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2
120°	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9
122.5°	750.8	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7
125°	827.0	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5
127.5°	901.2	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1
130°	947.7	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8
132.5°	1000.0	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3
135°	1070.0	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2
137.5°	1143.6	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8
140°	1187.9	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8
142.5°	1233.4	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2
145°	1298.7	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5
147.5°	1357.0	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4
150°	1396.8	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9
152.5°	1432.0	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6
155°	1484.9	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0
157.5°	1530.0	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6
160°	1557.4	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5
162.5°	1582.3	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5
165°	1615.6	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4
167.5°	1643.4	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2
170°	1658.2	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7
172.5°	1668.5	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0
175°	1680.9	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1
177.5°	1686.1	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	19.4	18.9	18.2	17.8	17.7	17.5	17.4	17.3
90°	48.4	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.4	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.2	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	313.9	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.1	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	442.0	441.4	440.5	439.5	438.6	437.6





TEST NUMBER: P331554-830

CATALOG NUMBER: S122DIW-S675D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.8	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.4	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	650.4	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	755.0	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	833.6	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	909.9	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	962.1	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1013.0	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.8	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.5	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.5	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1317.9	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.0	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1496.6	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1539.7	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1565.4	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1588.7	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1618.6	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1643.3	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1657.0	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1667.2	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1678.3	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)