

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644711

Luminaire Tested: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P644711  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1250 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9300.8 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 87.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644711  
CATALOG NUMBER: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644711

CATALOG NUMBER: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	100	97	94	91	93	90	88	85	78	76	74	66	65	63	55	54	54	49				
2	93	87	82	78	87	81	77	73	71	67	65	61	58	57	51	50	49	44				
3	87	79	73	68	80	74	68	64	64	60	57	56	53	51	48	46	44	40				
4	80	71	65	59	75	67	61	57	59	54	51	51	48	45	44	42	40	37				
5	75	65	58	53	70	61	55	50	54	49	45	47	44	41	41	38	36	33				
6	70	59	52	47	65	56	49	45	49	44	41	43	40	37	38	35	33	31				
7	65	54	47	42	61	51	45	40	45	41	37	40	36	34	35	32	30	28				
8	61	50	43	38	57	47	41	36	42	37	34	37	33	31	33	30	28	26				
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24				
10	53	42	36	31	50	40	34	30	36	31	28	32	28	26	29	26	24	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	41352	41352	41352
5°	40796	41672	42320
10°	41498	42547	43006
15°	42643	43278	43345
20°	42837	43318	42597
25°	41851	42314	41388
30°	39623	40070	38915
35°	36018	36018	35269
40°	29624	29329	28697
45°	17714	20817	16891
50°	5725	11601	5373
55°	2027	3882	2027
60°	129	1098	65
65°	76	76	0
70°	94	0	0
75°	0	0	0
80°	0	0	0
85°	371	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 20817 cd/sqm



TEST NUMBER: P644711

CATALOG NUMBER: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	308.0	3.3
10°-20°	911.4	9.8
20°-30°	1348.7	14.5
30°-40°	1394.0	15.0
40°-50°	811.1	8.7
50°-60°	137.4	1.5
60°-70°	5.4	0.1
70°-80°	0.8	0.0
80°-90°	2.6	0.0
90°-100°	100.3	1.1
100°-110°	714.6	7.7
110°-120°	970.2	10.4
120°-130°	789.6	8.5
130°-140°	635.1	6.8
140°-150°	500.7	5.4
150°-160°	366.1	3.9
160°-170°	227.4	2.4
170°-180°	77.5	0.8
0°-30°	2568.0	27.6
0°-40°	3962.0	42.6
0°-60°	4910.6	52.8
0°-90°	4919.3	52.9
90°-120°	1785.1	19.2
90°-150°	3710.5	39.9
90°-180°	4382.0	47.1
0°-180°	9300.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3201	3201	3201	3201	3201	
5°	3146	3230	3214	3222	3264	301
15°	3189	3301	3236	3219	3241	897
25°	2936	3034	2969	2880	2904	1341
35°	2284	2321	2284	2227	2237	1399
45°	970	1128	1140	1101	925	750
55°	90	105	172	97	90	99
65°	2	2	2	0	0	3
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	5	10	15	15	2
95°	41	76	41	46	56	46
105°	159	244	928	1186	785	168
115°	282	342	800	1663	1944	280
125°	405	460	754	1319	1560	360
135°	503	558	759	1086	1247	387
145°	595	645	764	946	1046	374
155°	698	723	780	858	898	320
165°	775	785	800	821	836	218
175°	816	821	816	810	805	77
180°	816	816	816	816	816	



TEST NUMBER: P644711

CATALOG NUMBER: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3201.4	3201.4	3201.4	3201.4	3201.4
2.5°	3159.4	3222.0	3199.4	3201.7	3217.4
5°	3146.4	3229.5	3213.9	3222.3	3263.9
7.5°	3155.9	3240.0	3237.9	3240.3	3280.9
10°	3163.9	3251.9	3243.9	3242.2	3278.9
12.5°	3179.9	3275.7	3243.9	3240.1	3270.9
15°	3188.9	3301.3	3236.4	3219.4	3241.4
17.5°	3158.4	3283.5	3195.4	3150.1	3158.9
20°	3116.4	3243.5	3151.4	3084.3	3098.9
22.5°	3050.4	3171.6	3089.4	3006.4	3024.9
25°	2936.5	3034.2	2969.0	2879.6	2904.0
27.5°	2774.5	2851.7	2810.5	2723.9	2739.0
30°	2656.6	2720.1	2686.6	2601.8	2609.1
32.5°	2520.6	2574.4	2538.6	2465.6	2465.1
35°	2284.2	2320.9	2284.2	2226.9	2236.7
37.5°	1974.8	2002.7	1965.3	1930.9	1935.8
40°	1756.9	1778.9	1739.4	1706.8	1701.9
42.5°	1485.0	1546.1	1507.5	1463.1	1470.0
45°	969.7	1128.5	1139.6	1100.6	924.7
47.5°	488.8	662.3	793.2	601.9	431.3
50°	284.9	390.0	577.3	318.7	267.4
52.5°	186.9	231.4	403.4	201.4	177.4
55°	90.0	104.6	172.4	97.3	90.0
57.5°	31.0	47.6	76.5	48.7	34.5
60°	5.0	19.7	42.5	14.7	2.5
62.5°	3.0	5.9	26.5	2.9	0.5
65°	2.5	2.5	2.5	0.0	0.0
67.5°	2.5	2.5	0.0	0.0	0.0
70°	2.5	2.5	0.0	0.0	0.0
72.5°	2.5	2.5	0.0	0.0	0.0
75°	0.0	2.4	0.0	0.0	0.0
77.5°	0.0	2.4	0.0	0.0	0.0
80°	0.0	2.4	0.0	0.0	0.0
82.5°	0.0	2.4	0.0	0.0	0.0
85°	2.5	2.5	0.0	0.0	0.0
87.5°	2.0	3.0	2.1	3.1	3.1
90°	0.0	5.0	10.3	15.4	15.4
92.5°	12.3	17.3	22.6	31.9	35.9
95°	41.0	76.2	41.0	46.4	56.4
97.5°	72.8	146.1	301.6	89.0	77.0
100°	97.5	182.7	605.3	178.2	118.0
102.5°	122.1	211.4	818.7	470.2	257.5
105°	159.0	244.3	928.5	1186.2	784.9
107.5°	196.0	260.2	886.5	1726.3	1617.0
110°	220.6	280.8	861.8	1814.0	1949.4



TEST NUMBER: P644711

CATALOG NUMBER: OMN4DIP-SR4F0-125D125U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	245.2	305.4	837.2	1762.7	1990.4
115°	282.2	342.3	800.3	1663.4	1944.3
117.5°	320.1	379.3	791.0	1555.8	1844.8
120°	348.8	404.0	774.6	1474.0	1775.0
122.5°	369.4	428.5	754.1	1403.7	1680.6
125°	405.3	460.4	754.1	1318.8	1559.5
127.5°	435.0	491.2	755.1	1220.2	1457.9
130°	451.4	511.6	759.2	1154.3	1380.0
132.5°	472.0	532.2	759.2	1124.6	1310.2
135°	502.7	557.9	759.2	1086.1	1246.6
137.5°	528.4	587.6	759.2	1043.5	1180.9
140°	548.9	604.1	759.2	1018.6	1144.0
142.5°	569.4	620.6	763.3	989.7	1107.1
145°	595.1	645.2	764.4	946.2	1046.5
147.5°	625.9	670.0	770.5	914.9	992.1
150°	646.4	686.5	774.6	894.1	959.3
152.5°	666.9	703.0	774.6	877.4	930.6
155°	697.7	722.8	779.8	857.6	897.8
157.5°	722.3	746.4	785.9	845.1	874.2
160°	738.7	758.8	790.0	836.8	861.8
162.5°	751.0	771.1	794.1	832.5	849.5
165°	774.6	784.7	800.3	821.1	836.2
167.5°	788.0	797.0	805.4	815.9	824.9
170°	800.3	805.3	805.4	815.8	820.8
172.5°	804.4	813.4	809.5	811.7	816.7
175°	815.7	820.7	815.7	810.4	805.4
177.5°	815.7	819.7	815.7	815.6	811.6
180°	815.7	815.7	815.7	815.7	815.7

(END OF REPORT)