

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331574-830

Luminaire Tested: **S122DIW-S865D1240U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331574-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D1240U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7645.6 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.0	2.0
10°-20°	450.6	5.9
20°-30°	653.9	8.6
30°-40°	690.0	9.0
40°-50°	611.0	8.0
50°-60°	487.6	6.4
60°-70°	331.4	4.3
70°-80°	169.9	2.2
80°-90°	46.7	0.6
90°-100°	91.8	1.2
100°-110°	285.0	3.7
110°-120°	487.2	6.4
120°-130°	640.7	8.4
130°-140°	719.1	9.4
140°-150°	705.1	9.2
150°-160°	591.4	7.7
160°-170°	392.2	5.1
170°-180°	137.1	1.8
0°-30°	1259.4	16.5
0°-40°	1949.5	25.5
0°-60°	3048.0	39.9
0°-90°	3596.0	47.0
90°-120°	864.0	11.3
90°-150°	2928.8	38.3
90°-180°	4050.0	53.0
0°-180°	7645.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	42	1	42	1	42	20
95°	76	64	76	64	76	84
105°	271	263	271	263	271	285
115°	489	489	489	489	489	483
125°	714	711	714	711	714	636
135°	931	920	931	920	931	717
145°	1129	1117	1129	1117	1129	705
155°	1287	1277	1287	1277	1287	592
165°	1391	1390	1391	1390	1391	392
175°	1441	1446	1441	1446	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	21.3	21.3	21.7	21.1	21.1	21.6	21.8	21.3	22.0	22.5	21.9
90°	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7	42.2	42.8	36.8
92.5°	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1	38.9	38.8	37.4
95°	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2	78.2	78.2	77.7
97.5°	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5	131.5	131.5	130.4
100°	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6	168.6	168.6	167.9
102.5°	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2	209.0	208.8	207.7
105°	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9	269.4	268.9	268.3
107.5°	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5	335.4	335.1	335.1
110°	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7	425.4	426.0	426.2
115°	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2	493.5	493.7	494.3
117.5°	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4	560.1	560.7	562.2
120°	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7	603.7	603.7	605.9
122.5°	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4	650.0	650.6	652.1
125°	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0	717.8	718.6	719.4
127.5°	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7	783.6	784.6	785.6
130°	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6	828.0	828.6	829.2
132.5°	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2	872.4	873.5	873.5
135°	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7	935.9	936.1	935.7
137.5°	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3	997.6	997.8	997.0
140°	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8	1038.8	1038.8	1037.5
142.5°	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4	1076.2	1076.0	1075.1
145°	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5	1133.2	1132.9	1131.3
147.5°	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5	1182.9	1182.3	1181.2
150°	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6	1212.5
152.5°	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9	1243.6
155°	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2	1285.8	1284.5	1283.6
157.5°	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4	1322.5	1320.7	1320.1
160°	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4	1344.7	1343.1	1342.8
162.5°	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4	1364.5	1362.7	1362.4
165°	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1	1390.3	1388.4	1388.4
167.5°	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4	1411.6	1409.6	1409.7
170°	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1	1423.2	1421.4	1421.6
172.5°	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0	1432.1	1430.1	1430.4
175°	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5	1441.6	1439.6	1440.2
177.5°	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3	1445.8
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	21.2	20.0	18.8	18.9	16.7	16.0	13.4	11.2	11.4	11.6	11.2
90°	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2	4.5	7.7	11.0
92.5°	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8	24.1	26.6	28.9
95°	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5	66.3	69.0	71.7
97.5°	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1	118.5	120.9	123.3
100°	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2	157.4	159.6	161.7
102.5°	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2	198.0	199.7	201.5
105°	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8	263.5	264.4	265.2
107.5°	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7	330.9	332.2	333.3
110°	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8	374.4	376.0	377.7





TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7	421.3	422.9	424.6
115°	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9	490.5	492.1	493.7
117.5°	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8	560.0	562.1	564.3
120°	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	605.9	608.1	610.3
122.5°	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7	648.4	651.0	653.6
125°	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2	713.7	716.1	718.6
127.5°	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1	778.2	781.3	784.4
130°	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2	818.7	822.3	825.8
132.5°	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2	863.0	865.9	868.7
135°	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3	923.2	926.2	929.3
137.5°	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5	986.0	988.4	990.9
140°	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7	1024.2	1026.6	1029.1
142.5°	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8	1063.3	1065.7	1068.2
145°	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0	1119.0	1120.9	1122.8
147.5°	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2	1169.4	1171.7	1174.0
150°	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4	1203.0	1204.7	1206.3
152.5°	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7	1233.3	1234.9	1236.5
155°	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1	1278.0	1278.7	1279.6
157.5°	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0	1316.5	1317.1	1317.7
160°	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4	1340.0	1340.6	1341.1
162.5°	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9	1361.1	1361.2	1361.3
165°	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6	1389.3	1389.0	1388.7
167.5°	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5	1412.7	1411.9	1411.1
170°	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3	1425.4	1424.7	1423.8
172.5°	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0	1434.3	1433.4	1432.6
175°	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8	1445.0	1444.2	1443.3
177.5°	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2	1449.5	1448.9	1448.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	11.3	11.8	12.4	13.7	14.3	15.1	14.4	14.3	14.2	13.1	13.1
90°	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7	41.2	40.6	40.4
92.5°	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1	39.2	39.3	39.4
95°	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2	78.2	78.2	77.9
97.5°	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5	131.5	131.5	131.5
100°	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6	168.6	168.6	168.5
102.5°	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2	209.4	209.6	209.6
105°	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9	270.5	271.1	271.4
107.5°	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5	335.7	336.0	335.5
110°	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	379.7



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7	424.0	423.4	422.8
115°	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2	492.9	492.7	492.1
117.5°	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4	558.7	558.1	557.4
120°	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7	603.7	603.7	603.3
122.5°	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4	648.8	648.1	647.4
125°	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0	716.1	715.4	714.8
127.5°	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7	781.7	780.7	779.8
130°	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6	827.0	826.4	825.7
132.5°	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2	870.0	868.8	867.8
135°	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7	935.4	935.1	934.5
137.5°	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3	997.1	996.9	996.3
140°	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8	1038.8	1038.8	1038.3
142.5°	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4	1076.7	1076.9	1076.4
145°	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5	1133.8	1134.0	1133.6
147.5°	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5	1184.1	1184.7	1184.5
150°	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8
152.5°	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0
155°	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2	1288.5	1289.9	1290.2
157.5°	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4	1326.2	1328.0	1328.3
160°	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4	1348.0	1349.6	1349.9
162.5°	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4	1368.2	1370.1	1370.4
165°	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1	1394.0	1396.0	1396.2
167.5°	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4	1415.3	1417.2	1417.5
170°	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1	1427.0	1429.0	1429.1
172.5°	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0	1435.9	1437.8	1437.8
175°	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5	1445.4	1447.3	1447.5
177.5°	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	13.2	12.7	12.7	12.3	12.7	12.7	13.2	13.1	13.1	14.2	14.3
90°	40.7	41.0	41.3	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7
92.5°	39.4	39.5	39.6	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1
95°	77.4	76.8	76.3	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2
97.5°	131.4	131.4	131.3	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5
100°	168.2	168.0	167.7	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6
102.5°	209.3	209.1	208.8	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2
105°	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9
107.5°	334.2	333.0	331.7	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5
110°	378.9	378.1	377.2	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	422.2	421.6	421.0	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7
115°	491.3	490.5	489.7	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2
117.5°	556.6	555.7	555.0	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4
120°	602.5	601.7	600.9	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7
122.5°	646.9	646.2	645.6	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4
125°	714.5	714.3	714.0	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0
127.5°	778.9	778.1	777.2	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7
130°	824.5	823.5	822.4	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6
132.5°	867.0	866.0	865.2	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2
135°	933.7	932.9	932.1	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7
137.5°	995.1	994.1	993.0	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3
140°	1037.2	1036.1	1035.0	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8
142.5°	1075.3	1074.2	1073.2	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4
145°	1132.6	1131.4	1130.4	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5
147.5°	1183.5	1182.4	1181.4	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5
150°	1216.1	1215.2	1214.4	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2
152.5°	1247.9	1247.0	1245.9	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0
155°	1289.4	1288.5	1287.7	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2
157.5°	1327.0	1325.7	1324.4	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4
160°	1348.9	1347.7	1346.7	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4
162.5°	1369.0	1367.7	1366.4	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4
165°	1394.9	1393.5	1392.1	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1
167.5°	1416.1	1414.7	1413.2	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4
170°	1427.5	1425.9	1424.2	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1
172.5°	1436.2	1434.6	1433.0	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0
175°	1445.8	1444.2	1442.6	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5
177.5°	1449.3	1447.9	1446.6	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	14.4	15.1	14.3	13.7	12.4	11.8	11.3	11.2	11.6	11.4	11.2
90°	42.2	42.8	36.8	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2
92.5°	38.9	38.8	37.4	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8
95°	78.2	78.2	77.7	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5
97.5°	131.5	131.5	130.4	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1
100°	168.6	168.6	167.9	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2
102.5°	209.0	208.8	207.7	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2
105°	269.4	268.9	268.3	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8
107.5°	335.4	335.1	335.1	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7
110°	380.1	380.1	380.1	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	425.4	426.0	426.2	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7
115°	493.5	493.7	494.3	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9
117.5°	560.1	560.7	562.2	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8
120°	603.7	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7
122.5°	650.0	650.6	652.1	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7
125°	717.8	718.6	719.4	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2
127.5°	783.6	784.6	785.6	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1
130°	828.0	828.6	829.2	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2
132.5°	872.4	873.5	873.5	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2
135°	935.9	936.1	935.7	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3
137.5°	997.6	997.8	997.0	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5
140°	1038.8	1038.8	1037.5	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7
142.5°	1076.2	1076.0	1075.1	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8
145°	1133.2	1132.9	1131.3	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0
147.5°	1182.9	1182.3	1181.2	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2
150°	1214.4	1213.6	1212.5	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4
152.5°	1245.9	1244.9	1243.6	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7
155°	1285.8	1284.5	1283.6	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1
157.5°	1322.5	1320.7	1320.1	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0
160°	1344.7	1343.1	1342.8	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4
162.5°	1364.5	1362.7	1362.4	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9
165°	1390.3	1388.4	1388.4	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6
167.5°	1411.6	1409.6	1409.7	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5
170°	1423.2	1421.4	1421.6	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3
172.5°	1432.1	1430.1	1430.4	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0
175°	1441.6	1439.6	1440.2	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8
177.5°	1446.6	1445.3	1445.8	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.4	16.0	16.7	18.9	18.8	20.0	21.2	21.9	22.5	22.0	21.3
90°	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7
92.5°	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1
95°	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2
97.5°	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5
100°	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6
102.5°	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2
105°	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9
107.5°	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5
110°	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1





TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7
115°	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2
117.5°	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4
120°	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7
122.5°	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4
125°	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0
127.5°	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7
130°	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6
132.5°	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2
135°	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7
137.5°	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3
140°	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8
142.5°	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4
145°	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5
147.5°	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5
150°	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2
152.5°	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0
155°	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2
157.5°	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4
160°	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4
162.5°	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4
165°	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1
167.5°	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4
170°	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1
172.5°	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0
175°	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5
177.5°	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	21.8	21.6	21.1	21.1	21.7	21.3	21.3
90°	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331574-830

CATALOG NUMBER: S122DIW-S865D1240U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)