

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331579-830

Luminaire Tested: **S122DIW-S865D1440U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331579-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9023.9 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	88	81	75	70	80	74	69	64	61	57	54	48	46	44	37	36	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	47	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	1.7
10°-20°	450.6	5.0
20°-30°	653.9	7.2
30°-40°	690.0	7.6
40°-50°	611.0	6.8
50°-60°	487.6	5.4
60°-70°	331.4	3.7
70°-80°	169.9	1.9
80°-90°	45.5	0.5
90°-100°	61.8	0.7
100°-110°	226.6	2.5
110°-120°	605.8	6.7
120°-130°	1000.0	11.1
130°-140°	1063.4	11.8
140°-150°	988.4	11.0
150°-160°	794.7	8.8
160°-170°	512.1	5.7
170°-180°	176.3	2.0
0°-30°	1259.4	14.0
0°-40°	1949.5	21.6
0°-60°	3048.0	33.8
0°-90°	3594.8	39.8
90°-120°	894.2	9.9
90°-150°	3946.0	43.7
90°-180°	5429.0	60.2
0°-180°	9023.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	36	1	36	1	36	18
95°	58	87	58	87	58	54
105°	102	408	102	408	102	106
115°	110	771	110	771	110	275
125°	1146	1090	1146	1090	1146	992
135°	1393	1349	1393	1349	1393	1073
145°	1589	1564	1589	1564	1589	993
155°	1724	1723	1724	1723	1724	795
165°	1811	1815	1811	1815	1811	511
175°	1846	1857	1846	1857	1846	176
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	20.3	20.2	20.5	19.9	19.8	20.1	19.8	18.9	19.1	19.4	19.4
90°	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8	28.3	26.8	24.4
92.5°	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6	31.9	31.1	29.9
95°	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2	53.7	52.3	50.2
97.5°	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4	71.2	69.9	65.1
100°	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2	78.8	76.4	71.4
102.5°	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7	81.6	78.5	72.9
105°	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3	85.0	81.8	76.1
107.5°	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8	111.1	114.5	120.0
110°	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0	204.8	234.6	320.7



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4	483.1	591.7	612.9
115°	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3	689.2	827.1	819.6
117.5°	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4	882.8	916.2	911.0
120°	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8	986.2	982.6	977.2
122.5°	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2	1048.0	1045.8	1040.0
125°	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9	1134.8	1132.7	1127.1
127.5°	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1	1214.1	1211.1	1206.8
130°	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0	1264.7	1261.4	1258.1
132.5°	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4	1314.7	1311.8	1308.5
135°	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0	1385.1	1382.1	1379.4
137.5°	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6	1450.7	1447.7	1444.7
140°	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0	1493.4	1490.6	1487.4
142.5°	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2	1532.8	1530.3	1526.5
145°	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0	1587.9	1585.8	1580.7
147.5°	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8	1636.2	1634.7	1629.7
150°	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2	1665.4	1663.6	1658.8
152.5°	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9	1692.1	1690.4	1685.8
155°	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1	1728.3	1726.5	1723.1
157.5°	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7	1758.7	1756.6	1754.1
160°	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4	1776.6	1774.8	1773.0
162.5°	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0	1793.0	1790.9	1789.4
165°	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0	1810.2
167.5°	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1	1830.0	1828.0	1827.1
170°	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7	1838.6	1836.5	1835.9
172.5°	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1	1845.0	1843.0	1842.4
175°	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1	1852.0	1849.9	1849.4
177.5°	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8	1853.2	1851.5	1851.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	19.4	18.9	18.5	18.9	16.8	16.1	13.5	11.3	11.4	11.6	11.2
90°	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3	4.6	7.9	11.2
92.5°	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1	26.8	26.5	26.2
95°	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1	77.3	67.5	57.7
97.5°	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0	145.2	117.5	89.8
100°	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2	196.4	155.6	114.8
102.5°	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0	299.4	290.8	282.1
105°	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6	416.4	425.4	434.3
107.5°	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9	528.1	535.4	542.5
110°	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9	600.1	606.3	612.7



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5	668.0	673.5	679.1
115°	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8	775.9	780.9	786.0
117.5°	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6	873.3	878.9	884.6
120°	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4	942.8	947.3	951.8
122.5°	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4	1003.1	1007.9	1012.6
125°	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9	1093.7	1097.6	1101.5
127.5°	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7	1177.0	1181.3	1185.5
130°	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2	1230.0	1234.7	1239.5
132.5°	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8	1282.9	1286.9	1291.0
135°	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6	1353.3	1358.1	1362.8
137.5°	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1	1422.4	1425.8	1429.1
140°	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2	1467.5	1470.0	1472.3
142.5°	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8	1505.9	1508.1	1510.2
145°	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4	1564.1	1563.8	1563.5
147.5°	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2	1616.1	1615.0	1613.8
150°	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5	1649.4	1647.4	1645.3
152.5°	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5	1678.2	1675.8	1673.5
155°	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6	1719.9	1717.2	1714.5
157.5°	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6	1753.3	1751.1	1748.8
160°	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1773.0	1771.3	1769.5
162.5°	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0	1790.3	1788.5	1786.7
165°	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1	1813.3	1811.5	1809.7
167.5°	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2	1830.4	1828.6	1826.8
170°	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9	1840.1	1838.3	1836.5
172.5°	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3	1846.5	1844.7	1843.0
175°	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6	1854.5	1852.5	1850.4
177.5°	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9	1856.3	1854.6	1852.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	11.4	11.5	11.4	11.9	11.9	11.9	11.7	12.0	12.3	11.6	11.8
90°	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8	31.3	32.8	33.8
92.5°	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6	33.5	34.2	34.8
95°	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2	56.7	58.2	58.8
97.5°	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4	73.5	74.7	75.5
100°	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2	83.6	86.0	87.5
102.5°	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7	87.8	91.0	92.9
105°	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3	91.6	94.9	97.1
107.5°	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8	104.4	101.1	100.1
110°	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0	145.2	115.5	101.1



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4	265.7	157.0	103.1
115°	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3	413.3	275.4	195.7
117.5°	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4	816.1	782.7	730.8
120°	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8	993.3	996.9	978.5
122.5°	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2	1052.3	1054.4	1051.6
125°	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9	1139.0	1141.0	1142.6
127.5°	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1	1220.1	1223.1	1224.8
130°	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0	1271.3	1274.5	1276.0
132.5°	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4	1320.2	1323.0	1324.3
135°	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0	1391.0	1394.0	1395.2
137.5°	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6	1456.5	1459.4	1460.4
140°	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0	1498.7	1501.4	1501.9
142.5°	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2	1537.7	1540.1	1540.6
145°	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0	1592.0	1594.2	1594.5
147.5°	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8	1639.3	1640.9	1641.0
150°	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2	1669.0	1670.8	1670.8
152.5°	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9	1695.7	1697.5	1697.4
155°	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1	1731.9	1733.7	1733.4
157.5°	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7	1762.6	1764.7	1764.5
160°	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4	1780.2	1782.0	1781.9
162.5°	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0	1797.1	1799.0	1798.7
165°	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4
167.5°	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1	1834.2	1836.3	1836.0
170°	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7	1842.8	1844.8	1844.6
172.5°	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1	1849.2	1851.2	1851.0
175°	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1	1856.1	1858.2	1857.8
177.5°	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8	1856.5	1858.2	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	11.9	11.5	11.6	11.2	11.6	11.5	11.9	11.8	11.6	12.3	12.0
90°	34.4	35.0	35.6	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8
92.5°	35.2	35.4	35.8	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6
95°	58.5	58.2	58.0	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2
97.5°	75.9	76.3	76.6	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4
100°	88.0	88.6	89.3	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2
102.5°	93.8	94.5	95.4	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7
105°	98.3	99.5	100.7	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3
107.5°	101.2	102.5	103.7	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8
110°	102.4	103.5	104.7	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	104.2	105.1	106.0	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4
115°	174.3	152.8	131.4	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3
117.5°	660.3	589.7	519.2	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4
120°	938.4	898.1	857.9	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8
122.5°	1043.8	1036.0	1028.2	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2
125°	1143.5	1144.3	1145.3	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9
127.5°	1224.9	1225.1	1225.3	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1
130°	1275.7	1275.4	1275.2	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0
132.5°	1324.0	1323.7	1323.4	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4
135°	1394.6	1394.0	1393.4	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0
137.5°	1459.3	1458.4	1457.4	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6
140°	1500.5	1499.0	1497.5	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0
142.5°	1539.1	1537.6	1536.2	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2
145°	1593.0	1591.5	1590.0	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0
147.5°	1639.7	1638.5	1637.2	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8
150°	1669.4	1667.9	1666.4	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2
152.5°	1695.4	1693.6	1691.6	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9
155°	1731.1	1728.7	1726.3	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1
157.5°	1762.3	1759.9	1757.6	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7
160°	1779.8	1777.6	1775.6	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4
162.5°	1796.2	1793.7	1791.1	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0
165°	1817.3	1815.2	1813.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2
167.5°	1833.3	1830.6	1828.0	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1
170°	1841.9	1839.2	1836.5	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7
172.5°	1848.3	1845.6	1843.0	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1
175°	1854.8	1851.8	1848.9	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1
177.5°	1855.8	1853.7	1851.5	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	11.7	11.9	11.9	11.9	11.4	11.5	11.4	11.2	11.6	11.4	11.3
90°	28.3	26.8	24.4	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3
92.5°	31.9	31.1	29.9	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1
95°	53.7	52.3	50.2	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1
97.5°	71.2	69.9	65.1	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0
100°	78.8	76.4	71.4	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2
102.5°	81.6	78.5	120.9	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0
105°	85.0	81.8	163.1	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6
107.5°	111.1	114.5	212.0	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9
110°	204.8	234.6	320.7	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	483.1	591.7	612.9	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5
115°	689.2	827.1	819.6	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8
117.5°	882.8	916.2	911.0	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6
120°	986.2	982.6	977.2	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4
122.5°	1048.0	1045.8	1040.0	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4
125°	1134.8	1132.7	1127.1	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9
127.5°	1214.1	1211.1	1206.8	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7
130°	1264.7	1261.4	1258.1	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2
132.5°	1314.7	1311.8	1308.5	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8
135°	1385.1	1382.1	1379.4	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6
137.5°	1450.7	1447.7	1444.7	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1
140°	1493.4	1490.6	1487.4	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2
142.5°	1532.8	1530.3	1526.5	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8
145°	1587.9	1585.8	1580.7	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4
147.5°	1636.2	1634.7	1629.7	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2
150°	1665.4	1663.6	1658.8	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5
152.5°	1692.1	1690.4	1685.8	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5
155°	1728.3	1726.5	1723.1	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6
157.5°	1758.7	1756.6	1754.1	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6
160°	1776.6	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8
162.5°	1793.0	1790.9	1789.4	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0
165°	1813.2	1811.0	1810.2	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1
167.5°	1830.0	1828.0	1827.1	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2
170°	1838.6	1836.5	1835.9	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9
172.5°	1845.0	1843.0	1842.4	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3
175°	1852.0	1849.9	1849.4	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6
177.5°	1853.2	1851.5	1851.2	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.5	16.1	16.8	18.9	18.5	18.9	19.4	19.4	19.4	19.1	18.9
90°	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8
92.5°	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6
95°	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2
97.5°	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4
100°	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2
102.5°	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7
105°	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3
107.5°	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8
110°	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4
115°	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3
117.5°	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4
120°	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8
122.5°	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2
125°	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9
127.5°	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1
130°	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0
132.5°	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4
135°	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0
137.5°	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6
140°	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0
142.5°	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2
145°	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0
147.5°	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8
150°	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2
152.5°	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9
155°	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1
157.5°	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7
160°	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4
162.5°	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0
165°	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2
167.5°	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1
170°	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7
172.5°	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1
175°	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1
177.5°	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	19.8	20.1	19.8	19.9	20.5	20.2	20.3
90°	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331579-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)