

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331584-830

Luminaire Tested: **S122DIW-S865D1440U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331584-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8024.2 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	1.5
10°-20°	344.2	4.3
20°-30°	505.9	6.3
30°-40°	587.6	7.3
40°-50°	587.0	7.3
50°-60°	511.9	6.4
60°-70°	378.5	4.7
70°-80°	214.4	2.7
80°-90°	64.4	0.8
90°-100°	106.7	1.3
100°-110°	331.4	4.1
110°-120°	566.4	7.1
120°-130°	744.9	9.3
130°-140°	836.1	10.4
140°-150°	819.8	10.2
150°-160°	687.6	8.6
160°-170°	456.0	5.7
170°-180°	159.4	2.0
0°-30°	972.3	12.1
0°-40°	1559.9	19.4
0°-60°	2658.7	33.1
0°-90°	3316.0	41.3
90°-120°	1004.5	12.5
90°-150°	3405.2	42.4
90°-180°	4708.0	58.7
0°-180°	8024.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	19	50	47	48	6
95°	74	87	91	91	88	85
105°	306	310	313	315	316	323
115°	568	576	574	572	568	562
125°	827	839	836	831	830	739
135°	1070	1085	1088	1087	1083	826
145°	1299	1309	1317	1318	1313	811
155°	1485	1489	1493	1500	1496	683
165°	1616	1614	1614	1623	1617	455
175°	1681	1677	1674	1683	1675	160
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.3	18.6	18.9	19.2	19.5	20.2	21.1	22.1	23.0	23.9	23.2
90°	1.4	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1
92.5°	25.3	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3
95°	73.9	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0
97.5°	135.0	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9
100°	180.5	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0
102.5°	228.2	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0
105°	305.5	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2
107.5°	383.3	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8
110°	433.4	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.0	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6
115°	568.4	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7
117.5°	648.6	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2
120°	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9
122.5°	750.8	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7
125°	827.0	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5
127.5°	901.2	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1
130°	947.7	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8
132.5°	1000.0	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3
135°	1070.0	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2
137.5°	1143.6	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8
140°	1187.9	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8
142.5°	1233.4	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2
145°	1298.7	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5
147.5°	1357.0	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4
150°	1396.8	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9
152.5°	1432.0	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6
155°	1484.9	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0
157.5°	1530.0	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6
160°	1557.4	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5
162.5°	1582.3	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5
165°	1615.6	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4
167.5°	1643.4	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2
170°	1658.2	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7
172.5°	1668.5	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0
175°	1680.9	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1
177.5°	1686.1	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	22.3	21.6	20.7	20.3	20.2	20.0	19.8	19.7
90°	48.4	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.4	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.2	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	313.9	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.1	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331584-830

CATALOG NUMBER: S122DIW-S865D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.8	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.4	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	650.4	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	755.0	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	833.6	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	909.9	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	962.1	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1013.0	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.8	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.5	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.5	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1317.9	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.0	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1496.6	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1539.7	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1565.4	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1588.7	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1618.6	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1643.3	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1657.0	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1667.2	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1678.3	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)