

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331565-830

Luminaire Tested: **S122DIW-S865D710U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331565-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D710U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5983.8 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	47	45	43	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24	22
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.3	2.0
10°-20°	344.2	5.8
20°-30°	505.9	8.5
30°-40°	587.6	9.8
40°-50°	587.0	9.8
50°-60°	511.9	8.6
60°-70°	378.5	6.3
70°-80°	214.4	3.6
80°-90°	59.9	1.0
90°-100°	30.4	0.5
100°-110°	111.6	1.9
110°-120°	298.2	5.0
120°-130°	492.2	8.2
130°-140°	523.5	8.7
140°-150°	486.5	8.1
150°-160°	391.2	6.5
160°-170°	252.1	4.2
170°-180°	86.8	1.4
0°-30°	972.3	16.2
0°-40°	1559.9	26.1
0°-60°	2658.7	44.4
0°-90°	3311.5	55.3
90°-120°	440.1	7.4
90°-150°	1942.3	32.5
90°-180°	2672.0	44.7
0°-180°	5983.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	8	13	16	18	4
95°	43	23	26	29	28	52
105°	201	209	40	47	50	214
115°	379	391	407	116	54	373
125°	536	545	558	562	564	478
135°	664	674	680	686	686	512
145°	770	770	781	785	782	481
155°	848	843	850	853	849	391
165°	893	890	892	896	892	252
175°	914	910	911	915	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.1	18.0	17.9	17.8	17.6	17.5	17.2	17.1	16.9	16.7	16.1
90°	0.7	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9
92.5°	13.3	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6
95°	42.9	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5
97.5°	85.1	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1
100°	116.8	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7
102.5°	151.7	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2
105°	200.6	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8
107.5°	256.4	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7
110°	292.3	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9



TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	326.1	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8
115°	379.4	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2
117.5°	427.1	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5
120°	461.8	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4
122.5°	491.4	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9
125°	536.4	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6
127.5°	577.2	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6
130°	603.0	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5
132.5°	629.5	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1
135°	663.8	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7
137.5°	698.5	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1
140°	721.2	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1
142.5°	740.2	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5
145°	770.1	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7
147.5°	796.0	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4
150°	812.9	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7
152.5°	827.2	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9
155°	847.9	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7
157.5°	864.1	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6
160°	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5
162.5°	882.0	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5
165°	893.4	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5
167.5°	901.8	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8
170°	906.6	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0
172.5°	909.7	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1
175°	913.9	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6
177.5°	914.5	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	15.6	15.1	14.6	14.2	14.0	13.9	13.8	13.6
90°	14.7	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.1	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.2	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	35.6	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	40.0	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	41.8	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	43.5	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	53.1	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	86.1	71.4	56.8	49.8	50.3	51.0	51.6	52.1





TEST NUMBER: P331565-830

CATALOG NUMBER: S122DIW-S865D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	184.3	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	271.4	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	418.1	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	487.2	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	516.9	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	559.6	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	599.1	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	624.2	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	648.5	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	683.2	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	715.5	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	736.4	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	755.6	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	782.6	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.2	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	820.6	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	833.8	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	851.6	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	866.7	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	875.3	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	883.5	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	901.8	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	906.1	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	909.2	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	912.7	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.0	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)