

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331567-830

Luminaire Tested: **S122DIW-S865D970U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331567-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D970U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7240.9 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24	22
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.0	2.1
10°-20°	450.6	6.2
20°-30°	653.9	9.0
30°-40°	690.0	9.5
40°-50°	611.0	8.4
50°-60°	487.6	6.7
60°-70°	331.4	4.6
70°-80°	169.9	2.3
80°-90°	44.0	0.6
90°-100°	41.5	0.6
100°-110°	152.3	2.1
110°-120°	407.0	5.6
120°-130°	671.8	9.3
130°-140°	714.5	9.9
140°-150°	664.1	9.2
150°-160°	533.9	7.4
160°-170°	344.1	4.8
170°-180°	118.4	1.6
0°-30°	1259.4	17.4
0°-40°	1949.5	26.9
0°-60°	3048.0	42.1
0°-90°	3593.3	49.6
90°-120°	600.8	8.3
90°-150°	2651.1	36.6
90°-180°	3648.0	50.4
0°-180°	7240.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	24	1	24	1	24	12
95°	39	58	39	58	39	36
105°	68	274	68	274	68	71
115°	74	518	74	518	74	185
125°	770	732	770	732	770	666
135°	936	906	936	906	936	721
145°	1067	1051	1067	1051	1067	667
155°	1158	1157	1158	1157	1158	534
165°	1217	1220	1217	1220	1217	344
175°	1240	1247	1240	1247	1240	118
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	17.9	17.8	18.2	17.6	17.5	17.9	17.7	17.0	17.3	17.6	17.8
90°	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0	19.0	18.0	16.4
92.5°	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0	21.4	20.9	20.1
95°	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1	36.1	35.2	33.7
97.5°	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6	47.8	47.0	43.7
100°	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6	53.0	51.4	48.0
102.5°	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9	54.9	52.8	81.2
105°	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4	57.1	55.0	109.6
107.5°	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4	74.6	76.9	142.4
110°	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5	137.6	157.6	215.5



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5	324.5	397.6	411.8
115°	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3	463.0	555.7	550.7
117.5°	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6	593.0	615.5	612.1
120°	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0	662.6	660.2	656.6
122.5°	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6	704.1	702.7	698.7
125°	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8	762.4	761.0	757.2
127.5°	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7	815.7	813.6	810.8
130°	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9	849.7	847.5	845.3
132.5°	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1	883.3	881.4	879.1
135°	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6	930.6	928.6	926.7
137.5°	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6	974.7	972.7	970.6
140°	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1	1003.3	1001.5	999.3
142.5°	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4	1029.8	1028.1	1025.7
145°	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3	1066.9	1065.5	1062.1
147.5°	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3	1099.3	1098.3	1094.9
150°	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1	1118.9	1117.7	1114.5
152.5°	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1	1136.9	1135.7	1132.7
155°	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4	1161.2	1160.0	1157.6
157.5°	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9	1181.6	1180.2	1178.5
160°	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9	1193.6	1192.4	1191.3
162.5°	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0	1204.6	1203.2	1202.2
165°	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7	1216.2
167.5°	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9	1229.5	1228.1	1227.6
170°	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7	1235.3	1233.9	1233.5
172.5°	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0	1239.6	1238.2	1237.7
175°	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7	1244.3	1242.8	1242.5
177.5°	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2	1245.1	1244.0	1243.8
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	18.0	17.6	17.3	17.9	16.0	15.6	13.1	11.2	11.1	11.0	10.5
90°	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2	18.0	17.8	17.6
95°	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5	51.9	45.3	38.7
97.5°	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2	97.6	79.0	60.3
100°	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4	132.0	104.5	77.2
102.5°	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0	201.1	195.4	189.5
105°	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8	279.8	285.8	291.8
107.5°	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0	354.9	359.7	364.5
110°	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0	403.2	407.4	411.6





TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1	448.8	452.5	456.3
115°	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8	521.2	524.7	528.1
117.5°	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9	586.7	590.5	594.3
120°	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5	633.5	636.4	639.4
122.5°	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8	673.9	677.1	680.2
125°	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2	734.8	737.4	740.0
127.5°	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9	790.8	793.6	796.5
130°	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2	826.4	829.6	832.7
132.5°	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2	862.0	864.7	867.3
135°	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1	909.3	912.5	915.7
137.5°	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4	955.6	957.9	960.2
140°	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4	986.0	987.6	989.2
142.5°	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3	1011.7	1013.2	1014.6
145°	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0	1050.8	1050.7	1050.5
147.5°	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6	1085.7	1085.0	1084.2
150°	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6	1108.1	1106.7	1105.4
152.5°	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1	1127.5	1125.9	1124.4
155°	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3	1155.5	1153.7	1151.9
157.5°	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5	1178.0	1176.4	1174.9
160°	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1191.3	1190.1	1188.8
162.5°	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0	1202.8	1201.6	1200.3
165°	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5	1218.2	1217.0	1215.9
167.5°	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0	1229.7	1228.6	1227.4
170°	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5	1236.2	1235.1	1233.9
172.5°	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8	1240.6	1239.3	1238.2
175°	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4	1245.9	1244.5	1243.2
177.5°	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3	1247.2	1246.0	1244.9
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	10.5	10.4	10.2	10.5	10.3	10.1	9.8	10.0	10.2	9.4	9.5
90°	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.1	22.7
92.5°	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0	22.4	23.0	23.4
95°	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1	38.2	39.1	39.5
97.5°	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6	49.4	50.2	50.7
100°	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6	56.2	57.8	58.7
102.5°	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9	59.0	61.1	62.4
105°	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4	61.5	63.7	65.2
107.5°	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4	70.2	68.0	67.2
110°	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5	97.6	77.6	68.0



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5	178.5	105.5	69.3
115°	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3	277.7	185.0	131.5
117.5°	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6	548.3	525.8	491.0
120°	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0	667.3	669.8	657.4
122.5°	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6	707.0	708.4	706.5
125°	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8	765.3	766.7	767.6
127.5°	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7	819.7	821.8	822.8
130°	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9	854.1	856.3	857.3
132.5°	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1	887.0	888.9	889.8
135°	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6	934.5	936.5	937.4
137.5°	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6	978.5	980.5	981.2
140°	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1	1006.9	1008.7	1009.1
142.5°	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4	1033.1	1034.7	1035.0
145°	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3	1069.7	1071.0	1071.3
147.5°	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3	1101.4	1102.4	1102.5
150°	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1	1121.2	1122.5	1122.6
152.5°	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1	1139.3	1140.5	1140.5
155°	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4	1163.6	1164.8	1164.6
157.5°	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9	1184.3	1185.6	1185.5
160°	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9	1196.0	1197.2	1197.1
162.5°	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0	1207.3	1208.7	1208.5
165°	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4
167.5°	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9	1232.3	1233.7	1233.5
170°	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7	1238.0	1239.4	1239.3
172.5°	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0	1242.4	1243.8	1243.6
175°	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7	1247.1	1248.5	1248.2
177.5°	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2	1247.3	1248.4	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	9.6	9.2	9.3	8.9	9.3	9.2	9.6	9.5	9.4	10.2	10.0
90°	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0
92.5°	23.6	23.8	24.0	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0
95°	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1
97.5°	51.0	51.2	51.5	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6
100°	59.1	59.6	59.9	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6
102.5°	63.0	63.5	64.1	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9
105°	66.1	66.8	67.7	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4
107.5°	68.1	68.8	69.7	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4
110°	68.7	69.6	70.3	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	69.9	70.6	71.3	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5
115°	117.1	102.6	88.2	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3
117.5°	443.6	396.2	348.9	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6
120°	630.5	603.4	576.4	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0
122.5°	701.3	696.1	690.8	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6
125°	768.3	768.8	769.4	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8
127.5°	823.0	823.1	823.2	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7
130°	857.1	856.9	856.7	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9
132.5°	889.5	889.3	889.1	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1
135°	937.0	936.5	936.1	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6
137.5°	980.5	979.8	979.1	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6
140°	1008.1	1007.1	1006.1	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1
142.5°	1034.1	1033.0	1032.1	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4
145°	1070.3	1069.2	1068.3	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3
147.5°	1101.6	1100.8	1099.9	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3
150°	1121.6	1120.6	1119.6	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1
152.5°	1139.2	1137.8	1136.5	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1
155°	1163.0	1161.4	1159.8	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4
157.5°	1183.9	1182.4	1180.8	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9
160°	1195.7	1194.3	1193.0	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9
162.5°	1206.7	1205.0	1203.3	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0
165°	1221.0	1219.6	1218.1	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6
167.5°	1231.7	1229.9	1228.1	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9
170°	1237.5	1235.7	1233.9	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7
172.5°	1241.8	1240.0	1238.2	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0
175°	1246.1	1244.2	1242.2	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7
177.5°	1246.8	1245.4	1244.0	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	9.8	10.1	10.3	10.5	10.2	10.4	10.5	10.5	11.0	11.1	11.2
90°	19.0	18.0	16.4	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9
92.5°	21.4	20.9	20.1	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2
95°	36.1	35.2	33.7	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5
97.5°	47.8	47.0	43.7	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2
100°	53.0	51.4	48.0	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4
102.5°	54.9	52.8	81.2	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0
105°	57.1	55.0	109.6	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8
107.5°	74.6	76.9	142.4	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0
110°	137.6	157.6	215.5	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.5	397.6	411.8	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1
115°	463.0	555.7	550.7	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8
117.5°	593.0	615.5	612.1	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9
120°	662.6	660.2	656.6	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5
122.5°	704.1	702.7	698.7	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8
125°	762.4	761.0	757.2	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2
127.5°	815.7	813.6	810.8	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9
130°	849.7	847.5	845.3	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2
132.5°	883.3	881.4	879.1	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2
135°	930.6	928.6	926.7	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1
137.5°	974.7	972.7	970.6	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4
140°	1003.3	1001.5	999.3	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4
142.5°	1029.8	1028.1	1025.7	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3
145°	1066.9	1065.5	1062.1	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0
147.5°	1099.3	1098.3	1094.9	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6
150°	1118.9	1117.7	1114.5	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6
152.5°	1136.9	1135.7	1132.7	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1
155°	1161.2	1160.0	1157.6	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3
157.5°	1181.6	1180.2	1178.5	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5
160°	1193.6	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4
162.5°	1204.6	1203.2	1202.2	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0
165°	1218.1	1216.7	1216.2	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5
167.5°	1229.5	1228.1	1227.6	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0
170°	1235.3	1233.9	1233.5	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5
172.5°	1239.6	1238.2	1237.7	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8
175°	1244.3	1242.8	1242.5	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4
177.5°	1245.1	1244.0	1243.8	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.1	15.6	16.0	17.9	17.3	17.6	18.0	17.8	17.6	17.3	17.0
90°	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0
92.5°	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0
95°	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1
97.5°	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6
100°	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6
102.5°	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9
105°	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4
107.5°	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4
110°	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5





TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5
115°	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3
117.5°	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6
120°	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0
122.5°	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6
125°	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8
127.5°	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7
130°	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9
132.5°	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1
135°	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6
137.5°	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6
140°	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1
142.5°	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4
145°	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3
147.5°	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3
150°	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1
152.5°	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1
155°	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4
157.5°	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9
160°	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9
162.5°	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0
165°	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6
167.5°	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9
170°	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7
172.5°	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0
175°	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7
177.5°	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	17.7	17.9	17.5	17.6	18.2	17.8	17.9
90°	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331567-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)