

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645261

Luminaire Tested: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P645261  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - BATWING LENS - 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2871.9 lumens  
Efficiency: N/A  
Efficacy: 131.7 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 1.87 / 1.75  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645261

CATALOG NUMBER: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645261

CATALOG NUMBER: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	101	101	101	99				
1	109	104	100	97	106	102	98	95	98	95	92	94	91	89	90	88	86	84				
2	99	91	85	79	97	89	83	78	86	81	76	82	78	74	79	76	73	70				
3	91	80	72	66	88	79	71	65	75	69	64	73	67	63	70	65	62	59				
4	83	71	62	56	80	70	61	55	67	60	54	65	58	53	62	57	53	50				
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	43				
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	45	40	38				
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33				
8	60	47	38	32	59	46	38	32	44	37	32	43	36	32	42	36	31	29				
9	56	43	34	29	55	42	34	29	41	34	29	40	33	28	39	33	28	26				
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	25	24				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11988	11988	11988
5°	11810	12483	13211
10°	11437	13872	15826
15°	10882	15500	18041
20°	10237	16912	19345
25°	9536	17874	19996
30°	8917	18608	20314
35°	8509	18993	20660
40°	8226	19218	20927
45°	8241	19281	20936
50°	8372	19085	20343
55°	8749	18714	18472
60°	8922	17399	14999
65°	9039	15240	11018
70°	8639	11981	8559
75°	7754	8939	7218
80°	6583	7066	5783
85°	6391	5761	4798

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 20936 cd/sqm



TEST NUMBER: P645261

CATALOG NUMBER: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.1	2.7
10°-20°	253.1	8.8
20°-30°	420.4	14.6
30°-40°	530.4	18.5
40°-50°	567.0	19.7
50°-60°	500.4	17.4
60°-70°	321.2	11.2
70°-80°	142.4	5.0
80°-90°	36.9	1.3
90°-100°	9.7	0.3
100°-110°	6.2	0.2
110°-120°	4.7	0.2
120°-130°	3.0	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.7	26.1
0°-40°	1280.0	44.6
0°-60°	2347.4	81.7
0°-90°	2847.9	99.2
90°-120°	20.6	0.7
90°-150°	24.0	0.8
90°-180°	24.0	0.8
0°-180°	2871.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	729	751	770	796	815	68
15°	651	751	927	1039	1079	182
25°	535	726	1003	1097	1122	246
35°	432	663	964	1026	1048	271
45°	361	567	844	897	917	279
55°	311	446	665	668	656	276
65°	237	299	399	324	288	231
75°	124	138	143	122	116	133
85°	34	30	31	28	26	37
90°	12	12	10	10	7	8
95°	19	12	9	5	4	14
105°	12	10	5	2	0	13
115°	9	7	5	2	0	9
125°	5	5	5	2	0	5
135°	0	0	0	0	0	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P645261

CATALOG NUMBER: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	742.5	742.5	742.5	742.5	742.5
2.5°	737.0	747.8	748.1	752.3	757.7
5°	728.7	750.7	770.2	796.5	815.1
7.5°	711.5	750.6	813.0	874.1	904.5
10°	697.6	751.7	846.1	928.2	965.3
12.5°	679.7	751.3	879.3	978.0	1020.6
15°	651.0	750.6	927.3	1038.7	1079.3
17.5°	617.9	747.5	965.0	1076.6	1112.1
20°	595.8	744.3	984.3	1090.4	1125.9
22.5°	570.9	737.0	995.3	1097.3	1130.0
25°	535.3	726.1	1003.3	1097.1	1122.4
27.5°	500.4	710.5	1003.6	1083.2	1104.8
30°	478.3	697.8	998.1	1069.4	1089.6
32.5°	459.0	683.9	987.1	1052.8	1074.4
35°	431.7	663.0	963.6	1026.2	1048.2
37.5°	408.2	639.2	933.9	994.9	1020.6
40°	390.3	619.9	911.8	972.7	992.9
42.5°	376.4	599.3	885.5	945.0	962.5
45°	360.9	566.9	844.4	896.7	916.9
47.5°	344.3	533.4	797.1	846.4	859.6
50°	333.3	508.9	759.8	804.8	809.9
52.5°	326.4	483.1	723.9	752.2	753.2
55°	310.8	445.9	664.8	668.0	656.2
57.5°	290.1	402.6	589.9	573.0	544.6
60°	276.3	372.5	538.8	505.0	464.5
62.5°	262.5	343.9	484.9	430.3	383.0
65°	236.6	299.0	398.9	323.8	288.4
67.5°	206.5	249.8	313.2	242.3	218.6
70°	183.0	216.8	253.8	198.2	181.3
72.5°	160.9	183.9	205.5	163.8	155.1
75°	124.3	137.8	143.3	122.5	115.7
77.5°	91.5	92.2	99.5	86.3	82.9
80°	70.8	67.4	76.0	65.5	62.2
82.5°	54.2	49.5	55.3	47.6	45.6
85°	34.5	29.5	31.1	27.6	25.9
87.5°	20.4	16.3	15.9	14.5	12.4
90°	12.1	12.1	10.4	10.3	6.9
92.5°	16.2	12.2	9.0	7.5	4.1
95°	19.0	12.2	8.6	5.1	3.5
97.5°	16.9	11.9	6.6	3.4	1.7
100°	15.5	10.5	5.2	3.4	1.7
102.5°	14.2	10.4	5.2	2.0	0.3
105°	12.1	10.4	5.2	1.7	0.0
107.5°	11.7	8.7	5.2	1.7	0.0
110°	10.4	8.7	5.2	1.7	0.0



TEST NUMBER: P645261

CATALOG NUMBER: OMN4DP-SR4F0-75D840-CLB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	10.4	8.7	5.2	1.7	0.0
115°	8.6	6.9	5.2	1.7	0.0
117.5°	8.3	6.9	5.2	1.7	0.0
120°	6.9	6.9	5.2	1.7	0.0
122.5°	6.9	5.6	3.8	1.7	0.0
125°	5.2	5.2	5.2	1.7	0.0
127.5°	3.5	4.8	3.5	1.4	0.0
130°	3.5	3.5	3.5	0.0	0.0
132.5°	0.7	0.7	0.7	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)