

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331568-830

Luminaire Tested: **S122DIW-S865D970U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331568-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D970U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6758.0 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.0	2.3
10°-20°	450.6	6.7
20°-30°	653.9	9.7
30°-40°	690.0	10.2
40°-50°	611.0	9.0
50°-60°	487.6	7.2
60°-70°	331.4	4.9
70°-80°	169.9	2.5
80°-90°	45.5	0.7
90°-100°	71.7	1.1
100°-110°	222.6	3.3
110°-120°	380.6	5.6
120°-130°	500.5	7.4
130°-140°	561.7	8.3
140°-150°	550.8	8.1
150°-160°	462.0	6.8
160°-170°	306.4	4.5
170°-180°	107.1	1.6
0°-30°	1259.4	18.6
0°-40°	1949.5	28.8
0°-60°	3048.0	45.1
0°-90°	3594.8	53.2
90°-120°	674.9	10.0
90°-150°	2287.8	33.9
90°-180°	3163.0	46.8
0°-180°	6758.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	32	1	32	1	32	16
95°	59	50	59	50	59	66
105°	212	205	212	205	212	223
115°	382	382	382	382	382	377
125°	558	556	558	556	558	497
135°	728	719	728	719	728	560
145°	882	872	882	872	882	551
155°	1005	998	1005	998	1005	463
165°	1086	1085	1086	1085	1086	306
175°	1126	1129	1126	1129	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	19.5	19.4	19.9	19.4	19.3	19.9	20.0	19.5	20.1	20.7	20.3
90°	32.4	32.2	32.0	31.9	31.6	31.7	32.1	32.5	33.0	33.4	28.7
92.5°	30.9	30.9	30.8	30.8	30.7	30.7	30.6	30.5	30.4	30.3	29.2
95°	59.2	59.6	60.0	60.4	60.9	61.1	61.1	61.1	61.1	61.1	60.7
97.5°	102.5	102.5	102.6	102.6	102.7	102.7	102.7	102.7	102.7	102.7	101.9
100°	130.8	131.0	131.2	131.4	131.7	131.8	131.8	131.8	131.8	131.8	131.1
102.5°	162.9	163.1	163.2	163.5	163.7	163.7	163.5	163.4	163.2	163.1	162.2
105°	212.0	212.0	212.0	212.0	212.0	211.7	211.3	210.8	210.5	210.0	209.6
107.5°	258.2	259.1	260.0	261.1	262.0	262.4	262.3	262.1	261.9	261.7	261.7
110°	294.1	294.6	295.3	296.0	296.6	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	328.4	328.9	329.3	329.8	330.3	330.7	331.3	331.8	332.2	332.8	333.0
115°	381.8	382.5	383.1	383.8	384.4	384.8	385.0	385.2	385.5	385.7	386.1
117.5°	432.8	433.5	434.1	434.8	435.4	435.9	436.5	437.0	437.5	438.0	439.2
120°	468.7	469.4	470.0	470.6	471.3	471.6	471.6	471.6	471.6	471.6	473.3
122.5°	503.9	504.4	504.8	505.3	505.8	506.2	506.7	507.3	507.7	508.2	509.4
125°	557.5	557.7	558.0	558.2	558.4	558.8	559.4	560.1	560.7	561.4	561.9
127.5°	606.4	607.1	607.8	608.4	609.1	609.8	610.6	611.3	612.1	612.9	613.7
130°	641.5	642.3	643.2	644.0	644.9	645.5	646.0	646.4	646.9	647.2	647.7
132.5°	675.1	675.8	676.5	677.2	677.9	678.6	679.6	680.5	681.5	682.4	682.3
135°	727.5	728.1	728.7	729.3	730.0	730.4	730.7	730.8	731.0	731.2	730.8
137.5°	774.8	775.6	776.5	777.3	778.2	778.7	778.9	779.0	779.2	779.4	778.8
140°	807.7	808.5	809.4	810.2	811.1	811.4	811.4	811.4	811.4	811.4	810.4
142.5°	837.4	838.3	839.1	840.0	840.8	841.1	841.0	840.8	840.7	840.5	839.8
145°	882.1	883.0	883.8	884.7	885.5	885.8	885.6	885.4	885.1	885.0	883.7
147.5°	922.0	922.8	923.6	924.4	925.2	925.4	924.9	924.4	924.0	923.5	922.7
150°	948.0	948.6	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0	947.2
152.5°	972.4	973.2	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4	971.4
155°	1005.2	1005.9	1006.5	1007.2	1007.8	1007.6	1006.5	1005.5	1004.4	1003.3	1002.7
157.5°	1033.5	1034.5	1035.6	1036.6	1037.6	1037.4	1035.9	1034.5	1033.0	1031.6	1031.2
160°	1051.1	1052.0	1052.8	1053.7	1054.5	1054.2	1053.0	1051.7	1050.5	1049.1	1049.0
162.5°	1066.4	1067.3	1068.4	1069.4	1070.4	1070.3	1068.7	1067.3	1065.9	1064.4	1064.2
165°	1086.4	1087.5	1088.5	1089.6	1090.6	1090.4	1088.9	1087.5	1086.0	1084.5	1084.5
167.5°	1102.9	1103.9	1105.0	1106.2	1107.2	1107.0	1105.6	1104.1	1102.6	1101.1	1101.2
170°	1111.3	1112.5	1113.8	1115.0	1116.3	1116.3	1114.7	1113.2	1111.7	1110.3	1110.5
172.5°	1118.1	1119.4	1120.7	1121.9	1123.2	1123.0	1121.6	1120.1	1118.6	1117.1	1117.4
175°	1125.6	1126.8	1128.1	1129.4	1130.7	1130.5	1129.1	1127.6	1126.1	1124.5	1125.0
177.5°	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0	1129.4
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	19.8	18.9	18.0	18.3	16.2	15.7	13.2	11.2	11.2	11.2	10.7
90°	24.0	19.4	14.7	11.1	8.6	6.0	3.5	0.9	3.5	6.0	8.6
92.5°	28.2	27.1	25.9	24.5	22.6	20.7	18.9	17.0	18.9	20.7	22.6
95°	60.2	59.9	59.4	58.2	56.0	53.9	51.7	49.7	51.7	53.9	56.0
97.5°	101.1	100.3	99.5	98.1	96.3	94.4	92.6	90.7	92.6	94.4	96.3
100°	130.4	129.8	129.2	128.0	126.3	124.6	122.9	121.2	122.9	124.6	126.3
102.5°	161.5	160.6	159.9	158.7	157.4	156.0	154.7	153.4	154.7	156.0	157.4
105°	209.2	208.8	208.3	207.8	207.2	206.5	205.9	205.3	205.9	206.5	207.2
107.5°	261.7	261.7	261.7	261.3	260.3	259.4	258.5	257.6	258.5	259.4	260.3
110°	296.9	296.9	296.9	296.2	295.0	293.7	292.5	291.2	292.5	293.7	295.0





TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.1	333.3	333.5	332.9	331.7	330.4	329.1	327.8	329.1	330.4	331.7
115°	386.5	386.9	387.4	386.9	385.7	384.4	383.1	381.8	383.1	384.4	385.7
117.5°	440.4	441.6	442.7	442.5	440.8	439.1	437.4	435.7	437.4	439.1	440.8
120°	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	473.3	475.0	476.7
122.5°	510.7	511.8	513.0	512.6	510.6	508.5	506.5	504.4	506.5	508.5	510.6
125°	562.6	563.3	563.9	563.3	561.4	559.4	557.5	555.6	557.5	559.4	561.4
127.5°	614.4	615.2	616.0	615.1	612.7	610.3	607.8	605.5	607.8	610.3	612.7
130°	648.1	648.6	648.9	647.8	645.1	642.2	639.5	636.8	639.5	642.2	645.1
132.5°	682.2	682.1	682.0	680.9	678.6	676.4	674.1	671.8	674.1	676.4	678.6
135°	730.4	730.0	729.5	728.2	725.9	723.5	721.2	718.9	721.2	723.5	725.9
137.5°	778.3	777.7	777.2	775.9	774.0	772.1	770.2	768.3	770.2	772.1	774.0
140°	809.4	808.3	807.2	805.7	803.8	801.9	800.0	798.1	800.0	801.9	803.8
142.5°	839.1	838.3	837.6	836.3	834.3	832.5	830.6	828.7	830.6	832.5	834.3
145°	882.4	881.2	879.9	878.5	877.0	875.5	874.0	872.5	874.0	875.5	877.0
147.5°	921.8	921.0	920.1	918.8	917.0	915.3	913.5	911.7	913.5	915.3	917.0
150°	946.3	945.5	944.6	943.5	942.3	940.9	939.7	938.4	939.7	940.9	942.3
152.5°	970.3	969.4	968.4	967.2	965.9	964.7	963.4	962.1	963.4	964.7	965.9
155°	1002.1	1001.5	1000.8	1000.1	999.6	998.9	998.2	997.6	998.2	998.9	999.6
157.5°	1030.9	1030.5	1030.1	1029.6	1029.3	1028.8	1028.4	1027.9	1028.4	1028.8	1029.3
160°	1048.8	1048.6	1048.3	1048.0	1047.5	1047.2	1046.7	1046.3	1046.7	1047.2	1047.5
162.5°	1064.0	1063.8	1063.6	1063.5	1063.4	1063.3	1063.2	1063.1	1063.2	1063.3	1063.4
165°	1084.5	1084.5	1084.5	1084.6	1084.8	1085.1	1085.2	1085.4	1085.2	1085.1	1084.8
167.5°	1101.2	1101.3	1101.3	1101.6	1102.2	1102.9	1103.5	1104.2	1103.5	1102.9	1102.2
170°	1110.7	1110.9	1111.2	1111.5	1112.2	1112.9	1113.4	1114.1	1113.4	1112.9	1112.2
172.5°	1117.6	1117.8	1117.9	1118.4	1119.1	1119.6	1120.3	1121.0	1120.3	1119.6	1119.1
175°	1125.4	1125.9	1126.2	1126.8	1127.5	1128.1	1128.7	1129.4	1128.7	1128.1	1127.5
177.5°	1129.6	1130.0	1130.3	1130.8	1131.2	1131.8	1132.3	1132.8	1132.3	1131.8	1131.2
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	10.7	10.9	11.4	12.3	12.7	13.2	12.6	12.5	12.4	11.3	11.3
90°	11.1	14.7	19.4	24.0	28.7	33.4	33.0	32.5	32.1	31.7	31.6
92.5°	24.5	25.9	27.1	28.2	29.2	30.3	30.4	30.5	30.6	30.7	30.7
95°	58.2	59.4	59.9	60.2	60.7	61.1	61.1	61.1	61.1	61.1	60.9
97.5°	98.1	99.5	100.3	101.1	101.9	102.7	102.7	102.7	102.7	102.7	102.7
100°	128.0	129.2	129.8	130.4	131.1	131.8	131.8	131.8	131.8	131.8	131.7
102.5°	158.7	159.9	160.6	161.5	162.2	163.1	163.2	163.4	163.5	163.7	163.7
105°	207.8	208.3	208.8	209.2	209.6	210.0	210.5	210.8	211.3	211.7	212.0
107.5°	261.3	261.7	261.7	261.7	261.7	261.7	261.9	262.1	262.3	262.4	262.0
110°	296.2	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.6



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	332.9	333.5	333.3	333.1	333.0	332.8	332.2	331.8	331.3	330.7	330.3
115°	386.9	387.4	386.9	386.5	386.1	385.7	385.5	385.2	385.0	384.8	384.4
117.5°	442.5	442.7	441.6	440.4	439.2	438.0	437.5	437.0	436.5	435.9	435.4
120°	478.4	478.4	476.7	475.0	473.3	471.6	471.6	471.6	471.6	471.6	471.3
122.5°	512.6	513.0	511.8	510.7	509.4	508.2	507.7	507.3	506.7	506.2	505.8
125°	563.3	563.9	563.3	562.6	561.9	561.4	560.7	560.1	559.4	558.8	558.4
127.5°	615.1	616.0	615.2	614.4	613.7	612.9	612.1	611.3	610.6	609.8	609.1
130°	647.8	648.9	648.6	648.1	647.7	647.2	646.9	646.4	646.0	645.5	644.9
132.5°	680.9	682.0	682.1	682.2	682.3	682.4	681.5	680.5	679.6	678.6	677.9
135°	728.2	729.5	730.0	730.4	730.8	731.2	731.0	730.8	730.7	730.4	730.0
137.5°	775.9	777.2	777.7	778.3	778.8	779.4	779.2	779.0	778.9	778.7	778.2
140°	805.7	807.2	808.3	809.4	810.4	811.4	811.4	811.4	811.4	811.4	811.1
142.5°	836.3	837.6	838.3	839.1	839.8	840.5	840.7	840.8	841.0	841.1	840.8
145°	878.5	879.9	881.2	882.4	883.7	885.0	885.1	885.4	885.6	885.8	885.5
147.5°	918.8	920.1	921.0	921.8	922.7	923.5	924.0	924.4	924.9	925.4	925.2
150°	943.5	944.6	945.5	946.3	947.2	948.0	948.6	949.2	949.9	950.6	950.6
152.5°	967.2	968.4	969.4	970.3	971.4	972.4	973.2	974.0	974.9	975.6	975.6
155°	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4	1005.5	1006.5	1007.6	1007.8
157.5°	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0	1034.5	1035.9	1037.4	1037.6
160°	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5	1051.7	1053.0	1054.2	1054.5
162.5°	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9	1067.3	1068.7	1070.3	1070.4
165°	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0	1087.5	1088.9	1090.4	1090.6
167.5°	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6	1104.1	1105.6	1107.0	1107.2
170°	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7	1113.2	1114.7	1116.3	1116.3
172.5°	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6	1120.1	1121.6	1123.0	1123.2
175°	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1	1127.6	1129.1	1130.5	1130.7
177.5°	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	11.4	10.9	10.9	10.5	10.9	10.9	11.4	11.3	11.3	12.4	12.5
90°	31.9	32.0	32.2	32.4	32.2	32.0	31.9	31.6	31.7	32.1	32.5
92.5°	30.8	30.8	30.9	30.9	30.9	30.8	30.8	30.7	30.7	30.6	30.5
95°	60.4	60.0	59.6	59.2	59.6	60.0	60.4	60.9	61.1	61.1	61.1
97.5°	102.6	102.6	102.5	102.5	102.5	102.6	102.6	102.7	102.7	102.7	102.7
100°	131.4	131.2	131.0	130.8	131.0	131.2	131.4	131.7	131.8	131.8	131.8
102.5°	163.5	163.2	163.1	162.9	163.1	163.2	163.5	163.7	163.7	163.5	163.4
105°	212.0	212.0	212.0	212.0	212.0	212.0	212.0	212.0	211.7	211.3	210.8
107.5°	261.1	260.0	259.1	258.2	259.1	260.0	261.1	262.0	262.4	262.3	262.1
110°	296.0	295.3	294.6	294.1	294.6	295.3	296.0	296.6	296.9	296.9	296.9



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	329.8	329.3	328.9	328.4	328.9	329.3	329.8	330.3	330.7	331.3	331.8
115°	383.8	383.1	382.5	381.8	382.5	383.1	383.8	384.4	384.8	385.0	385.2
117.5°	434.8	434.1	433.5	432.8	433.5	434.1	434.8	435.4	435.9	436.5	437.0
120°	470.6	470.0	469.4	468.7	469.4	470.0	470.6	471.3	471.6	471.6	471.6
122.5°	505.3	504.8	504.4	503.9	504.4	504.8	505.3	505.8	506.2	506.7	507.3
125°	558.2	558.0	557.7	557.5	557.7	558.0	558.2	558.4	558.8	559.4	560.1
127.5°	608.4	607.8	607.1	606.4	607.1	607.8	608.4	609.1	609.8	610.6	611.3
130°	644.0	643.2	642.3	641.5	642.3	643.2	644.0	644.9	645.5	646.0	646.4
132.5°	677.2	676.5	675.8	675.1	675.8	676.5	677.2	677.9	678.6	679.6	680.5
135°	729.3	728.7	728.1	727.5	728.1	728.7	729.3	730.0	730.4	730.7	730.8
137.5°	777.3	776.5	775.6	774.8	775.6	776.5	777.3	778.2	778.7	778.9	779.0
140°	810.2	809.4	808.5	807.7	808.5	809.4	810.2	811.1	811.4	811.4	811.4
142.5°	840.0	839.1	838.3	837.4	838.3	839.1	840.0	840.8	841.1	841.0	840.8
145°	884.7	883.8	883.0	882.1	883.0	883.8	884.7	885.5	885.8	885.6	885.4
147.5°	924.4	923.6	922.8	922.0	922.8	923.6	924.4	925.2	925.4	924.9	924.4
150°	949.9	949.2	948.6	948.0	948.6	949.2	949.9	950.6	950.6	949.9	949.2
152.5°	974.9	974.0	973.2	972.4	973.2	974.0	974.9	975.6	975.6	974.9	974.0
155°	1007.2	1006.5	1005.9	1005.2	1005.9	1006.5	1007.2	1007.8	1007.6	1006.5	1005.5
157.5°	1036.6	1035.6	1034.5	1033.5	1034.5	1035.6	1036.6	1037.6	1037.4	1035.9	1034.5
160°	1053.7	1052.8	1052.0	1051.1	1052.0	1052.8	1053.7	1054.5	1054.2	1053.0	1051.7
162.5°	1069.4	1068.4	1067.3	1066.4	1067.3	1068.4	1069.4	1070.4	1070.3	1068.7	1067.3
165°	1089.6	1088.5	1087.5	1086.4	1087.5	1088.5	1089.6	1090.6	1090.4	1088.9	1087.5
167.5°	1106.2	1105.0	1103.9	1102.9	1103.9	1105.0	1106.2	1107.2	1107.0	1105.6	1104.1
170°	1115.0	1113.8	1112.5	1111.3	1112.5	1113.8	1115.0	1116.3	1116.3	1114.7	1113.2
172.5°	1121.9	1120.7	1119.4	1118.1	1119.4	1120.7	1121.9	1123.2	1123.0	1121.6	1120.1
175°	1129.4	1128.1	1126.8	1125.6	1126.8	1128.1	1129.4	1130.7	1130.5	1129.1	1127.6
177.5°	1132.0	1131.1	1130.0	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	12.6	13.2	12.7	12.3	11.4	10.9	10.7	10.7	11.2	11.2	11.2
90°	33.0	33.4	28.7	24.0	19.4	14.7	11.1	8.6	6.0	3.5	0.9
92.5°	30.4	30.3	29.2	28.2	27.1	25.9	24.5	22.6	20.7	18.9	17.0
95°	61.1	61.1	60.7	60.2	59.9	59.4	58.2	56.0	53.9	51.7	49.7
97.5°	102.7	102.7	101.9	101.1	100.3	99.5	98.1	96.3	94.4	92.6	90.7
100°	131.8	131.8	131.1	130.4	129.8	129.2	128.0	126.3	124.6	122.9	121.2
102.5°	163.2	163.1	162.2	161.5	160.6	159.9	158.7	157.4	156.0	154.7	153.4
105°	210.5	210.0	209.6	209.2	208.8	208.3	207.8	207.2	206.5	205.9	205.3
107.5°	261.9	261.7	261.7	261.7	261.7	261.7	261.3	260.3	259.4	258.5	257.6
110°	296.9	296.9	296.9	296.9	296.9	296.9	296.2	295.0	293.7	292.5	291.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.2	332.8	333.0	333.1	333.3	333.5	332.9	331.7	330.4	329.1	327.8
115°	385.5	385.7	386.1	386.5	386.9	387.4	386.9	385.7	384.4	383.1	381.8
117.5°	437.5	438.0	439.2	440.4	441.6	442.7	442.5	440.8	439.1	437.4	435.7
120°	471.6	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6
122.5°	507.7	508.2	509.4	510.7	511.8	513.0	512.6	510.6	508.5	506.5	504.4
125°	560.7	561.4	561.9	562.6	563.3	563.9	563.3	561.4	559.4	557.5	555.6
127.5°	612.1	612.9	613.7	614.4	615.2	616.0	615.1	612.7	610.3	607.8	605.5
130°	646.9	647.2	647.7	648.1	648.6	648.9	647.8	645.1	642.2	639.5	636.8
132.5°	681.5	682.4	682.3	682.2	682.1	682.0	680.9	678.6	676.4	674.1	671.8
135°	731.0	731.2	730.8	730.4	730.0	729.5	728.2	725.9	723.5	721.2	718.9
137.5°	779.2	779.4	778.8	778.3	777.7	777.2	775.9	774.0	772.1	770.2	768.3
140°	811.4	811.4	810.4	809.4	808.3	807.2	805.7	803.8	801.9	800.0	798.1
142.5°	840.7	840.5	839.8	839.1	838.3	837.6	836.3	834.3	832.5	830.6	828.7
145°	885.1	885.0	883.7	882.4	881.2	879.9	878.5	877.0	875.5	874.0	872.5
147.5°	924.0	923.5	922.7	921.8	921.0	920.1	918.8	917.0	915.3	913.5	911.7
150°	948.6	948.0	947.2	946.3	945.5	944.6	943.5	942.3	940.9	939.7	938.4
152.5°	973.2	972.4	971.4	970.3	969.4	968.4	967.2	965.9	964.7	963.4	962.1
155°	1004.4	1003.3	1002.7	1002.1	1001.5	1000.8	1000.1	999.6	998.9	998.2	997.6
157.5°	1033.0	1031.6	1031.2	1030.9	1030.5	1030.1	1029.6	1029.3	1028.8	1028.4	1027.9
160°	1050.5	1049.1	1049.0	1048.8	1048.6	1048.3	1048.0	1047.5	1047.2	1046.7	1046.3
162.5°	1065.9	1064.4	1064.2	1064.0	1063.8	1063.6	1063.5	1063.4	1063.3	1063.2	1063.1
165°	1086.0	1084.5	1084.5	1084.5	1084.5	1084.5	1084.6	1084.8	1085.1	1085.2	1085.4
167.5°	1102.6	1101.1	1101.2	1101.2	1101.3	1101.3	1101.6	1102.2	1102.9	1103.5	1104.2
170°	1111.7	1110.3	1110.5	1110.7	1110.9	1111.2	1111.5	1112.2	1112.9	1113.4	1114.1
172.5°	1118.6	1117.1	1117.4	1117.6	1117.8	1117.9	1118.4	1119.1	1119.6	1120.3	1121.0
175°	1126.1	1124.5	1125.0	1125.4	1125.9	1126.2	1126.8	1127.5	1128.1	1128.7	1129.4
177.5°	1130.0	1129.0	1129.4	1129.6	1130.0	1130.3	1130.8	1131.2	1131.8	1132.3	1132.8
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	13.2	15.7	16.2	18.3	18.0	18.9	19.8	20.3	20.7	20.1	19.5
90°	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0	32.5
92.5°	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4	30.5
95°	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1	61.1
97.5°	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7	102.7
100°	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8	131.8
102.5°	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2	163.4
105°	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5	210.8
107.5°	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9	262.1
110°	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9	296.9





TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2	331.8
115°	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5	385.2
117.5°	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5	437.0
120°	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6	471.6
122.5°	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7	507.3
125°	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7	560.1
127.5°	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1	611.3
130°	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9	646.4
132.5°	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5	680.5
135°	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0	730.8
137.5°	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2	779.0
140°	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4	811.4
142.5°	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7	840.8
145°	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1	885.4
147.5°	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0	924.4
150°	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6	949.2
152.5°	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2	974.0
155°	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4	1005.5
157.5°	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0	1034.5
160°	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5	1051.7
162.5°	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9	1067.3
165°	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0	1087.5
167.5°	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6	1104.1
170°	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7	1113.2
172.5°	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6	1120.1
175°	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1	1127.6
177.5°	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0	1131.1
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	20.0	19.9	19.3	19.4	19.9	19.4	19.5
90°	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.6	296.0	295.3	294.6	294.1



TEST NUMBER: P331568-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)