

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644507

Luminaire Tested: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P644507  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7501.1 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644507

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644507

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	101	97	94	91	93	90	88	85	78	76	74	66	65	64	55	55	54	49				
2	93	87	82	78	87	82	77	74	71	68	65	61	59	57	52	50	49	45				
3	87	79	73	68	81	74	69	64	65	61	57	56	53	51	48	46	44	41				
4	81	71	65	60	75	67	61	57	59	55	51	51	48	46	44	42	40	37				
5	75	65	58	53	70	61	55	50	54	49	46	47	44	41	41	39	37	34				
6	70	59	52	47	65	56	50	45	50	45	41	44	40	37	38	35	33	31				
7	65	54	47	42	61	51	45	40	46	41	37	40	37	34	35	33	31	28				
8	61	50	43	38	57	47	41	37	42	37	34	37	34	31	33	30	28	26				
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24				
10	53	42	36	31	50	40	34	30	36	31	28	32	29	26	29	26	24	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	33609	33609	33609
5°	33158	33869	34396
10°	33728	34580	34953
15°	34659	35175	35230
20°	34816	35208	34621
25°	34015	34392	33639
30°	32204	32567	31629
35°	29274	29274	28665
40°	24077	23837	23325
45°	14396	16919	13728
50°	4654	9429	4367
55°	1646	3157	1646
60°	106	891	52
65°	61	61	0
70°	76	0	0
75°	0	0	0
80°	0	0	0
85°	296	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 16919 cd/sqm



TEST NUMBER: P644507

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	250.3	3.3
10°-20°	740.7	9.9
20°-30°	1096.2	14.6
30°-40°	1133.0	15.1
40°-50°	659.2	8.8
50°-60°	111.7	1.5
60°-70°	4.4	0.1
70°-80°	0.6	0.0
80°-90°	2.0	0.0
90°-100°	80.2	1.1
100°-110°	571.3	7.6
110°-120°	775.6	10.3
120°-130°	631.3	8.4
130°-140°	507.7	6.8
140°-150°	400.3	5.3
150°-160°	292.7	3.9
160°-170°	181.8	2.4
170°-180°	62.0	0.8
0°-30°	2087.2	27.8
0°-40°	3220.2	42.9
0°-60°	3991.1	53.2
0°-90°	3998.2	53.3
90°-120°	1427.1	19.0
90°-150°	2966.4	39.5
90°-180°	3503.0	46.7
0°-180°	7501.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2602	2602	2602	2602	2602	
5°	2557	2625	2612	2619	2653	245
15°	2592	2683	2630	2617	2634	729
25°	2387	2466	2413	2340	2360	1090
35°	1856	1886	1856	1810	1818	1137
45°	788	917	926	894	752	609
55°	73	85	140	79	73	81
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	4	8	12	12	2
95°	33	61	33	37	45	37
105°	127	195	742	948	628	134
115°	226	274	640	1330	1554	224
125°	324	368	603	1054	1247	288
135°	402	446	607	868	997	309
145°	476	516	611	756	837	299
155°	558	578	623	686	718	256
165°	619	627	640	656	668	174
175°	652	656	652	648	644	62
180°	652	652	652	652	652	



TEST NUMBER: P644507

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2602.0	2602.0	2602.0	2602.0	2602.0
2.5°	2567.8	2618.7	2600.3	2602.3	2615.0
5°	2557.3	2624.8	2612.1	2619.0	2652.8
7.5°	2565.0	2633.3	2631.6	2633.6	2666.6
10°	2571.5	2643.0	2636.5	2635.2	2664.9
12.5°	2584.5	2662.4	2636.5	2633.4	2658.4
15°	2591.8	2683.2	2630.4	2616.6	2634.5
17.5°	2567.0	2668.7	2597.1	2560.3	2567.4
20°	2532.9	2636.2	2561.4	2506.8	2518.7
22.5°	2479.3	2577.8	2511.0	2443.5	2458.6
25°	2386.7	2466.1	2413.1	2340.4	2360.3
27.5°	2255.0	2317.8	2284.3	2213.9	2226.2
30°	2159.2	2210.8	2183.5	2114.6	2120.6
32.5°	2048.7	2092.4	2063.3	2004.0	2003.6
35°	1856.5	1886.3	1856.5	1810.0	1817.9
37.5°	1605.1	1627.7	1597.3	1569.4	1573.4
40°	1427.9	1445.8	1413.7	1387.2	1383.3
42.5°	1206.9	1256.6	1225.2	1189.2	1194.8
45°	788.1	917.2	926.2	894.5	751.5
47.5°	397.3	538.3	644.7	489.2	350.6
50°	231.6	317.0	469.2	259.0	217.3
52.5°	151.9	188.1	327.8	163.7	144.2
55°	73.1	85.0	140.2	79.1	73.1
57.5°	25.2	38.7	62.2	39.5	28.0
60°	4.1	16.0	34.5	12.0	2.0
62.5°	2.4	4.8	21.5	2.4	0.4
65°	2.0	2.0	2.0	0.0	0.0
67.5°	2.0	2.0	0.0	0.0	0.0
70°	2.0	2.0	0.0	0.0	0.0
72.5°	2.0	2.0	0.0	0.0	0.0
75°	0.0	2.0	0.0	0.0	0.0
77.5°	0.0	2.0	0.0	0.0	0.0
80°	0.0	2.0	0.0	0.0	0.0
82.5°	0.0	2.0	0.0	0.0	0.0
85°	2.0	2.0	0.0	0.0	0.0
87.5°	1.6	2.4	1.6	2.5	2.5
90°	0.0	4.0	8.2	12.3	12.3
92.5°	9.8	13.9	18.0	25.5	28.7
95°	32.8	60.9	32.8	37.1	45.1
97.5°	58.2	116.8	241.2	71.1	61.5
100°	77.9	146.1	483.9	142.5	94.3
102.5°	97.6	169.0	654.6	375.9	205.9
105°	127.1	195.3	742.3	948.3	627.5
107.5°	156.7	208.0	708.7	1380.1	1292.7
110°	176.4	224.5	689.0	1450.2	1558.5

TEST NUMBER: P644507

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	196.0	244.2	669.3	1409.2	1591.3
115°	225.6	273.7	639.8	1329.8	1554.4
117.5°	255.9	303.2	632.4	1243.8	1474.8
120°	278.9	323.0	619.3	1178.4	1419.0
122.5°	295.3	342.6	602.9	1122.2	1343.6
125°	324.0	368.1	602.9	1054.3	1246.8
127.5°	347.8	392.7	603.7	975.5	1165.6
130°	360.9	409.0	607.0	922.8	1103.2
132.5°	377.3	425.4	607.0	899.1	1047.5
135°	401.9	446.0	607.0	868.3	996.6
137.5°	422.4	469.7	607.0	834.2	944.1
140°	438.8	482.9	607.0	814.3	914.6
142.5°	455.2	496.1	610.3	791.2	885.1
145°	475.7	515.8	611.1	756.5	836.7
147.5°	500.4	535.6	616.0	731.4	793.2
150°	516.8	548.8	619.3	714.8	766.9
152.5°	533.2	562.0	619.3	701.5	744.0
155°	557.8	577.8	623.4	685.6	717.7
157.5°	577.5	596.7	628.3	675.6	698.9
160°	590.6	606.6	631.6	669.0	689.0
162.5°	600.4	616.5	634.9	665.5	679.2
165°	619.3	627.3	639.8	656.5	668.5
167.5°	630.0	637.2	643.9	652.3	659.5
170°	639.8	643.8	643.9	652.2	656.2
172.5°	643.1	650.3	647.2	648.9	652.9
175°	652.1	656.1	652.1	647.9	643.9
177.5°	652.1	655.3	652.1	652.0	648.8
180°	652.1	652.1	652.1	652.1	652.1

(END OF REPORT)