

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331862-830

Luminaire Tested: **S122RDIW-S1005D1440U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331862-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8307.4 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67		57	56	55		45	44	43	38
2	89	82	76	71	81	75	70	66	63	59	56		51	49	47		41	39	38	33
3	81	73	66	60	74	67	61	56	56	52	48		46	43	40		37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42		41	38	35		33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	36		38	34	31		30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32		34	31	28		28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29		31	28	25		26	23	21	18
8	55	43	36	31	51	40	34	29	34	29	26		29	25	22		24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23		27	23	20		22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21		25	21	19		21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.1	2.4
10°-20°	549.1	6.6
20°-30°	707.5	8.5
30°-40°	672.4	8.1
40°-50°	576.0	6.9
50°-60°	438.6	5.3
60°-70°	277.3	3.3
70°-80°	138.5	1.7
80°-90°	42.8	0.5
90°-100°	106.7	1.3
100°-110°	331.4	4.0
110°-120°	566.4	6.8
120°-130°	744.9	9.0
130°-140°	836.1	10.1
140°-150°	819.8	9.9
150°-160°	687.6	8.3
160°-170°	456.0	5.5
170°-180°	159.4	1.9
0°-30°	1453.7	17.5
0°-40°	2126.0	25.6
0°-60°	3140.7	37.8
0°-90°	3599.2	43.3
90°-120°	1004.5	12.1
90°-150°	3405.2	41.0
90°-180°	4708.0	56.7
0°-180°	8307.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	29
90°	48	1	48	1	48	22
95°	88	74	88	74	88	98
105°	316	306	316	306	316	332
115°	568	568	568	568	568	561
125°	830	827	830	827	830	740
135°	1083	1070	1083	1070	1083	833
145°	1313	1299	1313	1299	1313	820
155°	1496	1485	1496	1485	1496	689
165°	1617	1616	1617	1616	1617	456
175°	1675	1681	1675	1681	1675	159
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	18.9	19.4	19.3	19.3	19.2	19.2	19.4	20.1	19.6	20.4	18.4
90°	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4	49.1	49.8	42.8
92.5°	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4	45.3	45.1	43.5
95°	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0	91.0	91.0	90.3
97.5°	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9	152.9	152.9	151.7
100°	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0	196.0	196.0	195.1
102.5°	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2	243.0	242.7	241.5
105°	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9	313.2	312.6	312.0
107.5°	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1	389.8	389.6	389.6
110°	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8	494.6	495.3	495.6
115°	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4	573.7	574.1	574.7
117.5°	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4	651.2	652.0	653.7
120°	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9	701.9	701.9	704.5
122.5°	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0	755.7	756.5	758.3
125°	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6	834.5	835.5	836.5
127.5°	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9	911.1	912.3	913.4
130°	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1	962.8	963.4	964.0
132.5°	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0	1014.3	1015.7	1015.6
135°	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8	1088.2	1088.4	1087.8
137.5°	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5	1159.8	1160.1	1159.2
140°	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8	1207.8	1207.8	1206.3
142.5°	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5	1251.2	1251.0	1249.9
145°	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9	1317.5	1317.2	1315.3
147.5°	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0	1375.4	1374.6	1373.4
150°	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0	1409.8
152.5°	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4	1445.9
155°	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6	1495.0	1493.4	1492.4
157.5°	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7	1537.6	1535.5	1534.9
160°	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4	1563.5	1561.6	1561.3
162.5°	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7	1586.5	1584.3	1584.0
165°	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6	1616.4	1614.2	1614.2
167.5°	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3	1641.2	1638.9	1639.0
170°	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0	1654.7	1652.6	1652.8
172.5°	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2	1665.0	1662.7	1663.1
175°	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3	1676.1	1673.9	1674.5
177.5°	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4	1680.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	17.0	16.2	14.8	13.1	12.9	12.8	14.9	17.1	15.5	14.5	14.1
90°	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4	5.2	9.0	12.8
92.5°	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3	28.1	30.8	33.6
95°	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9	77.0	80.2	83.3
97.5°	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0	137.8	140.5	143.4
100°	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5	182.9	185.5	188.0
102.5°	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2	230.3	232.2	234.2
105°	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5	306.4	307.4	308.3
107.5°	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3	384.7	386.2	387.6
110°	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4	435.3	437.2	439.0





TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0	489.8	491.7	493.6
115°	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4	570.2	572.1	574.1
117.5°	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6	651.0	653.6	656.1
120°	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	704.5	707.0	709.5
122.5°	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8	753.8	756.9	759.9
125°	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0	829.8	832.6	835.5
127.5°	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2	904.7	908.3	912.0
130°	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7	951.9	956.0	960.1
132.5°	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0	1003.4	1006.7	1010.1
135°	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0	1073.5	1076.9	1080.3
137.5°	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6	1146.4	1149.2	1152.1
140°	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9	1190.7	1193.6	1196.5
142.5°	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4	1236.2	1239.1	1241.9
145°	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7	1301.0	1303.2	1305.3
147.5°	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0	1359.6	1362.3	1365.0
150°	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8	1398.6	1400.6	1402.5
152.5°	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0	1433.9	1435.8	1437.7
155°	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9	1485.8	1486.8	1487.7
157.5°	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0	1530.7	1531.3	1532.0
160°	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4	1558.0	1558.6	1559.2
162.5°	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3	1582.5	1582.6	1582.7
165°	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6	1615.3	1615.0	1614.7
167.5°	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4	1642.5	1641.5	1640.6
170°	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2	1657.3	1656.3	1655.4
172.5°	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5	1667.5	1666.6	1665.7
175°	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9	1680.0	1679.0	1678.1
177.5°	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1	1685.4	1684.6	1683.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	14.3	14.8	15.0	16.4	17.8	18.6	18.5	17.8	17.6	17.5	17.0
90°	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4	47.9	47.2	47.0
92.5°	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4	45.5	45.7	45.8
95°	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0	91.0	91.0	90.6
97.5°	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9	152.9	152.9	152.9
100°	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0	196.0	196.0	196.0
102.5°	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2	243.5	243.7	243.6
105°	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9	314.5	315.1	315.5
107.5°	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1	390.4	390.6	390.0
110°	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	441.4



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8	493.0	492.3	491.5
115°	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4	573.1	572.8	572.1
117.5°	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4	649.7	648.9	648.0
120°	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9	701.9	701.9	701.4
122.5°	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0	754.2	753.5	752.7
125°	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6	832.6	831.7	831.1
127.5°	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9	908.8	907.7	906.6
130°	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1	961.5	960.8	959.9
132.5°	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0	1011.5	1010.1	1008.9
135°	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8	1087.5	1087.2	1086.6
137.5°	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5	1159.3	1159.0	1158.3
140°	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8	1207.8	1207.8	1207.2
142.5°	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5	1251.8	1252.0	1251.5
145°	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9	1318.1	1318.4	1318.0
147.5°	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0	1376.7	1377.4	1377.1
150°	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8
152.5°	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2
155°	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6	1498.2	1499.7	1500.1
157.5°	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7	1541.9	1544.1	1544.4
160°	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4	1567.3	1569.1	1569.5
162.5°	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7	1590.8	1592.9	1593.3
165°	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6	1620.8	1623.1	1623.3
167.5°	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3	1645.6	1647.8	1648.0
170°	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0	1659.2	1661.4	1661.5
172.5°	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2	1669.4	1671.6	1671.8
175°	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3	1680.5	1682.7	1682.9
177.5°	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	17.0	16.5	17.2	16.6	17.2	16.5	17.0	17.0	17.5	17.6	17.8
90°	47.4	47.7	48.0	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4
92.5°	45.8	45.9	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4
95°	90.0	89.4	88.7	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0
97.5°	152.8	152.7	152.7	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9
100°	195.6	195.3	195.0	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0
102.5°	243.4	243.1	242.7	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2
105°	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9
107.5°	388.6	387.1	385.7	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1
110°	440.5	439.5	438.6	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	490.9	490.2	489.5	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8
115°	571.2	570.2	569.3	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4
117.5°	647.1	646.1	645.2	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4
120°	700.5	699.6	698.6	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9
122.5°	752.1	751.4	750.6	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0
125°	830.8	830.5	830.2	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6
127.5°	905.6	904.6	903.6	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9
130°	958.7	957.4	956.1	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1
132.5°	1008.0	1006.9	1005.9	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0
135°	1085.6	1084.7	1083.7	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8
137.5°	1157.1	1155.7	1154.5	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5
140°	1205.9	1204.7	1203.3	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8
142.5°	1250.3	1249.0	1247.7	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5
145°	1316.7	1315.5	1314.2	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9
147.5°	1375.9	1374.7	1373.6	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0
150°	1413.8	1412.9	1411.9	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9
152.5°	1451.0	1449.7	1448.6	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7
155°	1499.1	1498.2	1497.2	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6
157.5°	1542.8	1541.3	1539.8	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7
160°	1568.2	1567.0	1565.8	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4
162.5°	1591.8	1590.3	1588.7	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7
165°	1621.7	1620.2	1618.6	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6
167.5°	1646.4	1644.7	1643.1	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3
170°	1659.6	1657.7	1655.9	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0
172.5°	1669.9	1668.0	1666.1	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2
175°	1680.9	1679.0	1677.2	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3
177.5°	1685.0	1683.5	1681.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	18.5	18.6	17.8	16.4	15.0	14.8	14.3	14.1	14.5	15.5	17.1
90°	49.1	49.8	42.8	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4
92.5°	45.3	45.1	43.5	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3
95°	91.0	91.0	90.3	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9
97.5°	152.9	152.9	151.7	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0
100°	196.0	196.0	195.1	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5
102.5°	243.0	242.7	241.5	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2
105°	313.2	312.6	312.0	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5
107.5°	389.8	389.6	389.6	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3
110°	442.0	442.0	442.0	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.6	495.3	495.6	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0
115°	573.7	574.1	574.7	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4
117.5°	651.2	652.0	653.7	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6
120°	701.9	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9
122.5°	755.7	756.5	758.3	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8
125°	834.5	835.5	836.5	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0
127.5°	911.1	912.3	913.4	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2
130°	962.8	963.4	964.0	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7
132.5°	1014.3	1015.7	1015.6	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0
135°	1088.2	1088.4	1087.8	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0
137.5°	1159.8	1160.1	1159.2	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6
140°	1207.8	1207.8	1206.3	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9
142.5°	1251.2	1251.0	1249.9	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4
145°	1317.5	1317.2	1315.3	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7
147.5°	1375.4	1374.6	1373.4	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0
150°	1411.9	1411.0	1409.8	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8
152.5°	1448.6	1447.4	1445.9	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0
155°	1495.0	1493.4	1492.4	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9
157.5°	1537.6	1535.5	1534.9	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0
160°	1563.5	1561.6	1561.3	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4
162.5°	1586.5	1584.3	1584.0	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3
165°	1616.4	1614.2	1614.2	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6
167.5°	1641.2	1638.9	1639.0	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4
170°	1654.7	1652.6	1652.8	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2
172.5°	1665.0	1662.7	1663.1	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5
175°	1676.1	1673.9	1674.5	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9
177.5°	1681.9	1680.4	1680.9	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.9	12.8	12.9	13.1	14.8	16.2	17.0	18.4	20.4	19.6	20.1
90°	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4
92.5°	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4
95°	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0
97.5°	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9
100°	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0
102.5°	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2
105°	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9
107.5°	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1
110°	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0





TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8
115°	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4
117.5°	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4
120°	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9
122.5°	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0
125°	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6
127.5°	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9
130°	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1
132.5°	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0
135°	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8
137.5°	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5
140°	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8
142.5°	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5
145°	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9
147.5°	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0
150°	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9
152.5°	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7
155°	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6
157.5°	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7
160°	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4
162.5°	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7
165°	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6
167.5°	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3
170°	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0
172.5°	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2
175°	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3
177.5°	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	19.4	19.2	19.2	19.3	19.3	19.4	18.9
90°	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331862-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)