

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644511

Luminaire Tested: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P644511  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - FLAT FROSTED LENS - 1000 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7351.0 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 58.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644511  
CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644511

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	47	36	29	24	31	26	22	26	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	20	24	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24332	24332	24332
5°	24060	24225	24392
10°	23868	23968	24137
15°	23545	23545	23682
20°	23216	23039	22969
25°	22611	22427	22135
30°	21942	21636	21216
35°	21258	20731	20247
40°	20440	19835	19144
45°	19758	19009	18071
50°	18902	18078	17151
55°	18182	17258	16220
60°	17347	16420	15029
65°	16451	15274	14101
70°	15583	14134	13166
75°	14579	12919	12277
80°	13343	11818	11251
85°	12542	11023	10263

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19758 cd/sqm



TEST NUMBER: P644511

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.8	1.9
10°-20°	397.8	5.4
20°-30°	578.4	7.9
30°-40°	658.0	9.0
40°-50°	641.5	8.7
50°-60°	547.6	7.4
60°-70°	398.0	5.4
70°-80°	225.0	3.1
80°-90°	70.8	1.0
90°-100°	92.8	1.3
100°-110°	604.0	8.2
110°-120°	816.4	11.1
120°-130°	663.8	9.0
130°-140°	532.7	7.2
140°-150°	419.8	5.7
150°-160°	306.9	4.2
160°-170°	190.7	2.6
170°-180°	65.0	0.9
0°-30°	1118.0	15.2
0°-40°	1776.0	24.2
0°-60°	2965.1	40.3
0°-90°	3659.0	49.8
90°-120°	1513.3	20.6
90°-150°	3129.5	42.6
90°-180°	3692.0	50.2
0°-180°	7351.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1507	1507	1507	1507	1507	
5°	1484	1506	1495	1493	1505	141
15°	1409	1427	1409	1407	1417	397
25°	1269	1281	1259	1236	1242	584
35°	1078	1082	1052	1027	1027	673
45°	865	861	832	804	791	666
55°	646	644	613	584	576	576
65°	431	427	400	375	369	427
75°	234	226	207	199	197	248
85°	68	60	60	57	55	73
90°	8	14	21	23	23	10
95°	51	72	41	45	51	51
105°	144	211	783	996	658	152
115°	243	291	673	1395	1630	242
125°	344	390	634	1106	1308	305
135°	422	468	637	911	1045	325
145°	499	541	641	793	877	313
155°	585	606	654	719	753	269
165°	650	658	671	688	701	182
175°	684	688	684	680	675	65
180°	684	684	684	684	684	

TEST NUMBER: P644511

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1507.0	1507.0	1507.0	1507.0	1507.0
2.5°	1493.9	1513.1	1502.1	1502.2	1508.7
5°	1484.5	1506.5	1494.7	1492.9	1505.0
7.5°	1468.9	1490.5	1476.7	1474.6	1490.2
10°	1455.8	1475.8	1461.9	1458.1	1472.2
12.5°	1437.7	1457.8	1443.9	1438.4	1452.5
15°	1408.6	1426.6	1408.6	1406.8	1416.8
17.5°	1375.8	1391.4	1370.5	1363.7	1371.3
20°	1351.2	1365.2	1340.9	1330.8	1336.8
22.5°	1320.0	1334.1	1308.1	1293.1	1300.8
25°	1269.2	1281.2	1258.9	1236.5	1242.5
27.5°	1214.6	1223.9	1201.5	1178.6	1180.6
30°	1176.9	1182.9	1160.5	1136.0	1138.0
32.5°	1137.5	1142.0	1117.9	1091.6	1092.0
35°	1078.5	1082.5	1051.8	1027.2	1027.2
37.5°	1015.8	1018.2	985.4	958.7	955.9
40°	969.8	973.8	941.1	914.3	908.3
42.5°	927.2	928.0	898.5	871.6	864.0
45°	865.3	861.2	832.5	803.5	791.4
47.5°	798.4	798.4	765.6	736.6	725.4
50°	752.5	752.5	719.7	690.8	682.8
52.5°	709.8	708.2	677.0	648.1	636.8
55°	645.9	643.9	613.1	584.2	576.2
57.5°	578.2	578.2	549.5	518.5	509.7
60°	537.2	537.2	508.5	477.5	465.4
62.5°	492.9	491.3	462.6	434.9	427.7
65°	430.6	426.6	399.8	375.1	369.1
67.5°	371.1	367.1	338.7	318.9	314.9
70°	330.1	326.1	299.4	282.9	278.9
72.5°	290.7	285.1	261.6	248.4	244.4
75°	233.7	225.7	207.1	198.8	196.8
77.5°	179.6	166.0	158.3	152.5	150.5
80°	143.5	131.5	127.1	123.0	121.0
82.5°	112.4	100.3	99.2	96.7	94.7
85°	67.7	59.6	59.5	57.4	55.4
87.5°	29.5	26.0	27.1	27.6	27.6
90°	8.2	14.4	20.9	23.2	23.2
92.5°	25.1	24.9	27.9	35.3	37.1
95°	50.8	72.2	40.6	45.0	51.4
97.5°	75.4	130.8	258.6	78.3	66.6
100°	96.1	161.6	511.6	151.4	101.0
102.5°	115.1	183.9	690.6	396.2	216.3
105°	143.6	211.1	782.6	996.5	658.1
107.5°	174.1	224.4	747.3	1449.4	1355.7
110°	193.1	241.6	726.7	1522.9	1634.4



TEST NUMBER: P644511

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	213.8	262.3	706.0	1479.9	1668.8
115°	242.7	291.2	673.0	1394.6	1630.1
117.5°	274.5	322.2	665.3	1304.4	1546.7
120°	298.6	342.9	651.5	1235.9	1488.2
122.5°	314.2	363.4	634.3	1176.9	1409.0
125°	343.9	390.1	634.3	1105.7	1307.5
127.5°	366.8	415.5	635.2	1023.0	1222.4
130°	380.5	431.0	638.6	967.7	1157.0
132.5°	396.1	446.6	637.0	942.9	1098.5
135°	421.5	467.8	636.6	910.6	1045.2
137.5°	443.0	492.6	636.6	874.9	990.1
140°	460.2	506.5	636.6	854.0	959.1
142.5°	477.4	520.3	640.0	829.8	928.2
145°	498.9	541.0	640.9	793.3	877.4
147.5°	524.7	561.7	646.0	767.1	831.8
150°	541.9	575.6	649.5	749.6	804.3
152.5°	559.1	589.4	649.5	735.6	780.2
155°	585.0	606.0	653.8	719.0	752.7
157.5°	605.6	625.8	658.9	708.5	732.9
160°	619.4	636.2	662.4	701.6	722.6
162.5°	629.7	646.5	665.8	698.0	712.3
165°	649.5	657.9	671.0	688.5	701.1
167.5°	660.7	668.2	675.3	684.0	691.6
170°	671.0	675.2	675.3	684.0	688.2
172.5°	674.4	682.0	678.7	680.5	684.7
175°	683.9	688.1	683.9	679.5	675.3
177.5°	683.9	687.2	683.9	683.8	680.4
180°	683.9	683.9	683.9	683.9	683.9

(END OF REPORT)