

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331864-830

Luminaire Tested: **S122RDIW-S1005D1440U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331864-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7997.8 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25770	25770	25770
5°	25869	25449	25590
10°	25671	25032	24819
15°	25377	24289	23590
20°	24967	23230	22063
25°	24549	22026	20587
30°	23968	20789	18690
35°	23402	19446	17026
40°	22835	18054	15099
45°	22165	16493	13358
50°	21481	14913	11645
55°	20777	13216	10001
60°	19963	11428	8302
65°	19037	9605	7561
70°	17934	7912	6954
75°	16581	7211	6488
80°	14635	6453	5904
85°	11504	5076	5076



TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.4	1.9
10°-20°	410.2	5.1
20°-30°	576.1	7.2
30°-40°	628.2	7.9
40°-50°	577.6	7.2
50°-60°	453.6	5.7
60°-70°	295.8	3.7
70°-80°	152.5	1.9
80°-90°	46.3	0.6
90°-100°	106.7	1.3
100°-110°	331.4	4.1
110°-120°	566.4	7.1
120°-130°	744.9	9.3
130°-140°	836.1	10.5
140°-150°	819.8	10.2
150°-160°	687.6	8.6
160°-170°	456.0	5.7
170°-180°	159.4	2.0
0°-30°	1135.7	14.2
0°-40°	1763.9	22.1
0°-60°	2795.1	34.9
0°-90°	3289.6	41.1
90°-120°	1004.5	12.6
90°-150°	3405.2	42.6
90°-180°	4708.0	58.9
0°-180°	7997.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1596	1596	1596	1596	1596	
5°	1596	1588	1570	1582	1579	151
15°	1518	1500	1453	1426	1411	427
25°	1378	1329	1236	1179	1156	633
35°	1187	1111	987	899	864	743
45°	971	871	722	623	585	749
55°	738	623	470	386	355	659
65°	498	381	251	205	198	494
75°	266	168	116	106	104	281
85°	62	33	27	27	27	73
90°	1	19	50	47	48	6
95°	74	87	91	91	88	85
105°	306	310	313	315	316	323
115°	568	576	574	572	568	562
125°	827	839	836	831	830	739
135°	1070	1085	1088	1087	1083	826
145°	1299	1309	1317	1318	1313	811
155°	1485	1489	1493	1500	1496	683
165°	1616	1614	1614	1623	1617	455
175°	1681	1677	1674	1683	1675	160
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1601.9	1600.6	1599.3	1598.1	1596.8	1594.7	1591.9	1589.1	1586.3	1583.5	1586.0
5°	1596.1	1594.5	1592.9	1591.3	1589.7	1586.9	1582.6	1578.5	1574.3	1570.2	1573.0
7.5°	1579.7	1577.7	1575.7	1573.7	1571.7	1568.3	1563.4	1558.5	1553.7	1548.8	1549.6
10°	1565.8	1563.6	1561.3	1559.1	1556.8	1552.5	1546.1	1539.6	1533.2	1526.8	1525.9
12.5°	1548.5	1545.7	1542.9	1540.2	1537.5	1531.9	1523.7	1515.5	1507.3	1499.1	1497.3
15°	1518.2	1514.6	1511.1	1507.5	1504.0	1496.8	1485.9	1475.0	1464.1	1453.1	1447.1
17.5°	1480.8	1475.5	1470.1	1464.7	1459.3	1449.6	1435.6	1421.6	1407.6	1393.6	1386.4
20°	1453.1	1446.7	1440.3	1433.9	1427.5	1416.3	1400.1	1384.1	1368.1	1352.0	1344.0
22.5°	1423.1	1415.9	1408.7	1401.6	1394.3	1381.7	1363.6	1345.5	1327.4	1309.3	1298.9
25°	1378.0	1367.7	1357.4	1347.2	1336.9	1321.3	1300.0	1278.8	1257.6	1236.4	1223.3
27.5°	1323.7	1312.6	1301.4	1290.2	1279.0	1261.5	1237.7	1213.7	1189.9	1166.0	1150.7
30°	1285.6	1273.4	1261.2	1249.0	1236.8	1217.9	1192.1	1166.5	1140.9	1115.1	1098.7
32.5°	1248.6	1234.4	1220.1	1205.9	1191.6	1171.4	1145.2	1119.0	1092.8	1066.6	1047.9
35°	1187.3	1171.0	1154.6	1138.2	1121.9	1099.6	1071.3	1043.1	1014.8	986.6	966.4
37.5°	1126.1	1108.1	1090.1	1072.1	1054.2	1030.2	1000.0	970.0	939.8	909.7	887.5
40°	1083.4	1064.1	1044.8	1025.6	1006.4	981.1	950.0	918.9	887.7	856.6	833.8
42.5°	1039.4	1019.2	998.9	978.5	958.3	932.1	899.9	867.7	835.6	803.4	779.9
45°	970.7	949.1	927.7	906.2	884.7	857.1	823.3	789.7	755.9	722.3	699.5
47.5°	903.6	880.9	858.1	835.3	812.5	783.7	748.9	714.1	679.3	644.5	621.9
50°	855.2	832.4	809.5	786.7	763.9	734.9	699.6	664.3	629.0	593.7	571.6
52.5°	807.8	783.9	760.2	736.3	712.5	683.3	648.8	614.3	579.7	545.2	523.8
55°	738.1	713.1	688.1	663.0	638.0	608.1	573.4	538.8	504.2	469.5	450.2
57.5°	666.8	641.1	615.4	589.7	564.0	534.5	501.2	467.9	434.6	401.2	383.6
60°	618.2	592.6	566.8	541.2	515.5	486.2	453.1	420.0	386.9	353.9	337.5
62.5°	570.9	545.2	519.5	493.8	468.2	439.5	408.0	376.5	345.0	313.5	297.8
65°	498.3	472.3	446.4	420.4	394.4	366.9	338.0	309.2	280.2	251.4	240.4
67.5°	428.4	402.7	376.8	351.0	325.2	299.3	273.3	247.3	221.3	195.3	190.3
70°	379.9	354.9	329.8	304.8	279.7	256.2	234.0	211.9	189.7	167.6	164.4
72.5°	333.7	309.6	285.7	261.6	237.6	216.7	199.0	181.2	163.3	145.6	142.9
75°	265.8	243.3	220.8	198.4	175.9	159.2	148.3	137.4	126.5	115.6	113.3
77.5°	199.1	179.4	159.7	140.0	120.2	107.7	102.5	97.2	91.9	86.7	85.4
80°	157.4	141.1	124.7	108.3	92.0	82.2	79.0	75.8	72.6	69.4	68.1
82.5°	119.3	106.5	93.8	81.0	68.2	60.7	58.5	56.4	54.2	52.0	51.3
85°	62.1	55.3	48.6	41.8	35.2	31.3	30.3	29.4	28.4	27.4	27.4
87.5°	18.8	17.4	16.2	14.9	13.6	13.7	15.0	16.4	17.8	19.2	18.9
90°	1.4	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1
92.5°	25.3	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3
95°	73.9	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0
97.5°	135.0	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9
100°	180.5	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0
102.5°	228.2	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0
105°	305.5	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2
107.5°	383.3	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8
110°	433.4	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.0	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6
115°	568.4	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7
117.5°	648.6	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2
120°	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9
122.5°	750.8	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7
125°	827.0	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5
127.5°	901.2	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1
130°	947.7	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8
132.5°	1000.0	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3
135°	1070.0	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2
137.5°	1143.6	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8
140°	1187.9	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8
142.5°	1233.4	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2
145°	1298.7	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5
147.5°	1357.0	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4
150°	1396.8	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9
152.5°	1432.0	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6
155°	1484.9	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0
157.5°	1530.0	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6
160°	1557.4	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5
162.5°	1582.3	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5
165°	1615.6	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4
167.5°	1643.4	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2
170°	1658.2	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7
172.5°	1668.5	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0
175°	1680.9	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1
177.5°	1686.1	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1588.6	1591.1	1593.7	1594.7	1594.2	1593.7	1593.2	1592.7
5°	1575.9	1578.9	1581.7	1582.6	1581.7	1580.7	1579.8	1578.9
7.5°	1550.4	1551.2	1552.1	1551.7	1550.0	1548.3	1546.7	1545.0
10°	1524.8	1523.9	1523.0	1521.5	1519.6	1517.7	1515.7	1513.8
12.5°	1495.6	1493.8	1492.1	1489.7	1486.5	1483.3	1480.1	1476.9
15°	1441.0	1434.8	1428.7	1424.1	1420.9	1417.7	1414.5	1411.3
17.5°	1379.1	1371.9	1364.6	1358.2	1352.7	1347.2	1341.6	1336.1
20°	1336.0	1327.9	1319.9	1312.4	1305.3	1298.3	1291.2	1284.1
22.5°	1288.6	1278.3	1267.9	1260.1	1254.9	1249.6	1244.3	1239.1
25°	1210.1	1197.0	1183.8	1174.9	1170.0	1165.2	1160.4	1155.6
27.5°	1135.3	1119.9	1104.6	1093.1	1085.4	1077.8	1070.2	1062.5
30°	1082.4	1066.0	1049.6	1037.2	1028.5	1019.8	1011.2	1002.5
32.5°	1029.3	1010.6	991.8	978.5	970.3	962.1	953.9	945.8
35°	946.1	926.0	905.7	892.0	885.0	877.9	870.8	863.8
37.5°	865.2	842.9	820.6	805.4	797.4	789.3	781.2	773.1
40°	811.0	788.2	765.4	749.9	741.5	733.1	724.8	716.4
42.5°	756.3	732.7	709.2	693.3	685.2	677.1	669.1	661.0
45°	676.7	653.8	631.0	615.9	608.1	600.4	592.7	585.0
47.5°	599.2	576.6	553.8	539.0	532.1	525.1	518.0	511.0
50°	549.4	527.3	505.1	490.6	483.9	477.1	470.4	463.6
52.5°	502.4	481.0	459.7	445.8	439.6	433.4	427.2	420.9
55°	430.9	411.7	392.4	379.8	373.6	367.5	361.5	355.3
57.5°	366.0	348.3	330.6	319.2	314.1	309.0	303.9	298.7
60°	321.1	304.8	288.4	277.7	272.5	267.4	262.2	257.1
62.5°	282.3	266.6	251.1	241.7	238.7	235.5	232.4	229.4
65°	229.5	218.6	207.6	201.7	200.8	199.8	198.9	197.9
67.5°	185.3	180.3	175.2	172.2	171.3	170.2	169.2	168.1
70°	161.2	158.0	154.8	152.5	151.2	149.9	148.6	147.3
72.5°	140.3	137.5	134.8	133.1	132.3	131.6	130.7	130.0
75°	111.0	108.9	106.6	105.3	105.0	104.6	104.3	104.0
77.5°	84.1	82.8	81.5	80.6	80.1	79.6	79.1	78.6
80°	66.7	65.5	64.2	63.5	63.5	63.5	63.5	63.5
82.5°	50.4	49.7	48.9	48.5	48.5	48.5	48.5	48.5
85°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
87.5°	18.4	18.0	17.6	17.5	17.5	17.6	17.7	17.7
90°	48.4	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.4	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.2	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	313.9	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.1	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	442.0	441.4	440.5	439.5	438.6	437.6





TEST NUMBER: P331864-830

CATALOG NUMBER: S122RDIW-S1005D1440U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.8	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.4	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	650.4	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	755.0	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	833.6	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	909.9	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	962.1	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1013.0	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.8	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.5	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.5	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1317.9	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.0	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1496.6	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1539.7	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1565.4	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1588.7	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1618.6	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1643.3	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1657.0	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1667.2	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1678.3	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)