

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644537

Luminaire Tested: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644537
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8503.9 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 76.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644537

CATALOG NUMBER: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644537

CATALOG NUMBER: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	99	95	92	89	91	88	85	83	74	72	71	62	60	59	50	49	49	43				43
2	92	86	80	76	84	79	75	71	67	64	62	57	54	53	46	45	44	39				39
3	85	77	71	66	78	72	66	62	61	57	54	52	49	47	43	41	40	36				36
4	79	70	63	58	73	65	59	54	56	52	48	48	44	42	40	38	36	33				33
5	73	63	56	51	68	59	53	48	51	46	43	44	40	38	37	35	33	30				30
6	68	57	50	45	63	54	47	43	47	42	38	40	37	34	34	32	30	27				27
7	63	52	45	40	59	49	43	38	43	38	35	37	34	31	32	29	27	25				25
8	59	48	41	36	55	45	39	35	40	35	31	34	31	28	30	27	25	23				23
9	55	44	37	33	51	42	36	31	37	32	29	32	28	26	28	25	23	21				21
10	52	41	34	30	48	38	33	29	34	29	26	30	26	24	26	23	21	19				19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	33609	33609	33609
5°	33158	33869	34396
10°	33728	34580	34953
15°	34659	35175	35230
20°	34816	35208	34621
25°	34015	34392	33639
30°	32204	32567	31629
35°	29274	29274	28665
40°	24077	23837	23325
45°	14396	16919	13728
50°	4654	9429	4367
55°	1646	3157	1646
60°	106	891	52
65°	61	61	0
70°	76	0	0
75°	0	0	0
80°	0	0	0
85°	296	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 16919 cd/sqm



TEST NUMBER: P644537

CATALOG NUMBER: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.3	2.9
10°-20°	740.7	8.7
20°-30°	1096.2	12.9
30°-40°	1133.0	13.3
40°-50°	659.2	7.8
50°-60°	111.7	1.3
60°-70°	4.4	0.1
70°-80°	0.6	0.0
80°-90°	2.5	0.0
90°-100°	103.1	1.2
100°-110°	734.8	8.6
110°-120°	997.6	11.7
120°-130°	811.9	9.5
130°-140°	653.0	7.7
140°-150°	514.8	6.1
150°-160°	376.4	4.4
160°-170°	233.8	2.7
170°-180°	79.7	0.9
0°-30°	2087.2	24.5
0°-40°	3220.2	37.9
0°-60°	3991.1	46.9
0°-90°	3998.6	47.0
90°-120°	1835.5	21.6
90°-150°	3815.3	44.9
90°-180°	4505.0	53.0
0°-180°	8503.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2602	2602	2602	2602	2602	
5°	2557	2625	2612	2619	2653	245
15°	2592	2683	2630	2617	2634	729
25°	2387	2466	2413	2340	2360	1090
35°	1856	1886	1856	1810	1818	1137
45°	788	917	926	894	752	609
55°	73	85	140	79	73	81
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	5	10	16	16	2
95°	42	78	42	48	58	47
105°	164	251	955	1220	807	172
115°	290	352	823	1710	1999	288
125°	417	473	775	1356	1604	370
135°	517	574	781	1117	1282	398
145°	612	664	786	973	1076	384
155°	717	743	802	882	923	329
165°	796	807	823	844	860	224
175°	839	844	839	833	828	79
180°	839	839	839	839	839	



TEST NUMBER: P644537

CATALOG NUMBER: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2602.0	2602.0	2602.0	2602.0	2602.0
2.5°	2567.8	2618.7	2600.3	2602.3	2615.0
5°	2557.3	2624.8	2612.1	2619.0	2652.8
7.5°	2565.0	2633.3	2631.6	2633.6	2666.6
10°	2571.5	2643.0	2636.5	2635.2	2664.9
12.5°	2584.5	2662.4	2636.5	2633.4	2658.4
15°	2591.8	2683.2	2630.4	2616.6	2634.5
17.5°	2567.0	2668.7	2597.1	2560.3	2567.4
20°	2532.9	2636.2	2561.4	2506.8	2518.7
22.5°	2479.3	2577.8	2511.0	2443.5	2458.6
25°	2386.7	2466.1	2413.1	2340.4	2360.3
27.5°	2255.0	2317.8	2284.3	2213.9	2226.2
30°	2159.2	2210.8	2183.5	2114.6	2120.6
32.5°	2048.7	2092.4	2063.3	2004.0	2003.6
35°	1856.5	1886.3	1856.5	1810.0	1817.9
37.5°	1605.1	1627.7	1597.3	1569.4	1573.4
40°	1427.9	1445.8	1413.7	1387.2	1383.3
42.5°	1206.9	1256.6	1225.2	1189.2	1194.8
45°	788.1	917.2	926.2	894.5	751.5
47.5°	397.3	538.3	644.7	489.2	350.6
50°	231.6	317.0	469.2	259.0	217.3
52.5°	151.9	188.1	327.8	163.7	144.2
55°	73.1	85.0	140.2	79.1	73.1
57.5°	25.2	38.7	62.2	39.5	28.0
60°	4.1	16.0	34.5	12.0	2.0
62.5°	2.4	4.8	21.5	2.4	0.4
65°	2.0	2.0	2.0	0.0	0.0
67.5°	2.0	2.0	0.0	0.0	0.0
70°	2.0	2.0	0.0	0.0	0.0
72.5°	2.0	2.0	0.0	0.0	0.0
75°	0.0	2.0	0.0	0.0	0.0
77.5°	0.0	2.0	0.0	0.0	0.0
80°	0.0	2.0	0.0	0.0	0.0
82.5°	0.0	2.0	0.0	0.0	0.0
85°	2.0	2.0	0.0	0.0	0.0
87.5°	1.6	2.7	2.1	3.2	3.2
90°	0.0	5.2	10.5	15.8	15.8
92.5°	12.7	17.8	23.2	32.8	36.9
95°	42.2	78.3	42.2	47.7	58.0
97.5°	74.9	150.2	310.2	91.5	79.1
100°	100.2	187.9	622.4	183.2	121.3
102.5°	125.5	217.3	841.9	483.5	264.8
105°	163.5	251.2	954.8	1219.7	807.1
107.5°	201.5	267.5	911.5	1775.1	1662.6
110°	226.8	288.7	886.2	1865.2	2004.5



TEST NUMBER: P644537

CATALOG NUMBER: OMN4DIP-SR4F0-100D125U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.1	314.0	860.9	1812.5	2046.7
115°	290.1	352.0	822.9	1710.4	1999.2
117.5°	329.2	390.0	813.4	1599.8	1896.8
120°	358.7	415.4	796.5	1515.6	1825.1
122.5°	379.8	440.7	775.4	1443.3	1728.1
125°	416.7	473.4	775.4	1356.0	1603.6
127.5°	447.3	505.1	776.5	1254.6	1499.1
130°	464.2	526.1	780.7	1186.8	1418.9
132.5°	485.3	547.2	780.7	1156.4	1347.2
135°	516.9	573.7	780.7	1116.8	1281.8
137.5°	543.3	604.2	780.7	1073.0	1214.3
140°	564.4	621.1	780.7	1047.4	1176.3
142.5°	585.5	638.1	784.9	1017.6	1138.3
145°	611.9	663.5	786.0	972.9	1076.1
147.5°	643.5	688.9	792.3	940.7	1020.2
150°	664.6	705.9	796.5	919.4	986.4
152.5°	685.7	722.9	796.5	902.2	956.9
155°	717.4	743.2	801.8	881.8	923.1
157.5°	742.7	767.5	808.1	868.9	898.8
160°	759.6	780.2	812.3	860.4	886.2
162.5°	772.2	792.9	816.6	856.0	873.5
165°	796.5	806.8	822.9	844.3	859.8
167.5°	810.2	819.5	828.2	838.9	848.2
170°	822.9	828.0	828.2	838.8	844.0
172.5°	827.1	836.4	832.4	834.6	839.8
175°	838.7	843.9	838.7	833.3	828.2
177.5°	838.7	842.8	838.7	838.6	834.5
180°	838.7	838.7	838.7	838.7	838.7

(END OF REPORT)