

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331848-830

Luminaire Tested: **S122RDIW-S1005D435U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331848-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4699.8 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	60	57	55	52
3	86	77	70	64	82	73	67	62	66	61	57	60	56	52	53	50	48	44
4	80	69	61	55	75	66	58	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	38	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25770	25770	25770
5°	25869	25449	25590
10°	25671	25032	24819
15°	25377	24289	23590
20°	24967	23230	22063
25°	24549	22026	20587
30°	23968	20789	18690
35°	23402	19446	17026
40°	22835	18054	15099
45°	22165	16493	13358
50°	21481	14913	11645
55°	20777	13216	10001
60°	19963	11428	8302
65°	19037	9605	7561
70°	17934	7912	6954
75°	16581	7211	6488
80°	14635	6453	5904
85°	11504	5076	5076



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	3.2
10°-20°	410.2	8.7
20°-30°	576.1	12.3
30°-40°	628.2	13.4
40°-50°	577.6	12.3
50°-60°	453.6	9.7
60°-70°	295.8	6.3
70°-80°	152.5	3.2
80°-90°	41.6	0.9
90°-100°	32.1	0.7
100°-110°	99.6	2.1
110°-120°	170.2	3.6
120°-130°	223.9	4.8
130°-140°	251.3	5.3
140°-150°	246.4	5.2
150°-160°	206.6	4.4
160°-170°	137.1	2.9
170°-180°	47.9	1.0
0°-30°	1135.7	24.2
0°-40°	1763.9	37.5
0°-60°	2795.1	59.5
0°-90°	3284.9	69.9
90°-120°	301.9	6.4
90°-150°	1023.3	21.8
90°-180°	1415.0	30.1
0°-180°	4699.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1596	1596	1596	1596	1596	
5°	1596	1588	1570	1582	1579	151
15°	1518	1500	1453	1426	1411	427
25°	1378	1329	1236	1179	1156	633
35°	1187	1111	987	899	864	743
45°	971	871	722	623	585	749
55°	738	623	470	386	355	659
65°	498	381	251	205	198	494
75°	266	168	116	106	104	281
85°	62	33	27	27	27	73
90°	0	6	15	14	14	4
95°	22	26	27	27	26	25
105°	92	93	94	95	95	97
115°	171	173	172	172	171	169
125°	248	252	251	250	249	222
135°	322	326	327	327	325	248
145°	390	393	396	396	394	244
155°	446	448	449	451	450	205
165°	486	485	485	488	486	137
175°	505	504	503	506	504	48
180°	506	506	506	506	506	



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1601.9	1600.6	1599.3	1598.1	1596.8	1594.7	1591.9	1589.1	1586.3	1583.5	1586.0
5°	1596.1	1594.5	1592.9	1591.3	1589.7	1586.9	1582.6	1578.5	1574.3	1570.2	1573.0
7.5°	1579.7	1577.7	1575.7	1573.7	1571.7	1568.3	1563.4	1558.5	1553.7	1548.8	1549.6
10°	1565.8	1563.6	1561.3	1559.1	1556.8	1552.5	1546.1	1539.6	1533.2	1526.8	1525.9
12.5°	1548.5	1545.7	1542.9	1540.2	1537.5	1531.9	1523.7	1515.5	1507.3	1499.1	1497.3
15°	1518.2	1514.6	1511.1	1507.5	1504.0	1496.8	1485.9	1475.0	1464.1	1453.1	1447.1
17.5°	1480.8	1475.5	1470.1	1464.7	1459.3	1449.6	1435.6	1421.6	1407.6	1393.6	1386.4
20°	1453.1	1446.7	1440.3	1433.9	1427.5	1416.3	1400.1	1384.1	1368.1	1352.0	1344.0
22.5°	1423.1	1415.9	1408.7	1401.6	1394.3	1381.7	1363.6	1345.5	1327.4	1309.3	1298.9
25°	1378.0	1367.7	1357.4	1347.2	1336.9	1321.3	1300.0	1278.8	1257.6	1236.4	1223.3
27.5°	1323.7	1312.6	1301.4	1290.2	1279.0	1261.5	1237.7	1213.7	1189.9	1166.0	1150.7
30°	1285.6	1273.4	1261.2	1249.0	1236.8	1217.9	1192.1	1166.5	1140.9	1115.1	1098.7
32.5°	1248.6	1234.4	1220.1	1205.9	1191.6	1171.4	1145.2	1119.0	1092.8	1066.6	1047.9
35°	1187.3	1171.0	1154.6	1138.2	1121.9	1099.6	1071.3	1043.1	1014.8	986.6	966.4
37.5°	1126.1	1108.1	1090.1	1072.1	1054.2	1030.2	1000.0	970.0	939.8	909.7	887.5
40°	1083.4	1064.1	1044.8	1025.6	1006.4	981.1	950.0	918.9	887.7	856.6	833.8
42.5°	1039.4	1019.2	998.9	978.5	958.3	932.1	899.9	867.7	835.6	803.4	779.9
45°	970.7	949.1	927.7	906.2	884.7	857.1	823.3	789.7	755.9	722.3	699.5
47.5°	903.6	880.9	858.1	835.3	812.5	783.7	748.9	714.1	679.3	644.5	621.9
50°	855.2	832.4	809.5	786.7	763.9	734.9	699.6	664.3	629.0	593.7	571.6
52.5°	807.8	783.9	760.2	736.3	712.5	683.3	648.8	614.3	579.7	545.2	523.8
55°	738.1	713.1	688.1	663.0	638.0	608.1	573.4	538.8	504.2	469.5	450.2
57.5°	666.8	641.1	615.4	589.7	564.0	534.5	501.2	467.9	434.6	401.2	383.6
60°	618.2	592.6	566.8	541.2	515.5	486.2	453.1	420.0	386.9	353.9	337.5
62.5°	570.9	545.2	519.5	493.8	468.2	439.5	408.0	376.5	345.0	313.5	297.8
65°	498.3	472.3	446.4	420.4	394.4	366.9	338.0	309.2	280.2	251.4	240.4
67.5°	428.4	402.7	376.8	351.0	325.2	299.3	273.3	247.3	221.3	195.3	190.3
70°	379.9	354.9	329.8	304.8	279.7	256.2	234.0	211.9	189.7	167.6	164.4
72.5°	333.7	309.6	285.7	261.6	237.6	216.7	199.0	181.2	163.3	145.6	142.9
75°	265.8	243.3	220.8	198.4	175.9	159.2	148.3	137.4	126.5	115.6	113.3
77.5°	199.1	179.4	159.7	140.0	120.2	107.7	102.5	97.2	91.9	86.7	85.4
80°	157.4	141.1	124.7	108.3	92.0	82.2	79.0	75.8	72.6	69.4	68.1
82.5°	119.3	106.5	93.8	81.0	68.2	60.7	58.5	56.4	54.2	52.0	51.3
85°	62.1	55.3	48.6	41.8	35.2	31.3	30.3	29.4	28.4	27.4	27.4
87.5°	18.6	16.8	14.9	13.1	11.3	10.6	11.0	11.4	11.8	12.3	12.0
90°	0.5	1.6	2.7	3.9	5.0	6.6	8.7	10.7	12.8	15.0	14.8
92.5°	7.6	8.5	9.2	10.1	10.9	11.6	12.1	12.6	13.1	13.6	13.6
95°	22.2	23.2	24.1	25.1	26.0	26.6	26.8	27.0	27.1	27.3	27.3
97.5°	40.5	41.4	42.2	43.1	43.9	44.5	44.9	45.2	45.6	45.9	45.9
100°	54.2	55.0	55.7	56.6	57.3	57.8	58.1	58.3	58.6	58.9	58.9
102.5°	68.6	69.2	69.7	70.4	71.0	71.5	71.8	72.2	72.6	73.0	73.0
105°	91.8	92.1	92.4	92.7	92.9	93.2	93.4	93.6	93.8	94.0	94.2
107.5°	115.2	115.6	116.0	116.5	116.9	117.1	117.1	117.1	117.1	117.1	117.2
110°	130.3	130.8	131.4	132.0	132.5	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.7	147.2	147.8	148.4	148.9	149.2	149.1	149.0	148.9	148.8	148.6
115°	170.8	171.4	171.9	172.5	173.1	173.2	173.1	172.9	172.7	172.5	172.4
117.5°	194.9	195.7	196.4	197.2	197.9	198.0	197.6	197.0	196.4	196.0	195.7
120°	210.9	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	210.9
122.5°	225.6	226.6	227.4	228.4	229.3	229.5	228.9	228.4	227.9	227.3	227.2
125°	248.5	249.4	250.2	251.1	251.9	252.2	251.9	251.7	251.4	251.1	250.8
127.5°	270.8	271.9	273.0	274.1	275.1	275.5	275.2	274.8	274.5	274.2	273.8
130°	284.8	286.1	287.3	288.5	289.7	290.3	290.1	289.9	289.7	289.5	289.4
132.5°	300.6	301.5	302.6	303.6	304.5	305.1	305.1	305.2	305.2	305.2	304.8
135°	321.6	322.6	323.7	324.7	325.7	326.3	326.5	326.7	326.9	327.1	327.0
137.5°	343.7	344.5	345.3	346.2	347.0	347.6	347.9	348.2	348.4	348.6	348.6
140°	357.0	357.9	358.7	359.6	360.4	361.1	361.6	362.0	362.5	363.0	363.0
142.5°	370.7	371.6	372.4	373.2	374.1	374.7	374.9	375.3	375.6	376.0	376.1
145°	390.3	391.0	391.6	392.3	392.9	393.6	394.2	394.7	395.3	395.9	396.0
147.5°	407.8	408.6	409.4	410.2	411.0	411.6	412.0	412.4	412.7	413.1	413.3
150°	419.8	420.4	420.9	421.5	422.1	422.5	422.9	423.3	423.7	424.0	424.3
152.5°	430.4	430.9	431.5	432.1	432.6	433.2	433.6	434.0	434.5	435.0	435.4
155°	446.2	446.5	446.8	447.1	447.4	447.7	448.0	448.3	448.6	448.8	449.3
157.5°	459.9	460.1	460.2	460.4	460.6	460.7	460.9	461.1	461.3	461.5	462.1
160°	468.1	468.3	468.4	468.6	468.8	468.9	469.0	469.1	469.2	469.3	469.9
162.5°	475.5	475.6	475.6	475.6	475.7	475.8	475.9	476.0	476.1	476.2	476.7
165°	485.5	485.4	485.3	485.2	485.1	485.1	485.1	485.1	485.1	485.1	485.8
167.5°	493.9	493.6	493.3	493.0	492.8	492.6	492.6	492.6	492.6	492.6	493.2
170°	498.3	498.0	497.8	497.5	497.2	497.0	496.9	496.8	496.7	496.6	497.3
172.5°	501.4	501.1	500.9	500.6	500.3	500.1	500.0	499.9	499.8	499.7	500.4
175°	505.2	504.9	504.6	504.4	504.1	503.8	503.6	503.4	503.2	503.0	503.7
177.5°	506.7	506.5	506.2	506.1	505.8	505.6	505.5	505.3	505.1	505.0	505.5
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1588.6	1591.1	1593.7	1594.7	1594.2	1593.7	1593.2	1592.7
5°	1575.9	1578.9	1581.7	1582.6	1581.7	1580.7	1579.8	1578.9
7.5°	1550.4	1551.2	1552.1	1551.7	1550.0	1548.3	1546.7	1545.0
10°	1524.8	1523.9	1523.0	1521.5	1519.6	1517.7	1515.7	1513.8
12.5°	1495.6	1493.8	1492.1	1489.7	1486.5	1483.3	1480.1	1476.9
15°	1441.0	1434.8	1428.7	1424.1	1420.9	1417.7	1414.5	1411.3
17.5°	1379.1	1371.9	1364.6	1358.2	1352.7	1347.2	1341.6	1336.1
20°	1336.0	1327.9	1319.9	1312.4	1305.3	1298.3	1291.2	1284.1
22.5°	1288.6	1278.3	1267.9	1260.1	1254.9	1249.6	1244.3	1239.1
25°	1210.1	1197.0	1183.8	1174.9	1170.0	1165.2	1160.4	1155.6
27.5°	1135.3	1119.9	1104.6	1093.1	1085.4	1077.8	1070.2	1062.5
30°	1082.4	1066.0	1049.6	1037.2	1028.5	1019.8	1011.2	1002.5
32.5°	1029.3	1010.6	991.8	978.5	970.3	962.1	953.9	945.8
35°	946.1	926.0	905.7	892.0	885.0	877.9	870.8	863.8
37.5°	865.2	842.9	820.6	805.4	797.4	789.3	781.2	773.1
40°	811.0	788.2	765.4	749.9	741.5	733.1	724.8	716.4
42.5°	756.3	732.7	709.2	693.3	685.2	677.1	669.1	661.0
45°	676.7	653.8	631.0	615.9	608.1	600.4	592.7	585.0
47.5°	599.2	576.6	553.8	539.0	532.1	525.1	518.0	511.0
50°	549.4	527.3	505.1	490.6	483.9	477.1	470.4	463.6
52.5°	502.4	481.0	459.7	445.8	439.6	433.4	427.2	420.9
55°	430.9	411.7	392.4	379.8	373.6	367.5	361.5	355.3
57.5°	366.0	348.3	330.6	319.2	314.1	309.0	303.9	298.7
60°	321.1	304.8	288.4	277.7	272.5	267.4	262.2	257.1
62.5°	282.3	266.6	251.1	241.7	238.7	235.5	232.4	229.4
65°	229.5	218.6	207.6	201.7	200.8	199.8	198.9	197.9
67.5°	185.3	180.3	175.2	172.2	171.3	170.2	169.2	168.1
70°	161.2	158.0	154.8	152.5	151.2	149.9	148.6	147.3
72.5°	140.3	137.5	134.8	133.1	132.3	131.6	130.7	130.0
75°	111.0	108.9	106.6	105.3	105.0	104.6	104.3	104.0
77.5°	84.1	82.8	81.5	80.6	80.1	79.6	79.1	78.6
80°	66.7	65.5	64.2	63.5	63.5	63.5	63.5	63.5
82.5°	50.4	49.7	48.9	48.5	48.5	48.5	48.5	48.5
85°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
87.5°	11.7	11.3	11.0	10.9	10.9	10.9	10.9	11.0
90°	14.6	14.4	14.2	14.1	14.2	14.3	14.4	14.5
92.5°	13.7	13.7	13.8	13.8	13.8	13.8	13.9	13.9
95°	27.3	27.3	27.3	27.2	27.1	26.9	26.7	26.5
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.9	58.9	58.9	58.9	58.8	58.7	58.6	58.5
102.5°	73.0	73.1	73.2	73.2	73.1	73.0	73.0	72.9
105°	94.3	94.5	94.7	94.8	94.8	94.8	94.8	94.8
107.5°	117.3	117.3	117.4	117.3	116.8	116.3	115.9	115.5
110°	132.8	132.8	132.8	132.6	132.3	132.1	131.8	131.5



TEST NUMBER: P331848-830

CATALOG NUMBER: S122RDIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	148.5	148.2	148.0	147.7	147.5	147.3	147.1	146.9
115°	172.3	172.2	172.1	171.9	171.6	171.4	171.1	170.8
117.5°	195.5	195.2	195.0	194.7	194.4	194.2	193.9	193.6
120°	210.9	210.9	210.9	210.8	210.6	210.3	210.0	209.7
122.5°	226.9	226.7	226.4	226.2	226.0	225.8	225.6	225.4
125°	250.5	250.2	250.0	249.8	249.7	249.6	249.5	249.4
127.5°	273.4	273.1	272.8	272.5	272.1	271.8	271.5	271.3
130°	289.2	289.0	288.8	288.5	288.1	287.8	287.4	287.0
132.5°	304.4	304.0	303.6	303.2	302.9	302.6	302.3	302.0
135°	326.9	326.8	326.7	326.5	326.2	325.9	325.6	325.4
137.5°	348.5	348.4	348.4	348.1	347.7	347.3	346.9	346.6
140°	363.0	363.0	363.0	362.8	362.4	362.0	361.7	361.3
142.5°	376.1	376.2	376.3	376.1	375.7	375.3	374.9	374.6
145°	396.1	396.2	396.2	396.1	395.7	395.3	394.9	394.5
147.5°	413.5	413.8	414.0	413.9	413.5	413.1	412.7	412.5
150°	424.6	424.9	425.2	425.2	424.9	424.6	424.3	424.0
152.5°	435.6	436.0	436.4	436.4	436.0	435.6	435.4	435.0
155°	449.8	450.3	450.7	450.8	450.5	450.3	450.0	449.7
157.5°	462.7	463.4	464.0	464.1	463.6	463.2	462.8	462.3
160°	470.4	471.0	471.6	471.6	471.3	470.9	470.5	470.1
162.5°	477.4	478.1	478.7	478.8	478.3	477.9	477.4	477.0
165°	486.4	487.1	487.8	487.9	487.4	486.9	486.4	486.0
167.5°	493.9	494.6	495.2	495.3	494.7	494.3	493.8	493.3
170°	497.9	498.6	499.3	499.4	498.8	498.2	497.7	497.1
172.5°	501.1	501.7	502.4	502.4	501.8	501.2	500.7	500.1
175°	504.4	505.0	505.7	505.8	505.2	504.6	504.1	503.5
177.5°	506.0	506.3	506.8	506.8	506.3	506.0	505.5	505.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1

(END OF REPORT)