

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644777

Luminaire Tested: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644777
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1250 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5960.7 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644777

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644777

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	111	111	111	111	103	103	103	95	95	95	88	88	88	85
1	109	106	103	100	105	102	99	97	95	93	91	89	87	86	83	82	81	78
2	102	96	92	88	98	93	89	86	88	84	81	82	80	78	77	76	74	71
3	96	88	82	78	92	86	80	76	81	77	73	76	73	70	72	69	67	65
4	90	81	74	69	86	79	73	68	74	70	66	71	67	63	67	64	61	59
5	84	74	67	62	81	72	66	61	69	63	59	65	61	58	62	59	56	54
6	78	68	61	56	76	67	60	56	63	58	54	61	56	52	58	54	51	49
7	74	63	56	51	71	62	55	51	59	53	49	56	51	48	54	50	47	45
8	69	58	51	47	67	57	51	46	55	49	45	52	47	44	50	46	43	41
9	65	54	47	43	63	53	47	42	51	45	41	49	44	40	47	43	40	38
10	61	50	44	39	59	49	43	39	47	42	38	46	41	37	44	40	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	42519	42519	42519
5°	41949	42848	43514
10°	42669	43748	44219
15°	43847	44501	44569
20°	44047	44542	43799
25°	43033	43509	42557
30°	40742	41201	40014
35°	37035	37035	36266
40°	30460	30157	29508
45°	18212	21405	17368
50°	5886	11928	5526
55°	2083	3993	2083
60°	132	1129	67
65°	79	79	0
70°	98	0	0
75°	0	0	0
80°	0	0	0
85°	385	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 21405 cd/sqm



TEST NUMBER: P644777

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.7	5.3
10°-20°	937.1	15.7
20°-30°	1386.8	23.3
30°-40°	1433.4	24.0
40°-50°	834.0	14.0
50°-60°	141.3	2.4
60°-70°	5.6	0.1
70°-80°	0.8	0.0
80°-90°	1.1	0.0
90°-100°	20.7	0.3
100°-110°	147.4	2.5
110°-120°	200.2	3.4
120°-130°	162.9	2.7
130°-140°	131.0	2.2
140°-150°	103.3	1.7
150°-160°	75.5	1.3
160°-170°	46.9	0.8
170°-180°	16.0	0.3
0°-30°	2640.5	44.3
0°-40°	4073.9	68.3
0°-60°	5049.2	84.7
0°-90°	5056.7	84.8
90°-120°	368.3	6.2
90°-150°	765.5	12.8
90°-180°	904.0	15.2
0°-180°	5960.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3292	3292	3292	3292	3292	
5°	3235	3321	3305	3313	3356	310
15°	3279	3394	3328	3310	3333	922
25°	3019	3120	3053	2961	2986	1379
35°	2349	2386	2349	2290	2300	1439
45°	997	1160	1172	1132	951	771
55°	92	108	177	100	92	102
65°	3	3	3	0	0	3
75°	0	2	0	0	0	1
85°	3	3	0	0	0	1
90°	0	1	2	3	3	1
95°	8	16	8	10	12	9
105°	33	50	192	245	162	35
115°	58	71	165	343	401	58
125°	84	95	156	272	322	74
135°	104	115	157	224	257	80
145°	123	133	158	195	216	77
155°	144	149	161	177	185	66
165°	160	162	165	169	172	45
175°	168	169	168	167	166	16
180°	168	168	168	168	168	



TEST NUMBER: P644777

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3291.8	3291.8	3291.8	3291.8	3291.8
2.5°	3248.6	3312.9	3289.7	3292.2	3308.2
5°	3235.3	3320.7	3304.6	3313.3	3356.0
7.5°	3245.0	3331.5	3329.3	3331.8	3373.5
10°	3253.2	3343.7	3335.5	3333.8	3371.4
12.5°	3269.7	3368.2	3335.5	3331.6	3363.2
15°	3278.9	3394.5	3327.8	3310.3	3332.9
17.5°	3247.6	3376.2	3285.6	3239.1	3248.1
20°	3204.4	3335.1	3240.4	3171.4	3186.4
22.5°	3136.6	3261.2	3176.7	3091.3	3110.4
25°	3019.4	3119.9	3052.8	2960.9	2986.0
27.5°	2852.9	2932.3	2889.9	2800.8	2816.4
30°	2731.6	2796.9	2762.4	2675.2	2682.8
32.5°	2591.8	2647.1	2610.3	2535.3	2534.8
35°	2348.7	2386.4	2348.7	2289.8	2299.9
37.5°	2030.6	2059.2	2020.8	1985.5	1990.5
40°	1806.5	1829.1	1788.5	1755.0	1750.0
42.5°	1526.9	1589.7	1550.0	1504.5	1511.5
45°	997.0	1160.4	1171.8	1131.7	950.8
47.5°	502.6	681.0	815.6	618.9	443.5
50°	292.9	401.0	593.6	327.7	275.0
52.5°	192.2	237.9	414.7	207.1	182.4
55°	92.5	107.6	177.3	100.0	92.5
57.5°	31.9	48.9	78.6	50.0	35.5
60°	5.1	20.2	43.7	15.1	2.6
62.5°	3.1	6.1	27.2	3.0	0.5
65°	2.6	2.6	2.6	0.0	0.0
67.5°	2.6	2.6	0.0	0.0	0.0
70°	2.6	2.6	0.0	0.0	0.0
72.5°	2.6	2.6	0.0	0.0	0.0
75°	0.0	2.5	0.0	0.0	0.0
77.5°	0.0	2.5	0.0	0.0	0.0
80°	0.0	2.5	0.0	0.0	0.0
82.5°	0.0	2.5	0.0	0.0	0.0
85°	2.6	2.6	0.0	0.0	0.0
87.5°	2.1	2.3	0.4	0.6	0.6
90°	0.0	1.0	2.1	3.2	3.2
92.5°	2.5	3.6	4.7	6.6	7.4
95°	8.5	15.7	8.5	9.6	11.6
97.5°	15.0	30.1	62.2	18.4	15.9
100°	20.1	37.7	124.9	36.8	24.3
102.5°	25.2	43.6	168.9	97.0	53.1
105°	32.8	50.4	191.6	244.7	161.9
107.5°	40.4	53.7	182.9	356.2	333.6
110°	45.5	57.9	177.8	374.3	402.2



TEST NUMBER: P644777

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	50.6	63.0	172.7	363.7	410.7
115°	58.2	70.6	165.1	343.2	401.1
117.5°	66.0	78.3	163.2	321.0	380.6
120°	72.0	83.4	159.8	304.1	366.2
122.5°	76.2	88.4	155.6	289.6	346.7
125°	83.6	95.0	155.6	272.1	321.8
127.5°	89.8	101.3	155.8	251.7	300.8
130°	93.1	105.6	156.6	238.1	284.7
132.5°	97.4	109.8	156.6	232.0	270.3
135°	103.7	115.1	156.6	224.1	257.2
137.5°	109.0	121.2	156.6	215.3	243.6
140°	113.2	124.6	156.6	210.2	236.0
142.5°	117.5	128.0	157.5	204.2	228.4
145°	122.8	133.1	157.7	195.2	215.9
147.5°	129.1	138.2	159.0	188.8	204.7
150°	133.4	141.6	159.8	184.5	197.9
152.5°	137.6	145.0	159.8	181.0	192.0
155°	143.9	149.1	160.9	176.9	185.2
157.5°	149.0	154.0	162.1	174.3	180.4
160°	152.4	156.5	163.0	172.6	177.8
162.5°	155.0	159.1	163.8	171.8	175.3
165°	159.8	161.9	165.1	169.4	172.5
167.5°	162.6	164.4	166.2	168.3	170.2
170°	165.1	166.1	166.2	168.3	169.3
172.5°	166.0	167.8	167.0	167.5	168.5
175°	168.3	169.3	168.3	167.2	166.2
177.5°	168.3	169.1	168.3	168.3	167.4
180°	168.3	168.3	168.3	168.3	168.3

(END OF REPORT)