

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644782

Luminaire Tested: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644782
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 1250 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6391.7 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644782

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644782

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	116	116	116	116	111	111	111	111	103	103	103	96	96	96	89	89	89	86				
1	109	105	102	100	105	102	99	97	95	93	91	89	88	86	83	82	81	78				
2	102	96	91	87	98	93	89	85	87	84	81	82	80	77	78	75	74	71				
3	95	88	82	77	92	85	80	75	80	76	72	76	72	69	72	69	67	64				
4	89	80	73	68	86	78	72	67	74	69	65	70	66	63	67	63	60	58				
5	83	73	66	61	80	71	65	60	68	63	58	65	60	57	62	58	55	53				
6	78	67	60	55	75	66	59	54	63	57	53	60	55	51	57	53	50	48				
7	73	62	55	50	71	61	54	49	58	52	48	56	51	47	53	49	46	44				
8	68	57	50	46	66	56	50	45	54	48	44	52	47	43	50	45	42	40				
9	64	53	46	42	62	52	46	41	50	44	40	48	43	40	46	42	39	37				
10	61	50	43	38	59	49	42	38	47	41	37	45	40	37	43	39	36	34				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	44080	44080	44080
5°	43747	44348	45214
10°	44455	45331	46074
15°	45565	46184	46493
20°	45813	46236	45707
25°	44937	45046	44498
30°	42964	42849	41814
35°	39224	38899	38089
40°	32583	32106	31501
45°	20466	23283	19527
50°	7849	13787	7280
55°	3704	5788	3761
60°	1793	2922	1594
65°	1650	1727	1492
70°	1650	1650	1454
75°	1667	1667	1412
80°	1718	1532	1339
85°	1897	1526	1141

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 23283 cd/sqm



TEST NUMBER: P644782

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.7	5.1
10°-20°	972.2	15.2
20°-30°	1444.2	22.6
30°-40°	1511.6	23.6
40°-50°	915.6	14.3
50°-60°	211.3	3.3
60°-70°	58.1	0.9
70°-80°	34.0	0.5
80°-90°	12.1	0.2
90°-100°	20.7	0.3
100°-110°	147.4	2.3
110°-120°	200.2	3.1
120°-130°	162.9	2.5
130°-140°	131.0	2.0
140°-150°	103.3	1.6
150°-160°	75.5	1.2
160°-170°	46.9	0.7
170°-180°	16.0	0.3
0°-30°	2745.1	42.9
0°-40°	4256.7	66.6
0°-60°	5383.6	84.2
0°-90°	5487.8	85.9
90°-120°	368.3	5.8
90°-150°	765.5	12.0
90°-180°	904.0	14.1
0°-180°	6391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3413	3413	3413	3413	3413	
5°	3374	3452	3420	3434	3487	323
15°	3407	3510	3454	3426	3477	959
25°	3153	3246	3161	3080	3122	1444
35°	2488	2525	2467	2410	2416	1529
45°	1120	1274	1275	1230	1069	860
55°	164	187	257	177	167	171
65°	54	56	56	51	49	54
75°	33	33	33	31	28	35
85°	13	13	10	10	8	13
90°	0	1	2	3	3	1
95°	8	16	8	10	12	9
105°	33	50	192	245	162	35
115°	58	71	165	343	401	58
125°	84	95	156	272	322	74
135°	104	115	157	224	257	80
145°	123	133	158	195	216	77
155°	144	149	161	177	185	66
165°	160	162	165	169	172	45
175°	168	169	168	167	166	16
180°	168	168	168	168	168	



TEST NUMBER: P644782

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3412.6	3412.6	3412.6	3412.6	3412.6
2.5°	3379.7	3440.0	3406.4	3409.1	3437.2
5°	3374.0	3451.9	3420.3	3434.3	3487.1
7.5°	3383.3	3464.7	3446.0	3450.9	3508.7
10°	3389.4	3474.9	3456.2	3455.0	3512.8
12.5°	3403.8	3493.3	3458.3	3450.8	3506.6
15°	3407.4	3510.4	3453.7	3426.5	3476.8
17.5°	3374.0	3487.6	3411.0	3354.9	3395.1
20°	3332.9	3448.5	3363.7	3285.0	3325.2
22.5°	3269.2	3382.7	3291.8	3206.9	3249.1
25°	3153.0	3246.0	3160.7	3079.5	3122.2
27.5°	3006.0	3071.4	2998.3	2921.3	2945.4
30°	2880.6	2946.0	2872.9	2793.5	2803.5
32.5°	2740.8	2796.1	2724.9	2653.7	2661.7
35°	2487.5	2525.2	2466.9	2410.5	2415.5
37.5°	2179.1	2184.1	2144.7	2093.3	2094.3
40°	1932.4	1947.5	1904.1	1863.1	1868.2
42.5°	1638.4	1697.7	1655.4	1618.4	1619.4
45°	1120.4	1273.7	1274.6	1229.8	1069.0
47.5°	618.8	796.2	910.2	705.8	533.0
50°	390.6	503.7	686.1	412.6	362.3
52.5°	279.6	330.3	501.1	291.8	265.7
55°	164.5	187.1	257.0	177.1	167.0
57.5°	100.2	119.8	150.1	118.3	100.7
60°	69.4	87.0	113.1	79.3	61.7
62.5°	61.2	66.7	88.4	63.1	57.6
65°	54.0	56.5	56.5	51.3	48.8
67.5°	47.8	50.3	47.8	45.2	42.7
70°	43.7	46.2	43.7	41.1	38.5
72.5°	39.6	42.1	39.6	36.9	34.4
75°	33.4	33.4	33.4	30.8	28.3
77.5°	27.2	27.2	26.7	24.6	22.1
80°	23.1	23.1	20.6	20.5	18.0
82.5°	19.0	19.0	16.4	16.4	13.9
85°	12.8	12.8	10.3	10.2	7.7
87.5°	6.2	6.4	4.5	4.7	2.7
90°	0.0	1.0	2.1	3.2	3.2
92.5°	2.5	3.6	4.7	6.6	7.4
95°	8.5	15.7	8.5	9.6	11.6
97.5°	15.0	30.1	62.2	18.4	15.9
100°	20.1	37.7	124.9	36.8	24.3
102.5°	25.2	43.6	168.9	97.0	53.1
105°	32.8	50.4	191.6	244.7	161.9
107.5°	40.4	53.7	182.9	356.2	333.6
110°	45.5	57.9	177.8	374.3	402.2



TEST NUMBER: P644782

CATALOG NUMBER: OMN4DIP-SR4F0-125D25U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	50.6	63.0	172.7	363.7	410.7
115°	58.2	70.6	165.1	343.2	401.1
117.5°	66.0	78.3	163.2	321.0	380.6
120°	72.0	83.4	159.8	304.1	366.2
122.5°	76.2	88.4	155.6	289.6	346.7
125°	83.6	95.0	155.6	272.1	321.8
127.5°	89.8	101.3	155.8	251.7	300.8
130°	93.1	105.6	156.6	238.1	284.7
132.5°	97.4	109.8	156.6	232.0	270.3
135°	103.7	115.1	156.6	224.1	257.2
137.5°	109.0	121.2	156.6	215.3	243.6
140°	113.2	124.6	156.6	210.2	236.0
142.5°	117.5	128.0	157.5	204.2	228.4
145°	122.8	133.1	157.7	195.2	215.9
147.5°	129.1	138.2	159.0	188.8	204.7
150°	133.4	141.6	159.8	184.5	197.9
152.5°	137.6	145.0	159.8	181.0	192.0
155°	143.9	149.1	160.9	176.9	185.2
157.5°	149.0	154.0	162.1	174.3	180.4
160°	152.4	156.5	163.0	172.6	177.8
162.5°	155.0	159.1	163.8	171.8	175.3
165°	159.8	161.9	165.1	169.4	172.5
167.5°	162.6	164.4	166.2	168.3	170.2
170°	165.1	166.1	166.2	168.3	169.3
172.5°	166.0	167.8	167.0	167.5	168.5
175°	168.3	169.3	168.3	167.2	166.2
177.5°	168.3	169.1	168.3	168.3	167.4
180°	168.3	168.3	168.3	168.3	168.3

(END OF REPORT)