

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644897

Luminaire Tested: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644897
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 500 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6530.4 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644897
CATALOG NUMBER: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644897

CATALOG NUMBER: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31	
1	95	91	88	85	85	82	79	77	65	64	62	50	49	48	36	35	35	36	35	35	29	
2	87	81	76	71	78	73	69	65	59	56	53	46	44	42	33	32	31	33	32	31	26	
3	80	72	66	61	72	66	60	56	53	49	46	41	39	37	31	29	28	31	29	28	24	
4	74	65	58	53	67	59	53	49	48	44	41	38	35	33	28	27	26	28	27	26	21	
5	69	58	51	46	62	53	47	42	44	39	36	35	32	29	26	24	23	26	24	23	20	
6	63	53	45	40	57	48	42	37	40	35	32	32	29	26	24	22	21	24	22	21	18	
7	59	48	41	36	53	44	38	33	36	32	29	29	26	24	22	21	19	22	21	19	16	
8	55	44	37	32	50	40	34	30	33	29	26	27	24	22	21	19	17	21	19	17	15	
9	51	40	33	29	46	37	31	27	31	26	23	25	22	20	19	17	16	19	17	16	14	
10	48	37	30	26	43	34	28	24	28	24	21	23	20	18	18	16	15	18	16	15	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17014	17014	17014
5°	16786	17145	17412
10°	17074	17506	17695
15°	17545	17807	17833
20°	17625	17823	17526
25°	17219	17410	17028
30°	16302	16487	16011
35°	14819	14819	14512
40°	12189	12068	11806
45°	7289	8565	6949
50°	2355	4773	2210
55°	833	1597	833
60°	54	452	26
65°	31	31	0
70°	38	0	0
75°	0	0	0
80°	0	0	0
85°	148	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 8565 cd/sqm



TEST NUMBER: P644897

CATALOG NUMBER: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.7	1.9
10°-20°	375.0	5.7
20°-30°	554.9	8.5
30°-40°	573.6	8.8
40°-50°	333.7	5.1
50°-60°	56.5	0.9
60°-70°	2.2	0.0
70°-80°	0.3	0.0
80°-90°	2.2	0.0
90°-100°	103.1	1.6
100°-110°	734.8	11.3
110°-120°	997.6	15.3
120°-130°	811.9	12.4
130°-140°	653.0	10.0
140°-150°	514.8	7.9
150°-160°	376.4	5.8
160°-170°	233.8	3.6
170°-180°	79.7	1.2
0°-30°	1056.6	16.2
0°-40°	1630.2	25.0
0°-60°	2020.4	30.9
0°-90°	2025.1	31.0
90°-120°	1835.5	28.1
90°-150°	3815.3	58.4
90°-180°	4505.0	69.0
0°-180°	6530.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1317	1317	1317	1317	1317	
5°	1295	1329	1322	1326	1343	124
15°	1312	1358	1332	1325	1334	369
25°	1208	1248	1222	1185	1195	552
35°	940	955	940	916	920	576
45°	399	464	469	453	380	309
55°	37	43	71	40	37	41
65°	1	1	1	0	0	1
75°	0	1	0	0	0	0
85°	1	1	0	0	0	0
90°	0	5	10	16	16	2
95°	42	78	42	48	58	47
105°	164	251	955	1220	807	172
115°	290	352	823	1710	1999	288
125°	417	473	775	1356	1604	370
135°	517	574	781	1117	1282	398
145°	612	664	786	973	1076	384
155°	717	743	802	882	923	329
165°	796	807	823	844	860	224
175°	839	844	839	833	828	79
180°	839	839	839	839	839	



TEST NUMBER: P644897

CATALOG NUMBER: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1317.2	1317.2	1317.2	1317.2	1317.2
2.5°	1299.9	1325.6	1316.4	1317.3	1323.8
5°	1294.6	1328.7	1322.3	1325.8	1342.9
7.5°	1298.5	1333.0	1332.2	1333.2	1349.9
10°	1301.8	1337.9	1334.7	1334.0	1349.1
12.5°	1308.3	1347.7	1334.7	1333.1	1345.8
15°	1312.0	1358.3	1331.6	1324.6	1333.6
17.5°	1299.5	1351.0	1314.7	1296.1	1299.7
20°	1282.2	1334.5	1296.6	1269.0	1275.0
22.5°	1255.1	1304.9	1271.1	1236.9	1244.6
25°	1208.2	1248.4	1221.6	1184.8	1194.8
27.5°	1141.6	1173.3	1156.4	1120.7	1127.0
30°	1093.0	1119.2	1105.4	1070.5	1073.5
32.5°	1037.1	1059.2	1044.5	1014.5	1014.3
35°	939.8	954.9	939.8	916.3	920.3
37.5°	812.5	824.0	808.6	794.5	796.5
40°	722.9	731.9	715.7	702.2	700.2
42.5°	611.0	636.1	620.2	602.0	604.8
45°	399.0	464.3	468.9	452.8	380.4
47.5°	201.1	272.5	326.4	247.7	177.5
50°	117.2	160.5	237.5	131.1	110.0
52.5°	76.9	95.2	166.0	82.9	73.0
55°	37.0	43.0	70.9	40.0	37.0
57.5°	12.8	19.6	31.5	20.0	14.2
60°	2.1	8.1	17.5	6.1	1.0
62.5°	1.2	2.4	10.9	1.2	0.2
65°	1.0	1.0	1.0	0.0	0.0
67.5°	1.0	1.0	0.0	0.0	0.0
70°	1.0	1.0	0.0	0.0	0.0
72.5°	1.0	1.0	0.0	0.0	0.0
75°	0.0	1.0	0.0	0.0	0.0
77.5°	0.0	1.0	0.0	0.0	0.0
80°	0.0	1.0	0.0	0.0	0.0
82.5°	0.0	1.0	0.0	0.0	0.0
85°	1.0	1.0	0.0	0.0	0.0
87.5°	0.8	1.9	2.1	3.2	3.2
90°	0.0	5.2	10.5	15.8	15.8
92.5°	12.7	17.8	23.2	32.8	36.9
95°	42.2	78.3	42.2	47.7	58.0
97.5°	74.9	150.2	310.2	91.5	79.1
100°	100.2	187.9	622.4	183.2	121.3
102.5°	125.5	217.3	841.9	483.5	264.8
105°	163.5	251.2	954.8	1219.7	807.1
107.5°	201.5	267.5	911.5	1775.1	1662.6
110°	226.8	288.7	886.2	1865.2	2004.5



TEST NUMBER: P644897

CATALOG NUMBER: OMN4DIP-SR4F0-50D125U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.1	314.0	860.9	1812.5	2046.7
115°	290.1	352.0	822.9	1710.4	1999.2
117.5°	329.2	390.0	813.4	1599.8	1896.8
120°	358.7	415.4	796.5	1515.6	1825.1
122.5°	379.8	440.7	775.4	1443.3	1728.1
125°	416.7	473.4	775.4	1356.0	1603.6
127.5°	447.3	505.1	776.5	1254.6	1499.1
130°	464.2	526.1	780.7	1186.8	1418.9
132.5°	485.3	547.2	780.7	1156.4	1347.2
135°	516.9	573.7	780.7	1116.8	1281.8
137.5°	543.3	604.2	780.7	1073.0	1214.3
140°	564.4	621.1	780.7	1047.4	1176.3
142.5°	585.5	638.1	784.9	1017.6	1138.3
145°	611.9	663.5	786.0	972.9	1076.1
147.5°	643.5	688.9	792.3	940.7	1020.2
150°	664.6	705.9	796.5	919.4	986.4
152.5°	685.7	722.9	796.5	902.2	956.9
155°	717.4	743.2	801.8	881.8	923.1
157.5°	742.7	767.5	808.1	868.9	898.8
160°	759.6	780.2	812.3	860.4	886.2
162.5°	772.2	792.9	816.6	856.0	873.5
165°	796.5	806.8	822.9	844.3	859.8
167.5°	810.2	819.5	828.2	838.9	848.2
170°	822.9	828.0	828.2	838.8	844.0
172.5°	827.1	836.4	832.4	834.6	839.8
175°	838.7	843.9	838.7	833.3	828.2
177.5°	838.7	842.8	838.7	838.6	834.5
180°	838.7	838.7	838.7	838.7	838.7

(END OF REPORT)