

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331804-830

Luminaire Tested: **S122RDIW-S485D1440U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331804-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6314.8 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.2
10°-20°	199.9	3.2
20°-30°	280.7	4.4
30°-40°	306.1	4.8
40°-50°	281.5	4.5
50°-60°	221.1	3.5
60°-70°	144.1	2.3
70°-80°	74.3	1.2
80°-90°	26.0	0.4
90°-100°	106.7	1.7
100°-110°	331.4	5.2
110°-120°	566.4	9.0
120°-130°	744.9	11.8
130°-140°	836.1	13.2
140°-150°	819.8	13.0
150°-160°	687.6	10.9
160°-170°	456.0	7.2
170°-180°	159.4	2.5
0°-30°	553.4	8.8
0°-40°	859.6	13.6
0°-60°	1362.1	21.6
0°-90°	1606.5	25.4
90°-120°	1004.5	15.9
90°-150°	3405.2	53.9
90°-180°	4708.0	74.6
0°-180°	6314.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	19	50	47	48	5
95°	74	87	91	91	88	85
105°	306	310	313	315	316	323
115°	568	576	574	572	568	562
125°	827	839	836	831	830	739
135°	1070	1085	1088	1087	1083	826
145°	1299	1309	1317	1318	1313	811
155°	1485	1489	1493	1500	1496	683
165°	1616	1614	1614	1623	1617	455
175°	1681	1677	1674	1683	1675	160
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.3	9.0	8.8	8.6	8.3	8.9	10.3	11.7	13.1	14.4	14.2
90°	1.4	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1
92.5°	25.3	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3
95°	73.9	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0
97.5°	135.0	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9
100°	180.5	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0
102.5°	228.2	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0
105°	305.5	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2
107.5°	383.3	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8
110°	433.4	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.0	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6
115°	568.4	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7
117.5°	648.6	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2
120°	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9
122.5°	750.8	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7
125°	827.0	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5
127.5°	901.2	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1
130°	947.7	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8
132.5°	1000.0	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3
135°	1070.0	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2
137.5°	1143.6	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8
140°	1187.9	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8
142.5°	1233.4	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2
145°	1298.7	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5
147.5°	1357.0	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4
150°	1396.8	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9
152.5°	1432.0	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6
155°	1484.9	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0
157.5°	1530.0	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6
160°	1557.4	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5
162.5°	1582.3	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5
165°	1615.6	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4
167.5°	1643.4	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2
170°	1658.2	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7
172.5°	1668.5	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0
175°	1680.9	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1
177.5°	1686.1	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	13.9	13.7	13.5	13.4	13.4	13.5	13.6	13.6
90°	48.4	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.4	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.2	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	313.9	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.1	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331804-830

CATALOG NUMBER: S122RDIW-S485D1440U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.8	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.4	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	650.4	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	755.0	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	833.6	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	909.9	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	962.1	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1013.0	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.8	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.5	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.5	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1317.9	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.0	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1496.6	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1539.7	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1565.4	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1588.7	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1618.6	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1643.3	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1657.0	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1667.2	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1678.3	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)