

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791-830

Luminaire Tested: **S122RDIW-S485D710U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331791-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4274.4 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37								
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32								
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28								
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24								
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18								
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16								
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15								
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13								
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12								
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.7
10°-20°	199.9	4.7
20°-30°	280.7	6.6
30°-40°	306.1	7.2
40°-50°	281.5	6.6
50°-60°	221.1	5.2
60°-70°	144.1	3.4
70°-80°	74.3	1.7
80°-90°	21.5	0.5
90°-100°	30.4	0.7
100°-110°	111.6	2.6
110°-120°	298.2	7.0
120°-130°	492.2	11.5
130°-140°	523.5	12.2
140°-150°	486.5	11.4
150°-160°	391.2	9.2
160°-170°	252.1	5.9
170°-180°	86.8	2.0
0°-30°	553.4	12.9
0°-40°	859.6	20.1
0°-60°	1362.1	31.9
0°-90°	1602.1	37.5
90°-120°	440.1	10.3
90°-150°	1942.3	45.4
90°-180°	2672.0	62.5
0°-180°	4274.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	8	13	16	18	3
95°	43	23	26	29	28	52
105°	201	209	40	47	50	214
115°	379	391	407	116	54	373
125°	536	545	558	562	564	478
135°	664	674	680	686	686	512
145°	770	770	781	785	782	481
155°	848	843	850	853	849	391
165°	893	890	892	896	892	252
175°	914	910	911	915	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.1	8.5	7.8	7.1	6.4	6.2	6.4	6.7	6.9	7.2	7.2
90°	0.7	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9
92.5°	13.3	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6
95°	42.9	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5
97.5°	85.1	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1
100°	116.8	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7
102.5°	151.7	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2
105°	200.6	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8
107.5°	256.4	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7
110°	292.3	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	326.1	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8
115°	379.4	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2
117.5°	427.1	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5
120°	461.8	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4
122.5°	491.4	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9
125°	536.4	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6
127.5°	577.2	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6
130°	603.0	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5
132.5°	629.5	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1
135°	663.8	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7
137.5°	698.5	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1
140°	721.2	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1
142.5°	740.2	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5
145°	770.1	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7
147.5°	796.0	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4
150°	812.9	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7
152.5°	827.2	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9
155°	847.9	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7
157.5°	864.1	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6
160°	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5
162.5°	882.0	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5
165°	893.4	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5
167.5°	901.8	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8
170°	906.6	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0
172.5°	909.7	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1
175°	913.9	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6
177.5°	914.5	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	7.2	7.2	7.3	7.3	7.4	7.4	7.4	7.5
90°	14.7	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.1	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.2	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	35.6	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	40.0	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	41.8	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	43.5	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	53.1	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	86.1	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331791-830

CATALOG NUMBER: S122RDIW-S485D710U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	184.3	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	271.4	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	418.1	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	487.2	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	516.9	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	559.6	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	599.1	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	624.2	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	648.5	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	683.2	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	715.5	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	736.4	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	755.6	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	782.6	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.2	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	820.6	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	833.8	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	851.6	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	866.7	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	875.3	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	883.5	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	901.8	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	906.1	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	909.2	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	912.7	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.0	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)