

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644992

Luminaire Tested: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644992
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 500 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3924.8 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644992
CATALOG NUMBER: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644992

CATALOG NUMBER: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56																			
1	101	97	94	91	94	91	88	86	79	77	75	68	66	65	57	57	56	51																			
2	94	88	83	78	87	82	78	74	72	68	66	62	60	58	53	52	50	46																			
3	87	79	73	68	81	74	69	64	65	61	58	57	54	52	49	47	45	42																			
4	81	71	65	59	75	67	61	57	60	55	51	52	49	46	45	43	41	38																			
5	75	65	58	53	70	61	55	50	54	50	46	48	44	42	42	39	37	34																			
6	70	59	52	47	65	56	50	45	50	45	41	44	40	38	39	36	34	31																			
7	65	54	47	42	61	51	45	40	46	41	37	41	37	34	36	33	31	29																			
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	34	31	28	26																			
9	57	46	39	34	53	44	37	33	39	34	31	35	31	28	31	28	26	24																			
10	53	42	36	31	50	40	34	30	36	32	28	33	29	26	29	26	24	22																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17638	17638	17638
5°	17505	17745	18092
10°	17788	18139	18436
15°	18232	18481	18604
20°	18331	18502	18289
25°	17980	18025	17805
30°	17192	17146	16732
35°	15694	15565	15240
40°	13037	12847	12604
45°	8189	9316	7813
50°	3141	5516	2914
55°	1482	2315	1504
60°	718	1168	638
65°	660	691	596
70°	661	661	582
75°	669	669	564
80°	692	610	536
85°	756	608	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 9316 cd/sqm



TEST NUMBER: P644992

CATALOG NUMBER: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.5	3.4
10°-20°	389.0	9.9
20°-30°	577.9	14.7
30°-40°	604.8	15.4
40°-50°	366.4	9.3
50°-60°	84.5	2.2
60°-70°	23.2	0.6
70°-80°	13.6	0.3
80°-90°	5.4	0.1
90°-100°	39.6	1.0
100°-110°	281.9	7.2
110°-120°	382.7	9.8
120°-130°	311.5	7.9
130°-140°	250.5	6.4
140°-150°	197.5	5.0
150°-160°	144.4	3.7
160°-170°	89.7	2.3
170°-180°	30.6	0.8
0°-30°	1098.4	28.0
0°-40°	1703.3	43.4
0°-60°	2154.2	54.9
0°-90°	2196.4	56.0
90°-120°	704.2	17.9
90°-150°	1463.7	37.3
90°-180°	1728.0	44.0
0°-180°	3924.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1366	1366	1366	1366	1366	
5°	1350	1381	1369	1374	1395	129
15°	1363	1405	1382	1371	1391	384
25°	1262	1299	1265	1232	1249	578
35°	995	1010	987	964	966	612
45°	448	510	510	492	428	344
55°	66	75	103	71	67	68
65°	22	23	23	20	20	22
75°	13	13	13	12	11	14
85°	5	5	4	4	3	5
90°	0	2	4	6	6	1
95°	16	30	16	18	22	18
105°	63	96	366	468	310	66
115°	111	135	316	656	767	110
125°	160	182	298	520	615	142
135°	198	220	300	428	492	153
145°	235	254	302	373	413	147
155°	275	285	308	338	354	126
165°	306	310	316	324	330	86
175°	322	324	322	320	318	30
180°	322	322	322	322	322	



TEST NUMBER: P644992

CATALOG NUMBER: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1365.5	1365.5	1365.5	1365.5	1365.5
2.5°	1352.3	1376.5	1363.0	1364.1	1375.4
5°	1350.1	1381.2	1368.6	1374.2	1395.3
7.5°	1353.8	1386.4	1378.9	1380.8	1404.0
10°	1356.2	1390.4	1383.0	1382.5	1405.6
12.5°	1362.0	1397.8	1383.8	1380.8	1403.1
15°	1363.4	1404.7	1382.0	1371.1	1391.2
17.5°	1350.1	1395.5	1364.9	1342.4	1358.5
20°	1333.6	1379.9	1346.0	1314.5	1330.5
22.5°	1308.1	1353.6	1317.2	1283.2	1300.1
25°	1261.6	1298.8	1264.7	1232.2	1249.3
27.5°	1202.8	1229.0	1199.7	1168.9	1178.6
30°	1152.7	1178.8	1149.6	1117.8	1121.8
32.5°	1096.7	1118.8	1090.3	1061.8	1065.1
35°	995.3	1010.4	987.1	964.5	966.5
37.5°	871.9	874.0	858.2	837.6	838.0
40°	773.2	779.3	761.9	745.5	747.5
42.5°	655.6	679.3	662.4	647.6	648.0
45°	448.3	509.6	510.0	492.1	427.7
47.5°	247.6	318.6	364.2	282.4	213.3
50°	156.3	201.5	274.5	165.1	145.0
52.5°	111.9	132.2	200.5	116.8	106.3
55°	65.8	74.9	102.8	70.9	66.8
57.5°	40.1	47.9	60.0	47.3	40.3
60°	27.8	34.8	45.2	31.7	24.7
62.5°	24.5	26.7	35.4	25.2	23.0
65°	21.6	22.6	22.6	20.5	19.5
67.5°	19.1	20.1	19.1	18.1	17.1
70°	17.5	18.5	17.5	16.4	15.4
72.5°	15.8	16.8	15.8	14.8	13.8
75°	13.4	13.4	13.4	12.3	11.3
77.5°	10.9	10.9	10.7	9.8	8.8
80°	9.3	9.3	8.2	8.2	7.2
82.5°	7.6	7.6	6.6	6.6	5.6
85°	5.1	5.1	4.1	4.1	3.1
87.5°	2.5	2.9	2.5	2.8	2.0
90°	0.0	2.0	4.0	6.1	6.1
92.5°	4.9	6.8	8.9	12.6	14.2
95°	16.2	30.0	16.2	18.3	22.3
97.5°	28.7	57.6	119.0	35.1	30.4
100°	38.4	72.1	238.8	70.3	46.5
102.5°	48.2	83.4	323.0	185.5	101.6
105°	62.7	96.4	366.3	467.9	309.6
107.5°	77.3	102.6	349.7	681.0	637.8
110°	87.0	110.8	340.0	715.5	769.0



TEST NUMBER: P644992

CATALOG NUMBER: OMN4DIP-SR4F0-50D50U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	96.7	120.5	330.2	695.3	785.1
115°	111.3	135.0	315.7	656.1	766.9
117.5°	126.3	149.6	312.0	613.7	727.7
120°	137.6	159.4	305.6	581.4	700.2
122.5°	145.7	169.0	297.5	553.7	662.9
125°	159.9	181.6	297.5	520.2	615.2
127.5°	171.6	193.8	297.9	481.3	575.1
130°	178.1	201.8	299.5	455.3	544.3
132.5°	186.2	209.9	299.5	443.6	516.8
135°	198.3	220.1	299.5	428.4	491.7
137.5°	208.4	231.8	299.5	411.6	465.8
140°	216.5	238.3	299.5	401.8	451.3
142.5°	224.6	244.8	301.1	390.4	436.7
145°	234.7	254.5	301.5	373.2	412.8
147.5°	246.9	264.3	303.9	360.9	391.4
150°	255.0	270.8	305.6	352.7	378.4
152.5°	263.1	277.3	305.6	346.1	367.1
155°	275.2	285.1	307.6	338.3	354.1
157.5°	284.9	294.4	310.0	333.3	344.8
160°	291.4	299.3	311.6	330.1	340.0
162.5°	296.2	304.2	313.2	328.4	335.1
165°	305.6	309.5	315.7	323.9	329.8
167.5°	310.8	314.4	317.7	321.8	325.4
170°	315.7	317.7	317.7	321.8	323.8
172.5°	317.3	320.9	319.3	320.2	322.2
175°	321.7	323.7	321.7	319.7	317.7
177.5°	321.7	323.3	321.7	321.7	320.1
180°	321.7	321.7	321.7	321.7	321.7

(END OF REPORT)