

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645047

Luminaire Tested: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P645047  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6517.3 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645047

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645047

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46						46														
1	99	95	92	89	91	88	85	83	74	72	70	61	60	59	49	49	48	43						43														
2	91	85	80	76	84	79	75	71	67	64	61	56	54	52	46	45	43	39						39														
3	85	77	71	66	78	71	66	62	61	57	54	51	49	46	42	41	39	35						35														
4	79	69	63	57	72	65	59	54	55	51	48	47	44	42	39	37	36	32						32														
5	73	63	56	51	67	59	52	48	51	46	43	43	40	37	36	34	32	29						29														
6	68	57	50	45	63	53	47	43	46	42	38	40	36	34	34	31	29	27						27														
7	63	52	45	40	58	49	43	38	43	38	34	37	33	31	31	29	27	24						24														
8	59	48	41	36	55	45	39	34	39	35	31	34	30	28	29	27	25	22						22														
9	55	44	37	33	51	41	35	31	36	32	28	32	28	25	27	25	23	21						21														
10	52	41	34	30	48	38	32	28	34	29	26	29	26	23	25	23	21	19						19														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25336	25336	25336
5°	24996	25533	25930
10°	25425	26068	26350
15°	26127	26516	26558
20°	26246	26542	26099
25°	25642	25926	25359
30°	24277	24551	23843
35°	22068	22068	21611
40°	18151	17969	17583
45°	10852	12754	10350
50°	3509	7108	3292
55°	1241	2380	1241
60°	80	672	39
65°	46	46	0
70°	57	0	0
75°	0	0	0
80°	0	0	0
85°	222	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 12754 cd/sqm



TEST NUMBER: P645047

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	188.7	2.9
10°-20°	558.4	8.6
20°-30°	826.3	12.7
30°-40°	854.1	13.1
40°-50°	497.0	7.6
50°-60°	84.2	1.3
60°-70°	3.3	0.1
70°-80°	0.5	0.0
80°-90°	1.9	0.0
90°-100°	80.2	1.2
100°-110°	571.3	8.8
110°-120°	775.6	11.9
120°-130°	631.3	9.7
130°-140°	507.7	7.8
140°-150°	400.3	6.1
150°-160°	292.7	4.5
160°-170°	181.8	2.8
170°-180°	62.0	1.0
0°-30°	1573.4	24.1
0°-40°	2427.5	37.2
0°-60°	3008.7	46.2
0°-90°	3014.4	46.3
90°-120°	1427.1	21.9
90°-150°	2966.4	45.5
90°-180°	3503.0	53.7
0°-180°	6517.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1962	1962	1962	1962	1962	
5°	1928	1979	1969	1974	2000	185
15°	1954	2023	1983	1972	1986	550
25°	1799	1859	1819	1764	1779	822
35°	1400	1422	1400	1364	1370	857
45°	594	691	698	674	567	459
55°	55	64	106	60	55	61
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	4	8	12	12	2
95°	33	61	33	37	45	37
105°	127	195	742	948	628	134
115°	226	274	640	1330	1554	224
125°	324	368	603	1054	1247	288
135°	402	446	607	868	997	309
145°	476	516	611	756	837	299
155°	558	578	623	686	718	256
165°	619	627	640	656	668	174
175°	652	656	652	648	644	62
180°	652	652	652	652	652	



TEST NUMBER: P645047

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1961.5	1961.5	1961.5	1961.5	1961.5
2.5°	1935.8	1974.1	1960.3	1961.7	1971.3
5°	1927.8	1978.7	1969.2	1974.3	1999.8
7.5°	1933.6	1985.1	1983.9	1985.3	2010.2
10°	1938.5	1992.4	1987.5	1986.5	2009.0
12.5°	1948.3	2007.0	1987.5	1985.2	2004.1
15°	1953.8	2022.7	1982.9	1972.5	1986.0
17.5°	1935.2	2011.8	1957.8	1930.1	1935.5
20°	1909.4	1987.3	1930.9	1889.7	1898.7
22.5°	1869.0	1943.3	1892.9	1842.0	1853.4
25°	1799.2	1859.1	1819.1	1764.3	1779.3
27.5°	1700.0	1747.3	1722.0	1668.9	1678.2
30°	1627.7	1666.6	1646.1	1594.1	1598.6
32.5°	1544.4	1577.3	1555.4	1510.7	1510.4
35°	1399.5	1422.0	1399.5	1364.5	1370.5
37.5°	1210.0	1227.0	1204.2	1183.1	1186.1
40°	1076.5	1089.9	1065.7	1045.8	1042.8
42.5°	909.9	947.3	923.6	896.5	900.7
45°	594.1	691.4	698.2	674.4	566.6
47.5°	299.5	405.8	486.0	368.8	264.3
50°	174.6	238.9	353.7	195.3	163.8
52.5°	114.5	141.8	247.1	123.4	108.7
55°	55.1	64.1	105.7	59.6	55.1
57.5°	19.0	29.2	46.9	29.8	21.1
60°	3.1	12.0	26.0	9.0	1.5
62.5°	1.8	3.6	16.2	1.8	0.3
65°	1.5	1.5	1.5	0.0	0.0
67.5°	1.5	1.5	0.0	0.0	0.0
70°	1.5	1.5	0.0	0.0	0.0
72.5°	1.5	1.5	0.0	0.0	0.0
75°	0.0	1.5	0.0	0.0	0.0
77.5°	0.0	1.5	0.0	0.0	0.0
80°	0.0	1.5	0.0	0.0	0.0
82.5°	0.0	1.5	0.0	0.0	0.0
85°	1.5	1.5	0.0	0.0	0.0
87.5°	1.2	2.0	1.6	2.5	2.5
90°	0.0	4.0	8.2	12.3	12.3
92.5°	9.8	13.9	18.0	25.5	28.7
95°	32.8	60.9	32.8	37.1	45.1
97.5°	58.2	116.8	241.2	71.1	61.5
100°	77.9	146.1	483.9	142.5	94.3
102.5°	97.6	169.0	654.6	375.9	205.9
105°	127.1	195.3	742.3	948.3	627.5
107.5°	156.7	208.0	708.7	1380.1	1292.7
110°	176.4	224.5	689.0	1450.2	1558.5



TEST NUMBER: P645047

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U940-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	196.0	244.2	669.3	1409.2	1591.3
115°	225.6	273.7	639.8	1329.8	1554.4
117.5°	255.9	303.2	632.4	1243.8	1474.8
120°	278.9	323.0	619.3	1178.4	1419.0
122.5°	295.3	342.6	602.9	1122.2	1343.6
125°	324.0	368.1	602.9	1054.3	1246.8
127.5°	347.8	392.7	603.7	975.5	1165.6
130°	360.9	409.0	607.0	922.8	1103.2
132.5°	377.3	425.4	607.0	899.1	1047.5
135°	401.9	446.0	607.0	868.3	996.6
137.5°	422.4	469.7	607.0	834.2	944.1
140°	438.8	482.9	607.0	814.3	914.6
142.5°	455.2	496.1	610.3	791.2	885.1
145°	475.7	515.8	611.1	756.5	836.7
147.5°	500.4	535.6	616.0	731.4	793.2
150°	516.8	548.8	619.3	714.8	766.9
152.5°	533.2	562.0	619.3	701.5	744.0
155°	557.8	577.8	623.4	685.6	717.7
157.5°	577.5	596.7	628.3	675.6	698.9
160°	590.6	606.6	631.6	669.0	689.0
162.5°	600.4	616.5	634.9	665.5	679.2
165°	619.3	627.3	639.8	656.5	668.5
167.5°	630.0	637.2	643.9	652.3	659.5
170°	639.8	643.8	643.9	652.2	656.2
172.5°	643.1	650.3	647.2	648.9	652.9
175°	652.1	656.1	652.1	647.9	643.9
177.5°	652.1	655.3	652.1	652.0	648.8
180°	652.1	652.1	652.1	652.1	652.1

(END OF REPORT)