

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331793-830

Luminaire Tested: **S122RDIW-S485D970U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331793-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5401.3 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28				
2	86	79	74	69	78	72	67	63	58	54	51	45	42	41	32	31	30	25				
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	21				
4	73	62	55	50	65	57	50	46	46	41	38	36	33	30	26	25	23	19				
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	20	17				
6	62	50	43	37	55	46	39	34	37	33	29	29	26	24	22	20	18	15				
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	16	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12				
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11				
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16356	16356	16356	16356
5°	18266	16459	14593	16459
10°	20266	16342	12650	16342
15°	21264	16104	9967	16104
20°	18433	15747	8624	15747
25°	12089	15262	7701	15262
30°	8138	14673	6969	14673
35°	6591	13931	6286	13931
40°	5861	13122	5817	13122
45°	5304	12177	5190	12177
50°	4828	11235	4808	11235
55°	4538	10196	4479	10196
60°	3794	9242	3749	9242
65°	3202	8390	3629	8390
70°	2960	7492	3423	7492
75°	2770	6519	3163	6519
80°	2548	5365	2817	5365
85°	2334	4242	2482	4242



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.8
10°-20°	267.6	5.0
20°-30°	344.8	6.4
30°-40°	327.7	6.1
40°-50°	280.7	5.2
50°-60°	213.8	4.0
60°-70°	135.1	2.5
70°-80°	67.5	1.2
80°-90°	20.6	0.4
90°-100°	41.5	0.8
100°-110°	152.3	2.8
110°-120°	407.0	7.5
120°-130°	671.8	12.4
130°-140°	714.5	13.2
140°-150°	664.1	12.3
150°-160°	533.9	9.9
160°-170°	344.1	6.4
170°-180°	118.4	2.2
0°-30°	708.4	13.1
0°-40°	1036.1	19.2
0°-60°	1530.5	28.3
0°-90°	1753.8	32.5
90°-120°	600.8	11.1
90°-150°	2651.1	49.1
90°-180°	3648.0	67.5
0°-180°	5401.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1013	1013	1013	1013	1013	
5°	1127	1016	900	1016	1127	111
15°	1272	963	596	963	1272	343
25°	679	857	432	857	679	322
35°	334	707	319	707	334	214
45°	232	533	227	533	232	180
55°	161	362	159	362	161	141
65°	84	220	95	220	84	85
75°	44	104	51	104	44	47
85°	13	23	13	23	13	14
90°	24	1	24	1	24	11
95°	39	58	39	58	39	36
105°	68	274	68	274	68	71
115°	74	518	74	518	74	185
125°	770	732	770	732	770	666
135°	936	906	936	906	936	721
145°	1067	1051	1067	1051	1067	667
155°	1158	1157	1158	1157	1158	534
165°	1217	1220	1217	1220	1217	344
175°	1240	1247	1240	1247	1240	118
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1054.1	1055.0	1055.8	1053.9	1053.9	1052.2	1048.5	1045.7	1037.7	1036.6	1036.6
5°	1127.0	1126.3	1127.8	1123.1	1116.8	1115.4	1108.7	1099.9	1090.8	1080.5	1078.5
7.5°	1199.6	1198.5	1195.7	1194.9	1190.1	1179.4	1168.7	1157.2	1142.0	1127.1	1119.6
10°	1236.1	1247.7	1240.8	1228.4	1230.9	1214.4	1205.5	1190.4	1177.7	1155.6	1150.7
12.5°	1272.1	1276.8	1274.5	1267.5	1264.4	1252.9	1241.0	1227.9	1204.5	1184.6	1167.2
15°	1272.1	1278.7	1280.5	1278.4	1280.2	1279.4	1273.1	1262.2	1241.8	1219.9	1201.0
17.5°	1178.2	1182.8	1194.3	1202.1	1212.0	1232.8	1243.1	1247.2	1244.1	1231.6	1218.2
20°	1072.8	1065.1	1097.5	1114.0	1128.1	1163.3	1193.5	1205.1	1223.8	1223.5	1219.9
22.5°	923.6	925.4	956.1	975.7	1016.9	1052.1	1086.6	1130.3	1166.4	1190.2	1204.2
25°	678.6	692.0	722.6	749.3	795.1	860.6	920.1	989.1	1054.1	1105.6	1154.5
27.5°	509.6	510.7	534.9	559.7	586.8	640.5	715.4	797.8	890.6	967.1	1055.3
30°	436.5	434.3	444.6	459.7	483.0	524.4	580.8	661.8	754.3	869.8	972.5
32.5°	384.7	384.7	392.5	403.7	422.9	450.9	489.6	555.3	642.8	756.3	876.8
35°	334.4	334.0	339.7	347.8	355.8	373.8	400.2	434.7	494.9	600.9	724.1
37.5°	298.3	299.9	302.7	307.7	316.6	326.6	342.5	365.6	408.5	471.2	574.7
40°	278.1	278.8	282.7	286.9	292.2	299.9	312.9	331.6	362.9	412.8	488.5
42.5°	259.5	260.1	263.0	266.8	271.0	278.8	289.5	305.7	331.1	370.0	432.5
45°	232.3	232.3	234.8	236.5	241.1	248.2	256.9	270.3	287.9	316.8	358.4
47.5°	206.8	206.9	208.5	211.5	214.4	219.9	228.6	239.5	252.3	274.7	310.1
50°	192.2	192.6	193.6	196.0	197.8	202.7	209.4	219.0	232.3	249.6	279.1
52.5°	180.3	180.1	181.4	182.6	183.7	187.3	192.3	200.7	212.6	227.6	252.1
55°	161.2	159.8	161.9	163.6	164.8	166.2	168.9	174.3	184.5	197.1	215.4
57.5°	137.2	136.7	138.2	139.8	143.1	146.9	149.3	152.7	158.0	167.0	185.2
60°	117.5	117.5	120.7	121.8	125.6	130.5	135.5	138.4	143.6	149.6	163.0
62.5°	100.1	100.4	101.9	102.9	105.1	111.1	118.1	124.2	129.2	135.0	143.8
65°	83.8	84.5	84.5	85.2	86.6	88.0	90.8	95.8	104.5	112.6	119.3
67.5°	71.1	71.4	71.5	72.2	72.6	74.1	75.2	77.5	79.5	87.2	95.5
70°	62.7	63.7	63.3	64.1	64.4	65.1	66.5	67.6	70.8	72.5	77.5
72.5°	54.8	55.5	55.5	55.9	56.8	56.9	58.1	59.1	61.2	62.7	65.3
75°	44.4	44.0	44.4	45.1	45.4	45.7	45.7	47.1	48.3	49.7	51.4
77.5°	34.2	34.6	34.5	34.6	34.6	35.3	35.2	35.8	36.9	37.6	38.5
80°	27.4	27.8	27.4	27.8	28.2	28.5	28.2	28.5	29.6	30.3	30.3
82.5°	21.3	21.3	21.6	21.6	21.7	21.8	22.2	22.3	23.1	22.9	23.2
85°	12.6	12.3	12.3	12.3	12.6	13.0	12.6	12.6	13.0	13.0	13.0
87.5°	9.3	9.6	9.5	9.4	9.3	9.2	9.0	9.0	8.6	8.7	8.1
90°	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0	19.0	18.0	16.4
92.5°	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0	21.4	20.9	20.1
95°	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1	36.1	35.2	33.7
97.5°	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6	47.8	47.0	43.7
100°	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6	53.0	51.4	48.0
102.5°	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9	54.9	52.8	81.2
105°	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4	57.1	55.0	109.6
107.5°	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4	74.6	76.9	142.4
110°	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5	137.6	157.6	215.5



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5	324.5	397.6	411.8
115°	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3	463.0	555.7	550.7
117.5°	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6	593.0	615.5	612.1
120°	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0	662.6	660.2	656.6
122.5°	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6	704.1	702.7	698.7
125°	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8	762.4	761.0	757.2
127.5°	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7	815.7	813.6	810.8
130°	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9	849.7	847.5	845.3
132.5°	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1	883.3	881.4	879.1
135°	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6	930.6	928.6	926.7
137.5°	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6	974.7	972.7	970.6
140°	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1	1003.3	1001.5	999.3
142.5°	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4	1029.8	1028.1	1025.7
145°	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3	1066.9	1065.5	1062.1
147.5°	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3	1099.3	1098.3	1094.9
150°	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1	1118.9	1117.7	1114.5
152.5°	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1	1136.9	1135.7	1132.7
155°	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4	1161.2	1160.0	1157.6
157.5°	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9	1181.6	1180.2	1178.5
160°	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9	1193.6	1192.4	1191.3
162.5°	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0	1204.6	1203.2	1202.2
165°	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7	1216.2
167.5°	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9	1229.5	1228.1	1227.6
170°	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7	1235.3	1233.9	1233.5
172.5°	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0	1239.6	1238.2	1237.7
175°	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7	1244.3	1242.8	1242.5
177.5°	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2	1245.1	1244.0	1243.8
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1037.2	1035.0	1033.0	1027.9	1025.4	1019.7	1018.9	1018.6	1011.3	1004.3	1002.3
5°	1072.8	1067.2	1058.8	1048.9	1038.7	1028.1	1021.1	1015.5	1001.4	988.0	980.2
7.5°	1108.7	1096.6	1082.0	1063.4	1047.8	1030.4	1017.5	1005.8	985.8	966.7	953.8
10°	1135.5	1115.8	1096.5	1070.7	1050.7	1031.0	1012.7	996.8	974.3	949.0	930.9
12.5°	1152.1	1130.4	1103.7	1078.6	1052.6	1027.6	1003.1	982.7	956.3	930.1	908.7
15°	1174.6	1151.3	1119.0	1083.1	1049.6	1016.9	988.7	963.4	928.9	897.6	871.5
17.5°	1193.0	1160.9	1126.1	1084.7	1045.9	1004.4	968.1	935.7	897.3	859.5	828.9
20°	1198.8	1167.2	1127.0	1085.5	1039.7	990.8	951.8	916.5	875.3	834.2	799.0
22.5°	1195.1	1170.5	1125.9	1076.2	1029.4	978.2	934.1	893.2	847.5	805.5	764.7
25°	1170.4	1161.9	1119.6	1065.5	1011.9	952.4	901.4	856.7	804.6	759.6	715.2
27.5°	1112.4	1130.7	1104.5	1046.7	987.2	923.4	866.1	815.2	761.1	710.4	666.2
30°	1056.7	1098.5	1087.2	1033.8	967.2	904.6	840.2	787.0	729.3	677.2	633.6
32.5°	980.3	1049.5	1060.5	1015.8	947.0	878.1	810.6	757.7	697.5	642.5	600.0
35°	858.8	962.3	1009.8	981.3	912.3	838.1	768.4	706.8	646.2	592.0	549.8
37.5°	713.9	854.8	934.1	936.0	872.7	795.5	719.6	658.5	596.4	543.3	497.6
40°	619.8	772.6	875.7	898.6	845.1	761.7	684.9	622.6	562.1	510.0	457.6
42.5°	535.4	687.6	814.4	854.1	811.6	728.8	651.8	586.6	527.7	478.4	424.9
45°	432.9	566.0	705.7	776.8	753.3	676.5	595.2	533.3	478.0	435.4	384.0
47.5°	365.2	459.0	594.2	690.4	689.9	619.9	540.0	480.6	429.3	389.5	347.8
50°	326.6	408.3	522.7	631.8	640.9	582.2	506.1	447.3	399.5	357.6	324.1
52.5°	292.0	359.3	462.1	566.8	592.8	541.9	468.2	413.9	367.4	328.9	300.2
55°	246.8	298.8	377.0	474.9	514.3	478.3	412.8	362.2	324.5	292.2	267.5
57.5°	208.7	247.8	310.5	389.3	435.2	412.6	358.6	317.4	285.2	255.9	236.5
60°	184.8	216.8	269.9	335.8	386.4	370.6	324.5	286.2	258.7	233.4	215.1
62.5°	162.3	189.8	235.4	288.8	335.3	328.7	291.1	258.8	234.8	211.7	196.2
65°	130.5	150.6	186.2	228.1	265.4	268.5	241.5	219.6	198.1	179.8	166.2
67.5°	104.0	117.1	142.1	177.4	205.4	215.4	198.8	182.1	165.0	150.9	139.0
70°	87.7	98.2	116.5	145.1	170.7	181.3	171.7	158.7	143.9	132.3	122.2
72.5°	71.1	81.3	94.8	115.7	137.8	149.2	145.9	136.5	124.5	114.9	105.3
75°	53.5	56.6	65.8	79.9	97.2	107.0	109.4	104.5	95.0	87.7	82.0
77.5°	39.6	41.5	45.8	53.3	64.5	73.2	76.9	76.3	69.7	65.5	60.2
80°	31.7	32.7	34.9	38.0	46.5	55.2	57.7	57.7	53.2	51.4	46.1
82.5°	24.0	24.9	26.1	27.9	31.9	39.5	42.2	42.8	39.9	37.6	33.5
85°	13.8	13.4	14.0	15.2	15.8	17.9	22.1	22.9	22.1	19.3	18.3
87.5°	7.7	7.7	7.4	6.7	6.6	6.4	7.4	8.4	7.6	7.3	7.2
90°	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2	18.0	17.8	17.6
95°	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5	51.9	45.3	38.7
97.5°	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2	97.6	79.0	60.3
100°	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4	132.0	104.5	77.2
102.5°	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0	201.1	195.4	189.5
105°	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8	279.8	285.8	291.8
107.5°	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0	354.9	359.7	364.5
110°	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0	403.2	407.4	411.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1	448.8	452.5	456.3
115°	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8	521.2	524.7	528.1
117.5°	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9	586.7	590.5	594.3
120°	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5	633.5	636.4	639.4
122.5°	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8	673.9	677.1	680.2
125°	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2	734.8	737.4	740.0
127.5°	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9	790.8	793.6	796.5
130°	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2	826.4	829.6	832.7
132.5°	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2	862.0	864.7	867.3
135°	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1	909.3	912.5	915.7
137.5°	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4	955.6	957.9	960.2
140°	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4	986.0	987.6	989.2
142.5°	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3	1011.7	1013.2	1014.6
145°	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0	1050.8	1050.7	1050.5
147.5°	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6	1085.7	1085.0	1084.2
150°	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6	1108.1	1106.7	1105.4
152.5°	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1	1127.5	1125.9	1124.4
155°	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3	1155.5	1153.7	1151.9
157.5°	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5	1178.0	1176.4	1174.9
160°	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1191.3	1190.1	1188.8
162.5°	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0	1202.8	1201.6	1200.3
165°	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5	1218.2	1217.0	1215.9
167.5°	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0	1229.7	1228.6	1227.4
170°	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5	1236.2	1235.1	1233.9
172.5°	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8	1240.6	1239.3	1238.2
175°	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4	1245.9	1244.5	1243.2
177.5°	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3	1247.2	1246.0	1244.9
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	998.6	996.6	993.0	987.4	984.0	978.1	974.1	976.4	976.9	976.4	975.8
5°	971.9	964.4	954.2	944.3	935.2	925.4	919.7	917.3	912.3	909.6	908.1
7.5°	939.3	926.6	912.2	895.0	880.4	865.2	857.3	853.5	843.4	837.9	833.1
10°	915.1	895.0	880.6	858.1	844.4	824.3	810.6	811.0	797.2	789.5	783.8
12.5°	888.4	866.4	842.4	822.1	803.0	786.9	770.3	763.6	749.0	741.6	726.4
15°	844.0	818.3	793.1	765.5	746.2	721.2	697.3	668.1	644.5	624.1	618.4
17.5°	795.6	763.8	738.4	706.2	673.0	630.9	603.2	586.3	572.0	561.3	553.3
20°	762.4	730.0	702.9	654.3	609.6	581.1	560.7	547.7	532.9	521.3	514.9
22.5°	727.5	693.7	656.8	602.5	567.7	544.8	526.6	511.6	501.6	492.6	486.8
25°	677.9	640.9	580.0	542.7	514.6	490.7	478.0	468.8	458.3	445.9	440.4
27.5°	625.6	566.8	523.0	495.3	468.4	452.9	441.5	427.8	418.4	412.8	407.0
30°	586.4	527.6	493.5	463.2	444.2	427.0	413.6	405.9	396.7	387.2	383.3
32.5°	542.7	495.8	463.1	437.9	418.6	403.9	393.3	380.8	374.2	368.3	360.2
35°	488.5	453.0	423.1	402.7	384.4	372.4	360.1	352.7	340.7	335.8	332.6
37.5°	442.6	411.8	389.5	368.0	353.5	340.3	332.7	320.9	315.8	308.9	302.2
40°	416.7	386.4	365.0	347.4	331.2	321.3	311.9	302.4	294.6	291.4	283.3
42.5°	390.3	365.6	344.1	324.9	314.1	303.6	291.6	284.6	276.5	271.5	266.5
45°	353.7	332.0	313.6	297.7	285.8	274.9	267.1	255.5	251.0	240.7	236.5
47.5°	321.6	301.3	283.9	268.8	257.1	250.1	238.7	229.6	222.3	216.0	210.7
50°	298.8	281.9	265.0	251.7	241.1	230.9	219.3	214.7	203.4	200.3	197.1
52.5°	278.0	261.9	246.5	233.4	222.8	212.9	202.6	196.7	189.1	185.9	183.6
55°	248.8	233.4	218.6	207.0	196.4	186.2	179.8	172.5	168.9	166.5	163.6
57.5°	219.5	205.7	194.3	182.6	171.9	163.8	156.5	152.0	148.4	145.2	141.8
60°	201.0	187.6	177.4	166.5	155.6	148.9	143.3	138.0	133.7	128.8	127.4
62.5°	181.3	169.6	160.2	149.6	140.1	133.9	128.7	123.7	118.6	111.4	109.4
65°	154.2	145.1	135.2	126.4	117.9	112.0	104.2	98.6	96.4	95.8	95.4
67.5°	129.7	121.0	112.5	103.6	95.9	90.3	86.3	85.5	84.1	83.6	82.7
70°	113.3	105.3	96.8	88.3	81.0	79.9	78.5	77.1	75.3	74.6	73.9
72.5°	98.7	90.3	81.9	75.1	71.9	70.6	69.2	67.8	66.6	65.9	65.5
75°	75.7	68.0	62.3	59.9	58.1	57.0	55.0	53.8	53.2	52.1	51.7
77.5°	54.5	50.1	47.5	46.0	44.1	43.0	41.8	40.7	40.0	39.8	39.2
80°	41.6	39.4	37.7	35.5	34.9	33.5	33.1	32.0	32.4	31.3	31.3
82.5°	32.2	29.6	28.1	27.1	26.4	25.3	24.9	24.4	24.5	23.8	23.8
85°	16.6	15.8	15.2	14.4	14.4	13.4	13.8	13.4	13.4	12.6	12.3
87.5°	7.3	7.4	7.2	7.4	7.8	7.8	8.0	7.9	8.1	8.4	8.2
90°	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.1	22.7
92.5°	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0	22.4	23.0	23.4
95°	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1	38.2	39.1	39.5
97.5°	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6	49.4	50.2	50.7
100°	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6	56.2	57.8	58.7
102.5°	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9	59.0	61.1	62.4
105°	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4	61.5	63.7	65.2
107.5°	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4	70.2	68.0	67.2
110°	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5	97.6	77.6	68.0



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5	178.5	105.5	69.3
115°	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3	277.7	185.0	131.5
117.5°	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6	548.3	525.8	491.0
120°	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0	667.3	669.8	657.4
122.5°	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6	707.0	708.4	706.5
125°	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8	765.3	766.7	767.6
127.5°	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7	819.7	821.8	822.8
130°	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9	854.1	856.3	857.3
132.5°	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1	887.0	888.9	889.8
135°	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6	934.5	936.5	937.4
137.5°	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6	978.5	980.5	981.2
140°	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1	1006.9	1008.7	1009.1
142.5°	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4	1033.1	1034.7	1035.0
145°	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3	1069.7	1071.0	1071.3
147.5°	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3	1101.4	1102.4	1102.5
150°	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1	1121.2	1122.5	1122.6
152.5°	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1	1139.3	1140.5	1140.5
155°	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4	1163.6	1164.8	1164.6
157.5°	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9	1184.3	1185.6	1185.5
160°	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9	1196.0	1197.2	1197.1
162.5°	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0	1207.3	1208.7	1208.5
165°	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4
167.5°	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9	1232.3	1233.7	1233.5
170°	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7	1238.0	1239.4	1239.3
172.5°	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0	1242.4	1243.8	1243.6
175°	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7	1247.1	1248.5	1248.2
177.5°	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2	1247.3	1248.4	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	972.7	973.3	972.4	973.0	972.4	973.3	972.7	975.8	976.4	976.9	976.4
5°	906.3	902.1	901.4	900.4	901.4	902.1	906.3	908.1	909.6	912.3	917.3
7.5°	827.1	826.4	824.7	822.2	824.7	826.4	827.1	833.1	837.9	843.4	853.5
10°	776.1	774.4	774.0	771.6	774.0	774.4	776.1	783.8	789.5	797.2	811.0
12.5°	716.4	705.1	703.9	697.8	703.9	705.1	716.4	726.4	741.6	749.0	763.6
15°	610.0	607.8	600.9	596.3	600.9	607.8	610.0	618.4	624.1	644.5	668.1
17.5°	549.1	542.2	540.1	539.1	540.1	542.2	549.1	553.3	561.3	572.0	586.3
20°	510.0	503.7	502.7	501.9	502.7	503.7	510.0	514.9	521.3	532.9	547.7
22.5°	483.0	476.4	473.6	471.6	473.6	476.4	483.0	486.8	492.6	501.6	511.6
25°	436.8	434.3	432.9	432.3	432.9	434.3	436.8	440.4	445.9	458.3	468.8
27.5°	400.7	395.3	394.2	392.4	394.2	395.3	400.7	407.0	412.8	418.4	427.8
30°	380.1	378.3	375.9	373.8	375.9	378.3	380.1	383.3	387.2	396.7	405.9
32.5°	355.9	354.5	352.2	351.3	352.2	354.5	355.9	360.2	368.3	374.2	380.8
35°	329.1	324.1	322.1	318.9	322.1	324.1	329.1	332.6	335.8	340.7	352.7
37.5°	300.8	298.1	295.2	296.2	295.2	298.1	300.8	302.2	308.9	315.8	320.9
40°	278.8	277.0	276.3	276.0	276.3	277.0	278.8	283.3	291.4	294.6	302.4
42.5°	261.3	256.5	254.6	254.6	254.6	256.5	261.3	266.5	271.5	276.5	284.6
45°	234.8	230.2	227.1	227.3	227.1	230.2	234.8	236.5	240.7	251.0	255.5
47.5°	207.6	207.5	205.5	206.1	205.5	207.5	207.6	210.7	216.0	222.3	229.6
50°	194.6	192.6	191.1	191.4	191.1	192.6	194.6	197.1	200.3	203.4	214.7
52.5°	182.3	180.4	179.3	180.8	179.3	180.4	182.3	183.6	185.9	189.1	196.7
55°	161.9	159.8	159.5	159.1	159.5	159.8	161.9	163.6	166.5	168.9	172.5
57.5°	139.2	137.8	135.6	134.8	135.6	137.8	139.2	141.8	145.2	148.4	152.0
60°	122.8	120.0	116.5	116.1	116.5	120.0	122.8	127.4	128.8	133.7	138.0
62.5°	107.9	107.4	106.7	106.6	106.7	107.4	107.9	109.4	111.4	118.6	123.7
65°	94.7	94.3	94.7	95.0	94.7	94.3	94.7	95.4	95.8	96.4	98.6
67.5°	82.5	81.9	81.2	81.5	81.2	81.9	82.5	82.7	83.6	84.1	85.5
70°	73.2	72.9	72.5	72.5	72.5	72.9	73.2	73.9	74.6	75.3	77.1
72.5°	64.2	64.1	63.8	63.5	63.8	64.1	64.2	65.5	65.9	66.6	67.8
75°	51.4	50.7	50.7	50.7	50.7	50.7	51.4	51.7	52.1	53.2	53.8
77.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.2	39.8	40.0	40.7
80°	31.0	30.6	30.3	30.3	30.3	30.6	31.0	31.3	31.3	32.4	32.0
82.5°	23.7	23.3	23.2	22.9	23.2	23.3	23.7	23.8	23.8	24.5	24.4
85°	12.6	13.0	12.6	13.4	12.6	13.0	12.6	12.3	12.6	13.4	13.4
87.5°	8.3	8.1	8.5	8.2	8.5	8.1	8.3	8.2	8.4	8.1	7.9
90°	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0
92.5°	23.6	23.8	24.0	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0
95°	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1
97.5°	51.0	51.2	51.5	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6
100°	59.1	59.6	59.9	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6
102.5°	63.0	63.5	64.1	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9
105°	66.1	66.8	67.7	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4
107.5°	68.1	68.8	69.7	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4
110°	68.7	69.6	70.3	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	69.9	70.6	71.3	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5
115°	117.1	102.6	88.2	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3
117.5°	443.6	396.2	348.9	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6
120°	630.5	603.4	576.4	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0
122.5°	701.3	696.1	690.8	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6
125°	768.3	768.8	769.4	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8
127.5°	823.0	823.1	823.2	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7
130°	857.1	856.9	856.7	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9
132.5°	889.5	889.3	889.1	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1
135°	937.0	936.5	936.1	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6
137.5°	980.5	979.8	979.1	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6
140°	1008.1	1007.1	1006.1	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1
142.5°	1034.1	1033.0	1032.1	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4
145°	1070.3	1069.2	1068.3	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3
147.5°	1101.6	1100.8	1099.9	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3
150°	1121.6	1120.6	1119.6	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1
152.5°	1139.2	1137.8	1136.5	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1
155°	1163.0	1161.4	1159.8	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4
157.5°	1183.9	1182.4	1180.8	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9
160°	1195.7	1194.3	1193.0	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9
162.5°	1206.7	1205.0	1203.3	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0
165°	1221.0	1219.6	1218.1	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6
167.5°	1231.7	1229.9	1228.1	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9
170°	1237.5	1235.7	1233.9	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7
172.5°	1241.8	1240.0	1238.2	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0
175°	1246.1	1244.2	1242.2	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7
177.5°	1246.8	1245.4	1244.0	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	974.1	978.1	984.0	987.4	993.0	996.6	998.6	1002.3	1004.3	1011.3	1018.6
5°	919.7	925.4	935.2	944.3	954.2	964.4	971.9	980.2	988.0	1001.4	1015.5
7.5°	857.3	865.2	880.4	895.0	912.2	926.6	939.3	953.8	966.7	985.8	1005.8
10°	810.6	824.3	844.4	858.1	880.6	895.0	915.1	930.9	949.0	974.3	996.8
12.5°	770.3	786.9	803.0	822.1	842.4	866.4	888.4	908.7	930.1	956.3	982.7
15°	697.3	721.2	746.2	765.5	793.1	818.3	844.0	871.5	897.6	928.9	963.4
17.5°	603.2	630.9	673.0	706.2	738.4	763.8	795.6	828.9	859.5	897.3	935.7
20°	560.7	581.1	609.6	654.3	702.9	730.0	762.4	799.0	834.2	875.3	916.5
22.5°	526.6	544.8	567.7	602.5	656.8	693.7	727.5	764.7	805.5	847.5	893.2
25°	478.0	490.7	514.6	542.7	580.0	640.9	677.9	715.2	759.6	804.6	856.7
27.5°	441.5	452.9	468.4	495.3	523.0	566.8	625.6	666.2	710.4	761.1	815.2
30°	413.6	427.0	444.2	463.2	493.5	527.6	586.4	633.6	677.2	729.3	787.0
32.5°	393.3	403.9	418.6	437.9	463.1	495.8	542.7	600.0	642.5	697.5	757.7
35°	360.1	372.4	384.4	402.7	423.1	453.0	488.5	549.8	592.0	646.2	706.8
37.5°	332.7	340.3	353.5	368.0	389.5	411.8	442.6	497.6	543.3	596.4	658.5
40°	311.9	321.3	331.2	347.4	365.0	386.4	416.7	457.6	510.0	562.1	622.6
42.5°	291.6	303.6	314.1	324.9	344.1	365.6	390.3	424.9	478.4	527.7	586.6
45°	267.1	274.9	285.8	297.7	313.6	332.0	353.7	384.0	435.4	478.0	533.3
47.5°	238.7	250.1	257.1	268.8	283.9	301.3	321.6	347.8	389.5	429.3	480.6
50°	219.3	230.9	241.1	251.7	265.0	281.9	298.8	324.1	357.6	399.5	447.3
52.5°	202.6	212.9	222.8	233.4	246.5	261.9	278.0	300.2	328.9	367.4	413.9
55°	179.8	186.2	196.4	207.0	218.6	233.4	248.8	267.5	292.2	324.5	362.2
57.5°	156.5	163.8	171.9	182.6	194.3	205.7	219.5	236.5	255.9	285.2	317.4
60°	143.3	148.9	155.6	166.5	177.4	187.6	201.0	215.1	233.4	258.7	286.2
62.5°	128.7	133.9	140.1	149.6	160.2	169.6	181.3	196.2	211.7	234.8	258.8
65°	104.2	112.0	117.9	126.4	135.2	145.1	154.2	166.2	179.8	198.1	219.6
67.5°	86.3	90.3	95.9	103.6	112.5	121.0	129.7	139.0	150.9	165.0	182.1
70°	78.5	79.9	81.0	88.3	96.8	105.3	113.3	122.2	132.3	143.9	158.7
72.5°	69.2	70.6	71.9	75.1	81.9	90.3	98.7	105.3	114.9	124.5	136.5
75°	55.0	57.0	58.1	59.9	62.3	68.0	75.7	82.0	87.7	95.0	104.5
77.5°	41.8	43.0	44.1	46.0	47.5	50.1	54.5	60.2	65.5	69.7	76.3
80°	33.1	33.5	34.9	35.5	37.7	39.4	41.6	46.1	51.4	53.2	57.7
82.5°	24.9	25.3	26.4	27.1	28.1	29.6	32.2	33.5	37.6	39.9	42.8
85°	13.8	13.4	14.4	14.4	15.2	15.8	16.6	18.3	19.3	22.1	22.9
87.5°	8.0	7.8	7.8	7.4	7.2	7.4	7.3	7.2	7.3	7.6	8.4
90°	19.0	18.0	16.4	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9
92.5°	21.4	20.9	20.1	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2
95°	36.1	35.2	33.7	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5
97.5°	47.8	47.0	43.7	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2
100°	53.0	51.4	48.0	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4
102.5°	54.9	52.8	81.2	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0
105°	57.1	55.0	109.6	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8
107.5°	74.6	76.9	142.4	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0
110°	137.6	157.6	215.5	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.5	397.6	411.8	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1
115°	463.0	555.7	550.7	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8
117.5°	593.0	615.5	612.1	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9
120°	662.6	660.2	656.6	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5
122.5°	704.1	702.7	698.7	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8
125°	762.4	761.0	757.2	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2
127.5°	815.7	813.6	810.8	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9
130°	849.7	847.5	845.3	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2
132.5°	883.3	881.4	879.1	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2
135°	930.6	928.6	926.7	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1
137.5°	974.7	972.7	970.6	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4
140°	1003.3	1001.5	999.3	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4
142.5°	1029.8	1028.1	1025.7	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3
145°	1066.9	1065.5	1062.1	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0
147.5°	1099.3	1098.3	1094.9	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6
150°	1118.9	1117.7	1114.5	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6
152.5°	1136.9	1135.7	1132.7	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1
155°	1161.2	1160.0	1157.6	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3
157.5°	1181.6	1180.2	1178.5	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5
160°	1193.6	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4
162.5°	1204.6	1203.2	1202.2	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0
165°	1218.1	1216.7	1216.2	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5
167.5°	1229.5	1228.1	1227.6	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0
170°	1235.3	1233.9	1233.5	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5
172.5°	1239.6	1238.2	1237.7	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8
175°	1244.3	1242.8	1242.5	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4
177.5°	1245.1	1244.0	1243.8	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1018.9	1019.7	1025.4	1027.9	1033.0	1035.0	1037.2	1036.6	1036.6	1037.7	1045.7
5°	1021.1	1028.1	1038.7	1048.9	1058.8	1067.2	1072.8	1078.5	1080.5	1090.8	1099.9
7.5°	1017.5	1030.4	1047.8	1063.4	1082.0	1096.6	1108.7	1119.6	1127.1	1142.0	1157.2
10°	1012.7	1031.0	1050.7	1070.7	1096.5	1115.8	1135.5	1150.7	1155.6	1177.7	1190.4
12.5°	1003.1	1027.6	1052.6	1078.6	1103.7	1130.4	1152.1	1167.2	1184.6	1204.5	1227.9
15°	988.7	1016.9	1049.6	1083.1	1119.0	1151.3	1174.6	1201.0	1219.9	1241.8	1262.2
17.5°	968.1	1004.4	1045.9	1084.7	1126.1	1160.9	1193.0	1218.2	1231.6	1244.1	1247.2
20°	951.8	990.8	1039.7	1085.5	1127.0	1167.2	1198.8	1219.9	1223.5	1223.8	1205.1
22.5°	934.1	978.2	1029.4	1076.2	1125.9	1170.5	1195.1	1204.2	1190.2	1166.4	1130.3
25°	901.4	952.4	1011.9	1065.5	1119.6	1161.9	1170.4	1154.5	1105.6	1054.1	989.1
27.5°	866.1	923.4	987.2	1046.7	1104.5	1130.7	1112.4	1055.3	967.1	890.6	797.8
30°	840.2	904.6	967.2	1033.8	1087.2	1098.5	1056.7	972.5	869.8	754.3	661.8
32.5°	810.6	878.1	947.0	1015.8	1060.5	1049.5	980.3	876.8	756.3	642.8	555.3
35°	768.4	838.1	912.3	981.3	1009.8	962.3	858.8	724.1	600.9	494.9	434.7
37.5°	719.6	795.5	872.7	936.0	934.1	854.8	713.9	574.7	471.2	408.5	365.6
40°	684.9	761.7	845.1	898.6	875.7	772.6	619.8	488.5	412.8	362.9	331.6
42.5°	651.8	728.8	811.6	854.1	814.4	687.6	535.4	432.5	370.0	331.1	305.7
45°	595.2	676.5	753.3	776.8	705.7	566.0	432.9	358.4	316.8	287.9	270.3
47.5°	540.0	619.9	689.9	690.4	594.2	459.0	365.2	310.1	274.7	252.3	239.5
50°	506.1	582.2	640.9	631.8	522.7	408.3	326.6	279.1	249.6	232.3	219.0
52.5°	468.2	541.9	592.8	566.8	462.1	359.3	292.0	252.1	227.6	212.6	200.7
55°	412.8	478.3	514.3	474.9	377.0	298.8	246.8	215.4	197.1	184.5	174.3
57.5°	358.6	412.6	435.2	389.3	310.5	247.8	208.7	185.2	167.0	158.0	152.7
60°	324.5	370.6	386.4	335.8	269.9	216.8	184.8	163.0	149.6	143.6	138.4
62.5°	291.1	328.7	335.3	288.8	235.4	189.8	162.3	143.8	135.0	129.2	124.2
65°	241.5	268.5	265.4	228.1	186.2	150.6	130.5	119.3	112.6	104.5	95.8
67.5°	198.8	215.4	205.4	177.4	142.1	117.1	104.0	95.5	87.2	79.5	77.5
70°	171.7	181.3	170.7	145.1	116.5	98.2	87.7	77.5	72.5	70.8	67.6
72.5°	145.9	149.2	137.8	115.7	94.8	81.3	71.1	65.3	62.7	61.2	59.1
75°	109.4	107.0	97.2	79.9	65.8	56.6	53.5	51.4	49.7	48.3	47.1
77.5°	76.9	73.2	64.5	53.3	45.8	41.5	39.6	38.5	37.6	36.9	35.8
80°	57.7	55.2	46.5	38.0	34.9	32.7	31.7	30.3	30.3	29.6	28.5
82.5°	42.2	39.5	31.9	27.9	26.1	24.9	24.0	23.2	22.9	23.1	22.3
85°	22.1	17.9	15.8	15.2	14.0	13.4	13.8	13.0	13.0	13.0	12.6
87.5°	7.4	6.4	6.6	6.7	7.4	7.7	7.7	8.1	8.7	8.6	9.0
90°	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0
92.5°	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0
95°	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1
97.5°	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6
100°	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6
102.5°	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9
105°	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4
107.5°	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4
110°	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5
115°	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3
117.5°	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6
120°	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0
122.5°	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6
125°	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8
127.5°	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7
130°	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9
132.5°	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1
135°	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6
137.5°	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6
140°	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1
142.5°	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4
145°	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3
147.5°	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3
150°	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1
152.5°	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1
155°	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4
157.5°	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9
160°	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9
162.5°	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0
165°	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6
167.5°	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9
170°	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7
172.5°	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0
175°	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7
177.5°	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1048.5	1052.2	1053.9	1053.9	1055.8	1055.0	1054.1
5°	1108.7	1115.4	1116.8	1123.1	1127.8	1126.3	1127.0
7.5°	1168.7	1179.4	1190.1	1194.9	1195.7	1198.5	1199.6
10°	1205.5	1214.4	1230.9	1228.4	1240.8	1247.7	1236.1
12.5°	1241.0	1252.9	1264.4	1267.5	1274.5	1276.8	1272.1
15°	1273.1	1279.4	1280.2	1278.4	1280.5	1278.7	1272.1
17.5°	1243.1	1232.8	1212.0	1202.1	1194.3	1182.8	1178.2
20°	1193.5	1163.3	1128.1	1114.0	1097.5	1065.1	1072.8
22.5°	1086.6	1052.1	1016.9	975.7	956.1	925.4	923.6
25°	920.1	860.6	795.1	749.3	722.6	692.0	678.6
27.5°	715.4	640.5	586.8	559.7	534.9	510.7	509.6
30°	580.8	524.4	483.0	459.7	444.6	434.3	436.5
32.5°	489.6	450.9	422.9	403.7	392.5	384.7	384.7
35°	400.2	373.8	355.8	347.8	339.7	334.0	334.4
37.5°	342.5	326.6	316.6	307.7	302.7	299.9	298.3
40°	312.9	299.9	292.2	286.9	282.7	278.8	278.1
42.5°	289.5	278.8	271.0	266.8	263.0	260.1	259.5
45°	256.9	248.2	241.1	236.5	234.8	232.3	232.3
47.5°	228.6	219.9	214.4	211.5	208.5	206.9	206.8
50°	209.4	202.7	197.8	196.0	193.6	192.6	192.2
52.5°	192.3	187.3	183.7	182.6	181.4	180.1	180.3
55°	168.9	166.2	164.8	163.6	161.9	159.8	161.2
57.5°	149.3	146.9	143.1	139.8	138.2	136.7	137.2
60°	135.5	130.5	125.6	121.8	120.7	117.5	117.5
62.5°	118.1	111.1	105.1	102.9	101.9	100.4	100.1
65°	90.8	88.0	86.6	85.2	84.5	84.5	83.8
67.5°	75.2	74.1	72.6	72.2	71.5	71.4	71.1
70°	66.5	65.1	64.4	64.1	63.3	63.7	62.7
72.5°	58.1	56.9	56.8	55.9	55.5	55.5	54.8
75°	45.7	45.7	45.4	45.1	44.4	44.0	44.4
77.5°	35.2	35.3	34.6	34.6	34.5	34.6	34.2
80°	28.2	28.5	28.2	27.8	27.4	27.8	27.4
82.5°	22.2	21.8	21.7	21.6	21.6	21.3	21.3
85°	12.6	13.0	12.6	12.3	12.3	12.3	12.6
87.5°	9.0	9.2	9.3	9.4	9.5	9.6	9.3
90°	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331793-830

CATALOG NUMBER: S122RDIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)