

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645137

Luminaire Tested: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645137
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3917.2 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645137

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645137

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	107	103	101	98	102	99	96	94	91	89	87	83	82	80	76	75	74	71
2	100	94	89	85	95	90	86	83	83	80	77	77	74	72	71	69	68	65
3	93	86	80	75	89	83	77	73	77	73	69	71	68	65	66	63	61	59
4	87	78	72	67	84	76	70	65	71	66	62	66	62	59	61	58	56	53
5	82	72	65	60	78	69	63	59	65	60	56	61	57	53	57	54	51	49
6	76	66	59	54	73	64	58	53	60	55	51	56	52	49	53	49	47	44
7	71	61	54	49	69	59	53	48	55	50	46	52	48	44	49	45	43	41
8	67	56	49	45	64	55	48	44	51	46	42	49	44	41	46	42	39	37
9	63	52	45	41	61	51	44	40	48	42	39	45	41	37	43	39	36	34
10	59	48	42	37	57	47	41	37	45	39	36	42	38	35	40	36	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25336	25336	25336
5°	24996	25533	25930
10°	25425	26068	26350
15°	26127	26516	26558
20°	26246	26542	26099
25°	25642	25926	25359
30°	24277	24551	23843
35°	22068	22068	21611
40°	18151	17969	17583
45°	10852	12754	10350
50°	3509	7108	3292
55°	1241	2380	1241
60°	80	672	39
65°	46	46	0
70°	57	0	0
75°	0	0	0
80°	0	0	0
85°	222	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 12754 cd/sqm



TEST NUMBER: P645137

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	4.8
10°-20°	558.4	14.3
20°-30°	826.3	21.1
30°-40°	854.1	21.8
40°-50°	497.0	12.7
50°-60°	84.2	2.1
60°-70°	3.3	0.1
70°-80°	0.5	0.0
80°-90°	0.8	0.0
90°-100°	20.7	0.5
100°-110°	147.4	3.8
110°-120°	200.2	5.1
120°-130°	162.9	4.2
130°-140°	131.0	3.3
140°-150°	103.3	2.6
150°-160°	75.5	1.9
160°-170°	46.9	1.2
170°-180°	16.0	0.4
0°-30°	1573.4	40.2
0°-40°	2427.5	62.0
0°-60°	3008.7	76.8
0°-90°	3013.3	76.9
90°-120°	368.3	9.4
90°-150°	765.5	19.5
90°-180°	904.0	23.1
0°-180°	3917.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1962	1962	1962	1962	1962	
5°	1928	1979	1969	1974	2000	185
15°	1954	2023	1983	1972	1986	550
25°	1799	1859	1819	1764	1779	822
35°	1400	1422	1400	1364	1370	857
45°	594	691	698	674	567	459
55°	55	64	106	60	55	61
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	1	2	3	3	1
95°	8	16	8	10	12	9
105°	33	50	192	245	162	35
115°	58	71	165	343	401	58
125°	84	95	156	272	322	74
135°	104	115	157	224	257	80
145°	123	133	158	195	216	77
155°	144	149	161	177	185	66
165°	160	162	165	169	172	45
175°	168	169	168	167	166	16
180°	168	168	168	168	168	

TEST NUMBER: P645137

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1961.5	1961.5	1961.5	1961.5	1961.5
2.5°	1935.8	1974.1	1960.3	1961.7	1971.3
5°	1927.8	1978.7	1969.2	1974.3	1999.8
7.5°	1933.6	1985.1	1983.9	1985.3	2010.2
10°	1938.5	1992.4	1987.5	1986.5	2009.0
12.5°	1948.3	2007.0	1987.5	1985.2	2004.1
15°	1953.8	2022.7	1982.9	1972.5	1986.0
17.5°	1935.2	2011.8	1957.8	1930.1	1935.5
20°	1909.4	1987.3	1930.9	1889.7	1898.7
22.5°	1869.0	1943.3	1892.9	1842.0	1853.4
25°	1799.2	1859.1	1819.1	1764.3	1779.3
27.5°	1700.0	1747.3	1722.0	1668.9	1678.2
30°	1627.7	1666.6	1646.1	1594.1	1598.6
32.5°	1544.4	1577.3	1555.4	1510.7	1510.4
35°	1399.5	1422.0	1399.5	1364.5	1370.5
37.5°	1210.0	1227.0	1204.2	1183.1	1186.1
40°	1076.5	1089.9	1065.7	1045.8	1042.8
42.5°	909.9	947.3	923.6	896.5	900.7
45°	594.1	691.4	698.2	674.4	566.6
47.5°	299.5	405.8	486.0	368.8	264.3
50°	174.6	238.9	353.7	195.3	163.8
52.5°	114.5	141.8	247.1	123.4	108.7
55°	55.1	64.1	105.7	59.6	55.1
57.5°	19.0	29.2	46.9	29.8	21.1
60°	3.1	12.0	26.0	9.0	1.5
62.5°	1.8	3.6	16.2	1.8	0.3
65°	1.5	1.5	1.5	0.0	0.0
67.5°	1.5	1.5	0.0	0.0	0.0
70°	1.5	1.5	0.0	0.0	0.0
72.5°	1.5	1.5	0.0	0.0	0.0
75°	0.0	1.5	0.0	0.0	0.0
77.5°	0.0	1.5	0.0	0.0	0.0
80°	0.0	1.5	0.0	0.0	0.0
82.5°	0.0	1.5	0.0	0.0	0.0
85°	1.5	1.5	0.0	0.0	0.0
87.5°	1.2	1.4	0.4	0.6	0.6
90°	0.0	1.0	2.1	3.2	3.2
92.5°	2.5	3.6	4.7	6.6	7.4
95°	8.5	15.7	8.5	9.6	11.6
97.5°	15.0	30.1	62.2	18.4	15.9
100°	20.1	37.7	124.9	36.8	24.3
102.5°	25.2	43.6	168.9	97.0	53.1
105°	32.8	50.4	191.6	244.7	161.9
107.5°	40.4	53.7	182.9	356.2	333.6
110°	45.5	57.9	177.8	374.3	402.2



TEST NUMBER: P645137

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	50.6	63.0	172.7	363.7	410.7
115°	58.2	70.6	165.1	343.2	401.1
117.5°	66.0	78.3	163.2	321.0	380.6
120°	72.0	83.4	159.8	304.1	366.2
122.5°	76.2	88.4	155.6	289.6	346.7
125°	83.6	95.0	155.6	272.1	321.8
127.5°	89.8	101.3	155.8	251.7	300.8
130°	93.1	105.6	156.6	238.1	284.7
132.5°	97.4	109.8	156.6	232.0	270.3
135°	103.7	115.1	156.6	224.1	257.2
137.5°	109.0	121.2	156.6	215.3	243.6
140°	113.2	124.6	156.6	210.2	236.0
142.5°	117.5	128.0	157.5	204.2	228.4
145°	122.8	133.1	157.7	195.2	215.9
147.5°	129.1	138.2	159.0	188.8	204.7
150°	133.4	141.6	159.8	184.5	197.9
152.5°	137.6	145.0	159.8	181.0	192.0
155°	143.9	149.1	160.9	176.9	185.2
157.5°	149.0	154.0	162.1	174.3	180.4
160°	152.4	156.5	163.0	172.6	177.8
162.5°	155.0	159.1	163.8	171.8	175.3
165°	159.8	161.9	165.1	169.4	172.5
167.5°	162.6	164.4	166.2	168.3	170.2
170°	165.1	166.1	166.2	168.3	169.3
172.5°	166.0	167.8	167.0	167.5	168.5
175°	168.3	169.3	168.3	167.2	166.2
177.5°	168.3	169.1	168.3	168.3	167.4
180°	168.3	168.3	168.3	168.3	168.3

(END OF REPORT)