

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645253

Luminaire Tested: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645253
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2023.2 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 18.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645253
CATALOG NUMBER: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645253

CATALOG NUMBER: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	103	102	100	100	98	97	96	95	94				92	
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86				84	
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78				76	
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71				69	
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65				63	
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59				58	
7	78	67	60	56	76	66	60	55	65	59	55	64	59	55	63	58	54				53	
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50				49	
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46				45	
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43				41	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17014	17014	17014
5°	16786	17145	17412
10°	17074	17506	17695
15°	17545	17807	17833
20°	17625	17823	17526
25°	17219	17410	17028
30°	16302	16487	16011
35°	14819	14819	14512
40°	12189	12068	11806
45°	7289	8565	6949
50°	2355	4773	2210
55°	833	1597	833
60°	54	452	26
65°	31	31	0
70°	38	0	0
75°	0	0	0
80°	0	0	0
85°	148	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 8565 cd/sqm



TEST NUMBER: P645253

CATALOG NUMBER: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.7	6.3
10°-20°	375.0	18.5
20°-30°	554.9	27.4
30°-40°	573.6	28.3
40°-50°	333.7	16.5
50°-60°	56.5	2.8
60°-70°	2.2	0.1
70°-80°	0.3	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1056.6	52.2
0°-40°	1630.2	80.6
0°-60°	2020.4	99.9
0°-90°	2023.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2023.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1317	1317	1317	1317	1317	
5°	1295	1329	1322	1326	1343	124
15°	1312	1358	1332	1325	1334	369
25°	1208	1248	1222	1185	1195	552
35°	940	955	940	916	920	576
45°	399	464	469	453	380	309
55°	37	43	71	40	37	41
65°	1	1	1	0	0	1
75°	0	1	0	0	0	0
85°	1	1	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P645253

CATALOG NUMBER: OMN4DP-SR4F0-50D940-BBM-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1317.2	1317.2	1317.2	1317.2	1317.2
2.5°	1299.9	1325.6	1316.4	1317.3	1323.8
5°	1294.6	1328.7	1322.3	1325.8	1342.9
7.5°	1298.5	1333.0	1332.2	1333.2	1349.9
10°	1301.8	1337.9	1334.7	1334.0	1349.1
12.5°	1308.3	1347.7	1334.7	1333.1	1345.8
15°	1312.0	1358.3	1331.6	1324.6	1333.6
17.5°	1299.5	1351.0	1314.7	1296.1	1299.7
20°	1282.2	1334.5	1296.6	1269.0	1275.0
22.5°	1255.1	1304.9	1271.1	1236.9	1244.6
25°	1208.2	1248.4	1221.6	1184.8	1194.8
27.5°	1141.6	1173.3	1156.4	1120.7	1127.0
30°	1093.0	1119.2	1105.4	1070.5	1073.5
32.5°	1037.1	1059.2	1044.5	1014.5	1014.3
35°	939.8	954.9	939.8	916.3	920.3
37.5°	812.5	824.0	808.6	794.5	796.5
40°	722.9	731.9	715.7	702.2	700.2
42.5°	611.0	636.1	620.2	602.0	604.8
45°	399.0	464.3	468.9	452.8	380.4
47.5°	201.1	272.5	326.4	247.7	177.5
50°	117.2	160.5	237.5	131.1	110.0
52.5°	76.9	95.2	166.0	82.9	73.0
55°	37.0	43.0	70.9	40.0	37.0
57.5°	12.8	19.6	31.5	20.0	14.2
60°	2.1	8.1	17.5	6.1	1.0
62.5°	1.2	2.4	10.9	1.2	0.2
65°	1.0	1.0	1.0	0.0	0.0
67.5°	1.0	1.0	0.0	0.0	0.0
70°	1.0	1.0	0.0	0.0	0.0
72.5°	1.0	1.0	0.0	0.0	0.0
75°	0.0	1.0	0.0	0.0	0.0
77.5°	0.0	1.0	0.0	0.0	0.0
80°	0.0	1.0	0.0	0.0	0.0
82.5°	0.0	1.0	0.0	0.0	0.0
85°	1.0	1.0	0.0	0.0	0.0
87.5°	0.8	0.8	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)