

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331807-830

Luminaire Tested: **S122RDIW-S675D435U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331807-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3819.7 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31
6	66	54	46	40	61	50	43	38	45	39	35	39	34	31	34	30	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25
8	57	44	37	31	53	42	35	30	37	32	27	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	2.6
10°-20°	273.3	7.2
20°-30°	383.7	10.0
30°-40°	418.4	11.0
40°-50°	384.7	10.1
50°-60°	302.2	7.9
60°-70°	197.0	5.2
70°-80°	101.6	2.7
80°-90°	27.7	0.7
90°-100°	18.6	0.5
100°-110°	68.1	1.8
110°-120°	182.0	4.8
120°-130°	300.5	7.9
130°-140°	319.6	8.4
140°-150°	297.0	7.8
150°-160°	238.8	6.3
160°-170°	153.9	4.0
170°-180°	53.0	1.4
0°-30°	756.5	19.8
0°-40°	1174.9	30.8
0°-60°	1861.8	48.7
0°-90°	2188.1	57.3
90°-120°	268.7	7.0
90°-150°	1185.9	31.0
90°-180°	1632.0	42.7
0°-180°	3819.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	0	5	8	10	11	3
95°	26	14	16	18	17	32
105°	122	128	25	29	31	131
115°	232	239	248	71	33	228
125°	328	333	340	343	344	292
135°	405	412	415	419	419	313
145°	470	470	476	479	477	294
155°	518	514	519	521	518	238
165°	545	543	544	547	544	154
175°	558	555	556	558	555	53
180°	557	557	557	557	557	



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.4	11.2	10.1	8.9	7.7	7.2	7.4	7.4	7.6	7.7	7.7
90°	0.4	1.4	2.4	3.4	4.3	5.2	5.9	6.6	7.4	8.0	8.5
92.5°	8.1	8.0	7.9	7.8	7.8	7.9	8.3	8.7	9.0	9.3	9.6
95°	26.2	23.2	20.3	17.3	14.3	13.2	13.9	14.4	15.1	15.7	16.1
97.5°	51.9	43.6	35.3	27.0	18.7	15.3	16.7	18.1	19.6	21.0	21.4
100°	71.4	59.0	46.8	34.5	22.2	16.9	18.4	19.9	21.4	23.0	23.7
102.5°	92.6	90.0	87.4	84.8	82.2	74.6	61.8	49.1	36.4	23.6	24.5
105°	122.4	125.2	127.8	130.5	133.2	122.3	97.9	73.4	49.0	24.6	25.5
107.5°	156.6	158.7	160.9	163.1	165.2	151.7	122.3	93.0	63.7	34.4	33.4
110°	178.4	180.3	182.2	184.1	186.0	174.0	148.1	122.2	96.3	70.5	61.5



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.1	200.8	202.5	204.1	205.8	203.4	197.0	190.6	184.2	177.9	145.2
115°	231.7	233.2	234.7	236.2	237.7	239.6	241.9	244.1	246.3	248.5	207.1
117.5°	260.7	262.4	264.1	265.8	267.5	269.2	270.7	272.2	273.8	275.3	265.3
120°	282.0	283.3	284.6	286.1	287.4	288.9	290.5	292.1	293.7	295.3	296.3
122.5°	300.0	301.4	302.8	304.3	305.7	307.3	309.1	310.8	312.5	314.3	315.0
125°	327.5	328.7	329.9	331.0	332.2	333.6	335.4	337.1	338.7	340.4	341.0
127.5°	352.4	353.7	355.0	356.3	357.6	358.8	360.1	361.4	362.7	363.9	364.9
130°	368.3	369.7	371.1	372.5	373.9	375.1	376.2	377.1	378.1	379.1	380.0
132.5°	384.4	385.5	386.7	388.0	389.2	390.3	391.2	392.3	393.2	394.3	395.1
135°	405.3	406.7	408.1	409.5	411.0	412.1	412.9	413.8	414.5	415.4	416.2
137.5°	426.5	427.4	428.5	429.5	430.5	431.4	432.3	433.3	434.1	435.1	435.9
140°	440.4	441.0	441.8	442.4	443.2	444.0	445.1	446.0	447.0	448.0	448.7
142.5°	451.9	452.6	453.2	453.8	454.5	455.4	456.5	457.6	458.7	459.9	460.6
145°	470.1	470.0	470.0	469.9	469.8	470.5	472.0	473.5	475.0	476.5	477.2
147.5°	486.0	485.7	485.3	485.0	484.7	485.2	486.7	488.2	489.7	491.3	491.7
150°	496.3	495.7	495.0	494.5	493.8	494.2	495.7	497.1	498.5	499.9	500.5
152.5°	505.0	504.4	503.6	502.9	502.2	502.6	503.9	505.3	506.6	508.0	508.5
155°	517.6	516.9	516.0	515.3	514.4	514.6	515.7	516.7	517.8	518.9	519.4
157.5°	527.5	526.9	526.2	525.6	524.9	524.9	525.7	526.4	527.2	527.9	528.5
160°	533.4	532.8	532.3	531.8	531.2	531.2	531.8	532.3	532.8	533.4	534.0
162.5°	538.6	538.0	537.4	537.0	536.4	536.4	536.8	537.2	537.7	538.2	538.9
165°	545.4	545.0	544.4	543.8	543.3	543.2	543.5	543.8	544.0	544.2	544.9
167.5°	550.6	550.1	549.6	549.0	548.5	548.4	548.6	548.8	549.1	549.3	550.0
170°	553.6	553.0	552.4	552.0	551.4	551.2	551.4	551.6	551.8	552.0	552.5
172.5°	555.4	555.0	554.4	553.8	553.3	553.2	553.3	553.5	553.6	553.8	554.5
175°	558.0	557.3	556.7	556.1	555.4	555.3	555.4	555.6	555.7	555.9	556.6
177.5°	558.4	557.9	557.3	556.9	556.4	556.1	556.2	556.3	556.4	556.4	556.9
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	7.6	7.5	7.4	7.4	7.4	7.4	7.5	7.5
90°	9.0	9.4	9.8	10.2	10.4	10.6	10.7	10.8
92.5°	9.8	10.1	10.3	10.5	10.6	10.7	10.7	10.8
95°	16.6	17.1	17.5	17.7	17.6	17.5	17.4	17.3
97.5°	21.8	22.1	22.4	22.7	22.8	22.9	23.0	23.1
100°	24.4	25.1	25.8	26.3	26.5	26.7	26.8	27.0
102.5°	25.4	26.4	27.3	27.9	28.2	28.5	28.7	28.9
105°	26.6	27.5	28.6	29.2	29.5	29.9	30.3	30.6
107.5°	32.4	31.4	30.3	30.1	30.4	30.8	31.1	31.5
110°	52.6	43.6	34.7	30.3	30.7	31.1	31.5	31.9



TEST NUMBER: P331807-830

CATALOG NUMBER: S122RDIW-S675D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.5	79.8	47.2	31.0	31.3	31.6	31.9	32.1
115°	165.7	124.2	82.8	58.8	52.4	45.9	39.5	33.0
117.5°	255.2	245.2	235.2	219.6	198.4	177.2	156.1	134.9
120°	297.5	298.5	299.6	294.1	282.0	269.9	257.8	245.7
122.5°	315.6	316.2	316.9	316.0	313.7	311.3	309.0	306.6
125°	341.7	342.3	342.9	343.4	343.7	343.9	344.2	344.4
127.5°	365.8	366.6	367.6	368.1	368.2	368.2	368.3	368.3
130°	381.1	382.0	383.0	383.5	383.4	383.3	383.2	383.1
132.5°	396.0	396.7	397.6	397.9	397.8	397.8	397.8	397.7
135°	417.2	418.0	419.0	419.2	419.1	419.0	418.8	418.6
137.5°	436.9	437.7	438.6	438.8	438.6	438.3	438.0	437.6
140°	449.6	450.4	451.2	451.4	450.9	450.4	450.1	449.6
142.5°	461.4	462.1	462.9	463.0	462.5	462.1	461.7	461.2
145°	477.9	478.4	479.1	479.2	478.7	478.2	477.9	477.4
147.5°	492.2	492.7	493.1	493.1	492.8	492.4	492.0	491.6
150°	501.1	501.5	502.1	502.2	501.7	501.2	500.8	500.4
152.5°	509.1	509.6	510.2	510.1	509.5	509.0	508.3	507.7
155°	520.0	520.5	521.0	520.9	520.2	519.5	518.8	518.1
157.5°	529.1	529.7	530.4	530.3	529.6	528.9	528.2	527.5
160°	534.4	535.0	535.6	535.5	534.9	534.2	533.6	533.0
162.5°	539.4	540.1	540.6	540.5	539.8	539.0	538.3	537.5
165°	545.5	546.1	546.8	546.8	546.1	545.5	544.9	544.2
167.5°	550.6	551.2	551.9	551.8	550.9	550.2	549.3	548.6
170°	553.2	553.8	554.4	554.3	553.6	552.7	552.0	551.1
172.5°	555.1	555.7	556.4	556.3	555.4	554.7	553.8	553.1
175°	557.2	557.8	558.5	558.4	557.4	556.6	555.6	554.8
177.5°	557.4	557.9	558.5	558.4	557.7	557.0	556.4	555.8
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8

(END OF REPORT)