

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331603-930

Luminaire Tested: **S122DIW-S1005D1240U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331603-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7629.3 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.8	2.0
10°-20°	450.1	5.9
20°-30°	653.3	8.6
30°-40°	689.3	9.0
40°-50°	610.4	8.0
50°-60°	487.1	6.4
60°-70°	331.1	4.3
70°-80°	169.7	2.2
80°-90°	44.3	0.6
90°-100°	46.0	0.6
100°-110°	168.6	2.2
110°-120°	450.7	5.9
120°-130°	744.0	9.8
130°-140°	791.2	10.4
140°-150°	735.4	9.6
150°-160°	591.2	7.7
160°-170°	381.0	5.0
170°-180°	131.1	1.7
0°-30°	1258.2	16.5
0°-40°	1947.5	25.5
0°-60°	3045.0	39.9
0°-90°	3590.1	47.1
90°-120°	665.3	8.7
90°-150°	2935.8	38.5
90°-180°	4039.0	52.9
0°-180°	7629.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	27	1	27	1	27	14
95°	43	65	43	65	43	40
105°	76	303	76	303	76	79
115°	82	574	82	574	82	205
125°	853	811	853	811	853	738
135°	1036	1003	1036	1003	1036	799
145°	1182	1164	1182	1164	1182	739
155°	1282	1282	1282	1282	1282	592
165°	1347	1350	1347	1350	1347	380
175°	1373	1381	1373	1381	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	18.3	18.3	18.7	18.1	18.0	18.3	18.2	17.4	17.7	18.0	18.1
90°	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2	21.0	20.0	18.2
92.5°	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3	23.7	23.2	22.3
95°	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1	40.0	38.9	37.3
97.5°	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8	52.9	52.1	48.5
100°	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4	58.6	56.8	53.1
102.5°	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0	60.7	58.5	89.9
105°	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7	63.3	60.8	121.3
107.5°	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2	82.7	85.2	157.8
110°	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2	152.4	174.6	238.6



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5	359.4	440.2	456.1
115°	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1	512.7	615.4	609.8
117.5°	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9	656.7	681.6	677.8
120°	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4	733.7	731.0	727.1
122.5°	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3	779.7	778.1	773.8
125°	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9	844.3	842.8	838.5
127.5°	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5	903.3	901.0	897.8
130°	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4	940.9	938.5	936.0
132.5°	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2	978.0	976.0	973.5
135°	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7	1030.5	1028.3	1026.2
137.5°	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4	1079.3	1077.1	1074.8
140°	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0	1111.0	1109.1	1106.6
142.5°	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2	1140.4	1138.6	1135.7
145°	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9	1181.4	1179.8	1176.1
147.5°	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5	1217.3	1216.1	1212.4
150°	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3	1239.0	1237.7	1234.1
152.5°	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3	1259.0	1257.6	1254.3
155°	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2	1285.9	1284.6	1281.9
157.5°	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9	1308.4	1306.9	1305.0
160°	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1	1321.8	1320.5	1319.2
162.5°	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5	1333.9	1332.4	1331.3
165°	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4	1346.7
167.5°	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0	1361.5	1359.9	1359.3
170°	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5	1367.9	1366.4	1365.9
172.5°	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2	1372.6	1371.1	1370.7
175°	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4	1377.9	1376.3	1375.9
177.5°	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0	1378.8	1377.5	1377.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	18.3	17.9	17.5	18.2	16.1	15.7	13.2	11.2	11.2	11.2	10.7
90°	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1	19.9	19.7	19.5
95°	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8	57.5	50.2	42.9
97.5°	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7	108.0	87.4	66.9
100°	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5	146.2	115.8	85.4
102.5°	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2	222.7	216.3	209.9
105°	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2	309.8	316.5	323.1
107.5°	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6	392.9	398.3	403.7
110°	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8	446.5	451.1	455.8





TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8	497.0	501.1	505.2
115°	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5	577.2	581.0	584.7
117.5°	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5	649.7	653.9	658.1
120°	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1	701.5	704.7	708.1
122.5°	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8	746.3	749.8	753.3
125°	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8	813.7	816.6	819.5
127.5°	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5	875.6	878.8	882.1
130°	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6	915.1	918.7	922.2
132.5°	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5	954.5	957.5	960.5
135°	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3	1006.8	1010.4	1013.9
137.5°	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7	1058.3	1060.7	1063.2
140°	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1	1091.8	1093.6	1095.4
142.5°	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8	1120.4	1122.0	1123.6
145°	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8	1163.7	1163.4	1163.2
147.5°	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1	1202.3	1201.5	1200.6
150°	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7	1227.2	1225.6	1224.0
152.5°	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3	1248.5	1246.8	1245.0
155°	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6	1279.5	1277.6	1275.5
157.5°	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1	1304.4	1302.7	1301.1
160°	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1319.2	1317.8	1316.5
162.5°	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3	1331.9	1330.6	1329.3
165°	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4	1349.1	1347.7	1346.4
167.5°	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2	1361.8	1360.5	1359.2
170°	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4	1369.0	1367.7	1366.4
172.5°	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1	1373.8	1372.5	1371.1
175°	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3	1379.7	1378.2	1376.6
177.5°	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3	1381.0	1379.8	1378.6
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	10.7	10.6	10.4	10.8	10.6	10.5	10.2	10.4	10.7	9.9	10.0
90°	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2	23.2	24.4	25.2
92.5°	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3	24.9	25.4	25.8
95°	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1	42.2	43.3	43.8
97.5°	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8	54.7	55.6	56.2
100°	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4	62.1	63.9	65.1
102.5°	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0	65.4	67.7	69.1
105°	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7	68.2	70.6	72.2
107.5°	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2	77.7	75.3	74.4
110°	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2	108.0	85.9	75.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5	197.7	116.8	76.7
115°	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1	307.5	204.9	145.6
117.5°	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9	607.1	582.3	543.6
120°	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4	739.0	741.7	728.1
122.5°	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3	782.9	784.5	782.4
125°	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9	847.4	849.0	850.0
127.5°	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5	907.8	910.0	911.3
130°	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4	945.8	948.2	949.3
132.5°	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2	982.2	984.3	985.2
135°	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7	1034.9	1037.1	1038.0
137.5°	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4	1083.6	1085.8	1086.5
140°	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0	1115.0	1117.0	1117.4
142.5°	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2	1144.0	1145.8	1146.1
145°	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9	1184.5	1186.0	1186.3
147.5°	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5	1219.6	1220.7	1220.8
150°	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3	1241.7	1243.0	1243.1
152.5°	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3	1261.6	1263.0	1262.9
155°	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2	1288.6	1289.9	1289.6
157.5°	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9	1311.4	1313.0	1312.8
160°	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1	1324.5	1325.8	1325.7
162.5°	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5	1336.9	1338.5	1338.2
165°	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6
167.5°	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0	1364.6	1366.1	1366.0
170°	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5	1371.0	1372.6	1372.3
172.5°	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2	1375.7	1377.3	1377.1
175°	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4	1381.0	1382.5	1382.2
177.5°	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0	1381.2	1382.5	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	10.1	9.7	9.8	9.4	9.8	9.7	10.1	10.0	9.9	10.7	10.4
90°	25.6	26.0	26.5	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2
92.5°	26.1	26.4	26.7	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3
95°	43.5	43.3	43.1	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1
97.5°	56.4	56.7	57.0	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8
100°	65.5	66.0	66.4	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4
102.5°	69.7	70.4	71.0	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0
105°	73.1	74.0	74.9	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7
107.5°	75.3	76.2	77.1	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2
110°	76.1	77.0	77.9	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	77.5	78.2	78.8	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5
115°	129.6	113.7	97.8	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1
117.5°	491.2	438.8	386.4	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9
120°	698.1	668.2	638.3	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4
122.5°	776.6	770.8	765.0	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3
125°	850.7	851.4	852.1	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9
127.5°	911.3	911.5	911.6	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5
130°	949.1	948.9	948.7	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4
132.5°	985.0	984.8	984.6	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2
135°	1037.5	1037.1	1036.7	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7
137.5°	1085.7	1085.0	1084.3	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4
140°	1116.3	1115.2	1114.1	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0
142.5°	1145.1	1143.9	1142.8	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2
145°	1185.1	1184.1	1182.9	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9
147.5°	1219.9	1219.0	1218.1	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5
150°	1242.0	1240.9	1239.7	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3
152.5°	1261.4	1260.0	1258.5	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3
155°	1287.8	1286.1	1284.3	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2
157.5°	1311.1	1309.4	1307.7	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9
160°	1324.1	1322.6	1321.0	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1
162.5°	1336.4	1334.4	1332.5	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5
165°	1352.0	1350.5	1348.9	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5
167.5°	1363.9	1362.0	1359.9	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0
170°	1370.4	1368.3	1366.4	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5
172.5°	1375.1	1373.1	1371.1	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2
175°	1380.0	1377.8	1375.5	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4
177.5°	1380.7	1379.1	1377.5	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	10.2	10.5	10.6	10.8	10.4	10.6	10.7	10.7	11.2	11.2	11.2
90°	21.0	20.0	18.2	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0
92.5°	23.7	23.2	22.3	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1
95°	40.0	38.9	37.3	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8
97.5°	52.9	52.1	48.5	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7
100°	58.6	56.8	53.1	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5
102.5°	60.7	58.5	89.9	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2
105°	63.3	60.8	121.3	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2
107.5°	82.7	85.2	157.8	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6
110°	152.4	174.6	238.6	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	440.2	456.1	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8
115°	512.7	615.4	609.8	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5
117.5°	656.7	681.6	677.8	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5
120°	733.7	731.0	727.1	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1
122.5°	779.7	778.1	773.8	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8
125°	844.3	842.8	838.5	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8
127.5°	903.3	901.0	897.8	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5
130°	940.9	938.5	936.0	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6
132.5°	978.0	976.0	973.5	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5
135°	1030.5	1028.3	1026.2	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3
137.5°	1079.3	1077.1	1074.8	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7
140°	1111.0	1109.1	1106.6	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1
142.5°	1140.4	1138.6	1135.7	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8
145°	1181.4	1179.8	1176.1	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8
147.5°	1217.3	1216.1	1212.4	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1
150°	1239.0	1237.7	1234.1	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7
152.5°	1259.0	1257.6	1254.3	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3
155°	1285.9	1284.6	1281.9	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6
157.5°	1308.4	1306.9	1305.0	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1
160°	1321.8	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5
162.5°	1333.9	1332.4	1331.3	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3
165°	1348.9	1347.4	1346.7	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4
167.5°	1361.5	1359.9	1359.3	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2
170°	1367.9	1366.4	1365.9	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4
172.5°	1372.6	1371.1	1370.7	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1
175°	1377.9	1376.3	1375.9	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3
177.5°	1378.8	1377.5	1377.3	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	13.2	15.7	16.1	18.2	17.5	17.9	18.3	18.1	18.0	17.7	17.4
90°	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2
92.5°	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3
95°	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1
97.5°	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8
100°	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4
102.5°	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0
105°	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7
107.5°	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2
110°	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2





TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5
115°	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1
117.5°	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9
120°	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4
122.5°	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3
125°	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9
127.5°	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5
130°	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4
132.5°	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2
135°	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7
137.5°	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4
140°	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0
142.5°	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2
145°	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9
147.5°	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5
150°	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3
152.5°	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3
155°	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2
157.5°	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9
160°	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1
162.5°	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5
165°	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5
167.5°	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0
170°	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5
172.5°	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2
175°	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4
177.5°	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	18.2	18.3	18.0	18.1	18.7	18.3	18.3
90°	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	108.0	85.9	75.3	76.1	77.0	77.9	78.8



TEST NUMBER: P331603-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)