

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P78156

Luminaire Tested: **DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W**

Issue Date: 02/20/2024

**Test Information**


Test Method: LM-79-08  
Report Number: P78156  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 02/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W  
Description: Define Geo Ring 3ft Diameter Direct/Indirect Fixture w/ Frosted Lens  
for Downlight and Bat-Wing Lens for UPLIGHT  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13847.3 lumens  
Efficiency: N/A  
Efficacy: 70.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.21  
Luminous Opening: Circular (Dia: 3' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 197.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P78156  
CATALOG NUMBER: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W

### Luminous Intensity Polar Plot





TEST NUMBER: P78156

CATALOG NUMBER: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    |    |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |    |    | 0  |    |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0  |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 105 | 105 | 105 | 105 | 96 | 96 | 96 | 96 | 78 | 78 | 78 | 62 | 62 | 62 | 47 | 47 | 47 | 47 | 47 | 47 | 41 |
| 1   | 96  | 91  | 88  | 84  | 87 | 83 | 80 | 77 | 68 | 66 | 64 | 55 | 53 | 52 | 42 | 41 | 40 | 40 | 40 | 40 | 34 |
| 2   | 87  | 80  | 74  | 69  | 79 | 73 | 68 | 64 | 60 | 56 | 53 | 48 | 46 | 43 | 37 | 35 | 34 | 34 | 34 | 34 | 29 |
| 3   | 80  | 70  | 63  | 58  | 72 | 64 | 58 | 53 | 53 | 49 | 45 | 43 | 40 | 37 | 33 | 31 | 29 | 29 | 29 | 29 | 25 |
| 4   | 73  | 62  | 55  | 49  | 66 | 57 | 50 | 45 | 47 | 42 | 38 | 38 | 35 | 32 | 30 | 27 | 25 | 25 | 25 | 25 | 21 |
| 5   | 67  | 56  | 48  | 42  | 61 | 51 | 44 | 39 | 42 | 37 | 33 | 34 | 30 | 27 | 27 | 24 | 22 | 22 | 22 | 22 | 19 |
| 6   | 62  | 50  | 42  | 36  | 56 | 46 | 39 | 34 | 38 | 33 | 29 | 31 | 27 | 24 | 24 | 22 | 19 | 19 | 19 | 19 | 16 |
| 7   | 57  | 45  | 37  | 32  | 52 | 41 | 35 | 30 | 35 | 29 | 25 | 28 | 24 | 21 | 22 | 19 | 17 | 17 | 17 | 17 | 15 |
| 8   | 53  | 41  | 33  | 28  | 48 | 38 | 31 | 26 | 32 | 26 | 23 | 26 | 22 | 19 | 20 | 18 | 16 | 16 | 16 | 16 | 13 |
| 9   | 49  | 37  | 30  | 25  | 45 | 34 | 28 | 23 | 29 | 24 | 20 | 24 | 20 | 17 | 19 | 16 | 14 | 14 | 14 | 14 | 12 |
| 10  | 46  | 34  | 27  | 22  | 42 | 32 | 25 | 21 | 27 | 22 | 18 | 22 | 18 | 16 | 18 | 15 | 13 | 13 | 13 | 13 | 11 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |      |
|-----|------|
|     | 0°   |
| 0°  | 3714 |
| 5°  | 3703 |
| 10° | 3651 |
| 15° | 3564 |
| 20° | 3444 |
| 25° | 3305 |
| 30° | 3145 |
| 35° | 2983 |
| 40° | 2820 |
| 45° | 2670 |
| 50° | 2532 |
| 55° | 2414 |
| 60° | 2310 |
| 65° | 2217 |
| 70° | 2127 |
| 75° | 2013 |
| 80° | 1875 |
| 85° | 1462 |



TEST NUMBER: P78156  
 CATALOG NUMBER: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 229.2   | 1.7       |
| 10°-20°   | 635.5   | 4.6       |
| 20°-30°   | 904.1   | 6.5       |
| 30°-40°   | 1002.9  | 7.2       |
| 40°-50°   | 958.4   | 6.9       |
| 50°-60°   | 815.7   | 5.9       |
| 60°-70°   | 610.7   | 4.4       |
| 70°-80°   | 363.3   | 2.6       |
| 80°-90°   | 101.9   | 0.7       |
| 90°-100°  | 163.7   | 1.2       |
| 100°-110° | 596.7   | 4.3       |
| 110°-120° | 1266.9  | 9.1       |
| 120°-130° | 1710.7  | 12.4      |
| 130°-140° | 1643.9  | 11.9      |
| 140°-150° | 1301.6  | 9.4       |
| 150°-160° | 886.3   | 6.4       |
| 160°-170° | 498.1   | 3.6       |
| 170°-180° | 157.5   | 1.1       |
| 0°-30°    | 1768.8  | 12.8      |
| 0°-40°    | 2771.8  | 20.0      |
| 0°-60°    | 4545.9  | 32.8      |
| 0°-90°    | 5621.8  | 40.6      |
| 90°-120°  | 2027.4  | 14.6      |
| 90°-150°  | 6683.6  | 48.3      |
| 90°-180°  | 8226.0  | 59.4      |
| 0°-180°   | 13847.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 2439 |      |
| 5°   | 2422 | 229  |
| 15°  | 2261 | 636  |
| 25°  | 1967 | 904  |
| 35°  | 1604 | 1003 |
| 45°  | 1240 | 958  |
| 55°  | 909  | 816  |
| 65°  | 615  | 611  |
| 75°  | 342  | 363  |
| 85°  | 84   | 97   |
| 90°  | 7    | 16   |
| 95°  | 146  | 153  |
| 105° | 549  | 597  |
| 115° | 1288 | 1267 |
| 125° | 1930 | 1711 |
| 135° | 2135 | 1644 |
| 145° | 2072 | 1302 |
| 155° | 1908 | 886  |
| 165° | 1747 | 498  |
| 175° | 1635 | 158  |
| 180° | 1620 |      |



TEST NUMBER: P78156  
CATALOG NUMBER: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 2439.2 |
| 2.5°   | 2435.5 |
| 5°     | 2422.5 |
| 7.5°   | 2396.4 |
| 10°    | 2361.1 |
| 12.5°  | 2314.6 |
| 15°    | 2260.7 |
| 17.5°  | 2197.5 |
| 20°    | 2125.0 |
| 22.5°  | 2048.8 |
| 25°    | 1967.0 |
| 27.5°  | 1879.6 |
| 30°    | 1788.5 |
| 32.5°  | 1695.5 |
| 35°    | 1604.4 |
| 37.5°  | 1511.5 |
| 40°    | 1418.5 |
| 42.5°  | 1331.1 |
| 45°    | 1240.0 |
| 47.5°  | 1154.5 |
| 50°    | 1069.0 |
| 52.5°  | 989.1  |
| 55°    | 909.1  |
| 57.5°  | 836.6  |
| 60°    | 758.5  |
| 62.5°  | 687.9  |
| 65°    | 615.4  |
| 67.5°  | 546.6  |
| 70°    | 477.8  |
| 72.5°  | 410.9  |
| 75°    | 342.1  |
| 77.5°  | 278.9  |
| 80°    | 213.8  |
| 82.5°  | 148.7  |
| 85°    | 83.7   |
| 87.5°  | 31.6   |
| 90°    | 7.3    |
| 92.5°  | 73.2   |
| 95°    | 146.4  |
| 97.5°  | 222.1  |
| 100°   | 312.4  |
| 102.5° | 417.3  |
| 105°   | 549.1  |
| 107.5° | 702.8  |
| 110°   | 878.5  |



TEST NUMBER: P78156  
CATALOG NUMBER: DFN2DIP-RG3F0-060D090US927-FLL-OOB-1DUDD-W

**CANDELA DISTRIBUTION (continued):**

|        | 0°     |
|--------|--------|
| 112.5° | 1078.6 |
| 115°   | 1288.5 |
| 117.5° | 1486.1 |
| 120°   | 1666.7 |
| 122.5° | 1818.0 |
| 125°   | 1930.2 |
| 127.5° | 2020.5 |
| 130°   | 2081.5 |
| 132.5° | 2118.1 |
| 135°   | 2135.2 |
| 137.5° | 2135.2 |
| 140°   | 2127.9 |
| 142.5° | 2105.9 |
| 145°   | 2071.8 |
| 147.5° | 2037.6 |
| 150°   | 1996.1 |
| 152.5° | 1952.2 |
| 155°   | 1908.3 |
| 157.5° | 1866.8 |
| 160°   | 1827.7 |
| 162.5° | 1786.3 |
| 165°   | 1747.2 |
| 167.5° | 1710.6 |
| 170°   | 1681.3 |
| 172.5° | 1654.5 |
| 175°   | 1635.0 |
| 177.5° | 1622.8 |
| 180°   | 1620.3 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

NEO-RAY

Report Number: SP1-2401-290-1

Test Date: 01/18/2024

Luminaire Tested: RNG2DIP-RG2F0-020D020US927-FLL-FLL-1-D-UDD-W

Data in this report applies to families of products including RNG2DIP-RG2F0-020D020US927-FLL-FLL-1-D-UDD-W.



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2401-290-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 01/19/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: **RNG2DIP-RG2F0-020D020US927-FLL-FLL-1-D-UDD-W**  
 Description: 2' RING DIRECT/INDIRECT FIXTURE WITH FROSTED LIGHT LEVEL 1

**Spectral Parameters**

CCT (K): 2655  
 CIE u': 0.2643  
 CIE v': 0.5293  
 Duv: 0.0008  
 CIE x: 0.4648  
 CIE y: 0.4137  
 CIE z: 0.1215  
 Peak Wavelength (nm): 625  
 Dominant Wavelength (nm): 584  
 Purity: 63.9

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 93.4 |      |      |
| R1:       | 93.4 | R9:  | 59.7 |
| R2:       | 96.8 | R10: | 92.1 |
| R3:       | 99.2 | R11: | 95.8 |
| R4:       | 94.0 | R12: | 87.6 |
| R5:       | 93.5 | R13: | 94.3 |
| R6:       | 97.2 | R14: | 98.8 |
| R7:       | 91.9 |      |      |
| R8:       | 81.5 |      |      |

Rf: 93.2  
 Rg: 98.9



**Test Conditions**


Stabilization Time: 23M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/15%  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2401-290-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 8/9/2023         | 2/9/2024             |
| Power Meter                    | XITRON 2801 IN0071    | 10/23/2023       | 10/23/2024           |
| AC Power Source                | CHROMA 61603 IN0063   | 10/24/2023       | 10/24/2024           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | ONSET IN0085          | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | ONSET IN0046          | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2401-290-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2401-290-1

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1543          | NR            | 490    | 19797         | NR            | 620    | 85353         | NR            | 750    | 8090          | NR            | 880    | 1792          | NR            |
| 365    | 1414          | NR            | 495    | 23402         | NR            | 625    | 85989         | NR            | 755    | 7198          | NR            | 885    | 2020          | NR            |
| 370    | 1551          | NR            | 500    | 26949         | NR            | 630    | 85515         | NR            | 760    | 6225          | NR            | 890    | 1828          | NR            |
| 375    | 1796          | NR            | 505    | 29825         | NR            | 635    | 83747         | NR            | 765    | 5688          | NR            | 895    | 1860          | NR            |
| 380    | 1726          | NR            | 510    | 32000         | NR            | 640    | 81402         | NR            | 770    | 5021          | NR            | 900    | 1911          | NR            |
| 385    | 1466          | NR            | 515    | 33805         | NR            | 645    | 78259         | NR            | 775    | 4504          | NR            | 905    | 1780          | NR            |
| 390    | 1558          | NR            | 520    | 35652         | NR            | 650    | 74273         | NR            | 780    | 3834          | NR            | 910    | 1898          | NR            |
| 395    | 1442          | NR            | 525    | 37021         | NR            | 655    | 70182         | NR            | 785    | 3465          | NR            | 915    | 1803          | NR            |
| 400    | 1203          | NR            | 530    | 38939         | NR            | 660    | 65368         | NR            | 790    | 3329          | NR            | 920    | 1835          | NR            |
| 405    | 1067          | NR            | 535    | 40941         | NR            | 665    | 60328         | NR            | 795    | 2970          | NR            | 925    | 1737          | NR            |
| 410    | 1017          | NR            | 540    | 42696         | NR            | 670    | 55011         | NR            | 800    | 2874          | NR            | 930    | 1738          | NR            |
| 415    | 1324          | NR            | 545    | 44809         | NR            | 675    | 49838         | NR            | 805    | 2736          | NR            | 935    | 2125          | NR            |
| 420    | 1972          | NR            | 550    | 46959         | NR            | 680    | 44927         | NR            | 810    | 2648          | NR            | 940    | 1637          | NR            |
| 425    | 3033          | NR            | 555    | 49260         | NR            | 685    | 40277         | NR            | 815    | 2400          | NR            | 945    | 1569          | NR            |
| 430    | 4609          | NR            | 560    | 51165         | NR            | 690    | 35795         | NR            | 820    | 2470          | NR            | 950    | 1938          | NR            |
| 435    | 7105          | NR            | 565    | 53562         | NR            | 695    | 31683         | NR            | 825    | 2425          | NR            | 955    | 1864          | NR            |
| 440    | 11197         | NR            | 570    | 56177         | NR            | 700    | 27880         | NR            | 830    | 2392          | NR            | 960    | 2093          | NR            |
| 445    | 18973         | NR            | 575    | 58898         | NR            | 705    | 24664         | NR            | 835    | 1867          | NR            | 965    | 2277          | NR            |
| 450    | 27311         | NR            | 580    | 62115         | NR            | 710    | 21670         | NR            | 840    | 1912          | NR            | 970    | 2629          | NR            |
| 455    | 25348         | NR            | 585    | 65028         | NR            | 715    | 19241         | NR            | 845    | 1927          | NR            | 975    | 2541          | NR            |
| 460    | 18677         | NR            | 590    | 68395         | NR            | 720    | 16927         | NR            | 850    | 2066          | NR            | 980    | 2508          | NR            |
| 465    | 16400         | NR            | 595    | 72374         | NR            | 725    | 14936         | NR            | 855    | 1671          | NR            | 985    | 2238          | NR            |
| 470    | 15032         | NR            | 600    | 75401         | NR            | 730    | 13104         | NR            | 860    | 1946          | NR            | 990    | 2619          | NR            |
| 475    | 13281         | NR            | 605    | 78653         | NR            | 735    | 11394         | NR            | 865    | 2045          | NR            | 995    | 1965          | NR            |
| 480    | 14079         | NR            | 610    | 81994         | NR            | 740    | 10108         | NR            | 870    | 2206          | NR            | 1000   | 3108          | NR            |
| 485    | 16672         | NR            | 615    | 84326         | NR            | 745    | 9008          | NR            | 875    | 1893          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: 4864.8

S/P: 1.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1543          | NR            | 490    | 19797         | NR            | 620    | 85353         | NR            | 750    | 8090          | NR            | 880    | 1792          | NR            |
| 365    | 1414          | NR            | 495    | 23402         | NR            | 625    | 85989         | NR            | 755    | 7198          | NR            | 885    | 2020          | NR            |
| 370    | 1551          | NR            | 500    | 26949         | NR            | 630    | 85515         | NR            | 760    | 6225          | NR            | 890    | 1828          | NR            |
| 375    | 1796          | NR            | 505    | 29825         | NR            | 635    | 83747         | NR            | 765    | 5688          | NR            | 895    | 1860          | NR            |
| 380    | 1726          | NR            | 510    | 32000         | NR            | 640    | 81402         | NR            | 770    | 5021          | NR            | 900    | 1911          | NR            |
| 385    | 1466          | NR            | 515    | 33805         | NR            | 645    | 78259         | NR            | 775    | 4504          | NR            | 905    | 1780          | NR            |
| 390    | 1558          | NR            | 520    | 35652         | NR            | 650    | 74273         | NR            | 780    | 3834          | NR            | 910    | 1898          | NR            |
| 395    | 1442          | NR            | 525    | 37021         | NR            | 655    | 70182         | NR            | 785    | 3465          | NR            | 915    | 1803          | NR            |
| 400    | 1203          | NR            | 530    | 38939         | NR            | 660    | 65368         | NR            | 790    | 3329          | NR            | 920    | 1835          | NR            |
| 405    | 1067          | NR            | 535    | 40941         | NR            | 665    | 60328         | NR            | 795    | 2970          | NR            | 925    | 1737          | NR            |
| 410    | 1017          | NR            | 540    | 42696         | NR            | 670    | 55011         | NR            | 800    | 2874          | NR            | 930    | 1738          | NR            |
| 415    | 1324          | NR            | 545    | 44809         | NR            | 675    | 49838         | NR            | 805    | 2736          | NR            | 935    | 2125          | NR            |
| 420    | 1972          | NR            | 550    | 46959         | NR            | 680    | 44927         | NR            | 810    | 2648          | NR            | 940    | 1637          | NR            |
| 425    | 3033          | NR            | 555    | 49260         | NR            | 685    | 40277         | NR            | 815    | 2400          | NR            | 945    | 1569          | NR            |
| 430    | 4609          | NR            | 560    | 51165         | NR            | 690    | 35795         | NR            | 820    | 2470          | NR            | 950    | 1938          | NR            |
| 435    | 7105          | NR            | 565    | 53562         | NR            | 695    | 31683         | NR            | 825    | 2425          | NR            | 955    | 1864          | NR            |
| 440    | 11197         | NR            | 570    | 56177         | NR            | 700    | 27880         | NR            | 830    | 2392          | NR            | 960    | 2093          | NR            |
| 445    | 18973         | NR            | 575    | 58898         | NR            | 705    | 24664         | NR            | 835    | 1867          | NR            | 965    | 2277          | NR            |
| 450    | 27311         | NR            | 580    | 62115         | NR            | 710    | 21670         | NR            | 840    | 1912          | NR            | 970    | 2629          | NR            |
| 455    | 25348         | NR            | 585    | 65028         | NR            | 715    | 19241         | NR            | 845    | 1927          | NR            | 975    | 2541          | NR            |
| 460    | 18677         | NR            | 590    | 68395         | NR            | 720    | 16927         | NR            | 850    | 2066          | NR            | 980    | 2508          | NR            |
| 465    | 16400         | NR            | 595    | 72374         | NR            | 725    | 14936         | NR            | 855    | 1671          | NR            | 985    | 2238          | NR            |
| 470    | 15032         | NR            | 600    | 75401         | NR            | 730    | 13104         | NR            | 860    | 1946          | NR            | 990    | 2619          | NR            |
| 475    | 13281         | NR            | 605    | 78653         | NR            | 735    | 11394         | NR            | 865    | 2045          | NR            | 995    | 1965          | NR            |
| 480    | 14079         | NR            | 610    | 81994         | NR            | 740    | 10108         | NR            | 870    | 2206          | NR            | 1000   | 3108          | NR            |
| 485    | 16672         | NR            | 615    | 84326         | NR            | 745    | 9008          | NR            | 875    | 1893          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-1

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 1804.6 M/P: 0.47**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1543          | NR            | 490    | 19797         | NR            | 620    | 85353         | NR            | 750    | 8090          | NR            | 880    | 1792          | NR            |
| 365    | 1414          | NR            | 495    | 23402         | NR            | 625    | 85989         | NR            | 755    | 7198          | NR            | 885    | 2020          | NR            |
| 370    | 1551          | NR            | 500    | 26949         | NR            | 630    | 85515         | NR            | 760    | 6225          | NR            | 890    | 1828          | NR            |
| 375    | 1796          | NR            | 505    | 29825         | NR            | 635    | 83747         | NR            | 765    | 5688          | NR            | 895    | 1860          | NR            |
| 380    | 1726          | NR            | 510    | 32000         | NR            | 640    | 81402         | NR            | 770    | 5021          | NR            | 900    | 1911          | NR            |
| 385    | 1466          | NR            | 515    | 33805         | NR            | 645    | 78259         | NR            | 775    | 4504          | NR            | 905    | 1780          | NR            |
| 390    | 1558          | NR            | 520    | 35652         | NR            | 650    | 74273         | NR            | 780    | 3834          | NR            | 910    | 1898          | NR            |
| 395    | 1442          | NR            | 525    | 37021         | NR            | 655    | 70182         | NR            | 785    | 3465          | NR            | 915    | 1803          | NR            |
| 400    | 1203          | NR            | 530    | 38939         | NR            | 660    | 65368         | NR            | 790    | 3329          | NR            | 920    | 1835          | NR            |
| 405    | 1067          | NR            | 535    | 40941         | NR            | 665    | 60328         | NR            | 795    | 2970          | NR            | 925    | 1737          | NR            |
| 410    | 1017          | NR            | 540    | 42696         | NR            | 670    | 55011         | NR            | 800    | 2874          | NR            | 930    | 1738          | NR            |
| 415    | 1324          | NR            | 545    | 44809         | NR            | 675    | 49838         | NR            | 805    | 2736          | NR            | 935    | 2125          | NR            |
| 420    | 1972          | NR            | 550    | 46959         | NR            | 680    | 44927         | NR            | 810    | 2648          | NR            | 940    | 1637          | NR            |
| 425    | 3033          | NR            | 555    | 49260         | NR            | 685    | 40277         | NR            | 815    | 2400          | NR            | 945    | 1569          | NR            |
| 430    | 4609          | NR            | 560    | 51165         | NR            | 690    | 35795         | NR            | 820    | 2470          | NR            | 950    | 1938          | NR            |
| 435    | 7105          | NR            | 565    | 53562         | NR            | 695    | 31683         | NR            | 825    | 2425          | NR            | 955    | 1864          | NR            |
| 440    | 11197         | NR            | 570    | 56177         | NR            | 700    | 27880         | NR            | 830    | 2392          | NR            | 960    | 2093          | NR            |
| 445    | 18973         | NR            | 575    | 58898         | NR            | 705    | 24664         | NR            | 835    | 1867          | NR            | 965    | 2277          | NR            |
| 450    | 27311         | NR            | 580    | 62115         | NR            | 710    | 21670         | NR            | 840    | 1912          | NR            | 970    | 2629          | NR            |
| 455    | 25348         | NR            | 585    | 65028         | NR            | 715    | 19241         | NR            | 845    | 1927          | NR            | 975    | 2541          | NR            |
| 460    | 18677         | NR            | 590    | 68395         | NR            | 720    | 16927         | NR            | 850    | 2066          | NR            | 980    | 2508          | NR            |
| 465    | 16400         | NR            | 595    | 72374         | NR            | 725    | 14936         | NR            | 855    | 1671          | NR            | 985    | 2238          | NR            |
| 470    | 15032         | NR            | 600    | 75401         | NR            | 730    | 13104         | NR            | 860    | 1946          | NR            | 990    | 2619          | NR            |
| 475    | 13281         | NR            | 605    | 78653         | NR            | 735    | 11394         | NR            | 865    | 2045          | NR            | 995    | 1965          | NR            |
| 480    | 14079         | NR            | 610    | 81994         | NR            | 740    | 10108         | NR            | 870    | 2206          | NR            | 1000   | 3108          | NR            |
| 485    | 16672         | NR            | 615    | 84326         | NR            | 745    | 9008          | NR            | 875    | 1893          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-1


TM-30-18

**Summary**

$R_f = 93.2$   
 $R_g = 98.9$   
 CIE  $R_a = 93.4$   
 $R_9 = 59.7$



**Color Vector Graphics**



REPORT NUMBER: SP1-2401-290-1

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 95 | CES51 = 98 | CES76 = 92 |
| CES02 = 64 | CES27 = 95 | CES52 = 99 | CES77 = 89 |
| CES03 = 32 | CES28 = 98 | CES53 = 97 | CES78 = 90 |
| CES04 = 71 | CES29 = 96 | CES54 = 96 | CES79 = 92 |
| CES05 = 52 | CES30 = 97 | CES55 = 95 | CES80 = 93 |
| CES06 = 52 | CES31 = 96 | CES56 = 96 | CES81 = 81 |
| CES07 = 44 | CES32 = 91 | CES57 = 95 | CES82 = 97 |
| CES08 = 43 | CES33 = 98 | CES58 = 96 | CES83 = 95 |
| CES09 = 29 | CES34 = 97 | CES59 = 97 | CES84 = 96 |
| CES10 = 77 | CES35 = 98 | CES60 = 96 | CES85 = 84 |
| CES11 = 60 | CES36 = 89 | CES61 = 95 | CES86 = 83 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 93 |
| CES13 = 44 | CES38 = 94 | CES63 = 95 | CES88 = 95 |
| CES14 = 74 | CES39 = 99 | CES64 = 94 | CES89 = 85 |
| CES15 = 72 | CES40 = 97 | CES65 = 91 | CES90 = 96 |
| CES16 = 49 | CES41 = 97 | CES66 = 93 | CES91 = 85 |
| CES17 = 50 | CES42 = 97 | CES67 = 92 | CES92 = 82 |
| CES18 = 57 | CES43 = 96 | CES68 = 93 | CES93 = 89 |
| CES19 = 72 | CES44 = 99 | CES69 = 94 | CES94 = 80 |
| CES20 = 68 | CES45 = 98 | CES70 = 91 | CES95 = 87 |
| CES21 = 87 | CES46 = 96 | CES71 = 90 | CES96 = 93 |
| CES22 = 79 | CES47 = 93 | CES72 = 96 | CES97 = 96 |
| CES23 = 92 | CES48 = 94 | CES73 = 88 | CES98 = 94 |
| CES24 = 91 | CES49 = 96 | CES74 = 91 | CES99 = 91 |
| CES25 = 72 | CES50 = 99 | CES75 = 91 |            |






REPORT NUMBER: SP1-2401-290-1

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2401-290-1

TM-30-18

Measure Comparisons



(END OF REPORT)