

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331604-930

Luminaire Tested: **S122DIW-S1005D1240U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331604-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7094.6 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.8	2.2
10°-20°	450.1	6.3
20°-30°	653.3	9.2
30°-40°	689.3	9.7
40°-50°	610.4	8.6
50°-60°	487.1	6.9
60°-70°	331.1	4.7
70°-80°	169.7	2.4
80°-90°	45.9	0.6
90°-100°	79.4	1.1
100°-110°	246.5	3.5
110°-120°	421.4	5.9
120°-130°	554.2	7.8
130°-140°	622.0	8.8
140°-150°	609.9	8.6
150°-160°	511.5	7.2
160°-170°	339.3	4.8
170°-180°	118.6	1.7
0°-30°	1258.2	17.7
0°-40°	1947.5	27.5
0°-60°	3045.0	42.9
0°-90°	3591.7	50.6
90°-120°	747.3	10.5
90°-150°	2533.4	35.7
90°-180°	3503.0	49.4
0°-180°	7094.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	36	1	36	1	36	17
95°	66	55	66	55	66	73
105°	235	227	235	227	235	247
115°	423	423	423	423	423	418
125°	617	615	617	615	617	550
135°	806	796	806	796	806	620
145°	977	966	977	966	977	610
155°	1113	1105	1113	1105	1113	512
165°	1203	1202	1203	1202	1203	339
175°	1246	1251	1246	1251	1246	118
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	20.2	20.1	20.6	20.1	20.0	20.5	20.6	20.2	20.8	21.4	20.9
90°	36.0	35.7	35.5	35.2	35.0	35.1	35.6	36.0	36.5	37.0	31.8
92.5°	34.2	34.2	34.2	34.1	34.1	34.0	33.9	33.8	33.7	33.6	32.4
95°	65.6	66.0	66.4	66.9	67.4	67.7	67.7	67.7	67.7	67.7	67.2
97.5°	113.6	113.6	113.7	113.7	113.7	113.7	113.7	113.7	113.7	113.7	112.8
100°	144.8	145.0	145.3	145.5	145.8	145.9	145.9	145.9	145.9	145.9	145.2
102.5°	180.3	180.6	180.8	181.1	181.3	181.3	181.2	180.9	180.8	180.6	179.7
105°	234.7	234.7	234.7	234.7	234.7	234.5	234.0	233.5	233.0	232.6	232.1
107.5°	285.8	286.9	288.0	289.1	290.2	290.7	290.4	290.2	290.1	289.8	289.8
110°	325.6	326.3	327.0	327.8	328.4	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.6	364.2	364.7	365.2	365.7	366.2	366.8	367.4	367.9	368.5	368.7
115°	422.9	423.5	424.3	425.0	425.7	426.2	426.4	426.6	426.9	427.1	427.5
117.5°	479.3	480.0	480.7	481.4	482.2	482.7	483.3	483.9	484.5	485.0	486.3
120°	519.1	519.8	520.5	521.1	521.9	522.2	522.2	522.2	522.2	522.2	524.1
122.5°	558.0	558.5	559.0	559.5	560.0	560.6	561.2	561.7	562.2	562.8	564.1
125°	617.3	617.6	617.8	618.1	618.3	618.8	619.5	620.2	620.9	621.6	622.3
127.5°	671.5	672.3	673.0	673.8	674.5	675.3	676.1	677.0	677.8	678.7	679.6
130°	710.4	711.3	712.3	713.2	714.2	714.9	715.3	715.8	716.2	716.7	717.2
132.5°	747.6	748.4	749.1	749.9	750.6	751.5	752.5	753.6	754.6	755.6	755.5
135°	805.5	806.2	807.0	807.6	808.4	808.9	809.1	809.3	809.5	809.8	809.3
137.5°	858.0	858.9	859.9	860.8	861.8	862.3	862.5	862.7	862.9	863.1	862.4
140°	894.4	895.3	896.3	897.2	898.1	898.5	898.5	898.5	898.5	898.5	897.4
142.5°	927.3	928.3	929.2	930.2	931.1	931.5	931.3	931.1	930.9	930.7	929.9
145°	976.8	977.8	978.7	979.7	980.6	980.9	980.7	980.5	980.2	980.0	978.6
147.5°	1021.0	1021.9	1022.8	1023.7	1024.6	1024.7	1024.3	1023.7	1023.2	1022.7	1021.7
150°	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8	1048.8
152.5°	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8	1075.7
155°	1113.2	1113.9	1114.6	1115.3	1116.0	1115.7	1114.6	1113.5	1112.2	1111.1	1110.4
157.5°	1144.4	1145.6	1146.7	1147.9	1149.0	1148.8	1147.1	1145.6	1143.9	1142.4	1141.9
160°	1163.9	1164.9	1165.8	1166.8	1167.7	1167.4	1166.0	1164.7	1163.2	1161.8	1161.6
162.5°	1180.9	1181.9	1183.1	1184.2	1185.4	1185.1	1183.5	1181.9	1180.3	1178.8	1178.5
165°	1203.1	1204.2	1205.4	1206.6	1207.7	1207.5	1205.8	1204.2	1202.6	1200.9	1200.9
167.5°	1221.2	1222.5	1223.7	1224.9	1226.1	1225.9	1224.3	1222.6	1221.0	1219.3	1219.4
170°	1230.5	1231.9	1233.4	1234.8	1236.2	1236.1	1234.4	1232.7	1231.1	1229.5	1229.7
172.5°	1238.1	1239.6	1241.0	1242.4	1243.7	1243.7	1242.0	1240.4	1238.8	1237.1	1237.3
175°	1246.3	1247.8	1249.2	1250.6	1252.1	1251.9	1250.3	1248.6	1247.0	1245.3	1245.8
177.5°	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2	1250.6
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	20.3	19.3	18.3	18.4	16.4	15.8	13.3	11.2	11.3	11.3	10.9
90°	26.7	21.5	16.3	12.3	9.5	6.7	3.9	1.1	3.9	6.7	9.5
92.5°	31.1	29.9	28.7	27.1	25.0	23.0	20.9	18.8	20.9	23.0	25.0
95°	66.7	66.3	65.8	64.4	62.0	59.7	57.3	55.0	57.3	59.7	62.0
97.5°	111.9	111.0	110.1	108.7	106.6	104.6	102.5	100.4	102.5	104.6	106.6
100°	144.5	143.7	143.1	141.8	139.9	138.0	136.2	134.3	136.2	138.0	139.9
102.5°	178.8	177.9	177.0	175.8	174.3	172.8	171.3	169.7	171.3	172.8	174.3
105°	231.6	231.1	230.7	230.1	229.4	228.7	228.0	227.3	228.0	228.7	229.4
107.5°	289.8	289.8	289.8	289.3	288.3	287.3	286.3	285.2	286.3	287.3	288.3
110°	328.8	328.8	328.8	328.1	326.7	325.2	323.8	322.5	323.8	325.2	326.7





TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.9	369.1	369.2	368.7	367.3	365.8	364.4	363.1	364.4	365.8	367.3
115°	428.0	428.5	428.9	428.5	427.1	425.7	424.3	422.9	424.3	425.7	427.1
117.5°	487.6	488.9	490.3	490.0	488.1	486.2	484.4	482.5	484.4	486.2	488.1
120°	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	524.1	526.0	527.9
122.5°	565.5	566.8	568.1	567.6	565.3	563.1	560.8	558.6	560.8	563.1	565.3
125°	623.1	623.7	624.4	623.7	621.6	619.5	617.3	615.2	617.3	619.5	621.6
127.5°	680.4	681.3	682.1	681.2	678.5	675.8	673.1	670.4	673.1	675.8	678.5
130°	717.7	718.2	718.6	717.3	714.3	711.3	708.2	705.2	708.2	711.3	714.3
132.5°	755.5	755.4	755.3	754.0	751.5	749.0	746.5	744.0	746.5	749.0	751.5
135°	808.9	808.4	807.9	806.4	803.8	801.2	798.6	796.1	798.6	801.2	803.8
137.5°	861.9	861.2	860.6	859.2	857.1	855.0	852.9	850.8	852.9	855.0	857.1
140°	896.3	895.0	893.9	892.3	890.1	888.0	885.9	883.8	885.9	888.0	890.1
142.5°	929.1	928.3	927.5	926.1	924.0	921.9	919.7	917.6	919.7	921.9	924.0
145°	977.1	975.8	974.4	972.8	971.2	969.6	967.9	966.2	967.9	969.6	971.2
147.5°	1020.8	1019.9	1019.0	1017.5	1015.5	1013.5	1011.5	1009.6	1011.5	1013.5	1015.5
150°	1047.9	1046.9	1046.0	1044.8	1043.4	1042.0	1040.6	1039.2	1040.6	1042.0	1043.4
152.5°	1074.6	1073.4	1072.3	1071.1	1069.6	1068.2	1066.8	1065.4	1066.8	1068.2	1069.6
155°	1109.6	1109.0	1108.2	1107.6	1106.9	1106.1	1105.5	1104.7	1105.5	1106.1	1106.9
157.5°	1141.5	1141.1	1140.7	1140.2	1139.8	1139.3	1138.8	1138.3	1138.8	1139.3	1139.8
160°	1161.3	1161.1	1160.9	1160.5	1160.1	1159.6	1159.1	1158.6	1159.1	1159.6	1160.1
162.5°	1178.3	1178.0	1177.8	1177.6	1177.5	1177.5	1177.4	1177.2	1177.4	1177.5	1177.5
165°	1200.9	1200.9	1200.9	1201.0	1201.3	1201.5	1201.8	1202.0	1201.8	1201.5	1201.3
167.5°	1219.4	1219.4	1219.5	1219.9	1220.6	1221.3	1222.0	1222.7	1222.0	1221.3	1220.6
170°	1230.0	1230.2	1230.4	1230.9	1231.6	1232.3	1233.0	1233.7	1233.0	1232.3	1231.6
172.5°	1237.5	1237.8	1238.0	1238.5	1239.2	1239.9	1240.6	1241.3	1240.6	1239.9	1239.2
175°	1246.3	1246.8	1247.2	1247.8	1248.5	1249.2	1249.9	1250.6	1249.9	1249.2	1248.5
177.5°	1250.9	1251.3	1251.7	1252.1	1252.7	1253.3	1253.8	1254.4	1253.8	1253.3	1252.7
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	10.9	11.3	11.8	12.8	13.4	13.9	13.3	13.2	13.1	12.0	12.0
90°	12.3	16.3	21.5	26.7	31.8	37.0	36.5	36.0	35.6	35.1	35.0
92.5°	27.1	28.7	29.9	31.1	32.4	33.6	33.7	33.8	33.9	34.0	34.1
95°	64.4	65.8	66.3	66.7	67.2	67.7	67.7	67.7	67.7	67.7	67.4
97.5°	108.7	110.1	111.0	111.9	112.8	113.7	113.7	113.7	113.7	113.7	113.7
100°	141.8	143.1	143.7	144.5	145.2	145.9	145.9	145.9	145.9	145.9	145.8
102.5°	175.8	177.0	177.9	178.8	179.7	180.6	180.8	180.9	181.2	181.3	181.3
105°	230.1	230.7	231.1	231.6	232.1	232.6	233.0	233.5	234.0	234.5	234.7
107.5°	289.3	289.8	289.8	289.8	289.8	289.8	290.1	290.2	290.4	290.7	290.2
110°	328.1	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.4



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.7	369.2	369.1	368.9	368.7	368.5	367.9	367.4	366.8	366.2	365.7
115°	428.5	428.9	428.5	428.0	427.5	427.1	426.9	426.6	426.4	426.2	425.7
117.5°	490.0	490.3	488.9	487.6	486.3	485.0	484.5	483.9	483.3	482.7	482.2
120°	529.8	529.8	527.9	526.0	524.1	522.2	522.2	522.2	522.2	522.2	521.9
122.5°	567.6	568.1	566.8	565.5	564.1	562.8	562.2	561.7	561.2	560.6	560.0
125°	623.7	624.4	623.7	623.1	622.3	621.6	620.9	620.2	619.5	618.8	618.3
127.5°	681.2	682.1	681.3	680.4	679.6	678.7	677.8	677.0	676.1	675.3	674.5
130°	717.3	718.6	718.2	717.7	717.2	716.7	716.2	715.8	715.3	714.9	714.2
132.5°	754.0	755.3	755.4	755.5	755.5	755.6	754.6	753.6	752.5	751.5	750.6
135°	806.4	807.9	808.4	808.9	809.3	809.8	809.5	809.3	809.1	808.9	808.4
137.5°	859.2	860.6	861.2	861.9	862.4	863.1	862.9	862.7	862.5	862.3	861.8
140°	892.3	893.9	895.0	896.3	897.4	898.5	898.5	898.5	898.5	898.5	898.1
142.5°	926.1	927.5	928.3	929.1	929.9	930.7	930.9	931.1	931.3	931.5	931.1
145°	972.8	974.4	975.8	977.1	978.6	980.0	980.2	980.5	980.7	980.9	980.6
147.5°	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2	1023.7	1024.3	1024.7	1024.6
150°	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6
152.5°	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4
155°	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2	1113.5	1114.6	1115.7	1116.0
157.5°	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9	1145.6	1147.1	1148.8	1149.0
160°	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2	1164.7	1166.0	1167.4	1167.7
162.5°	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3	1181.9	1183.5	1185.1	1185.4
165°	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6	1204.2	1205.8	1207.5	1207.7
167.5°	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0	1222.6	1224.3	1225.9	1226.1
170°	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1	1232.7	1234.4	1236.1	1236.2
172.5°	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8	1240.4	1242.0	1243.7	1243.7
175°	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0	1248.6	1250.3	1251.9	1252.1
177.5°	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	12.1	11.6	11.7	11.2	11.7	11.6	12.1	12.0	12.0	13.1	13.2
90°	35.2	35.5	35.7	36.0	35.7	35.5	35.2	35.0	35.1	35.6	36.0
92.5°	34.1	34.2	34.2	34.2	34.2	34.2	34.1	34.1	34.0	33.9	33.8
95°	66.9	66.4	66.0	65.6	66.0	66.4	66.9	67.4	67.7	67.7	67.7
97.5°	113.7	113.7	113.6	113.6	113.6	113.7	113.7	113.7	113.7	113.7	113.7
100°	145.5	145.3	145.0	144.8	145.0	145.3	145.5	145.8	145.9	145.9	145.9
102.5°	181.1	180.8	180.6	180.3	180.6	180.8	181.1	181.3	181.3	181.2	180.9
105°	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.5	234.0	233.5
107.5°	289.1	288.0	286.9	285.8	286.9	288.0	289.1	290.2	290.7	290.4	290.2
110°	327.8	327.0	326.3	325.6	326.3	327.0	327.8	328.4	328.8	328.8	328.8



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	365.2	364.7	364.2	363.6	364.2	364.7	365.2	365.7	366.2	366.8	367.4
115°	425.0	424.3	423.5	422.9	423.5	424.3	425.0	425.7	426.2	426.4	426.6
117.5°	481.4	480.7	480.0	479.3	480.0	480.7	481.4	482.2	482.7	483.3	483.9
120°	521.1	520.5	519.8	519.1	519.8	520.5	521.1	521.9	522.2	522.2	522.2
122.5°	559.5	559.0	558.5	558.0	558.5	559.0	559.5	560.0	560.6	561.2	561.7
125°	618.1	617.8	617.6	617.3	617.6	617.8	618.1	618.3	618.8	619.5	620.2
127.5°	673.8	673.0	672.3	671.5	672.3	673.0	673.8	674.5	675.3	676.1	677.0
130°	713.2	712.3	711.3	710.4	711.3	712.3	713.2	714.2	714.9	715.3	715.8
132.5°	749.9	749.1	748.4	747.6	748.4	749.1	749.9	750.6	751.5	752.5	753.6
135°	807.6	807.0	806.2	805.5	806.2	807.0	807.6	808.4	808.9	809.1	809.3
137.5°	860.8	859.9	858.9	858.0	858.9	859.9	860.8	861.8	862.3	862.5	862.7
140°	897.2	896.3	895.3	894.4	895.3	896.3	897.2	898.1	898.5	898.5	898.5
142.5°	930.2	929.2	928.3	927.3	928.3	929.2	930.2	931.1	931.5	931.3	931.1
145°	979.7	978.7	977.8	976.8	977.8	978.7	979.7	980.6	980.9	980.7	980.5
147.5°	1023.7	1022.8	1021.9	1021.0	1021.9	1022.8	1023.7	1024.6	1024.7	1024.3	1023.7
150°	1051.9	1051.2	1050.4	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2
152.5°	1079.5	1078.6	1077.7	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6
155°	1115.3	1114.6	1113.9	1113.2	1113.9	1114.6	1115.3	1116.0	1115.7	1114.6	1113.5
157.5°	1147.9	1146.7	1145.6	1144.4	1145.6	1146.7	1147.9	1149.0	1148.8	1147.1	1145.6
160°	1166.8	1165.8	1164.9	1163.9	1164.9	1165.8	1166.8	1167.7	1167.4	1166.0	1164.7
162.5°	1184.2	1183.1	1181.9	1180.9	1181.9	1183.1	1184.2	1185.4	1185.1	1183.5	1181.9
165°	1206.6	1205.4	1204.2	1203.1	1204.2	1205.4	1206.6	1207.7	1207.5	1205.8	1204.2
167.5°	1224.9	1223.7	1222.5	1221.2	1222.5	1223.7	1224.9	1226.1	1225.9	1224.3	1222.6
170°	1234.8	1233.4	1231.9	1230.5	1231.9	1233.4	1234.8	1236.2	1236.1	1234.4	1232.7
172.5°	1242.4	1241.0	1239.6	1238.1	1239.6	1241.0	1242.4	1243.7	1243.7	1242.0	1240.4
175°	1250.6	1249.2	1247.8	1246.3	1247.8	1249.2	1250.6	1252.1	1251.9	1250.3	1248.6
177.5°	1253.6	1252.5	1251.3	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	13.3	13.9	13.4	12.8	11.8	11.3	10.9	10.9	11.3	11.3	11.2
90°	36.5	37.0	31.8	26.7	21.5	16.3	12.3	9.5	6.7	3.9	1.1
92.5°	33.7	33.6	32.4	31.1	29.9	28.7	27.1	25.0	23.0	20.9	18.8
95°	67.7	67.7	67.2	66.7	66.3	65.8	64.4	62.0	59.7	57.3	55.0
97.5°	113.7	113.7	112.8	111.9	111.0	110.1	108.7	106.6	104.6	102.5	100.4
100°	145.9	145.9	145.2	144.5	143.7	143.1	141.8	139.9	138.0	136.2	134.3
102.5°	180.8	180.6	179.7	178.8	177.9	177.0	175.8	174.3	172.8	171.3	169.7
105°	233.0	232.6	232.1	231.6	231.1	230.7	230.1	229.4	228.7	228.0	227.3
107.5°	290.1	289.8	289.8	289.8	289.8	289.8	289.3	288.3	287.3	286.3	285.2
110°	328.8	328.8	328.8	328.8	328.8	328.8	328.1	326.7	325.2	323.8	322.5



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	367.9	368.5	368.7	368.9	369.1	369.2	368.7	367.3	365.8	364.4	363.1
115°	426.9	427.1	427.5	428.0	428.5	428.9	428.5	427.1	425.7	424.3	422.9
117.5°	484.5	485.0	486.3	487.6	488.9	490.3	490.0	488.1	486.2	484.4	482.5
120°	522.2	522.2	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2
122.5°	562.2	562.8	564.1	565.5	566.8	568.1	567.6	565.3	563.1	560.8	558.6
125°	620.9	621.6	622.3	623.1	623.7	624.4	623.7	621.6	619.5	617.3	615.2
127.5°	677.8	678.7	679.6	680.4	681.3	682.1	681.2	678.5	675.8	673.1	670.4
130°	716.2	716.7	717.2	717.7	718.2	718.6	717.3	714.3	711.3	708.2	705.2
132.5°	754.6	755.6	755.5	755.5	755.4	755.3	754.0	751.5	749.0	746.5	744.0
135°	809.5	809.8	809.3	808.9	808.4	807.9	806.4	803.8	801.2	798.6	796.1
137.5°	862.9	863.1	862.4	861.9	861.2	860.6	859.2	857.1	855.0	852.9	850.8
140°	898.5	898.5	897.4	896.3	895.0	893.9	892.3	890.1	888.0	885.9	883.8
142.5°	930.9	930.7	929.9	929.1	928.3	927.5	926.1	924.0	921.9	919.7	917.6
145°	980.2	980.0	978.6	977.1	975.8	974.4	972.8	971.2	969.6	967.9	966.2
147.5°	1023.2	1022.7	1021.7	1020.8	1019.9	1019.0	1017.5	1015.5	1013.5	1011.5	1009.6
150°	1050.4	1049.8	1048.8	1047.9	1046.9	1046.0	1044.8	1043.4	1042.0	1040.6	1039.2
152.5°	1077.7	1076.8	1075.7	1074.6	1073.4	1072.3	1071.1	1069.6	1068.2	1066.8	1065.4
155°	1112.2	1111.1	1110.4	1109.6	1109.0	1108.2	1107.6	1106.9	1106.1	1105.5	1104.7
157.5°	1143.9	1142.4	1141.9	1141.5	1141.1	1140.7	1140.2	1139.8	1139.3	1138.8	1138.3
160°	1163.2	1161.8	1161.6	1161.3	1161.1	1160.9	1160.5	1160.1	1159.6	1159.1	1158.6
162.5°	1180.3	1178.8	1178.5	1178.3	1178.0	1177.8	1177.6	1177.5	1177.5	1177.4	1177.2
165°	1202.6	1200.9	1200.9	1200.9	1200.9	1200.9	1201.0	1201.3	1201.5	1201.8	1202.0
167.5°	1221.0	1219.3	1219.4	1219.4	1219.4	1219.5	1219.9	1220.6	1221.3	1222.0	1222.7
170°	1231.1	1229.5	1229.7	1230.0	1230.2	1230.4	1230.9	1231.6	1232.3	1233.0	1233.7
172.5°	1238.8	1237.1	1237.3	1237.5	1237.8	1238.0	1238.5	1239.2	1239.9	1240.6	1241.3
175°	1247.0	1245.3	1245.8	1246.3	1246.8	1247.2	1247.8	1248.5	1249.2	1249.9	1250.6
177.5°	1251.3	1250.2	1250.6	1250.9	1251.3	1251.7	1252.1	1252.7	1253.3	1253.8	1254.4
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	13.3	15.8	16.4	18.4	18.3	19.3	20.3	20.9	21.4	20.8	20.2
90°	3.9	6.7	9.5	12.3	16.3	21.5	26.7	31.8	37.0	36.5	36.0
92.5°	20.9	23.0	25.0	27.1	28.7	29.9	31.1	32.4	33.6	33.7	33.8
95°	57.3	59.7	62.0	64.4	65.8	66.3	66.7	67.2	67.7	67.7	67.7
97.5°	102.5	104.6	106.6	108.7	110.1	111.0	111.9	112.8	113.7	113.7	113.7
100°	136.2	138.0	139.9	141.8	143.1	143.7	144.5	145.2	145.9	145.9	145.9
102.5°	171.3	172.8	174.3	175.8	177.0	177.9	178.8	179.7	180.6	180.8	180.9
105°	228.0	228.7	229.4	230.1	230.7	231.1	231.6	232.1	232.6	233.0	233.5
107.5°	286.3	287.3	288.3	289.3	289.8	289.8	289.8	289.8	289.8	290.1	290.2
110°	323.8	325.2	326.7	328.1	328.8	328.8	328.8	328.8	328.8	328.8	328.8





TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	364.4	365.8	367.3	368.7	369.2	369.1	368.9	368.7	368.5	367.9	367.4
115°	424.3	425.7	427.1	428.5	428.9	428.5	428.0	427.5	427.1	426.9	426.6
117.5°	484.4	486.2	488.1	490.0	490.3	488.9	487.6	486.3	485.0	484.5	483.9
120°	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	522.2	522.2
122.5°	560.8	563.1	565.3	567.6	568.1	566.8	565.5	564.1	562.8	562.2	561.7
125°	617.3	619.5	621.6	623.7	624.4	623.7	623.1	622.3	621.6	620.9	620.2
127.5°	673.1	675.8	678.5	681.2	682.1	681.3	680.4	679.6	678.7	677.8	677.0
130°	708.2	711.3	714.3	717.3	718.6	718.2	717.7	717.2	716.7	716.2	715.8
132.5°	746.5	749.0	751.5	754.0	755.3	755.4	755.5	755.5	755.6	754.6	753.6
135°	798.6	801.2	803.8	806.4	807.9	808.4	808.9	809.3	809.8	809.5	809.3
137.5°	852.9	855.0	857.1	859.2	860.6	861.2	861.9	862.4	863.1	862.9	862.7
140°	885.9	888.0	890.1	892.3	893.9	895.0	896.3	897.4	898.5	898.5	898.5
142.5°	919.7	921.9	924.0	926.1	927.5	928.3	929.1	929.9	930.7	930.9	931.1
145°	967.9	969.6	971.2	972.8	974.4	975.8	977.1	978.6	980.0	980.2	980.5
147.5°	1011.5	1013.5	1015.5	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2	1023.7
150°	1040.6	1042.0	1043.4	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4	1051.2
152.5°	1066.8	1068.2	1069.6	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7	1078.6
155°	1105.5	1106.1	1106.9	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2	1113.5
157.5°	1138.8	1139.3	1139.8	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9	1145.6
160°	1159.1	1159.6	1160.1	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2	1164.7
162.5°	1177.4	1177.5	1177.5	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3	1181.9
165°	1201.8	1201.5	1201.3	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6	1204.2
167.5°	1222.0	1221.3	1220.6	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0	1222.6
170°	1233.0	1232.3	1231.6	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1	1232.7
172.5°	1240.6	1239.9	1239.2	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8	1240.4
175°	1249.9	1249.2	1248.5	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0	1248.6
177.5°	1253.8	1253.3	1252.7	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3	1252.5
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	20.6	20.5	20.0	20.1	20.6	20.1	20.2
90°	35.6	35.1	35.0	35.2	35.5	35.7	36.0
92.5°	33.9	34.0	34.1	34.1	34.2	34.2	34.2
95°	67.7	67.7	67.4	66.9	66.4	66.0	65.6
97.5°	113.7	113.7	113.7	113.7	113.7	113.6	113.6
100°	145.9	145.9	145.8	145.5	145.3	145.0	144.8
102.5°	181.2	181.3	181.3	181.1	180.8	180.6	180.3
105°	234.0	234.5	234.7	234.7	234.7	234.7	234.7
107.5°	290.4	290.7	290.2	289.1	288.0	286.9	285.8
110°	328.8	328.8	328.4	327.8	327.0	326.3	325.6



TEST NUMBER: P331604-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	366.8	366.2	365.7	365.2	364.7	364.2	363.6
115°	426.4	426.2	425.7	425.0	424.3	423.5	422.9
117.5°	483.3	482.7	482.2	481.4	480.7	480.0	479.3
120°	522.2	522.2	521.9	521.1	520.5	519.8	519.1
122.5°	561.2	560.6	560.0	559.5	559.0	558.5	558.0
125°	619.5	618.8	618.3	618.1	617.8	617.6	617.3
127.5°	676.1	675.3	674.5	673.8	673.0	672.3	671.5
130°	715.3	714.9	714.2	713.2	712.3	711.3	710.4
132.5°	752.5	751.5	750.6	749.9	749.1	748.4	747.6
135°	809.1	808.9	808.4	807.6	807.0	806.2	805.5
137.5°	862.5	862.3	861.8	860.8	859.9	858.9	858.0
140°	898.5	898.5	898.1	897.2	896.3	895.3	894.4
142.5°	931.3	931.5	931.1	930.2	929.2	928.3	927.3
145°	980.7	980.9	980.6	979.7	978.7	977.8	976.8
147.5°	1024.3	1024.7	1024.6	1023.7	1022.8	1021.9	1021.0
150°	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8
152.5°	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8
155°	1114.6	1115.7	1116.0	1115.3	1114.6	1113.9	1113.2
157.5°	1147.1	1148.8	1149.0	1147.9	1146.7	1145.6	1144.4
160°	1166.0	1167.4	1167.7	1166.8	1165.8	1164.9	1163.9
162.5°	1183.5	1185.1	1185.4	1184.2	1183.1	1181.9	1180.9
165°	1205.8	1207.5	1207.7	1206.6	1205.4	1204.2	1203.1
167.5°	1224.3	1225.9	1226.1	1224.9	1223.7	1222.5	1221.2
170°	1234.4	1236.1	1236.2	1234.8	1233.4	1231.9	1230.5
172.5°	1242.0	1243.7	1243.7	1242.4	1241.0	1239.6	1238.1
175°	1250.3	1251.9	1252.1	1250.6	1249.2	1247.8	1246.3
177.5°	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7

(END OF REPORT)