

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P78458

Luminaire Tested: **DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W**

Issue Date: 02/20/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P78458  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 02/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W  
Description: Define Geo Ring 3ft Diameter Direct/Indirect Fixture w/ Frosted Lens  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6002.0 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.21  
Luminous Opening: Circular (Dia: 3' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 64.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P78458  
CATALOG NUMBER: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P78458

CATALOG NUMBER: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |    |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0  |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 107 | 107 | 107 | 107 | 99 | 99 | 99 | 99 | 84 | 84 | 84 | 69 | 69 | 69 | 56 | 56 | 56 | 50 |
| 1   | 98  | 94  | 90  | 86  | 90 | 87 | 83 | 80 | 73 | 71 | 69 | 61 | 60 | 58 | 50 | 49 | 48 | 43 |
| 2   | 89  | 82  | 76  | 71  | 82 | 76 | 71 | 66 | 64 | 61 | 57 | 54 | 51 | 49 | 44 | 42 | 40 | 36 |
| 3   | 82  | 72  | 65  | 59  | 75 | 67 | 61 | 55 | 57 | 52 | 48 | 48 | 44 | 41 | 39 | 37 | 35 | 31 |
| 4   | 75  | 64  | 56  | 50  | 69 | 59 | 52 | 47 | 51 | 45 | 41 | 43 | 39 | 36 | 35 | 32 | 30 | 26 |
| 5   | 69  | 57  | 49  | 43  | 63 | 53 | 46 | 41 | 45 | 40 | 36 | 38 | 34 | 31 | 32 | 29 | 26 | 23 |
| 6   | 63  | 51  | 43  | 37  | 58 | 48 | 41 | 35 | 41 | 35 | 31 | 35 | 31 | 27 | 29 | 26 | 23 | 20 |
| 7   | 59  | 46  | 38  | 33  | 54 | 43 | 36 | 31 | 37 | 32 | 28 | 32 | 27 | 24 | 27 | 23 | 21 | 18 |
| 8   | 54  | 42  | 34  | 29  | 50 | 39 | 32 | 28 | 34 | 29 | 25 | 29 | 25 | 22 | 24 | 21 | 19 | 16 |
| 9   | 51  | 39  | 31  | 26  | 47 | 36 | 29 | 25 | 31 | 26 | 22 | 27 | 23 | 20 | 23 | 19 | 17 | 15 |
| 10  | 47  | 35  | 28  | 23  | 44 | 33 | 27 | 22 | 29 | 24 | 20 | 25 | 21 | 18 | 21 | 18 | 15 | 13 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |      |
|-----|------|
|     | 0°   |
| 0°  | 1998 |
| 5°  | 1992 |
| 10° | 1964 |
| 15° | 1917 |
| 20° | 1852 |
| 25° | 1778 |
| 30° | 1692 |
| 35° | 1604 |
| 40° | 1517 |
| 45° | 1436 |
| 50° | 1362 |
| 55° | 1298 |
| 60° | 1243 |
| 65° | 1193 |
| 70° | 1144 |
| 75° | 1083 |
| 80° | 1008 |
| 85° | 786  |



TEST NUMBER: P78458  
 CATALOG NUMBER: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 123.3  | 2.1       |
| 10°-20°   | 341.8  | 5.7       |
| 20°-30°   | 486.3  | 8.1       |
| 30°-40°   | 539.5  | 9.0       |
| 40°-50°   | 515.5  | 8.6       |
| 50°-60°   | 438.7  | 7.3       |
| 60°-70°   | 328.5  | 5.5       |
| 70°-80°   | 195.4  | 3.3       |
| 80°-90°   | 54.4   | 0.9       |
| 90°-100°  | 48.1   | 0.8       |
| 100°-110° | 190.2  | 3.2       |
| 110°-120° | 337.3  | 5.6       |
| 120°-130° | 452.2  | 7.5       |
| 130°-140° | 524.7  | 8.7       |
| 140°-150° | 534.1  | 8.9       |
| 150°-160° | 463.7  | 7.7       |
| 160°-170° | 316.2  | 5.3       |
| 170°-180° | 112.0  | 1.9       |
| 0°-30°    | 951.4  | 15.9      |
| 0°-40°    | 1490.9 | 24.8      |
| 0°-60°    | 2445.2 | 40.7      |
| 0°-90°    | 3023.4 | 50.4      |
| 90°-120°  | 575.5  | 9.6       |
| 90°-150°  | 2086.5 | 34.8      |
| 90°-180°  | 2979.0 | 49.6      |
| 0°-180°   | 6002.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 1312 |      |
| 5°   | 1303 | 123  |
| 15°  | 1216 | 342  |
| 25°  | 1058 | 486  |
| 35°  | 863  | 539  |
| 45°  | 667  | 516  |
| 55°  | 489  | 439  |
| 65°  | 331  | 328  |
| 75°  | 184  | 195  |
| 85°  | 45   | 52   |
| 90°  | 1    | 5    |
| 95°  | 39   | 46   |
| 105° | 180  | 190  |
| 115° | 341  | 337  |
| 125° | 505  | 452  |
| 135° | 680  | 525  |
| 145° | 855  | 534  |
| 155° | 1008 | 464  |
| 165° | 1123 | 316  |
| 175° | 1180 | 112  |
| 180° | 1189 |      |



TEST NUMBER: P78458

CATALOG NUMBER: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 1312.0 |
| 2.5°   | 1310.0 |
| 5°     | 1303.0 |
| 7.5°   | 1289.0 |
| 10°    | 1270.0 |
| 12.5°  | 1245.0 |
| 15°    | 1216.0 |
| 17.5°  | 1182.0 |
| 20°    | 1143.0 |
| 22.5°  | 1102.0 |
| 25°    | 1058.0 |
| 27.5°  | 1011.0 |
| 30°    | 962.0  |
| 32.5°  | 912.0  |
| 35°    | 863.0  |
| 37.5°  | 813.0  |
| 40°    | 763.0  |
| 42.5°  | 716.0  |
| 45°    | 667.0  |
| 47.5°  | 621.0  |
| 50°    | 575.0  |
| 52.5°  | 532.0  |
| 55°    | 489.0  |
| 57.5°  | 450.0  |
| 60°    | 408.0  |
| 62.5°  | 370.0  |
| 65°    | 331.0  |
| 67.5°  | 294.0  |
| 70°    | 257.0  |
| 72.5°  | 221.0  |
| 75°    | 184.0  |
| 77.5°  | 150.0  |
| 80°    | 115.0  |
| 82.5°  | 80.0   |
| 85°    | 45.0   |
| 87.5°  | 17.0   |
| 90°    | 0.9    |
| 92.5°  | 16.6   |
| 95°    | 39.3   |
| 97.5°  | 69.0   |
| 100°   | 103.1  |
| 102.5° | 140.7  |
| 105°   | 180.0  |
| 107.5° | 219.3  |
| 110°   | 259.5  |



TEST NUMBER: P78458  
CATALOG NUMBER: DFN2DIP-RG3F0-030D030US940-FLL-FLL-1DUDD-W

**CANDELA DISTRIBUTION (continued):**

|        | 0°     |
|--------|--------|
| 112.5° | 299.6  |
| 115°   | 340.7  |
| 117.5° | 381.8  |
| 120°   | 422.8  |
| 122.5° | 463.0  |
| 125°   | 504.9  |
| 127.5° | 547.8  |
| 130°   | 591.4  |
| 132.5° | 635.1  |
| 135°   | 679.7  |
| 137.5° | 725.1  |
| 140°   | 767.9  |
| 142.5° | 812.5  |
| 145°   | 855.3  |
| 147.5° | 894.6  |
| 150°   | 934.8  |
| 152.5° | 971.5  |
| 155°   | 1008.1 |
| 157.5° | 1040.5 |
| 160°   | 1071.9 |
| 162.5° | 1099.0 |
| 165°   | 1122.6 |
| 167.5° | 1142.7 |
| 170°   | 1159.3 |
| 172.5° | 1172.4 |
| 175°   | 1180.2 |
| 177.5° | 1186.4 |
| 180°   | 1189.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

NEO-RAY

Report Number: SP1-2401-290-4

Test Date: 01/19/2024

Luminaire Tested: RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W

Data in this report applies to families of products including RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W.



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2401-290-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 01/19/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: **RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W**  
 Description: 2' RING DIRECT/INDIRECT FIXTURE WITH FROSTED LIGHT LEVEL 1

**Spectral Parameters**

CCT (K): 3758  
 CIE u': 0.2291  
 CIE v': 0.5077  
 Duv: 0.0012  
 CIE x: 0.3927  
 CIE y: 0.3866  
 CIE z: 0.2207  
 Peak Wavelength (nm): 622  
 Dominant Wavelength (nm): 579  
 Purity: 34

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 94.5 |      |      |
| R1:       | 96.0 | R9:  | 76.6 |
| R2:       | 99.4 | R10: | 97.1 |
| R3:       | 98.5 | R11: | 92.7 |
| R4:       | 91.3 | R12: | 73.3 |
| R5:       | 93.7 | R13: | 97.5 |
| R6:       | 96.5 | R14: | 99.6 |
| R7:       | 92.4 |      |      |
| R8:       | 88.3 |      |      |

Rf: 89  
 Rg: 95.5

**Test Conditions**

Stabilization Time: 24M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/27%  
 Sphere Temperature (°C): 25.0



REPORT NUMBER: SP1-2401-290-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 8/9/2023         | 2/9/2024             |
| Power Meter                    | XITRON 2801 IN0071    | 10/23/2023       | 10/23/2024           |
| AC Power Source                | CHROMA 61603 IN0063   | 10/24/2023       | 10/24/2024           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | ONSET IN0085          | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | ONSET IN0046          | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2401-290-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2401-290-4

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1835          | NR            | 490    | 33863         | NR            | 620    | 68794         | NR            | 750    | 6489          | NR            | 880    | 1195          | NR            |
| 365    | 1756          | NR            | 495    | 36543         | NR            | 625    | 68963         | NR            | 755    | 5711          | NR            | 885    | 1624          | NR            |
| 370    | 1802          | NR            | 500    | 39024         | NR            | 630    | 68221         | NR            | 760    | 5217          | NR            | 890    | 1275          | NR            |
| 375    | 1845          | NR            | 505    | 41399         | NR            | 635    | 66761         | NR            | 765    | 4671          | NR            | 895    | 1184          | NR            |
| 380    | 1842          | NR            | 510    | 43372         | NR            | 640    | 65207         | NR            | 770    | 4277          | NR            | 900    | 1288          | NR            |
| 385    | 1553          | NR            | 515    | 45125         | NR            | 645    | 62607         | NR            | 775    | 3684          | NR            | 905    | 1449          | NR            |
| 390    | 1519          | NR            | 520    | 46728         | NR            | 650    | 59420         | NR            | 780    | 3015          | NR            | 910    | 1184          | NR            |
| 395    | 1452          | NR            | 525    | 48116         | NR            | 655    | 56103         | NR            | 785    | 2857          | NR            | 915    | 1999          | NR            |
| 400    | 1256          | NR            | 530    | 49751         | NR            | 660    | 52566         | NR            | 790    | 2657          | NR            | 920    | 1299          | NR            |
| 405    | 1033          | NR            | 535    | 51317         | NR            | 665    | 48489         | NR            | 795    | 2474          | NR            | 925    | 1312          | NR            |
| 410    | 1023          | NR            | 540    | 52637         | NR            | 670    | 44555         | NR            | 800    | 2413          | NR            | 930    | 1526          | NR            |
| 415    | 1228          | NR            | 545    | 54148         | NR            | 675    | 40405         | NR            | 805    | 2307          | NR            | 935    | 1577          | NR            |
| 420    | 1723          | NR            | 550    | 55654         | NR            | 680    | 36707         | NR            | 810    | 1935          | NR            | 940    | 1108          | NR            |
| 425    | 2748          | NR            | 555    | 56944         | NR            | 685    | 32841         | NR            | 815    | 1648          | NR            | 945    | 1728          | NR            |
| 430    | 4401          | NR            | 560    | 57653         | NR            | 690    | 29037         | NR            | 820    | 1582          | NR            | 950    | 1356          | NR            |
| 435    | 7516          | NR            | 565    | 58559         | NR            | 695    | 25745         | NR            | 825    | 1937          | NR            | 955    | 564           | NR            |
| 440    | 12984         | NR            | 570    | 59300         | NR            | 700    | 22850         | NR            | 830    | 1558          | NR            | 960    | 1914          | NR            |
| 445    | 22972         | NR            | 575    | 59941         | NR            | 705    | 20102         | NR            | 835    | 1584          | NR            | 965    | 994           | NR            |
| 450    | 42364         | NR            | 580    | 60752         | NR            | 710    | 17680         | NR            | 840    | 1621          | NR            | 970    | 757           | NR            |
| 455    | 64528         | NR            | 585    | 61417         | NR            | 715    | 15746         | NR            | 845    | 1333          | NR            | 975    | 758           | NR            |
| 460    | 65971         | NR            | 590    | 62430         | NR            | 720    | 13934         | NR            | 850    | 1406          | NR            | 980    | 1163          | NR            |
| 465    | 51026         | NR            | 595    | 63801         | NR            | 725    | 12285         | NR            | 855    | 1655          | NR            | 985    | 952           | NR            |
| 470    | 43331         | NR            | 600    | 64806         | NR            | 730    | 10834         | NR            | 860    | 1737          | NR            | 990    | 1604          | NR            |
| 475    | 38626         | NR            | 605    | 66352         | NR            | 735    | 9292          | NR            | 865    | 1841          | NR            | 995    | 1145          | NR            |
| 480    | 33315         | NR            | 610    | 67770         | NR            | 740    | 8312          | NR            | 870    | 1490          | NR            | 1000   | 0             | NR            |
| 485    | 31961         | NR            | 615    | 68560         | NR            | 745    | 7359          | NR            | 875    | 1559          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 7174.5

S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1835          | NR            | 490    | 33863         | NR            | 620    | 68794         | NR            | 750    | 6489          | NR            | 880    | 1195          | NR            |
| 365    | 1756          | NR            | 495    | 36543         | NR            | 625    | 68963         | NR            | 755    | 5711          | NR            | 885    | 1624          | NR            |
| 370    | 1802          | NR            | 500    | 39024         | NR            | 630    | 68221         | NR            | 760    | 5217          | NR            | 890    | 1275          | NR            |
| 375    | 1845          | NR            | 505    | 41399         | NR            | 635    | 66761         | NR            | 765    | 4671          | NR            | 895    | 1184          | NR            |
| 380    | 1842          | NR            | 510    | 43372         | NR            | 640    | 65207         | NR            | 770    | 4277          | NR            | 900    | 1288          | NR            |
| 385    | 1553          | NR            | 515    | 45125         | NR            | 645    | 62607         | NR            | 775    | 3684          | NR            | 905    | 1449          | NR            |
| 390    | 1519          | NR            | 520    | 46728         | NR            | 650    | 59420         | NR            | 780    | 3015          | NR            | 910    | 1184          | NR            |
| 395    | 1452          | NR            | 525    | 48116         | NR            | 655    | 56103         | NR            | 785    | 2857          | NR            | 915    | 1999          | NR            |
| 400    | 1256          | NR            | 530    | 49751         | NR            | 660    | 52566         | NR            | 790    | 2657          | NR            | 920    | 1299          | NR            |
| 405    | 1033          | NR            | 535    | 51317         | NR            | 665    | 48489         | NR            | 795    | 2474          | NR            | 925    | 1312          | NR            |
| 410    | 1023          | NR            | 540    | 52637         | NR            | 670    | 44555         | NR            | 800    | 2413          | NR            | 930    | 1526          | NR            |
| 415    | 1228          | NR            | 545    | 54148         | NR            | 675    | 40405         | NR            | 805    | 2307          | NR            | 935    | 1577          | NR            |
| 420    | 1723          | NR            | 550    | 55654         | NR            | 680    | 36707         | NR            | 810    | 1935          | NR            | 940    | 1108          | NR            |
| 425    | 2748          | NR            | 555    | 56944         | NR            | 685    | 32841         | NR            | 815    | 1648          | NR            | 945    | 1728          | NR            |
| 430    | 4401          | NR            | 560    | 57653         | NR            | 690    | 29037         | NR            | 820    | 1582          | NR            | 950    | 1356          | NR            |
| 435    | 7516          | NR            | 565    | 58559         | NR            | 695    | 25745         | NR            | 825    | 1937          | NR            | 955    | 564           | NR            |
| 440    | 12984         | NR            | 570    | 59300         | NR            | 700    | 22850         | NR            | 830    | 1558          | NR            | 960    | 1914          | NR            |
| 445    | 22972         | NR            | 575    | 59941         | NR            | 705    | 20102         | NR            | 835    | 1584          | NR            | 965    | 994           | NR            |
| 450    | 42364         | NR            | 580    | 60752         | NR            | 710    | 17680         | NR            | 840    | 1621          | NR            | 970    | 757           | NR            |
| 455    | 64528         | NR            | 585    | 61417         | NR            | 715    | 15746         | NR            | 845    | 1333          | NR            | 975    | 758           | NR            |
| 460    | 65971         | NR            | 590    | 62430         | NR            | 720    | 13934         | NR            | 850    | 1406          | NR            | 980    | 1163          | NR            |
| 465    | 51026         | NR            | 595    | 63801         | NR            | 725    | 12285         | NR            | 855    | 1655          | NR            | 985    | 952           | NR            |
| 470    | 43331         | NR            | 600    | 64806         | NR            | 730    | 10834         | NR            | 860    | 1737          | NR            | 990    | 1604          | NR            |
| 475    | 38626         | NR            | 605    | 66352         | NR            | 735    | 9292          | NR            | 865    | 1841          | NR            | 995    | 1145          | NR            |
| 480    | 33315         | NR            | 610    | 67770         | NR            | 740    | 8312          | NR            | 870    | 1490          | NR            | 1000   | 0             | NR            |
| 485    | 31961         | NR            | 615    | 68560         | NR            | 745    | 7359          | NR            | 875    | 1559          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2971.3 M/P: 0.73

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1835          | NR            | 490    | 33863         | NR            | 620    | 68794         | NR            | 750    | 6489          | NR            | 880    | 1195          | NR            |
| 365    | 1756          | NR            | 495    | 36543         | NR            | 625    | 68963         | NR            | 755    | 5711          | NR            | 885    | 1624          | NR            |
| 370    | 1802          | NR            | 500    | 39024         | NR            | 630    | 68221         | NR            | 760    | 5217          | NR            | 890    | 1275          | NR            |
| 375    | 1845          | NR            | 505    | 41399         | NR            | 635    | 66761         | NR            | 765    | 4671          | NR            | 895    | 1184          | NR            |
| 380    | 1842          | NR            | 510    | 43372         | NR            | 640    | 65207         | NR            | 770    | 4277          | NR            | 900    | 1288          | NR            |
| 385    | 1553          | NR            | 515    | 45125         | NR            | 645    | 62607         | NR            | 775    | 3684          | NR            | 905    | 1449          | NR            |
| 390    | 1519          | NR            | 520    | 46728         | NR            | 650    | 59420         | NR            | 780    | 3015          | NR            | 910    | 1184          | NR            |
| 395    | 1452          | NR            | 525    | 48116         | NR            | 655    | 56103         | NR            | 785    | 2857          | NR            | 915    | 1999          | NR            |
| 400    | 1256          | NR            | 530    | 49751         | NR            | 660    | 52566         | NR            | 790    | 2657          | NR            | 920    | 1299          | NR            |
| 405    | 1033          | NR            | 535    | 51317         | NR            | 665    | 48489         | NR            | 795    | 2474          | NR            | 925    | 1312          | NR            |
| 410    | 1023          | NR            | 540    | 52637         | NR            | 670    | 44555         | NR            | 800    | 2413          | NR            | 930    | 1526          | NR            |
| 415    | 1228          | NR            | 545    | 54148         | NR            | 675    | 40405         | NR            | 805    | 2307          | NR            | 935    | 1577          | NR            |
| 420    | 1723          | NR            | 550    | 55654         | NR            | 680    | 36707         | NR            | 810    | 1935          | NR            | 940    | 1108          | NR            |
| 425    | 2748          | NR            | 555    | 56944         | NR            | 685    | 32841         | NR            | 815    | 1648          | NR            | 945    | 1728          | NR            |
| 430    | 4401          | NR            | 560    | 57653         | NR            | 690    | 29037         | NR            | 820    | 1582          | NR            | 950    | 1356          | NR            |
| 435    | 7516          | NR            | 565    | 58559         | NR            | 695    | 25745         | NR            | 825    | 1937          | NR            | 955    | 564           | NR            |
| 440    | 12984         | NR            | 570    | 59300         | NR            | 700    | 22850         | NR            | 830    | 1558          | NR            | 960    | 1914          | NR            |
| 445    | 22972         | NR            | 575    | 59941         | NR            | 705    | 20102         | NR            | 835    | 1584          | NR            | 965    | 994           | NR            |
| 450    | 42364         | NR            | 580    | 60752         | NR            | 710    | 17680         | NR            | 840    | 1621          | NR            | 970    | 757           | NR            |
| 455    | 64528         | NR            | 585    | 61417         | NR            | 715    | 15746         | NR            | 845    | 1333          | NR            | 975    | 758           | NR            |
| 460    | 65971         | NR            | 590    | 62430         | NR            | 720    | 13934         | NR            | 850    | 1406          | NR            | 980    | 1163          | NR            |
| 465    | 51026         | NR            | 595    | 63801         | NR            | 725    | 12285         | NR            | 855    | 1655          | NR            | 985    | 952           | NR            |
| 470    | 43331         | NR            | 600    | 64806         | NR            | 730    | 10834         | NR            | 860    | 1737          | NR            | 990    | 1604          | NR            |
| 475    | 38626         | NR            | 605    | 66352         | NR            | 735    | 9292          | NR            | 865    | 1841          | NR            | 995    | 1145          | NR            |
| 480    | 33315         | NR            | 610    | 67770         | NR            | 740    | 8312          | NR            | 870    | 1490          | NR            | 1000   | 0             | NR            |
| 485    | 31961         | NR            | 615    | 68560         | NR            | 745    | 7359          | NR            | 875    | 1559          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-4



TM-30-18

**Summary**

$R_f = 89$   
 $R_g = 95.5$   
 CIE  $R_a = 94.5$   
 $R_9 = 76.6$



**Color Vector Graphics**



REPORT NUMBER: SP1-2401-290-4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 86 | CES26 = 95  | CES51 = 89 | CES76 = 94 |
| CES02 = 62 | CES27 = 84  | CES52 = 94 | CES77 = 90 |
| CES03 = 31 | CES28 = 100 | CES53 = 89 | CES78 = 91 |
| CES04 = 69 | CES29 = 83  | CES54 = 85 | CES79 = 94 |
| CES05 = 49 | CES30 = 71  | CES55 = 82 | CES80 = 93 |
| CES06 = 51 | CES31 = 85  | CES56 = 84 | CES81 = 84 |
| CES07 = 42 | CES32 = 93  | CES57 = 81 | CES82 = 97 |
| CES08 = 41 | CES33 = 82  | CES58 = 82 | CES83 = 93 |
| CES09 = 29 | CES34 = 97  | CES59 = 95 | CES84 = 94 |
| CES10 = 74 | CES35 = 99  | CES60 = 87 | CES85 = 82 |
| CES11 = 57 | CES36 = 70  | CES61 = 89 | CES86 = 87 |
| CES12 = 63 | CES37 = 97  | CES62 = 72 | CES87 = 93 |
| CES13 = 43 | CES38 = 67  | CES63 = 86 | CES88 = 92 |
| CES14 = 74 | CES39 = 95  | CES64 = 82 | CES89 = 89 |
| CES15 = 71 | CES40 = 94  | CES65 = 86 | CES90 = 87 |
| CES16 = 47 | CES41 = 87  | CES66 = 80 | CES91 = 67 |
| CES17 = 49 | CES42 = 96  | CES67 = 80 | CES92 = 81 |
| CES18 = 56 | CES43 = 93  | CES68 = 86 | CES93 = 87 |
| CES19 = 71 | CES44 = 99  | CES69 = 87 | CES94 = 86 |
| CES20 = 66 | CES45 = 93  | CES70 = 87 | CES95 = 84 |
| CES21 = 85 | CES46 = 90  | CES71 = 77 | CES96 = 95 |
| CES22 = 78 | CES47 = 84  | CES72 = 93 | CES97 = 94 |
| CES23 = 91 | CES48 = 76  | CES73 = 85 | CES98 = 91 |
| CES24 = 90 | CES49 = 92  | CES74 = 87 | CES99 = 90 |
| CES25 = 71 | CES50 = 90  | CES75 = 82 |            |





REPORT NUMBER: SP1-2401-290-4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2401-290-4

TM-30-18

Measure Comparisons



(END OF REPORT)