

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331608-930

Luminaire Tested: **S122DIW-S1005D1240U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331608-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6813.8 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49			49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41			41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34			34
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29			29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25			25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22			22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17			17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15			15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14			14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	1.8
10°-20°	343.8	5.0
20°-30°	505.4	7.4
30°-40°	587.0	8.6
40°-50°	586.4	8.6
50°-60°	511.4	7.5
60°-70°	378.1	5.5
70°-80°	214.2	3.1
80°-90°	62.6	0.9
90°-100°	79.4	1.2
100°-110°	246.5	3.6
110°-120°	421.4	6.2
120°-130°	554.2	8.1
130°-140°	622.0	9.1
140°-150°	609.9	9.0
150°-160°	511.5	7.5
160°-170°	339.3	5.0
170°-180°	118.6	1.7
0°-30°	971.4	14.3
0°-40°	1558.4	22.9
0°-60°	2656.1	39.0
0°-90°	3311.0	48.6
90°-120°	747.3	11.0
90°-150°	2533.4	37.2
90°-180°	3503.0	51.4
0°-180°	6813.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	14	37	35	36	5
95°	55	65	68	68	66	63
105°	227	230	233	235	235	240
115°	423	429	427	426	423	418
125°	615	624	622	619	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	603
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1251	1248	1245	1252	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.2	18.3	18.4	18.6	18.7	19.0	19.6	20.2	20.8	21.4	20.6
90°	1.1	3.9	6.7	9.5	12.3	16.3	21.5	26.7	31.8	37.0	36.5
92.5°	18.8	20.9	23.0	25.0	27.1	28.7	29.9	31.1	32.4	33.6	33.7
95°	55.0	57.3	59.7	62.0	64.4	65.8	66.3	66.7	67.2	67.7	67.7
97.5°	100.4	102.5	104.6	106.6	108.7	110.1	111.0	111.9	112.8	113.7	113.7
100°	134.3	136.2	138.0	139.9	141.8	143.1	143.7	144.5	145.2	145.9	145.9
102.5°	169.7	171.3	172.8	174.3	175.8	177.0	177.9	178.8	179.7	180.6	180.8
105°	227.3	228.0	228.7	229.4	230.1	230.7	231.1	231.6	232.1	232.6	233.0
107.5°	285.2	286.3	287.3	288.3	289.3	289.8	289.8	289.8	289.8	289.8	290.1
110°	322.5	323.8	325.2	326.7	328.1	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.1	364.4	365.8	367.3	368.7	369.2	369.1	368.9	368.7	368.5	367.9
115°	422.9	424.3	425.7	427.1	428.5	428.9	428.5	428.0	427.5	427.1	426.9
117.5°	482.5	484.4	486.2	488.1	490.0	490.3	488.9	487.6	486.3	485.0	484.5
120°	522.2	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	522.2
122.5°	558.6	560.8	563.1	565.3	567.6	568.1	566.8	565.5	564.1	562.8	562.2
125°	615.2	617.3	619.5	621.6	623.7	624.4	623.7	623.1	622.3	621.6	620.9
127.5°	670.4	673.1	675.8	678.5	681.2	682.1	681.3	680.4	679.6	678.7	677.8
130°	705.2	708.2	711.3	714.3	717.3	718.6	718.2	717.7	717.2	716.7	716.2
132.5°	744.0	746.5	749.0	751.5	754.0	755.3	755.4	755.5	755.5	755.6	754.6
135°	796.1	798.6	801.2	803.8	806.4	807.9	808.4	808.9	809.3	809.8	809.5
137.5°	850.8	852.9	855.0	857.1	859.2	860.6	861.2	861.9	862.4	863.1	862.9
140°	883.8	885.9	888.0	890.1	892.3	893.9	895.0	896.3	897.4	898.5	898.5
142.5°	917.6	919.7	921.9	924.0	926.1	927.5	928.3	929.1	929.9	930.7	930.9
145°	966.2	967.9	969.6	971.2	972.8	974.4	975.8	977.1	978.6	980.0	980.2
147.5°	1009.6	1011.5	1013.5	1015.5	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2
150°	1039.2	1040.6	1042.0	1043.4	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4
152.5°	1065.4	1066.8	1068.2	1069.6	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7
155°	1104.7	1105.5	1106.1	1106.9	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2
157.5°	1138.3	1138.8	1139.3	1139.8	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9
160°	1158.6	1159.1	1159.6	1160.1	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2
162.5°	1177.2	1177.4	1177.5	1177.5	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3
165°	1202.0	1201.8	1201.5	1201.3	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6
167.5°	1222.7	1222.0	1221.3	1220.6	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0
170°	1233.7	1233.0	1232.3	1231.6	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1
172.5°	1241.3	1240.6	1239.9	1239.2	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8
175°	1250.6	1249.9	1249.2	1248.5	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0
177.5°	1254.4	1253.8	1253.3	1252.7	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	19.9	19.1	18.3	17.9	17.7	17.5	17.4	17.2
90°	36.0	35.6	35.1	35.0	35.2	35.5	35.7	36.0
92.5°	33.8	33.9	34.0	34.1	34.1	34.2	34.2	34.2
95°	67.7	67.7	67.7	67.4	66.9	66.4	66.0	65.6
97.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.6
100°	145.9	145.9	145.9	145.8	145.5	145.3	145.0	144.8
102.5°	180.9	181.2	181.3	181.3	181.1	180.8	180.6	180.3
105°	233.5	234.0	234.5	234.7	234.7	234.7	234.7	234.7
107.5°	290.2	290.4	290.7	290.2	289.1	288.0	286.9	285.8
110°	328.8	328.8	328.8	328.4	327.8	327.0	326.3	325.6



TEST NUMBER: P331608-930

CATALOG NUMBER: S122DIW-S1005D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	367.4	366.8	366.2	365.7	365.2	364.7	364.2	363.6
115°	426.6	426.4	426.2	425.7	425.0	424.3	423.5	422.9
117.5°	483.9	483.3	482.7	482.2	481.4	480.7	480.0	479.3
120°	522.2	522.2	522.2	521.9	521.1	520.5	519.8	519.1
122.5°	561.7	561.2	560.6	560.0	559.5	559.0	558.5	558.0
125°	620.2	619.5	618.8	618.3	618.1	617.8	617.6	617.3
127.5°	677.0	676.1	675.3	674.5	673.8	673.0	672.3	671.5
130°	715.8	715.3	714.9	714.2	713.2	712.3	711.3	710.4
132.5°	753.6	752.5	751.5	750.6	749.9	749.1	748.4	747.6
135°	809.3	809.1	808.9	808.4	807.6	807.0	806.2	805.5
137.5°	862.7	862.5	862.3	861.8	860.8	859.9	858.9	858.0
140°	898.5	898.5	898.5	898.1	897.2	896.3	895.3	894.4
142.5°	931.1	931.3	931.5	931.1	930.2	929.2	928.3	927.3
145°	980.5	980.7	980.9	980.6	979.7	978.7	977.8	976.8
147.5°	1023.7	1024.3	1024.7	1024.6	1023.7	1022.8	1021.9	1021.0
150°	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8
152.5°	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8
155°	1113.5	1114.6	1115.7	1116.0	1115.3	1114.6	1113.9	1113.2
157.5°	1145.6	1147.1	1148.8	1149.0	1147.9	1146.7	1145.6	1144.4
160°	1164.7	1166.0	1167.4	1167.7	1166.8	1165.8	1164.9	1163.9
162.5°	1181.9	1183.5	1185.1	1185.4	1184.2	1183.1	1181.9	1180.9
165°	1204.2	1205.8	1207.5	1207.7	1206.6	1205.4	1204.2	1203.1
167.5°	1222.6	1224.3	1225.9	1226.1	1224.9	1223.7	1222.5	1221.2
170°	1232.7	1234.4	1236.1	1236.2	1234.8	1233.4	1231.9	1230.5
172.5°	1240.4	1242.0	1243.7	1243.7	1242.4	1241.0	1239.6	1238.1
175°	1248.6	1250.3	1251.9	1252.1	1250.6	1249.2	1247.8	1246.3
177.5°	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7

(END OF REPORT)