

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331610-930

Luminaire Tested: **S122DIW-S1005D1440U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331610-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1440U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7665.2 lumens  
Efficiency: N/A  
Efficacy: 92.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	38	36	34	32	30	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.8	2.0
10°-20°	450.1	5.9
20°-30°	653.3	8.5
30°-40°	689.3	9.0
40°-50°	610.4	8.0
50°-60°	487.1	6.4
60°-70°	331.1	4.3
70°-80°	169.7	2.2
80°-90°	46.7	0.6
90°-100°	92.3	1.2
100°-110°	286.6	3.7
110°-120°	490.0	6.4
120°-130°	644.3	8.4
130°-140°	723.2	9.4
140°-150°	709.1	9.3
150°-160°	594.8	7.8
160°-170°	394.5	5.1
170°-180°	137.9	1.8
0°-30°	1258.2	16.4
0°-40°	1947.5	25.4
0°-60°	3045.0	39.7
0°-90°	3592.5	46.9
90°-120°	868.9	11.3
90°-150°	2945.5	38.4
90°-180°	4073.0	53.1
0°-180°	7665.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	42	1	42	1	42	20
95°	76	64	76	64	76	85
105°	273	264	273	264	273	287
115°	492	492	492	492	492	486
125°	718	715	718	715	718	640
135°	937	926	937	926	937	721
145°	1136	1123	1136	1123	1136	709
155°	1294	1284	1294	1284	1294	596
165°	1399	1398	1399	1398	1399	394
175°	1449	1454	1449	1454	1449	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	21.4	21.3	21.8	21.2	21.1	21.7	21.8	21.4	22.0	22.6	21.9
90°	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9	42.5	43.0	37.0
92.5°	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3	39.2	39.1	37.7
95°	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7	78.7	78.7	78.1
97.5°	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2	132.2	132.2	131.2
100°	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6	169.6	169.6	168.8
102.5°	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3	210.2	209.9	208.9
105°	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5	270.9	270.4	269.9
107.5°	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5	337.2	337.0	337.0
110°	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1	427.8	428.4	428.7
115°	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0	496.3	496.6	497.1
117.5°	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6	563.3	563.9	565.4
120°	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2	607.2	607.2	609.4
122.5°	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1	653.7	654.4	655.9
125°	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1	721.9	722.7	723.6
127.5°	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1	788.1	789.1	790.1
130°	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3	832.8	833.3	833.9
132.5°	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2	877.3	878.6	878.5
135°	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9	941.3	941.5	940.9
137.5°	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0	1003.2	1003.5	1002.7
140°	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7	1044.7	1044.7	1043.4
142.5°	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6	1082.3	1082.1	1081.2
145°	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0	1139.6	1139.4	1137.8
147.5°	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3	1189.7	1189.0	1188.0
150°	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5	1219.4
152.5°	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0	1250.7
155°	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5	1293.1	1291.8	1290.9
157.5°	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9	1330.0	1328.2	1327.7
160°	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0	1352.4	1350.8	1350.5
162.5°	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2	1372.3	1370.4	1370.2
165°	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1	1398.2	1396.3	1396.3
167.5°	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5	1419.6	1417.6	1417.7
170°	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3	1431.3	1429.5	1429.7
172.5°	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1	1440.2	1438.3	1438.6
175°	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7	1449.8	1447.9	1448.5
177.5°	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5	1454.0
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	21.2	20.0	18.8	18.8	16.7	16.1	13.4	11.3	11.4	11.6	11.2
90°	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2	4.5	7.7	11.1
92.5°	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9	24.3	26.7	29.1
95°	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9	66.6	69.4	72.1
97.5°	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8	119.2	121.6	124.0
100°	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1	158.2	160.5	162.7
102.5°	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4	199.2	200.9	202.6
105°	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2	265.1	265.9	266.7
107.5°	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6	332.8	334.0	335.3
110°	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9	376.5	378.1	379.8





TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1	423.7	425.3	427.0
115°	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6	493.3	494.9	496.6
117.5°	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0	563.1	565.3	567.5
120°	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	609.4	611.6	613.8
122.5°	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5	652.1	654.7	657.3
125°	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3	717.8	720.2	722.7
127.5°	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5	782.6	785.7	788.9
130°	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8	823.4	827.0	830.5
132.5°	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0	868.0	870.8	873.8
135°	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5	928.5	931.6	934.5
137.5°	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2	991.6	994.1	996.5
140°	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5	1030.0	1032.5	1034.9
142.5°	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9	1069.3	1071.8	1074.2
145°	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4	1125.4	1127.2	1129.1
147.5°	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8	1176.1	1178.4	1180.7
150°	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2	1209.8	1211.5	1213.2
152.5°	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7	1240.3	1241.9	1243.6
155°	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4	1285.2	1286.1	1286.9
157.5°	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5	1324.0	1324.6	1325.2
160°	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1	1347.7	1348.2	1348.7
162.5°	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7	1368.9	1369.0	1369.1
165°	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5	1397.3	1396.9	1396.7
167.5°	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6	1420.7	1419.9	1419.1
170°	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4	1433.5	1432.7	1431.9
172.5°	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2	1442.4	1441.6	1440.8
175°	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0	1453.2	1452.4	1451.6
177.5°	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5	1457.8	1457.2	1456.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	11.3	11.8	12.5	13.7	14.4	15.1	14.5	14.3	14.3	13.1	13.1
90°	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9	41.4	40.8	40.7
92.5°	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3	39.4	39.5	39.6
95°	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7	78.7	78.7	78.4
97.5°	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2	132.2	132.2	132.2
100°	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6	169.6	169.6	169.5
102.5°	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3	210.6	210.8	210.8
105°	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5	272.1	272.6	272.9
107.5°	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5	337.7	337.9	337.4
110°	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	381.8



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1	426.5	425.8	425.2
115°	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0	495.7	495.5	494.9
117.5°	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6	562.0	561.3	560.5
120°	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2	607.2	607.2	606.7
122.5°	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1	652.4	651.8	651.1
125°	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1	720.2	719.4	718.9
127.5°	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1	786.1	785.1	784.2
130°	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3	831.7	831.1	830.3
132.5°	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2	875.0	873.8	872.7
135°	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9	940.7	940.4	939.9
137.5°	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0	1002.8	1002.6	1001.9
140°	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7	1044.7	1044.7	1044.2
142.5°	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6	1082.8	1083.0	1082.6
145°	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0	1140.2	1140.4	1140.0
147.5°	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3	1190.8	1191.5	1191.2
150°	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8
152.5°	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1
155°	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5	1295.9	1297.2	1297.5
157.5°	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9	1333.7	1335.6	1335.9
160°	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0	1355.7	1357.3	1357.6
162.5°	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2	1376.1	1377.9	1378.2
165°	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1	1402.0	1403.9	1404.2
167.5°	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5	1423.4	1425.3	1425.6
170°	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3	1435.2	1437.1	1437.2
172.5°	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1	1444.1	1445.9	1446.1
175°	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7	1453.6	1455.6	1455.7
177.5°	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	13.2	12.7	12.8	12.4	12.8	12.7	13.2	13.1	13.1	14.3	14.3
90°	41.0	41.3	41.5	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9
92.5°	39.6	39.7	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3
95°	77.9	77.3	76.7	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7
97.5°	132.2	132.1	132.1	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2
100°	169.2	168.9	168.7	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6
102.5°	210.5	210.3	209.9	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3
105°	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5
107.5°	336.1	334.8	333.6	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5
110°	381.0	380.2	379.4	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	424.6	424.0	423.4	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1
115°	494.1	493.3	492.4	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0
117.5°	559.7	558.9	558.1	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6
120°	605.9	605.1	604.3	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2
122.5°	650.5	650.0	649.3	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1
125°	718.6	718.4	718.1	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1
127.5°	783.3	782.4	781.6	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1
130°	829.2	828.2	827.0	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3
132.5°	871.9	871.0	870.1	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2
135°	939.1	938.2	937.4	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9
137.5°	1000.9	999.7	998.7	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0
140°	1043.1	1042.0	1040.9	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7
142.5°	1081.5	1080.4	1079.3	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6
145°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0
147.5°	1190.2	1189.1	1188.1	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3
150°	1222.9	1222.1	1221.3	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1
152.5°	1255.1	1254.0	1253.0	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0
155°	1296.7	1295.9	1295.1	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5
157.5°	1334.6	1333.3	1332.0	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9
160°	1356.5	1355.4	1354.4	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0
162.5°	1376.9	1375.6	1374.3	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2
165°	1402.8	1401.5	1400.1	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1
167.5°	1424.2	1422.7	1421.3	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5
170°	1435.6	1433.9	1432.3	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3
172.5°	1444.5	1442.8	1441.2	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1
175°	1454.0	1452.4	1450.7	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7
177.5°	1457.5	1456.2	1454.8	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	14.5	15.1	14.4	13.7	12.5	11.8	11.3	11.2	11.6	11.4	11.3
90°	42.5	43.0	37.0	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2
92.5°	39.2	39.1	37.7	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9
95°	78.7	78.7	78.1	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9
97.5°	132.2	132.2	131.2	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8
100°	169.6	169.6	168.8	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1
102.5°	210.2	209.9	208.9	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4
105°	270.9	270.4	269.9	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2
107.5°	337.2	337.0	337.0	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6
110°	382.3	382.3	382.3	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.8	428.4	428.7	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1
115°	496.3	496.6	497.1	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6
117.5°	563.3	563.9	565.4	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0
120°	607.2	607.2	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2
122.5°	653.7	654.4	655.9	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5
125°	721.9	722.7	723.6	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3
127.5°	788.1	789.1	790.1	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5
130°	832.8	833.3	833.9	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8
132.5°	877.3	878.6	878.5	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0
135°	941.3	941.5	940.9	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5
137.5°	1003.2	1003.5	1002.7	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2
140°	1044.7	1044.7	1043.4	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5
142.5°	1082.3	1082.1	1081.2	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9
145°	1139.6	1139.4	1137.8	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4
147.5°	1189.7	1189.0	1188.0	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8
150°	1221.3	1220.5	1219.4	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2
152.5°	1253.0	1252.0	1250.7	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7
155°	1293.1	1291.8	1290.9	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4
157.5°	1330.0	1328.2	1327.7	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5
160°	1352.4	1350.8	1350.5	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1
162.5°	1372.3	1370.4	1370.2	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7
165°	1398.2	1396.3	1396.3	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5
167.5°	1419.6	1417.6	1417.7	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6
170°	1431.3	1429.5	1429.7	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4
172.5°	1440.2	1438.3	1438.6	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2
175°	1449.8	1447.9	1448.5	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0
177.5°	1454.8	1453.5	1454.0	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	13.4	16.1	16.7	18.8	18.8	20.0	21.2	21.9	22.6	22.0	21.4
90°	4.5	7.7	11.1	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9
92.5°	24.3	26.7	29.1	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3
95°	66.6	69.4	72.1	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7
97.5°	119.2	121.6	124.0	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2
100°	158.2	160.5	162.7	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6
102.5°	199.2	200.9	202.6	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3
105°	265.1	265.9	266.7	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5
107.5°	332.8	334.0	335.3	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5
110°	376.5	378.1	379.8	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3





TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	423.7	425.3	427.0	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1
115°	493.3	494.9	496.6	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0
117.5°	563.1	565.3	567.5	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6
120°	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2
122.5°	652.1	654.7	657.3	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1
125°	717.8	720.2	722.7	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1
127.5°	782.6	785.7	788.9	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1
130°	823.4	827.0	830.5	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3
132.5°	868.0	870.8	873.8	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2
135°	928.5	931.6	934.5	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9
137.5°	991.6	994.1	996.5	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0
140°	1030.0	1032.5	1034.9	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7
142.5°	1069.3	1071.8	1074.2	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6
145°	1125.4	1127.2	1129.1	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0
147.5°	1176.1	1178.4	1180.7	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3
150°	1209.8	1211.5	1213.2	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1
152.5°	1240.3	1241.9	1243.6	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0
155°	1285.2	1286.1	1286.9	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5
157.5°	1324.0	1324.6	1325.2	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9
160°	1347.7	1348.2	1348.7	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0
162.5°	1368.9	1369.0	1369.1	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2
165°	1397.3	1396.9	1396.7	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1
167.5°	1420.7	1419.9	1419.1	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5
170°	1433.5	1432.7	1431.9	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3
172.5°	1442.4	1441.6	1440.8	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1
175°	1453.2	1452.4	1451.6	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7
177.5°	1457.8	1457.2	1456.5	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	21.8	21.7	21.1	21.2	21.8	21.3	21.4
90°	41.4	40.8	40.7	41.0	41.3	41.5	41.8
92.5°	39.4	39.5	39.6	39.6	39.7	39.8	39.8
95°	78.7	78.7	78.4	77.9	77.3	76.7	76.2
97.5°	132.2	132.2	132.2	132.2	132.1	132.1	132.0
100°	169.6	169.6	169.5	169.2	168.9	168.7	168.4
102.5°	210.6	210.8	210.8	210.5	210.3	209.9	209.7
105°	272.1	272.6	272.9	272.9	272.9	272.9	272.9
107.5°	337.7	337.9	337.4	336.1	334.8	333.6	332.3
110°	382.3	382.3	381.8	381.0	380.2	379.4	378.5



TEST NUMBER: P331610-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	426.5	425.8	425.2	424.6	424.0	423.4	422.8
115°	495.7	495.5	494.9	494.1	493.3	492.4	491.6
117.5°	562.0	561.3	560.5	559.7	558.9	558.1	557.3
120°	607.2	607.2	606.7	605.9	605.1	604.3	603.5
122.5°	652.4	651.8	651.1	650.5	650.0	649.3	648.7
125°	720.2	719.4	718.9	718.6	718.4	718.1	717.8
127.5°	786.1	785.1	784.2	783.3	782.4	781.6	780.7
130°	831.7	831.1	830.3	829.2	828.2	827.0	826.0
132.5°	875.0	873.8	872.7	871.9	871.0	870.1	869.2
135°	940.7	940.4	939.9	939.1	938.2	937.4	936.6
137.5°	1002.8	1002.6	1001.9	1000.9	999.7	998.7	997.5
140°	1044.7	1044.7	1044.2	1043.1	1042.0	1040.9	1039.8
142.5°	1082.8	1083.0	1082.6	1081.5	1080.4	1079.3	1078.2
145°	1140.2	1140.4	1140.0	1139.0	1137.9	1136.8	1135.7
147.5°	1190.8	1191.5	1191.2	1190.2	1189.1	1188.1	1187.1
150°	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5
152.5°	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0
155°	1295.9	1297.2	1297.5	1296.7	1295.9	1295.1	1294.3
157.5°	1333.7	1335.6	1335.9	1334.6	1333.3	1332.0	1330.6
160°	1355.7	1357.3	1357.6	1356.5	1355.4	1354.4	1353.2
162.5°	1376.1	1377.9	1378.2	1376.9	1375.6	1374.3	1372.9
165°	1402.0	1403.9	1404.2	1402.8	1401.5	1400.1	1398.7
167.5°	1423.4	1425.3	1425.6	1424.2	1422.7	1421.3	1419.8
170°	1435.2	1437.1	1437.2	1435.6	1433.9	1432.3	1430.7
172.5°	1444.1	1445.9	1446.1	1444.5	1442.8	1441.2	1439.6
175°	1453.6	1455.6	1455.7	1454.0	1452.4	1450.7	1449.1
177.5°	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5

(END OF REPORT)