

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331598-930

Luminaire Tested: **S122DIW-S1005D970U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331598-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6326.8 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	25
7	61	49	41	35	56	46	39	34	40	35	31	35	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	23	20	24	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.8	2.4
10°-20°	450.1	7.1
20°-30°	653.3	10.3
30°-40°	689.3	10.9
40°-50°	610.4	9.6
50°-60°	487.1	7.7
60°-70°	331.1	5.2
70°-80°	169.7	2.7
80°-90°	44.8	0.7
90°-100°	62.0	1.0
100°-110°	192.6	3.0
110°-120°	329.2	5.2
120°-130°	432.9	6.8
130°-140°	485.9	7.7
140°-150°	476.4	7.5
150°-160°	399.6	6.3
160°-170°	265.0	4.2
170°-180°	92.6	1.5
0°-30°	1258.2	19.9
0°-40°	1947.5	30.8
0°-60°	3045.0	48.1
0°-90°	3590.6	56.8
90°-120°	583.8	9.2
90°-150°	1979.0	31.3
90°-180°	2736.0	43.2
0°-180°	6326.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	38
90°	28	1	28	1	28	14
95°	51	43	51	43	51	57
105°	183	178	183	178	183	193
115°	330	330	330	330	330	326
125°	482	481	482	481	482	430
135°	629	622	629	622	629	484
145°	763	755	763	755	763	476
155°	870	863	870	863	870	400
165°	940	939	940	939	940	265
175°	974	977	974	977	974	92
180°	978	978	978	978	978	



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	18.6	18.6	19.1	18.5	18.4	19.0	19.1	18.7	19.2	19.8	19.5
90°	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1	28.5	28.9	24.9
92.5°	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4	26.3	26.3	25.3
95°	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8	52.8	52.8	52.5
97.5°	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9	88.9	88.9	88.1
100°	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0	114.0	114.0	113.4
102.5°	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4	141.2	141.0	140.3
105°	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4	182.1	181.6	181.3
107.5°	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7	226.6	226.4	226.4
110°	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0	287.4	287.9	288.0
115°	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2	333.5	333.6	333.9
117.5°	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0	378.5	378.9	379.9
120°	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0	408.0	408.0	409.4
122.5°	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8	439.2	439.6	440.7
125°	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5	485.0	485.6	486.1
127.5°	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8	529.5	530.2	530.8
130°	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1	559.5	559.9	560.3
132.5°	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6	589.5	590.3	590.2
135°	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2	632.3	632.5	632.2
137.5°	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8	674.0	674.2	673.7
140°	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9	701.9	701.9	701.0
142.5°	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3	727.2	727.0	726.4
145°	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9	765.6	765.5	764.4
147.5°	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6	799.2	798.8	798.1
150°	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0	819.3
152.5°	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1	840.2
155°	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8	868.8	867.9	867.3
157.5°	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9	893.6	892.3	892.0
160°	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7	908.7	907.5	907.3
162.5°	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2	922.0	920.7	920.6
165°	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7	939.4	938.1	938.1
167.5°	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0	953.7	952.4	952.5
170°	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0	961.6	960.4	960.6
172.5°	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9	967.6	966.3	966.5
175°	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3	974.0	972.7	973.1
177.5°	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6	976.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	19.2	18.3	17.5	17.9	16.0	15.6	13.1	11.2	11.1	11.0	10.5
90°	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8	3.0	5.2	7.4
92.5°	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7	16.3	17.9	19.6
95°	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0	44.8	46.6	48.4
97.5°	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4	80.1	81.7	83.3
100°	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8	106.3	107.8	109.3
102.5°	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6	133.8	134.9	136.2
105°	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6	178.1	178.6	179.2
107.5°	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8	223.6	224.4	225.2
110°	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8	253.0	254.0	255.2



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6	284.7	285.8	286.9
115°	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3	331.4	332.5	333.6
117.5°	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9	378.4	379.8	381.3
120°	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	409.4	410.9	412.4
122.5°	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3	438.1	439.9	441.6
125°	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6	482.2	483.9	485.6
127.5°	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7	525.8	527.9	530.0
130°	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8	553.2	555.5	558.0
132.5°	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1	583.1	585.1	587.0
135°	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8	623.9	625.8	627.9
137.5°	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6	666.3	667.9	669.5
140°	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3	692.0	693.7	695.3
142.5°	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8	718.4	720.1	721.7
145°	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7	756.0	757.3	758.6
147.5°	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6	790.2	791.7	793.2
150°	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7	812.9	813.9	815.1
152.5°	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3	833.3	834.5	835.5
155°	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9	863.5	864.1	864.6
157.5°	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2	889.6	889.9	890.3
160°	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1	905.4	905.8	906.1
162.5°	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6	919.7	919.7	919.8
165°	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9	938.7	938.6	938.3
167.5°	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1	954.6	954.0	953.4
170°	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7	963.1	962.6	962.1
172.5°	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6	969.1	968.5	968.0
175°	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9	976.3	975.8	975.3
177.5°	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9	979.4	979.0	978.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	10.4	10.5	10.8	11.7	12.0	12.3	11.7	11.7	11.6	10.5	10.4
90°	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1	27.8	27.4	27.3
92.5°	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4	26.5	26.6	26.6
95°	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8	52.8	52.8	52.7
97.5°	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9	88.9	88.9	88.9
100°	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0	114.0	114.0	113.9
102.5°	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4	141.5	141.6	141.6
105°	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4	182.8	183.1	183.4
107.5°	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7	226.9	227.0	226.7
110°	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.6



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0	286.6	286.1	285.7
115°	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2	333.0	332.9	332.5
117.5°	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0	377.6	377.1	376.6
120°	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0	408.0	408.0	407.6
122.5°	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8	438.3	437.9	437.5
125°	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5	483.9	483.4	483.0
127.5°	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8	528.2	527.5	526.8
130°	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1	558.8	558.4	557.8
132.5°	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6	587.8	587.0	586.4
135°	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2	632.0	631.8	631.4
137.5°	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8	673.8	673.6	673.1
140°	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9	701.9	701.9	701.6
142.5°	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3	727.5	727.6	727.3
145°	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9	766.1	766.2	766.0
147.5°	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6	800.1	800.5	800.3
150°	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1	821.7	822.2	822.2
152.5°	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5	843.3	843.9	843.9
155°	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8	870.7	871.6	871.7
157.5°	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9	896.1	897.3	897.5
160°	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7	910.9	911.9	912.2
162.5°	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2	924.5	925.8	925.9
165°	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7	941.9	943.2	943.4
167.5°	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0	956.3	957.6	957.7
170°	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0	964.3	965.6	965.6
172.5°	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9	970.2	971.4	971.6
175°	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3	976.6	977.9	978.0
177.5°	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4	979.2	980.1	980.1
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	10.5	10.0	10.1	9.6	10.1	10.0	10.5	10.4	10.5	11.6	11.7
90°	27.6	27.7	27.9	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1
92.5°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4
95°	52.3	51.9	51.5	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8
97.5°	88.8	88.8	88.7	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9
100°	113.7	113.5	113.3	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0
102.5°	141.5	141.2	141.0	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4
105°	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4
107.5°	225.8	224.9	224.1	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7
110°	256.0	255.4	254.9	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	285.3	284.9	284.5	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0
115°	332.0	331.4	330.8	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2
117.5°	376.1	375.5	375.0	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0
120°	407.1	406.6	406.0	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0
122.5°	437.1	436.7	436.3	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8
125°	482.8	482.7	482.4	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5
127.5°	526.3	525.7	525.1	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8
130°	557.1	556.4	555.6	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1
132.5°	585.8	585.1	584.6	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6
135°	630.9	630.3	629.8	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2
137.5°	672.4	671.6	670.9	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8
140°	700.8	700.1	699.4	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9
142.5°	726.6	725.9	725.1	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3
145°	765.2	764.5	763.8	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9
147.5°	799.6	798.9	798.3	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6
150°	821.7	821.1	820.5	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1
152.5°	843.3	842.5	841.8	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5
155°	871.2	870.7	870.1	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8
157.5°	896.7	895.8	894.9	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9
160°	911.4	910.7	910.0	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7
162.5°	925.0	924.1	923.2	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2
165°	942.5	941.6	940.7	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7
167.5°	956.8	955.9	954.9	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0
170°	964.5	963.4	962.3	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0
172.5°	970.5	969.4	968.2	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9
175°	976.9	975.8	974.7	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3
177.5°	979.2	978.4	977.5	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	11.7	12.3	12.0	11.7	10.8	10.5	10.4	10.5	11.0	11.1	11.2
90°	28.5	28.9	24.9	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8
92.5°	26.3	26.3	25.3	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7
95°	52.8	52.8	52.5	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0
97.5°	88.9	88.9	88.1	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4
100°	114.0	114.0	113.4	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8
102.5°	141.2	141.0	140.3	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6
105°	182.1	181.6	181.3	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6
107.5°	226.6	226.4	226.4	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8
110°	256.8	256.8	256.8	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.4	287.9	288.0	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6
115°	333.5	333.6	333.9	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3
117.5°	378.5	378.9	379.9	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9
120°	408.0	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0
122.5°	439.2	439.6	440.7	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3
125°	485.0	485.6	486.1	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6
127.5°	529.5	530.2	530.8	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7
130°	559.5	559.9	560.3	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8
132.5°	589.5	590.3	590.2	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1
135°	632.3	632.5	632.2	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8
137.5°	674.0	674.2	673.7	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6
140°	701.9	701.9	701.0	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3
142.5°	727.2	727.0	726.4	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8
145°	765.6	765.5	764.4	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7
147.5°	799.2	798.8	798.1	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6
150°	820.5	820.0	819.3	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7
152.5°	841.8	841.1	840.2	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3
155°	868.8	867.9	867.3	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9
157.5°	893.6	892.3	892.0	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2
160°	908.7	907.5	907.3	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1
162.5°	922.0	920.7	920.6	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6
165°	939.4	938.1	938.1	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9
167.5°	953.7	952.4	952.5	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1
170°	961.6	960.4	960.6	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7
172.5°	967.6	966.3	966.5	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6
175°	974.0	972.7	973.1	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9
177.5°	977.5	976.6	976.9	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	13.1	15.6	16.0	17.9	17.5	18.3	19.2	19.5	19.8	19.2	18.7
90°	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1
92.5°	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4
95°	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8
97.5°	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9
100°	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0
102.5°	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4
105°	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4
107.5°	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7
110°	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0
115°	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2
117.5°	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0
120°	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0
122.5°	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8
125°	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5
127.5°	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8
130°	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1
132.5°	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6
135°	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2
137.5°	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8
140°	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9
142.5°	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3
145°	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9
147.5°	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6
150°	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1
152.5°	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5
155°	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8
157.5°	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9
160°	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7
162.5°	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2
165°	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7
167.5°	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0
170°	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0
172.5°	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9
175°	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3
177.5°	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	19.1	19.0	18.4	18.5	19.1	18.6	18.6
90°	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.6	256.0	255.4	254.9	254.4



TEST NUMBER: P331598-930

CATALOG NUMBER: S122DIW-S1005D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)