

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331517-930

Luminaire Tested: **S122DIW-S485D1240U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331517-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5653.6 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	20	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	1.1
10°-20°	167.6	3.0
20°-30°	246.3	4.4
30°-40°	286.1	5.1
40°-50°	285.8	5.1
50°-60°	249.2	4.4
60°-70°	184.3	3.3
70°-80°	104.4	1.8
80°-90°	31.5	0.6
90°-100°	46.0	0.8
100°-110°	168.6	3.0
110°-120°	450.7	8.0
120°-130°	744.0	13.2
130°-140°	791.2	14.0
140°-150°	735.4	13.0
150°-160°	591.2	10.5
160°-170°	381.0	6.7
170°-180°	131.1	2.3
0°-30°	473.4	8.4
0°-40°	759.4	13.4
0°-60°	1294.4	22.9
0°-90°	1614.5	28.6
90°-120°	665.3	11.8
90°-150°	2935.8	51.9
90°-180°	4039.0	71.4
0°-180°	5653.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	1	12	20	25	27	4
95°	65	34	39	44	43	79
105°	303	316	61	71	76	324
115°	574	591	615	175	82	564
125°	811	824	843	850	853	723
135°	1003	1019	1028	1038	1036	775
145°	1164	1164	1180	1186	1182	728
155°	1282	1274	1285	1290	1282	590
165°	1350	1345	1347	1354	1347	381
175°	1381	1375	1376	1382	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	9.0	9.2	9.5	9.8	10.0	10.3	10.4	10.5	10.7	10.8	10.7
90°	1.0	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0
92.5°	20.1	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7
95°	64.8	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0
97.5°	128.7	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9
100°	176.5	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6
102.5°	229.2	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7
105°	303.2	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3
107.5°	387.6	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7
110°	441.8	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.8	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4
115°	573.5	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7
117.5°	645.5	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7
120°	698.1	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7
122.5°	742.8	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7
125°	810.8	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3
127.5°	872.5	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3
130°	911.6	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9
132.5°	951.5	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0
135°	1003.3	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5
137.5°	1055.7	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3
140°	1090.1	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0
142.5°	1118.8	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4
145°	1163.8	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4
147.5°	1203.1	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3
150°	1228.7	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0
152.5°	1250.3	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0
155°	1281.6	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9
157.5°	1306.1	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4
160°	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8
162.5°	1333.3	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9
165°	1350.4	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9
167.5°	1363.2	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5
170°	1370.4	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9
172.5°	1375.1	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6
175°	1381.3	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9
177.5°	1382.3	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	10.6	10.5	10.4	10.4	10.4	10.3	10.3	10.3
90°	22.2	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.3	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	41.1	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	53.8	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	60.4	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	63.0	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	65.7	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	80.2	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	130.2	108.0	85.9	75.3	76.1	77.0	77.9	78.8



TEST NUMBER: P331517-930

CATALOG NUMBER: S122DIW-S485D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.5	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	410.1	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	631.9	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	736.4	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	781.3	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	845.9	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	905.5	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	943.4	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	980.2	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1032.7	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1081.4	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1113.0	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1142.2	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1182.9	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1218.5	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1240.3	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1260.3	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1287.2	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1309.9	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1323.1	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1335.5	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1363.0	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1369.5	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1374.2	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1379.4	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1380.0	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)