

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331499-930

Luminaire Tested: **S122DIW-S485D435U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331499-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3023.6 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	41	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	2.0
10°-20°	167.6	5.5
20°-30°	246.3	8.1
30°-40°	286.1	9.5
40°-50°	285.8	9.5
50°-60°	249.2	8.2
60°-70°	184.3	6.1
70°-80°	104.4	3.5
80°-90°	29.2	1.0
90°-100°	16.1	0.5
100°-110°	58.9	1.9
110°-120°	157.5	5.2
120°-130°	259.9	8.6
130°-140°	276.4	9.1
140°-150°	256.9	8.5
150°-160°	206.6	6.8
160°-170°	133.1	4.4
170°-180°	45.8	1.5
0°-30°	473.4	15.7
0°-40°	759.4	25.1
0°-60°	1294.4	42.8
0°-90°	1612.3	53.3
90°-120°	232.4	7.7
90°-150°	1025.8	33.9
90°-180°	1411.0	46.7
0°-180°	3023.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	0	4	7	9	9	2
95°	23	12	14	15	15	28
105°	106	110	21	25	26	113
115°	200	206	215	61	28	197
125°	283	288	294	297	298	252
135°	351	356	359	362	362	271
145°	407	407	412	414	413	254
155°	448	445	449	451	448	206
165°	472	470	471	473	471	133
175°	483	480	481	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.8	8.8	8.7	8.7	8.6	8.6	8.5	8.4	8.3	8.2	8.0
90°	0.3	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3
92.5°	7.0	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3
95°	22.7	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9
97.5°	44.9	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5
100°	61.7	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5
102.5°	80.1	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2
105°	105.9	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1
107.5°	135.4	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9
110°	154.3	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.2	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6
115°	200.4	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1
117.5°	225.5	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5
120°	243.9	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3
122.5°	259.5	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5
125°	283.3	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0
127.5°	304.8	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6
130°	318.5	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7
132.5°	332.5	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8
135°	350.6	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0
137.5°	368.9	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1
140°	380.9	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2
142.5°	390.9	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4
145°	406.7	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8
147.5°	420.4	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3
150°	429.3	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9
152.5°	436.8	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9
155°	447.8	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3
157.5°	456.3	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1
160°	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9
162.5°	465.9	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1
165°	471.8	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3
167.5°	476.3	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7
170°	478.8	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9
172.5°	480.5	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6
175°	482.7	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4
177.5°	483.0	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	7.7	7.5	7.3	7.1	7.0	6.9	6.8	6.8
90°	7.7	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.5	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.3	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	18.8	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.1	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.0	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.0	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	28.0	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	45.5	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331499-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	143.3	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	220.8	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	257.3	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.0	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	295.5	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	316.4	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	329.6	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	342.5	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	360.9	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	377.9	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	388.9	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.1	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.4	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	425.7	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.4	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.3	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	449.8	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	457.7	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.3	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	466.6	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.3	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	478.5	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.1	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.0	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.2	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)