

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331544-930

Luminaire Tested: **S122DIW-S675D1240U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331544-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5897.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	1.7
10°-20°	299.8	5.1
20°-30°	435.1	7.4
30°-40°	459.2	7.8
40°-50°	406.6	6.9
50°-60°	324.5	5.5
60°-70°	220.5	3.7
70°-80°	113.1	1.9
80°-90°	32.3	0.5
90°-100°	79.4	1.3
100°-110°	246.5	4.2
110°-120°	421.4	7.1
120°-130°	554.2	9.4
130°-140°	622.0	10.5
140°-150°	609.9	10.3
150°-160°	511.5	8.7
160°-170°	339.3	5.8
170°-180°	118.6	2.0
0°-30°	838.1	14.2
0°-40°	1297.3	22.0
0°-60°	2028.3	34.4
0°-90°	2394.2	40.6
90°-120°	747.3	12.7
90°-150°	2533.4	43.0
90°-180°	3503.0	59.4
0°-180°	5897.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	26
90°	36	1	36	1	36	17
95°	66	55	66	55	66	73
105°	235	227	235	227	235	247
115°	423	423	423	423	423	418
125°	617	615	617	615	617	550
135°	806	796	806	796	806	620
145°	977	966	977	966	977	610
155°	1113	1105	1113	1105	1113	512
165°	1203	1202	1203	1202	1203	339
175°	1246	1251	1246	1251	1246	118
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	15.8	15.8	16.1	15.7	15.7	16.0	16.1	15.9	16.3	16.7	16.1
90°	36.0	35.7	35.5	35.2	35.0	35.1	35.6	36.0	36.5	37.0	31.8
92.5°	34.2	34.2	34.2	34.1	34.1	34.0	33.9	33.8	33.7	33.6	32.4
95°	65.6	66.0	66.4	66.9	67.4	67.7	67.7	67.7	67.7	67.7	67.2
97.5°	113.6	113.6	113.7	113.7	113.7	113.7	113.7	113.7	113.7	113.7	112.8
100°	144.8	145.0	145.3	145.5	145.8	145.9	145.9	145.9	145.9	145.9	145.2
102.5°	180.3	180.6	180.8	181.1	181.3	181.3	181.2	180.9	180.8	180.6	179.7
105°	234.7	234.7	234.7	234.7	234.7	234.5	234.0	233.5	233.0	232.6	232.1
107.5°	285.8	286.9	288.0	289.1	290.2	290.7	290.4	290.2	290.1	289.8	289.8
110°	325.6	326.3	327.0	327.8	328.4	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.6	364.2	364.7	365.2	365.7	366.2	366.8	367.4	367.9	368.5	368.7
115°	422.9	423.5	424.3	425.0	425.7	426.2	426.4	426.6	426.9	427.1	427.5
117.5°	479.3	480.0	480.7	481.4	482.2	482.7	483.3	483.9	484.5	485.0	486.3
120°	519.1	519.8	520.5	521.1	521.9	522.2	522.2	522.2	522.2	522.2	524.1
122.5°	558.0	558.5	559.0	559.5	560.0	560.6	561.2	561.7	562.2	562.8	564.1
125°	617.3	617.6	617.8	618.1	618.3	618.8	619.5	620.2	620.9	621.6	622.3
127.5°	671.5	672.3	673.0	673.8	674.5	675.3	676.1	677.0	677.8	678.7	679.6
130°	710.4	711.3	712.3	713.2	714.2	714.9	715.3	715.8	716.2	716.7	717.2
132.5°	747.6	748.4	749.1	749.9	750.6	751.5	752.5	753.6	754.6	755.6	755.5
135°	805.5	806.2	807.0	807.6	808.4	808.9	809.1	809.3	809.5	809.8	809.3
137.5°	858.0	858.9	859.9	860.8	861.8	862.3	862.5	862.7	862.9	863.1	862.4
140°	894.4	895.3	896.3	897.2	898.1	898.5	898.5	898.5	898.5	898.5	897.4
142.5°	927.3	928.3	929.2	930.2	931.1	931.5	931.3	931.1	930.9	930.7	929.9
145°	976.8	977.8	978.7	979.7	980.6	980.9	980.7	980.5	980.2	980.0	978.6
147.5°	1021.0	1021.9	1022.8	1023.7	1024.6	1024.7	1024.3	1023.7	1023.2	1022.7	1021.7
150°	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8	1048.8
152.5°	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8	1075.7
155°	1113.2	1113.9	1114.6	1115.3	1116.0	1115.7	1114.6	1113.5	1112.2	1111.1	1110.4
157.5°	1144.4	1145.6	1146.7	1147.9	1149.0	1148.8	1147.1	1145.6	1143.9	1142.4	1141.9
160°	1163.9	1164.9	1165.8	1166.8	1167.7	1167.4	1166.0	1164.7	1163.2	1161.8	1161.6
162.5°	1180.9	1181.9	1183.1	1184.2	1185.4	1185.1	1183.5	1181.9	1180.3	1178.8	1178.5
165°	1203.1	1204.2	1205.4	1206.6	1207.7	1207.5	1205.8	1204.2	1202.6	1200.9	1200.9
167.5°	1221.2	1222.5	1223.7	1224.9	1226.1	1225.9	1224.3	1222.6	1221.0	1219.3	1219.4
170°	1230.5	1231.9	1233.4	1234.8	1236.2	1236.1	1234.4	1232.7	1231.1	1229.5	1229.7
172.5°	1238.1	1239.6	1241.0	1242.4	1243.7	1243.7	1242.0	1240.4	1238.8	1237.1	1237.3
175°	1246.3	1247.8	1249.2	1250.6	1252.1	1251.9	1250.3	1248.6	1247.0	1245.3	1245.8
177.5°	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2	1250.6
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	15.3	14.3	13.3	13.1	11.6	11.0	9.1	7.5	7.7	8.0	7.9
90°	26.7	21.5	16.3	12.3	9.5	6.7	3.9	1.1	3.9	6.7	9.5
92.5°	31.1	29.9	28.7	27.1	25.0	23.0	20.9	18.8	20.9	23.0	25.0
95°	66.7	66.3	65.8	64.4	62.0	59.7	57.3	55.0	57.3	59.7	62.0
97.5°	111.9	111.0	110.1	108.7	106.6	104.6	102.5	100.4	102.5	104.6	106.6
100°	144.5	143.7	143.1	141.8	139.9	138.0	136.2	134.3	136.2	138.0	139.9
102.5°	178.8	177.9	177.0	175.8	174.3	172.8	171.3	169.7	171.3	172.8	174.3
105°	231.6	231.1	230.7	230.1	229.4	228.7	228.0	227.3	228.0	228.7	229.4
107.5°	289.8	289.8	289.8	289.3	288.3	287.3	286.3	285.2	286.3	287.3	288.3
110°	328.8	328.8	328.8	328.1	326.7	325.2	323.8	322.5	323.8	325.2	326.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.9	369.1	369.2	368.7	367.3	365.8	364.4	363.1	364.4	365.8	367.3
115°	428.0	428.5	428.9	428.5	427.1	425.7	424.3	422.9	424.3	425.7	427.1
117.5°	487.6	488.9	490.3	490.0	488.1	486.2	484.4	482.5	484.4	486.2	488.1
120°	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	524.1	526.0	527.9
122.5°	565.5	566.8	568.1	567.6	565.3	563.1	560.8	558.6	560.8	563.1	565.3
125°	623.1	623.7	624.4	623.7	621.6	619.5	617.3	615.2	617.3	619.5	621.6
127.5°	680.4	681.3	682.1	681.2	678.5	675.8	673.1	670.4	673.1	675.8	678.5
130°	717.7	718.2	718.6	717.3	714.3	711.3	708.2	705.2	708.2	711.3	714.3
132.5°	755.5	755.4	755.3	754.0	751.5	749.0	746.5	744.0	746.5	749.0	751.5
135°	808.9	808.4	807.9	806.4	803.8	801.2	798.6	796.1	798.6	801.2	803.8
137.5°	861.9	861.2	860.6	859.2	857.1	855.0	852.9	850.8	852.9	855.0	857.1
140°	896.3	895.0	893.9	892.3	890.1	888.0	885.9	883.8	885.9	888.0	890.1
142.5°	929.1	928.3	927.5	926.1	924.0	921.9	919.7	917.6	919.7	921.9	924.0
145°	977.1	975.8	974.4	972.8	971.2	969.6	967.9	966.2	967.9	969.6	971.2
147.5°	1020.8	1019.9	1019.0	1017.5	1015.5	1013.5	1011.5	1009.6	1011.5	1013.5	1015.5
150°	1047.9	1046.9	1046.0	1044.8	1043.4	1042.0	1040.6	1039.2	1040.6	1042.0	1043.4
152.5°	1074.6	1073.4	1072.3	1071.1	1069.6	1068.2	1066.8	1065.4	1066.8	1068.2	1069.6
155°	1109.6	1109.0	1108.2	1107.6	1106.9	1106.1	1105.5	1104.7	1105.5	1106.1	1106.9
157.5°	1141.5	1141.1	1140.7	1140.2	1139.8	1139.3	1138.8	1138.3	1138.8	1139.3	1139.8
160°	1161.3	1161.1	1160.9	1160.5	1160.1	1159.6	1159.1	1158.6	1159.1	1159.6	1160.1
162.5°	1178.3	1178.0	1177.8	1177.6	1177.5	1177.5	1177.4	1177.2	1177.4	1177.5	1177.5
165°	1200.9	1200.9	1200.9	1201.0	1201.3	1201.5	1201.8	1202.0	1201.8	1201.5	1201.3
167.5°	1219.4	1219.4	1219.5	1219.9	1220.6	1221.3	1222.0	1222.7	1222.0	1221.3	1220.6
170°	1230.0	1230.2	1230.4	1230.9	1231.6	1232.3	1233.0	1233.7	1233.0	1232.3	1231.6
172.5°	1237.5	1237.8	1238.0	1238.5	1239.2	1239.9	1240.6	1241.3	1240.6	1239.9	1239.2
175°	1246.3	1246.8	1247.2	1247.8	1248.5	1249.2	1249.9	1250.6	1249.9	1249.2	1248.5
177.5°	1250.9	1251.3	1251.7	1252.1	1252.7	1253.3	1253.8	1254.4	1253.8	1253.3	1252.7
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	8.2	8.6	9.3	10.4	11.0	11.7	11.3	11.2	11.1	10.4	10.4
90°	12.3	16.3	21.5	26.7	31.8	37.0	36.5	36.0	35.6	35.1	35.0
92.5°	27.1	28.7	29.9	31.1	32.4	33.6	33.7	33.8	33.9	34.0	34.1
95°	64.4	65.8	66.3	66.7	67.2	67.7	67.7	67.7	67.7	67.7	67.4
97.5°	108.7	110.1	111.0	111.9	112.8	113.7	113.7	113.7	113.7	113.7	113.7
100°	141.8	143.1	143.7	144.5	145.2	145.9	145.9	145.9	145.9	145.9	145.8
102.5°	175.8	177.0	177.9	178.8	179.7	180.6	180.8	180.9	181.2	181.3	181.3
105°	230.1	230.7	231.1	231.6	232.1	232.6	233.0	233.5	234.0	234.5	234.7
107.5°	289.3	289.8	289.8	289.8	289.8	289.8	290.1	290.2	290.4	290.7	290.2
110°	328.1	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.8	328.4



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.7	369.2	369.1	368.9	368.7	368.5	367.9	367.4	366.8	366.2	365.7
115°	428.5	428.9	428.5	428.0	427.5	427.1	426.9	426.6	426.4	426.2	425.7
117.5°	490.0	490.3	488.9	487.6	486.3	485.0	484.5	483.9	483.3	482.7	482.2
120°	529.8	529.8	527.9	526.0	524.1	522.2	522.2	522.2	522.2	522.2	521.9
122.5°	567.6	568.1	566.8	565.5	564.1	562.8	562.2	561.7	561.2	560.6	560.0
125°	623.7	624.4	623.7	623.1	622.3	621.6	620.9	620.2	619.5	618.8	618.3
127.5°	681.2	682.1	681.3	680.4	679.6	678.7	677.8	677.0	676.1	675.3	674.5
130°	717.3	718.6	718.2	717.7	717.2	716.7	716.2	715.8	715.3	714.9	714.2
132.5°	754.0	755.3	755.4	755.5	755.5	755.6	754.6	753.6	752.5	751.5	750.6
135°	806.4	807.9	808.4	808.9	809.3	809.8	809.5	809.3	809.1	808.9	808.4
137.5°	859.2	860.6	861.2	861.9	862.4	863.1	862.9	862.7	862.5	862.3	861.8
140°	892.3	893.9	895.0	896.3	897.4	898.5	898.5	898.5	898.5	898.5	898.1
142.5°	926.1	927.5	928.3	929.1	929.9	930.7	930.9	931.1	931.3	931.5	931.1
145°	972.8	974.4	975.8	977.1	978.6	980.0	980.2	980.5	980.7	980.9	980.6
147.5°	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2	1023.7	1024.3	1024.7	1024.6
150°	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6
152.5°	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4
155°	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2	1113.5	1114.6	1115.7	1116.0
157.5°	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9	1145.6	1147.1	1148.8	1149.0
160°	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2	1164.7	1166.0	1167.4	1167.7
162.5°	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3	1181.9	1183.5	1185.1	1185.4
165°	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6	1204.2	1205.8	1207.5	1207.7
167.5°	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0	1222.6	1224.3	1225.9	1226.1
170°	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1	1232.7	1234.4	1236.1	1236.2
172.5°	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8	1240.4	1242.0	1243.7	1243.7
175°	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0	1248.6	1250.3	1251.9	1252.1
177.5°	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	10.4	10.1	10.1	9.9	10.1	10.1	10.4	10.4	10.4	11.1	11.2
90°	35.2	35.5	35.7	36.0	35.7	35.5	35.2	35.0	35.1	35.6	36.0
92.5°	34.1	34.2	34.2	34.2	34.2	34.2	34.1	34.1	34.0	33.9	33.8
95°	66.9	66.4	66.0	65.6	66.0	66.4	66.9	67.4	67.7	67.7	67.7
97.5°	113.7	113.7	113.6	113.6	113.6	113.7	113.7	113.7	113.7	113.7	113.7
100°	145.5	145.3	145.0	144.8	145.0	145.3	145.5	145.8	145.9	145.9	145.9
102.5°	181.1	180.8	180.6	180.3	180.6	180.8	181.1	181.3	181.3	181.2	180.9
105°	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.5	234.0	233.5
107.5°	289.1	288.0	286.9	285.8	286.9	288.0	289.1	290.2	290.7	290.4	290.2
110°	327.8	327.0	326.3	325.6	326.3	327.0	327.8	328.4	328.8	328.8	328.8



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	365.2	364.7	364.2	363.6	364.2	364.7	365.2	365.7	366.2	366.8	367.4
115°	425.0	424.3	423.5	422.9	423.5	424.3	425.0	425.7	426.2	426.4	426.6
117.5°	481.4	480.7	480.0	479.3	480.0	480.7	481.4	482.2	482.7	483.3	483.9
120°	521.1	520.5	519.8	519.1	519.8	520.5	521.1	521.9	522.2	522.2	522.2
122.5°	559.5	559.0	558.5	558.0	558.5	559.0	559.5	560.0	560.6	561.2	561.7
125°	618.1	617.8	617.6	617.3	617.6	617.8	618.1	618.3	618.8	619.5	620.2
127.5°	673.8	673.0	672.3	671.5	672.3	673.0	673.8	674.5	675.3	676.1	677.0
130°	713.2	712.3	711.3	710.4	711.3	712.3	713.2	714.2	714.9	715.3	715.8
132.5°	749.9	749.1	748.4	747.6	748.4	749.1	749.9	750.6	751.5	752.5	753.6
135°	807.6	807.0	806.2	805.5	806.2	807.0	807.6	808.4	808.9	809.1	809.3
137.5°	860.8	859.9	858.9	858.0	858.9	859.9	860.8	861.8	862.3	862.5	862.7
140°	897.2	896.3	895.3	894.4	895.3	896.3	897.2	898.1	898.5	898.5	898.5
142.5°	930.2	929.2	928.3	927.3	928.3	929.2	930.2	931.1	931.5	931.3	931.1
145°	979.7	978.7	977.8	976.8	977.8	978.7	979.7	980.6	980.9	980.7	980.5
147.5°	1023.7	1022.8	1021.9	1021.0	1021.9	1022.8	1023.7	1024.6	1024.7	1024.3	1023.7
150°	1051.9	1051.2	1050.4	1049.8	1050.4	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2
152.5°	1079.5	1078.6	1077.7	1076.8	1077.7	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6
155°	1115.3	1114.6	1113.9	1113.2	1113.9	1114.6	1115.3	1116.0	1115.7	1114.6	1113.5
157.5°	1147.9	1146.7	1145.6	1144.4	1145.6	1146.7	1147.9	1149.0	1148.8	1147.1	1145.6
160°	1166.8	1165.8	1164.9	1163.9	1164.9	1165.8	1166.8	1167.7	1167.4	1166.0	1164.7
162.5°	1184.2	1183.1	1181.9	1180.9	1181.9	1183.1	1184.2	1185.4	1185.1	1183.5	1181.9
165°	1206.6	1205.4	1204.2	1203.1	1204.2	1205.4	1206.6	1207.7	1207.5	1205.8	1204.2
167.5°	1224.9	1223.7	1222.5	1221.2	1222.5	1223.7	1224.9	1226.1	1225.9	1224.3	1222.6
170°	1234.8	1233.4	1231.9	1230.5	1231.9	1233.4	1234.8	1236.2	1236.1	1234.4	1232.7
172.5°	1242.4	1241.0	1239.6	1238.1	1239.6	1241.0	1242.4	1243.7	1243.7	1242.0	1240.4
175°	1250.6	1249.2	1247.8	1246.3	1247.8	1249.2	1250.6	1252.1	1251.9	1250.3	1248.6
177.5°	1253.6	1252.5	1251.3	1250.2	1251.3	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	11.3	11.7	11.0	10.4	9.3	8.6	8.2	7.9	8.0	7.7	7.5
90°	36.5	37.0	31.8	26.7	21.5	16.3	12.3	9.5	6.7	3.9	1.1
92.5°	33.7	33.6	32.4	31.1	29.9	28.7	27.1	25.0	23.0	20.9	18.8
95°	67.7	67.7	67.2	66.7	66.3	65.8	64.4	62.0	59.7	57.3	55.0
97.5°	113.7	113.7	112.8	111.9	111.0	110.1	108.7	106.6	104.6	102.5	100.4
100°	145.9	145.9	145.2	144.5	143.7	143.1	141.8	139.9	138.0	136.2	134.3
102.5°	180.8	180.6	179.7	178.8	177.9	177.0	175.8	174.3	172.8	171.3	169.7
105°	233.0	232.6	232.1	231.6	231.1	230.7	230.1	229.4	228.7	228.0	227.3
107.5°	290.1	289.8	289.8	289.8	289.8	289.8	289.3	288.3	287.3	286.3	285.2
110°	328.8	328.8	328.8	328.8	328.8	328.8	328.1	326.7	325.2	323.8	322.5



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	367.9	368.5	368.7	368.9	369.1	369.2	368.7	367.3	365.8	364.4	363.1
115°	426.9	427.1	427.5	428.0	428.5	428.9	428.5	427.1	425.7	424.3	422.9
117.5°	484.5	485.0	486.3	487.6	488.9	490.3	490.0	488.1	486.2	484.4	482.5
120°	522.2	522.2	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2
122.5°	562.2	562.8	564.1	565.5	566.8	568.1	567.6	565.3	563.1	560.8	558.6
125°	620.9	621.6	622.3	623.1	623.7	624.4	623.7	621.6	619.5	617.3	615.2
127.5°	677.8	678.7	679.6	680.4	681.3	682.1	681.2	678.5	675.8	673.1	670.4
130°	716.2	716.7	717.2	717.7	718.2	718.6	717.3	714.3	711.3	708.2	705.2
132.5°	754.6	755.6	755.5	755.5	755.4	755.3	754.0	751.5	749.0	746.5	744.0
135°	809.5	809.8	809.3	808.9	808.4	807.9	806.4	803.8	801.2	798.6	796.1
137.5°	862.9	863.1	862.4	861.9	861.2	860.6	859.2	857.1	855.0	852.9	850.8
140°	898.5	898.5	897.4	896.3	895.0	893.9	892.3	890.1	888.0	885.9	883.8
142.5°	930.9	930.7	929.9	929.1	928.3	927.5	926.1	924.0	921.9	919.7	917.6
145°	980.2	980.0	978.6	977.1	975.8	974.4	972.8	971.2	969.6	967.9	966.2
147.5°	1023.2	1022.7	1021.7	1020.8	1019.9	1019.0	1017.5	1015.5	1013.5	1011.5	1009.6
150°	1050.4	1049.8	1048.8	1047.9	1046.9	1046.0	1044.8	1043.4	1042.0	1040.6	1039.2
152.5°	1077.7	1076.8	1075.7	1074.6	1073.4	1072.3	1071.1	1069.6	1068.2	1066.8	1065.4
155°	1112.2	1111.1	1110.4	1109.6	1109.0	1108.2	1107.6	1106.9	1106.1	1105.5	1104.7
157.5°	1143.9	1142.4	1141.9	1141.5	1141.1	1140.7	1140.2	1139.8	1139.3	1138.8	1138.3
160°	1163.2	1161.8	1161.6	1161.3	1161.1	1160.9	1160.5	1160.1	1159.6	1159.1	1158.6
162.5°	1180.3	1178.8	1178.5	1178.3	1178.0	1177.8	1177.6	1177.5	1177.5	1177.4	1177.2
165°	1202.6	1200.9	1200.9	1200.9	1200.9	1200.9	1201.0	1201.3	1201.5	1201.8	1202.0
167.5°	1221.0	1219.3	1219.4	1219.4	1219.4	1219.5	1219.9	1220.6	1221.3	1222.0	1222.7
170°	1231.1	1229.5	1229.7	1230.0	1230.2	1230.4	1230.9	1231.6	1232.3	1233.0	1233.7
172.5°	1238.8	1237.1	1237.3	1237.5	1237.8	1238.0	1238.5	1239.2	1239.9	1240.6	1241.3
175°	1247.0	1245.3	1245.8	1246.3	1246.8	1247.2	1247.8	1248.5	1249.2	1249.9	1250.6
177.5°	1251.3	1250.2	1250.6	1250.9	1251.3	1251.7	1252.1	1252.7	1253.3	1253.8	1254.4
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	9.1	11.0	11.6	13.1	13.3	14.3	15.3	16.1	16.7	16.3	15.9
90°	3.9	6.7	9.5	12.3	16.3	21.5	26.7	31.8	37.0	36.5	36.0
92.5°	20.9	23.0	25.0	27.1	28.7	29.9	31.1	32.4	33.6	33.7	33.8
95°	57.3	59.7	62.0	64.4	65.8	66.3	66.7	67.2	67.7	67.7	67.7
97.5°	102.5	104.6	106.6	108.7	110.1	111.0	111.9	112.8	113.7	113.7	113.7
100°	136.2	138.0	139.9	141.8	143.1	143.7	144.5	145.2	145.9	145.9	145.9
102.5°	171.3	172.8	174.3	175.8	177.0	177.9	178.8	179.7	180.6	180.8	180.9
105°	228.0	228.7	229.4	230.1	230.7	231.1	231.6	232.1	232.6	233.0	233.5
107.5°	286.3	287.3	288.3	289.3	289.8	289.8	289.8	289.8	289.8	290.1	290.2
110°	323.8	325.2	326.7	328.1	328.8	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	364.4	365.8	367.3	368.7	369.2	369.1	368.9	368.7	368.5	367.9	367.4
115°	424.3	425.7	427.1	428.5	428.9	428.5	428.0	427.5	427.1	426.9	426.6
117.5°	484.4	486.2	488.1	490.0	490.3	488.9	487.6	486.3	485.0	484.5	483.9
120°	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	522.2	522.2
122.5°	560.8	563.1	565.3	567.6	568.1	566.8	565.5	564.1	562.8	562.2	561.7
125°	617.3	619.5	621.6	623.7	624.4	623.7	623.1	622.3	621.6	620.9	620.2
127.5°	673.1	675.8	678.5	681.2	682.1	681.3	680.4	679.6	678.7	677.8	677.0
130°	708.2	711.3	714.3	717.3	718.6	718.2	717.7	717.2	716.7	716.2	715.8
132.5°	746.5	749.0	751.5	754.0	755.3	755.4	755.5	755.5	755.6	754.6	753.6
135°	798.6	801.2	803.8	806.4	807.9	808.4	808.9	809.3	809.8	809.5	809.3
137.5°	852.9	855.0	857.1	859.2	860.6	861.2	861.9	862.4	863.1	862.9	862.7
140°	885.9	888.0	890.1	892.3	893.9	895.0	896.3	897.4	898.5	898.5	898.5
142.5°	919.7	921.9	924.0	926.1	927.5	928.3	929.1	929.9	930.7	930.9	931.1
145°	967.9	969.6	971.2	972.8	974.4	975.8	977.1	978.6	980.0	980.2	980.5
147.5°	1011.5	1013.5	1015.5	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2	1023.7
150°	1040.6	1042.0	1043.4	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4	1051.2
152.5°	1066.8	1068.2	1069.6	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7	1078.6
155°	1105.5	1106.1	1106.9	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2	1113.5
157.5°	1138.8	1139.3	1139.8	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9	1145.6
160°	1159.1	1159.6	1160.1	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2	1164.7
162.5°	1177.4	1177.5	1177.5	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3	1181.9
165°	1201.8	1201.5	1201.3	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6	1204.2
167.5°	1222.0	1221.3	1220.6	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0	1222.6
170°	1233.0	1232.3	1231.6	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1	1232.7
172.5°	1240.6	1239.9	1239.2	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8	1240.4
175°	1249.9	1249.2	1248.5	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0	1248.6
177.5°	1253.8	1253.3	1252.7	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3	1252.5
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	16.1	16.0	15.7	15.7	16.1	15.8	15.8
90°	35.6	35.1	35.0	35.2	35.5	35.7	36.0
92.5°	33.9	34.0	34.1	34.1	34.2	34.2	34.2
95°	67.7	67.7	67.4	66.9	66.4	66.0	65.6
97.5°	113.7	113.7	113.7	113.7	113.7	113.6	113.6
100°	145.9	145.9	145.8	145.5	145.3	145.0	144.8
102.5°	181.2	181.3	181.3	181.1	180.8	180.6	180.3
105°	234.0	234.5	234.7	234.7	234.7	234.7	234.7
107.5°	290.4	290.7	290.2	289.1	288.0	286.9	285.8
110°	328.8	328.8	328.4	327.8	327.0	326.3	325.6



TEST NUMBER: P331544-930

CATALOG NUMBER: S122DIW-S675D1240U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	366.8	366.2	365.7	365.2	364.7	364.2	363.6
115°	426.4	426.2	425.7	425.0	424.3	423.5	422.9
117.5°	483.3	482.7	482.2	481.4	480.7	480.0	479.3
120°	522.2	522.2	521.9	521.1	520.5	519.8	519.1
122.5°	561.2	560.6	560.0	559.5	559.0	558.5	558.0
125°	619.5	618.8	618.3	618.1	617.8	617.6	617.3
127.5°	676.1	675.3	674.5	673.8	673.0	672.3	671.5
130°	715.3	714.9	714.2	713.2	712.3	711.3	710.4
132.5°	752.5	751.5	750.6	749.9	749.1	748.4	747.6
135°	809.1	808.9	808.4	807.6	807.0	806.2	805.5
137.5°	862.5	862.3	861.8	860.8	859.9	858.9	858.0
140°	898.5	898.5	898.1	897.2	896.3	895.3	894.4
142.5°	931.3	931.5	931.1	930.2	929.2	928.3	927.3
145°	980.7	980.9	980.6	979.7	978.7	977.8	976.8
147.5°	1024.3	1024.7	1024.6	1023.7	1022.8	1021.9	1021.0
150°	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8
152.5°	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8
155°	1114.6	1115.7	1116.0	1115.3	1114.6	1113.9	1113.2
157.5°	1147.1	1148.8	1149.0	1147.9	1146.7	1145.6	1144.4
160°	1166.0	1167.4	1167.7	1166.8	1165.8	1164.9	1163.9
162.5°	1183.5	1185.1	1185.4	1184.2	1183.1	1181.9	1180.9
165°	1205.8	1207.5	1207.7	1206.6	1205.4	1204.2	1203.1
167.5°	1224.3	1225.9	1226.1	1224.9	1223.7	1222.5	1221.2
170°	1234.4	1236.1	1236.2	1234.8	1233.4	1231.9	1230.5
172.5°	1242.0	1243.7	1243.7	1242.4	1241.0	1239.6	1238.1
175°	1250.3	1251.9	1252.1	1250.6	1249.2	1247.8	1246.3
177.5°	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7

(END OF REPORT)