

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331535-930

Luminaire Tested: **S122DIW-S675D710U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331535-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4515.7 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41					41			
2	89	81	75	70	82	75	70	65	63	60	56	53	50	47	43	41	39	34					34			
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29					29			
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25					25			
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25	22					22			
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19					19			
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17					17			
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15					15			
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14					14			
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.8
10°-20°	229.0	5.1
20°-30°	336.6	7.5
30°-40°	391.0	8.7
40°-50°	390.6	8.7
50°-60°	340.6	7.5
60°-70°	251.9	5.6
70°-80°	142.7	3.2
80°-90°	40.3	0.9
90°-100°	26.3	0.6
100°-110°	96.5	2.1
110°-120°	257.9	5.7
120°-130°	425.7	9.4
130°-140°	452.8	10.0
140°-150°	420.8	9.3
150°-160°	338.4	7.5
160°-170°	218.0	4.8
170°-180°	75.1	1.7
0°-30°	647.0	14.3
0°-40°	1038.1	23.0
0°-60°	1769.3	39.2
0°-90°	2204.2	48.8
90°-120°	380.7	8.4
90°-150°	1680.1	37.2
90°-180°	2312.0	51.2
0°-180°	4515.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	7	11	14	15	3
95°	37	20	22	25	24	45
105°	174	181	35	41	43	185
115°	328	338	352	100	47	323
125°	464	472	482	486	488	414
135°	574	583	588	594	593	443
145°	666	666	675	679	676	416
155°	733	729	735	738	734	338
165°	773	770	771	775	771	218
175°	790	787	788	791	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.1	12.1	12.1	12.1	12.0	11.9	11.8	11.7	11.6	11.3
90°	0.6	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1
92.5°	11.5	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5
95°	37.1	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9
97.5°	73.6	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3
100°	101.0	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5
102.5°	131.2	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7
105°	173.5	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2
107.5°	221.8	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3
110°	252.8	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.1	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7
115°	328.2	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4
117.5°	369.4	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9
120°	399.5	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9
122.5°	425.1	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2
125°	464.0	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1
127.5°	499.3	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9
130°	521.6	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5
132.5°	544.5	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7
135°	574.2	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7
137.5°	604.2	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7
140°	623.9	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9
142.5°	640.3	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6
145°	666.1	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1
147.5°	688.5	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7
150°	703.2	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1
152.5°	715.5	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5
155°	733.4	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9
157.5°	747.5	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8
160°	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4
162.5°	763.0	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4
165°	772.8	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0
167.5°	780.1	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2
170°	784.2	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9
172.5°	786.9	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5
175°	790.5	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6
177.5°	791.1	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	11.0	10.7	10.4	10.1	10.0	9.9	9.9	9.7
90°	12.7	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	13.9	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	23.6	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	30.8	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	34.6	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	36.1	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	37.6	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	45.9	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	74.5	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331535-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.4	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	234.7	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	361.7	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	421.4	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	447.1	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.0	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	518.2	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	539.9	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	560.9	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	591.0	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	618.9	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	637.0	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	653.6	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	676.9	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	697.3	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	709.8	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	721.2	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	736.6	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	749.7	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	757.2	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	764.3	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	780.1	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	783.7	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	786.4	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	789.5	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	789.8	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)