

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331536-930

Luminaire Tested: **S122DIW-S675D710U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331536-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4209.7 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.9
10°-20°	229.0	5.4
20°-30°	336.6	8.0
30°-40°	391.0	9.3
40°-50°	390.6	9.3
50°-60°	340.6	8.1
60°-70°	251.9	6.0
70°-80°	142.7	3.4
80°-90°	41.2	1.0
90°-100°	45.4	1.1
100°-110°	141.1	3.4
110°-120°	241.2	5.7
120°-130°	317.1	7.5
130°-140°	356.0	8.5
140°-150°	349.0	8.3
150°-160°	292.8	7.0
160°-170°	194.2	4.6
170°-180°	67.9	1.6
0°-30°	647.0	15.4
0°-40°	1038.1	24.7
0°-60°	1769.3	42.0
0°-90°	2205.1	52.4
90°-120°	427.7	10.2
90°-150°	1449.8	34.4
90°-180°	2005.0	47.6
0°-180°	4209.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	8	21	20	20	3
95°	32	37	39	39	38	36
105°	130	132	133	134	134	137
115°	242	245	244	244	242	239
125°	352	357	356	354	353	315
135°	456	462	463	463	461	352
145°	553	557	561	561	559	345
155°	632	634	636	639	637	291
165°	688	687	687	691	688	194
175°	716	714	713	716	713	68
180°	717	717	717	717	717	



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.1	12.1	12.1	12.2	12.4	12.6	13.0	13.3	13.5	13.0
90°	0.6	2.2	3.8	5.5	7.1	9.4	12.3	15.2	18.2	21.2	20.9
92.5°	10.8	12.0	13.1	14.3	15.5	16.5	17.1	17.9	18.5	19.2	19.3
95°	31.5	32.8	34.2	35.5	36.9	37.7	37.9	38.2	38.5	38.7	38.7
97.5°	57.5	58.6	59.8	61.0	62.2	63.0	63.6	64.1	64.6	65.1	65.1
100°	76.8	77.9	79.0	80.1	81.1	81.9	82.3	82.7	83.1	83.5	83.5
102.5°	97.2	98.0	98.9	99.7	100.6	101.3	101.8	102.3	102.8	103.3	103.5
105°	130.0	130.4	130.9	131.3	131.7	132.0	132.3	132.6	132.8	133.1	133.4
107.5°	163.2	163.8	164.4	165.0	165.6	165.9	165.9	165.9	165.9	165.9	166.0
110°	184.5	185.3	186.1	186.9	187.8	188.2	188.2	188.2	188.2	188.2	188.2



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.7	208.6	209.4	210.2	211.0	211.3	211.2	211.1	211.0	210.9	210.6
115°	242.0	242.8	243.6	244.4	245.2	245.5	245.2	244.9	244.7	244.4	244.3
117.5°	276.1	277.2	278.3	279.3	280.4	280.5	279.8	279.1	278.3	277.6	277.3
120°	298.9	299.9	301.0	302.1	303.1	303.1	302.1	301.0	299.9	298.9	298.9
122.5°	319.7	321.0	322.3	323.5	324.8	325.1	324.3	323.6	322.9	322.1	321.8
125°	352.1	353.4	354.5	355.7	356.9	357.3	356.9	356.5	356.1	355.7	355.3
127.5°	383.7	385.2	386.8	388.2	389.8	390.4	389.9	389.4	388.9	388.4	387.9
130°	403.5	405.3	407.0	408.8	410.5	411.2	411.0	410.7	410.4	410.2	409.9
132.5°	425.8	427.2	428.7	430.1	431.5	432.3	432.3	432.4	432.4	432.4	431.9
135°	455.6	457.1	458.5	460.0	461.5	462.4	462.6	462.9	463.2	463.4	463.3
137.5°	486.9	488.1	489.3	490.6	491.7	492.5	492.8	493.3	493.6	493.9	493.8
140°	505.8	507.0	508.2	509.4	510.6	511.5	512.3	512.9	513.6	514.2	514.2
142.5°	525.1	526.4	527.6	528.8	529.9	530.8	531.2	531.7	532.1	532.6	532.7
145°	552.9	553.9	554.8	555.8	556.8	557.6	558.4	559.2	560.0	560.8	560.9
147.5°	577.8	578.9	580.0	581.1	582.3	583.1	583.7	584.2	584.7	585.3	585.5
150°	594.7	595.5	596.3	597.1	597.9	598.6	599.2	599.7	600.2	600.8	601.2
152.5°	609.7	610.5	611.3	612.1	612.9	613.7	614.3	615.0	615.6	616.3	616.8
155°	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.4	635.9	636.5
157.5°	651.4	651.8	652.0	652.2	652.6	652.8	653.1	653.3	653.5	653.8	654.7
160°	663.1	663.3	663.6	663.9	664.1	664.4	664.5	664.6	664.7	664.9	665.7
162.5°	673.7	673.8	673.8	673.8	673.9	674.0	674.2	674.3	674.4	674.6	675.5
165°	687.9	687.7	687.6	687.5	687.4	687.3	687.3	687.3	687.3	687.3	688.2
167.5°	699.8	699.4	699.0	698.5	698.1	697.9	697.9	697.8	697.8	697.8	698.7
170°	706.0	705.6	705.2	704.8	704.4	704.2	704.0	703.8	703.8	703.6	704.6
172.5°	710.4	710.0	709.6	709.1	708.7	708.5	708.3	708.3	708.1	707.9	708.9
175°	715.7	715.3	714.9	714.5	714.1	713.8	713.5	713.2	713.0	712.7	713.6
177.5°	717.9	717.5	717.2	716.9	716.6	716.3	716.1	715.9	715.7	715.4	716.1
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	12.6	12.1	11.6	11.3	11.2	11.0	10.9	10.8
90°	20.6	20.4	20.1	20.1	20.1	20.3	20.5	20.5
92.5°	19.3	19.4	19.5	19.5	19.5	19.6	19.6	19.6
95°	38.7	38.7	38.7	38.6	38.3	38.1	37.7	37.5
97.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.0	65.0
100°	83.5	83.5	83.5	83.4	83.3	83.2	83.0	82.9
102.5°	103.5	103.6	103.8	103.8	103.6	103.5	103.4	103.2
105°	133.6	133.9	134.2	134.3	134.3	134.3	134.3	134.3
107.5°	166.1	166.2	166.3	166.1	165.4	164.9	164.2	163.6
110°	188.2	188.2	188.2	187.9	187.5	187.1	186.7	186.4



TEST NUMBER: P331536-930

CATALOG NUMBER: S122DIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	209.9	209.6	209.3	209.0	208.7	208.4	208.1
115°	244.2	244.0	243.9	243.6	243.2	242.8	242.4	242.0
117.5°	277.0	276.6	276.3	275.9	275.5	275.1	274.7	274.3
120°	298.9	298.9	298.9	298.6	298.2	297.8	297.4	297.0
122.5°	321.5	321.1	320.8	320.5	320.2	319.9	319.6	319.4
125°	354.9	354.5	354.1	353.8	353.8	353.6	353.4	353.4
127.5°	387.4	386.9	386.5	386.0	385.6	385.1	384.7	384.3
130°	409.7	409.4	409.1	408.7	408.1	407.6	407.1	406.6
132.5°	431.3	430.6	430.1	429.6	429.2	428.7	428.3	427.9
135°	463.2	463.0	462.9	462.6	462.2	461.8	461.4	461.0
137.5°	493.7	493.6	493.5	493.2	492.6	492.1	491.5	491.0
140°	514.2	514.2	514.2	514.0	513.5	512.9	512.3	511.8
142.5°	532.9	533.0	533.0	532.9	532.3	531.7	531.2	530.7
145°	561.1	561.3	561.3	561.2	560.6	560.1	559.5	559.1
147.5°	585.9	586.1	586.4	586.4	585.9	585.3	584.8	584.3
150°	601.5	601.9	602.3	602.3	601.9	601.5	601.2	600.8
152.5°	617.3	617.8	618.3	618.3	617.8	617.3	616.8	616.3
155°	637.2	637.9	638.5	638.7	638.3	637.9	637.5	637.1
157.5°	655.6	656.5	657.4	657.5	656.9	656.2	655.6	654.9
160°	666.5	667.3	668.1	668.2	667.7	667.2	666.7	666.1
162.5°	676.4	677.4	678.2	678.3	677.7	677.1	676.5	675.8
165°	689.2	690.1	691.0	691.2	690.5	689.8	689.2	688.5
167.5°	699.7	700.6	701.6	701.6	701.0	700.3	699.6	698.9
170°	705.5	706.5	707.4	707.4	706.6	705.8	705.0	704.2
172.5°	709.9	710.8	711.8	711.8	711.0	710.2	709.4	708.6
175°	714.5	715.5	716.5	716.5	715.7	714.9	714.1	713.3
177.5°	716.7	717.4	718.0	718.0	717.4	716.7	716.1	715.4
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9

(END OF REPORT)