

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331589-927

Luminaire Tested: **S122DIW-S1005D435U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331589-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4584.7 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.6
10°-20°	334.1	7.3
20°-30°	491.0	10.7
30°-40°	570.4	12.4
40°-50°	569.8	12.4
50°-60°	496.9	10.8
60°-70°	367.4	8.0
70°-80°	208.1	4.5
80°-90°	57.1	1.2
90°-100°	15.6	0.3
100°-110°	57.2	1.2
110°-120°	153.0	3.3
120°-130°	252.6	5.5
130°-140°	268.6	5.9
140°-150°	249.7	5.4
150°-160°	200.7	4.4
160°-170°	129.3	2.8
170°-180°	44.5	1.0
0°-30°	943.8	20.6
0°-40°	1514.2	33.0
0°-60°	2580.8	56.3
0°-90°	3213.4	70.1
90°-120°	225.9	4.9
90°-150°	996.7	21.7
90°-180°	1371.0	29.9
0°-180°	4584.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	0	4	7	8	9	3
95°	22	12	13	15	15	27
105°	103	107	21	24	26	110
115°	195	201	209	60	28	192
125°	275	280	286	288	290	245
135°	341	346	349	352	352	263
145°	395	395	400	403	401	247
155°	435	432	436	438	436	200
165°	458	457	457	460	457	129
175°	469	467	467	469	466	45
180°	468	468	468	468	468	



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.3	17.0	16.7	16.5	16.2	15.9	15.6	15.3	15.0	14.4
90°	0.3	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1
92.5°	6.8	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1
95°	22.0	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5
97.5°	43.6	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0
100°	60.0	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9
102.5°	77.8	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6
105°	102.9	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5
107.5°	131.6	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0
110°	150.0	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.3	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0
115°	194.7	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0
117.5°	219.1	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0
120°	237.0	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1
122.5°	252.2	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7
125°	275.3	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6
127.5°	296.2	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7
130°	309.5	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4
132.5°	323.1	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1
135°	340.6	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8
137.5°	358.5	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4
140°	370.1	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2
142.5°	379.9	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1
145°	395.1	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1
147.5°	408.4	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3
150°	417.2	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6
152.5°	424.5	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4
155°	435.1	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6
157.5°	443.4	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2
160°	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8
162.5°	452.7	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9
165°	458.4	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0
167.5°	462.8	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2
170°	465.2	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4
172.5°	466.8	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0
175°	469.0	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8
177.5°	469.3	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	13.8	13.2	12.7	12.3	12.1	11.9	11.7	11.6
90°	7.5	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.2	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	13.9	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.3	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	20.5	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	21.4	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	22.3	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	27.3	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	44.2	36.7	29.2	25.5	25.8	26.1	26.5	26.8



TEST NUMBER: P331589-927

CATALOG NUMBER: S122DIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	94.6	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	139.3	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	214.5	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.0	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.2	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.2	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	307.4	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	320.3	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	332.8	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	350.6	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.2	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	377.9	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	387.8	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	401.6	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	413.7	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.1	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	427.9	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.0	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	444.7	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.2	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.4	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	462.8	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	464.9	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	466.5	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.3	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.5	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)