

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331579-930

Luminaire Tested: **S122DIW-S865D1440U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331579-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7805.7 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	88	81	75	70	80	74	69	64	61	57	54	48	46	44	37	36	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	47	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22727	22727	22727	22727
5°	25480	22875	20272	22875
10°	29198	22689	17544	22689
15°	32301	22272	15499	22272
20°	31809	21825	14129	21825
25°	28682	21232	13261	21232
30°	23702	20282	12629	20282
35°	17274	19291	12177	19291
40°	13797	18120	11927	18120
45°	12056	16762	11586	16762
50°	11333	15450	11359	15450
55°	10446	14117	11054	14117
60°	9571	12700	10585	12700
65°	8722	11427	10128	11427
70°	7917	10192	9451	10192
75°	7018	8808	8372	8808
80°	6034	7290	6741	7290
85°	5409	5409	4001	5409



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	1.7
10°-20°	389.7	5.0
20°-30°	565.6	7.2
30°-40°	596.9	7.6
40°-50°	528.5	6.8
50°-60°	421.7	5.4
60°-70°	286.7	3.7
70°-80°	147.0	1.9
80°-90°	39.4	0.5
90°-100°	53.5	0.7
100°-110°	196.0	2.5
110°-120°	524.0	6.7
120°-130°	865.0	11.1
130°-140°	919.9	11.8
140°-150°	855.0	11.0
150°-160°	687.4	8.8
160°-170°	443.0	5.7
170°-180°	152.5	2.0
0°-30°	1089.4	14.0
0°-40°	1686.3	21.6
0°-60°	2636.5	33.8
0°-90°	3109.5	39.8
90°-120°	773.5	9.9
90°-150°	3413.3	43.7
90°-180°	4696.0	60.2
0°-180°	7805.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1408	1408	1408	1408	1408	
5°	1572	1411	1251	1411	1572	157
15°	1932	1332	927	1332	1932	533
25°	1610	1192	744	1192	1610	728
35°	876	979	618	979	876	570
45°	528	734	507	734	528	415
55°	371	502	393	502	371	333
65°	228	299	265	299	228	227
75°	112	141	134	141	112	120
85°	29	29	22	29	29	33
90°	31	1	31	1	31	15
95°	50	75	50	75	50	47
105°	88	352	88	352	88	92
115°	95	667	95	667	95	238
125°	991	943	991	943	991	858
135°	1205	1166	1205	1166	1205	929
145°	1374	1353	1374	1353	1374	859
155°	1491	1490	1491	1490	1491	688
165°	1566	1570	1566	1570	1566	442
175°	1597	1606	1597	1606	1597	152
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1472.6	1473.0	1473.9	1467.0	1466.1	1466.1	1460.0	1454.8	1448.8	1440.6	1441.4
5°	1572.1	1578.1	1580.2	1573.8	1564.0	1562.9	1553.7	1538.6	1524.5	1513.1	1505.0
7.5°	1690.9	1693.3	1688.0	1679.4	1672.2	1659.2	1642.1	1625.4	1601.9	1580.4	1564.3
10°	1780.9	1784.2	1775.0	1762.5	1752.2	1737.1	1712.2	1686.8	1656.0	1626.2	1602.4
12.5°	1849.3	1857.3	1845.5	1843.9	1826.3	1805.5	1775.9	1763.0	1719.6	1678.1	1652.6
15°	1932.4	1931.9	1933.0	1922.6	1909.7	1906.4	1875.1	1841.0	1779.9	1755.5	1713.4
17.5°	1908.4	1916.6	1920.4	1920.3	1919.9	1917.9	1907.9	1886.4	1855.7	1816.2	1767.5
20°	1851.3	1862.1	1863.7	1876.2	1883.2	1892.4	1896.1	1890.2	1871.3	1838.3	1796.1
22.5°	1763.0	1766.0	1771.1	1790.5	1805.7	1828.8	1840.8	1860.8	1853.5	1837.4	1802.1
25°	1610.0	1604.6	1623.5	1633.2	1668.4	1705.2	1731.7	1760.9	1786.9	1802.5	1792.3
27.5°	1426.3	1418.1	1446.5	1472.3	1500.9	1540.8	1582.1	1630.8	1671.4	1722.2	1739.6
30°	1271.3	1276.2	1303.3	1330.8	1374.1	1430.4	1476.9	1530.5	1588.4	1645.1	1684.7
32.5°	1104.2	1123.0	1140.1	1182.3	1220.5	1283.2	1351.4	1418.4	1490.5	1555.1	1616.2
35°	876.4	898.1	921.9	952.7	1006.2	1068.4	1135.0	1225.3	1323.8	1412.0	1484.5
37.5°	737.7	734.3	747.9	770.1	813.5	863.7	940.4	1029.6	1145.5	1249.1	1351.4
40°	654.6	652.4	662.2	682.7	715.8	752.5	819.6	898.1	1005.7	1132.3	1254.0
42.5°	597.5	598.8	604.1	618.6	641.3	671.6	721.8	788.6	887.1	1006.3	1137.2
45°	528.0	531.8	537.8	544.8	557.7	582.6	610.7	658.4	736.3	835.8	964.6
47.5°	478.0	478.1	484.2	490.3	498.1	512.1	535.0	564.9	619.9	700.9	811.6
50°	451.2	447.4	451.8	456.6	464.7	474.4	489.6	517.7	554.5	620.0	712.5
52.5°	418.3	418.4	422.3	424.1	431.4	441.2	454.9	474.4	507.8	559.0	635.0
55°	371.1	373.8	376.0	379.2	385.7	392.7	403.6	416.5	442.5	480.9	537.2
57.5°	326.8	327.6	329.8	336.0	340.1	346.6	356.9	368.6	385.5	413.9	456.2
60°	296.4	296.4	300.8	303.5	308.9	315.4	323.5	334.8	350.0	373.2	407.4
62.5°	268.8	268.3	270.0	274.5	278.6	284.7	292.8	302.4	316.7	337.4	365.4
65°	228.3	227.2	230.5	231.5	235.9	241.8	248.3	258.6	269.9	285.1	310.0
67.5°	189.3	190.6	192.4	194.4	196.8	203.1	207.4	214.7	224.3	236.8	253.7
70°	167.7	167.7	167.7	169.3	172.6	175.9	180.2	186.1	195.3	206.1	221.3
72.5°	143.5	145.2	146.9	145.9	150.1	152.1	157.2	160.5	169.3	176.3	189.6
75°	112.5	112.5	112.5	115.2	116.8	118.5	121.7	125.0	129.3	137.9	145.0
77.5°	84.0	83.7	84.3	85.0	86.7	88.6	89.6	92.5	96.5	100.5	106.5
80°	64.9	66.0	66.5	67.6	67.6	68.7	69.2	73.1	75.7	78.4	82.3
82.5°	50.2	50.4	50.5	50.7	51.2	51.9	53.2	54.5	55.4	57.6	60.6
85°	29.2	28.7	28.7	29.8	29.2	29.2	30.3	31.4	31.4	31.9	33.5
87.5°	17.5	17.4	17.8	17.2	17.1	17.4	17.1	16.4	16.6	16.8	16.8
90°	31.3	30.8	30.2	29.8	29.3	28.4	27.1	25.8	24.5	23.2	21.1
92.5°	31.3	31.0	30.7	30.4	30.1	29.6	28.9	28.2	27.6	26.9	25.8
95°	49.9	50.1	50.4	50.6	50.9	50.4	49.1	47.8	46.5	45.2	43.5
97.5°	66.5	66.3	66.0	65.6	65.3	64.7	63.6	62.6	61.6	60.5	56.3
100°	77.7	77.2	76.6	76.1	75.7	74.4	72.3	70.2	68.2	66.1	61.7
102.5°	83.2	82.5	81.8	81.1	80.4	78.7	76.0	73.3	70.6	67.9	104.6
105°	88.1	87.1	86.1	85.0	84.0	82.1	79.2	76.4	73.5	70.8	141.0
107.5°	90.7	89.7	88.6	87.6	86.6	87.5	90.3	93.3	96.1	99.1	183.4
110°	91.6	90.6	89.5	88.5	87.5	99.9	125.6	151.4	177.2	202.9	277.4



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.5	91.7	90.9	90.1	89.2	135.8	229.8	323.8	417.8	511.8	530.2
115°	95.1	113.7	132.2	150.7	169.3	238.2	357.5	476.9	596.1	715.4	709.0
117.5°	388.2	449.1	510.1	571.1	632.1	677.0	705.9	734.7	763.6	792.5	788.0
120°	707.4	742.1	776.9	811.7	846.4	862.3	859.2	856.1	853.0	849.9	845.3
122.5°	882.6	889.4	896.2	902.9	909.6	912.1	910.3	908.4	906.5	904.7	899.6
125°	991.4	990.7	989.9	989.1	988.3	987.0	985.2	983.4	981.6	979.8	974.9
127.5°	1060.1	1059.9	1059.7	1059.6	1059.5	1058.0	1055.4	1052.8	1050.2	1047.6	1043.9
130°	1102.7	1103.0	1103.3	1103.5	1103.8	1102.4	1099.7	1096.8	1094.0	1091.1	1088.3
132.5°	1144.4	1144.8	1145.0	1145.3	1145.5	1144.4	1142.0	1139.5	1137.2	1134.7	1131.9
135°	1204.8	1205.3	1205.8	1206.3	1206.8	1205.8	1203.2	1200.6	1198.1	1195.5	1193.2
137.5°	1259.7	1260.6	1261.5	1262.3	1263.2	1262.4	1259.9	1257.4	1254.8	1252.3	1249.7
140°	1294.0	1295.3	1296.7	1298.0	1299.2	1298.7	1296.4	1294.0	1291.8	1289.4	1286.6
142.5°	1327.5	1328.8	1330.0	1331.3	1332.6	1332.2	1330.1	1328.0	1325.8	1323.7	1320.5
145°	1374.1	1375.3	1376.6	1377.9	1379.2	1379.0	1377.1	1375.3	1373.5	1371.7	1367.3
147.5°	1415.1	1416.2	1417.3	1418.4	1419.4	1419.4	1418.0	1416.7	1415.3	1414.0	1409.7
150°	1440.1	1441.4	1442.8	1444.1	1445.3	1445.2	1443.7	1442.1	1440.6	1439.0	1434.8
152.5°	1461.5	1463.2	1464.9	1466.6	1468.3	1468.4	1466.8	1465.3	1463.7	1462.2	1458.2
155°	1491.2	1493.2	1495.3	1497.4	1499.4	1499.7	1498.1	1496.6	1495.0	1493.5	1490.4
157.5°	1518.3	1520.3	1522.3	1524.4	1526.3	1526.5	1524.7	1523.0	1521.3	1519.5	1517.3
160°	1534.1	1535.9	1537.7	1539.5	1541.3	1541.4	1539.9	1538.3	1536.8	1535.2	1533.7
162.5°	1547.1	1549.3	1551.5	1553.7	1555.9	1556.2	1554.4	1552.7	1550.9	1549.2	1547.8
165°	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5	1565.8
167.5°	1578.8	1581.2	1583.5	1585.8	1588.1	1588.4	1586.6	1584.8	1583.0	1581.2	1580.5
170°	1586.2	1588.6	1590.9	1593.3	1595.5	1595.8	1594.0	1592.2	1590.4	1588.6	1588.0
172.5°	1591.8	1594.2	1596.4	1598.8	1601.1	1601.3	1599.5	1597.7	1595.9	1594.2	1593.7
175°	1596.7	1599.3	1601.8	1604.4	1607.0	1607.4	1605.6	1603.8	1602.0	1600.2	1599.7
177.5°	1599.7	1601.6	1603.4	1605.2	1607.1	1607.4	1605.9	1604.4	1603.0	1601.6	1601.3
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1444.5	1441.0	1438.8	1431.0	1424.1	1417.2	1415.0	1415.8	1406.4	1397.3	1393.3
5°	1500.7	1489.9	1479.6	1465.0	1447.7	1428.7	1419.0	1411.4	1392.5	1372.0	1360.1
7.5°	1551.1	1535.6	1515.9	1488.4	1463.1	1433.4	1414.5	1397.7	1370.0	1341.0	1323.2
10°	1581.8	1560.7	1535.3	1501.8	1471.0	1434.7	1409.2	1383.9	1351.4	1316.8	1295.1
12.5°	1608.3	1579.8	1554.8	1511.7	1475.3	1430.0	1399.8	1363.9	1329.8	1288.7	1267.5
15°	1671.1	1618.6	1571.0	1522.3	1477.4	1414.1	1380.6	1332.4	1287.5	1236.7	1212.4
17.5°	1719.7	1660.8	1585.8	1523.9	1471.5	1401.4	1352.2	1294.5	1241.4	1183.2	1150.1
20°	1747.4	1679.8	1599.1	1525.6	1462.8	1382.7	1329.2	1270.2	1208.0	1142.6	1106.9
22.5°	1763.8	1692.7	1613.0	1519.1	1445.5	1367.6	1300.2	1235.6	1172.6	1101.9	1064.5
25°	1769.0	1704.1	1619.8	1513.7	1423.9	1335.7	1254.6	1191.8	1115.5	1049.5	994.9
27.5°	1743.3	1696.7	1615.6	1503.5	1398.9	1295.8	1205.3	1134.2	1053.8	982.1	927.2
30°	1711.7	1684.7	1605.7	1493.1	1379.0	1268.1	1168.6	1087.9	1007.9	935.4	879.1
32.5°	1662.8	1656.9	1587.5	1478.4	1357.8	1233.1	1130.0	1048.6	959.9	888.6	834.9
35°	1566.7	1592.7	1548.8	1445.5	1317.8	1183.2	1071.7	978.7	886.7	818.5	768.2
37.5°	1437.9	1502.4	1490.9	1397.3	1264.0	1128.9	1005.8	908.6	820.9	752.1	702.7
40°	1349.2	1431.4	1443.3	1360.6	1225.9	1086.9	956.5	859.7	774.1	711.4	661.6
42.5°	1254.0	1350.1	1382.7	1316.5	1184.3	1042.7	912.3	812.0	727.4	666.4	622.2
45°	1094.5	1221.6	1280.5	1242.7	1115.0	970.0	835.8	734.1	657.3	600.0	565.9
47.5°	945.2	1084.1	1163.4	1150.1	1037.8	894.2	761.6	664.0	589.2	543.5	513.0
50°	839.6	982.4	1078.2	1082.6	982.4	840.2	707.1	615.1	546.4	503.7	478.7
52.5°	747.9	884.2	988.6	1011.5	920.6	783.9	658.2	566.6	506.1	466.8	444.6
55°	628.1	743.3	859.1	901.3	828.3	698.4	582.1	501.5	444.7	417.7	398.2
57.5°	522.2	618.2	725.1	771.8	726.8	615.6	506.5	436.6	390.4	366.8	351.9
60°	466.4	542.1	637.3	693.0	654.0	555.1	459.8	393.3	355.5	334.4	320.2
62.5°	414.4	481.5	562.0	612.9	591.7	498.4	413.1	354.3	321.6	301.9	291.7
65°	341.9	394.9	457.1	504.2	490.2	419.2	349.5	299.1	273.2	257.5	249.4
67.5°	281.5	319.8	363.0	404.2	392.9	342.7	286.6	247.4	228.1	214.6	209.7
70°	243.4	272.6	311.0	344.1	334.8	293.8	249.4	215.9	199.1	187.8	182.9
72.5°	207.1	231.1	260.4	287.4	281.2	247.0	210.0	184.7	171.8	161.3	157.4
75°	156.4	174.7	192.6	210.4	208.8	182.3	160.7	141.2	130.9	122.8	121.2
77.5°	115.4	125.7	137.9	148.5	145.5	130.4	113.4	102.2	94.7	89.3	88.4
80°	88.2	94.2	102.8	110.4	106.6	100.1	86.6	78.4	73.1	67.6	65.5
82.5°	63.9	69.9	75.1	79.2	76.3	70.2	61.9	56.3	53.2	49.4	48.6
85°	33.5	36.8	39.0	40.0	39.0	35.1	31.4	29.2	26.5	24.9	24.4
87.5°	16.8	16.4	16.0	16.4	14.5	13.9	11.7	9.8	9.9	10.0	9.7
90°	19.1	17.0	14.9	12.5	9.7	6.8	4.0	1.1	4.0	6.8	9.7
92.5°	24.9	23.8	22.7	22.4	22.7	22.9	23.2	23.4	23.2	22.9	22.7
95°	41.6	39.8	38.0	41.3	49.9	58.4	66.9	75.3	66.9	58.4	49.9
97.5°	52.2	48.0	43.9	53.7	77.7	101.7	125.6	149.6	125.6	101.7	77.7
100°	57.3	52.9	48.6	64.0	99.3	134.6	169.9	205.2	169.9	134.6	99.3
102.5°	141.2	177.9	214.5	236.6	244.0	251.5	259.0	266.4	259.0	251.5	244.0
105°	211.4	281.8	352.1	383.4	375.7	367.9	360.2	352.5	360.2	367.9	375.7
107.5°	267.7	352.1	436.5	475.6	469.3	463.1	456.8	450.6	456.8	463.1	469.3
110°	351.9	426.3	500.8	535.3	529.9	524.5	519.1	513.7	519.1	524.5	529.9



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	548.6	567.0	585.4	592.2	587.4	582.6	577.8	573.1	577.8	582.6	587.4
115°	702.5	696.1	689.7	684.3	679.9	675.5	671.2	666.8	671.2	675.5	679.9
117.5°	783.6	779.1	774.7	770.1	765.2	760.3	755.4	750.5	755.4	760.3	765.2
120°	840.7	836.0	831.4	827.1	823.3	819.4	815.5	811.7	815.5	819.4	823.3
122.5°	894.5	889.5	884.5	880.0	875.9	871.8	867.7	863.6	867.7	871.8	875.9
125°	970.0	965.2	960.3	956.1	952.8	949.4	946.1	942.7	946.1	949.4	952.8
127.5°	1040.2	1036.6	1032.9	1029.2	1025.5	1021.8	1018.1	1014.4	1018.1	1021.8	1025.5
130°	1085.5	1082.6	1079.8	1076.4	1072.2	1068.0	1064.0	1059.8	1064.0	1068.0	1072.2
132.5°	1129.0	1126.3	1123.4	1120.2	1116.7	1113.2	1109.7	1106.2	1109.7	1113.2	1116.7
135°	1190.8	1188.5	1186.2	1183.0	1178.8	1174.8	1170.6	1166.5	1170.6	1174.8	1178.8
137.5°	1247.1	1244.4	1241.8	1239.0	1236.2	1233.3	1230.4	1227.5	1230.4	1233.3	1236.2
140°	1283.8	1280.9	1278.1	1275.6	1273.6	1271.5	1269.4	1267.4	1269.4	1271.5	1273.6
142.5°	1317.3	1314.0	1310.8	1308.2	1306.4	1304.5	1302.6	1300.8	1302.6	1304.5	1306.4
145°	1363.0	1358.6	1354.2	1352.2	1352.4	1352.7	1352.9	1353.2	1352.9	1352.7	1352.4
147.5°	1405.3	1400.9	1396.6	1395.0	1396.0	1396.9	1397.9	1398.9	1397.9	1396.9	1396.0
150°	1430.8	1426.6	1422.5	1421.3	1423.2	1425.0	1426.8	1428.6	1426.8	1425.0	1423.2
152.5°	1454.3	1450.4	1446.5	1445.6	1447.6	1449.6	1451.6	1453.6	1451.6	1449.6	1447.6
155°	1487.4	1484.3	1481.2	1480.7	1483.0	1485.4	1487.7	1490.0	1487.7	1485.4	1483.0
157.5°	1515.2	1513.0	1510.8	1510.7	1512.7	1514.7	1516.6	1518.6	1516.6	1514.7	1512.7
160°	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1533.7	1532.2	1530.6
162.5°	1546.5	1545.2	1543.8	1543.9	1545.5	1547.0	1548.6	1550.0	1548.6	1547.0	1545.5
165°	1565.0	1564.2	1563.5	1563.8	1565.4	1566.9	1568.5	1570.0	1568.5	1566.9	1565.4
167.5°	1579.7	1579.0	1578.3	1578.7	1580.2	1581.8	1583.3	1584.9	1583.3	1581.8	1580.2
170°	1587.6	1587.1	1586.5	1587.1	1588.6	1590.2	1591.7	1593.3	1591.7	1590.2	1588.6
172.5°	1593.1	1592.6	1592.1	1592.6	1594.2	1595.7	1597.3	1598.8	1597.3	1595.7	1594.2
175°	1599.1	1598.6	1598.1	1598.8	1600.6	1602.4	1604.2	1606.0	1604.2	1602.4	1600.6
177.5°	1601.2	1600.9	1600.8	1601.3	1602.8	1604.3	1605.7	1607.1	1605.7	1604.3	1602.8
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1389.0	1386.4	1377.4	1372.6	1364.8	1357.5	1352.7	1354.9	1356.6	1355.7	1354.5
5°	1349.2	1339.0	1323.2	1309.7	1300.0	1282.1	1274.6	1270.8	1267.5	1263.7	1260.0
7.5°	1301.9	1285.6	1263.1	1243.8	1225.6	1203.5	1190.8	1183.2	1175.5	1166.9	1159.4
10°	1268.1	1245.4	1221.6	1194.5	1172.9	1152.8	1135.0	1123.1	1112.3	1102.0	1094.5
12.5°	1232.6	1206.4	1177.0	1140.0	1116.1	1087.5	1084.8	1063.8	1046.9	1040.6	1031.7
15°	1176.2	1139.3	1102.0	1058.2	1039.3	1013.3	997.0	980.8	966.2	955.9	953.2
17.5°	1112.0	1064.4	1027.2	995.7	964.7	938.1	923.2	910.2	898.1	884.4	882.6
20°	1063.1	1021.9	981.4	953.7	921.9	894.8	876.4	863.4	853.1	845.1	838.0
22.5°	1016.8	971.8	934.6	904.4	872.9	851.1	836.6	824.0	815.5	806.5	799.9
25°	942.4	907.3	866.7	832.6	806.6	792.6	780.6	769.8	764.4	758.5	750.9
27.5°	877.3	838.3	800.4	774.0	751.1	738.7	730.3	722.8	717.8	714.3	710.0
30°	831.5	792.0	762.2	736.3	717.4	704.9	699.5	695.2	689.3	687.1	684.9
32.5°	787.3	751.8	726.4	703.8	685.7	677.7	672.7	668.8	664.1	661.9	657.6
35°	725.0	695.2	670.3	657.9	643.3	636.2	632.4	627.0	622.6	620.5	620.0
37.5°	666.2	640.3	623.9	608.0	601.8	597.5	592.3	588.6	587.3	586.9	586.4
40°	628.1	607.0	592.4	579.4	576.7	570.2	565.9	562.6	562.6	563.2	562.6
42.5°	593.5	574.5	561.7	550.4	547.2	543.4	539.1	538.8	539.7	541.5	539.7
45°	541.0	527.5	518.3	512.8	506.9	503.1	502.6	504.2	504.8	505.3	506.9
47.5°	492.8	483.7	475.4	469.4	466.8	466.2	465.5	468.4	471.0	472.0	474.4
50°	464.1	453.9	446.9	443.0	440.9	439.9	440.9	444.2	446.3	449.0	450.6
52.5°	432.1	424.9	420.0	417.1	416.2	416.9	417.1	420.8	424.3	425.2	426.0
55°	387.9	382.5	381.4	376.5	378.7	378.1	380.8	383.0	386.3	389.6	390.0
57.5°	343.7	339.4	336.5	337.0	337.6	340.0	342.3	346.0	349.5	352.9	353.3
60°	314.3	312.2	310.5	310.5	311.6	314.9	317.6	321.3	323.5	325.7	327.3
62.5°	287.5	285.4	283.7	284.5	287.4	289.3	292.4	294.5	296.7	298.8	299.6
65°	245.1	244.0	245.6	246.7	247.2	250.0	253.7	255.4	257.5	258.6	262.4
67.5°	206.0	206.2	206.0	207.5	210.7	211.3	214.9	218.7	219.1	221.2	223.6
70°	179.6	180.7	181.8	182.9	185.6	186.6	189.3	190.9	193.1	194.8	196.4
72.5°	155.4	155.6	156.7	156.5	158.7	161.1	163.4	165.0	167.1	169.3	170.8
75°	119.5	119.5	120.7	121.2	123.9	126.6	126.0	127.1	129.3	131.4	132.6
77.5°	87.3	86.1	87.3	87.9	88.7	91.0	91.4	92.9	95.4	94.7	95.9
80°	66.5	64.9	66.5	67.1	67.1	69.8	69.8	70.8	72.5	70.8	72.5
82.5°	47.5	46.7	47.9	48.0	48.9	49.0	49.9	50.1	51.7	51.0	51.7
85°	23.8	23.2	23.8	23.2	23.8	24.4	24.4	23.8	23.8	24.9	23.2
87.5°	9.9	9.9	9.9	10.3	10.3	10.3	10.1	10.4	10.6	10.0	10.2
90°	12.5	14.9	17.0	19.1	21.1	23.2	24.5	25.8	27.1	28.4	29.3
92.5°	22.4	22.7	23.8	24.9	25.8	26.9	27.6	28.2	28.9	29.6	30.1
95°	41.3	38.0	39.8	41.6	43.5	45.2	46.5	47.8	49.1	50.4	50.9
97.5°	53.7	43.9	48.0	52.2	56.3	60.5	61.6	62.6	63.6	64.7	65.3
100°	64.0	48.6	52.9	57.3	61.7	66.1	68.2	70.2	72.3	74.4	75.7
102.5°	236.6	214.5	177.9	141.2	104.6	67.9	70.6	73.3	76.0	78.7	80.4
105°	383.4	352.1	281.8	211.4	141.0	70.8	73.5	76.4	79.2	82.1	84.0
107.5°	475.6	436.5	352.1	267.7	183.4	99.1	96.1	93.3	90.3	87.5	86.6
110°	535.3	500.8	426.3	351.9	277.4	202.9	177.2	151.4	125.6	99.9	87.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	592.2	585.4	567.0	548.6	530.2	511.8	417.8	323.8	229.8	135.8	89.2
115°	684.3	689.7	696.1	702.5	709.0	715.4	596.1	476.9	357.5	238.2	169.3
117.5°	770.1	774.7	779.1	783.6	788.0	792.5	763.6	734.7	705.9	677.0	632.1
120°	827.1	831.4	836.0	840.7	845.3	849.9	853.0	856.1	859.2	862.3	846.4
122.5°	880.0	884.5	889.5	894.5	899.6	904.7	906.5	908.4	910.3	912.1	909.6
125°	956.1	960.3	965.2	970.0	974.9	979.8	981.6	983.4	985.2	987.0	988.3
127.5°	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2	1052.8	1055.4	1058.0	1059.5
130°	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0	1096.8	1099.7	1102.4	1103.8
132.5°	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2	1139.5	1142.0	1144.4	1145.5
135°	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1	1200.6	1203.2	1205.8	1206.8
137.5°	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8	1257.4	1259.9	1262.4	1263.2
140°	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8	1294.0	1296.4	1298.7	1299.2
142.5°	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8	1328.0	1330.1	1332.2	1332.6
145°	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5	1375.3	1377.1	1379.0	1379.2
147.5°	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3	1416.7	1418.0	1419.4	1419.4
150°	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6	1442.1	1443.7	1445.2	1445.3
152.5°	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7	1465.3	1466.8	1468.4	1468.3
155°	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0	1496.6	1498.1	1499.7	1499.4
157.5°	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3	1523.0	1524.7	1526.5	1526.3
160°	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8	1538.3	1539.9	1541.4	1541.3
162.5°	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9	1552.7	1554.4	1556.2	1555.9
165°	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8
167.5°	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0	1584.8	1586.6	1588.4	1588.1
170°	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4	1592.2	1594.0	1595.8	1595.5
172.5°	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9	1597.7	1599.5	1601.3	1601.1
175°	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0	1603.8	1605.6	1607.4	1607.0
177.5°	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0	1604.4	1605.9	1607.4	1607.1
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1350.1	1349.2	1349.2	1345.3	1349.2	1349.2	1350.1	1354.5	1355.7	1356.6	1354.9
5°	1252.4	1250.8	1248.1	1250.8	1248.1	1250.8	1252.4	1260.0	1263.7	1267.5	1270.8
7.5°	1155.8	1149.2	1148.3	1141.9	1148.3	1149.2	1155.8	1159.4	1166.9	1175.5	1183.2
10°	1085.2	1080.9	1080.4	1070.1	1080.4	1080.9	1085.2	1094.5	1102.0	1112.3	1123.1
12.5°	1031.6	1021.2	1023.2	1017.2	1023.2	1021.2	1031.6	1031.7	1040.6	1046.9	1063.8
15°	938.7	938.7	936.5	927.2	936.5	938.7	938.7	953.2	955.9	966.2	980.8
17.5°	871.9	870.7	865.6	868.2	865.6	870.7	871.9	882.6	884.4	898.1	910.2
20°	832.0	828.8	822.3	822.3	822.3	828.8	832.0	838.0	845.1	853.1	863.4
22.5°	794.4	794.2	787.3	789.4	787.3	794.2	794.4	799.9	806.5	815.5	824.0
25°	750.3	746.0	742.8	744.4	742.8	746.0	750.3	750.9	758.5	764.4	769.8
27.5°	708.6	706.2	706.0	701.6	706.0	706.2	708.6	710.0	714.3	717.8	722.8
30°	684.4	679.0	680.0	677.4	680.0	679.0	684.4	684.9	687.1	689.3	695.2
32.5°	656.6	654.7	653.6	651.3	653.6	654.7	656.6	657.6	661.9	664.1	668.8
35°	618.9	619.5	616.7	617.8	616.7	619.5	618.9	620.0	620.5	622.6	627.0
37.5°	585.9	587.6	586.4	586.7	586.4	587.6	585.9	586.4	586.9	587.3	588.6
40°	564.3	564.3	564.3	565.9	564.3	564.3	564.3	562.6	563.2	562.6	562.6
42.5°	543.5	542.6	541.8	541.6	541.8	542.6	543.5	539.7	541.5	539.7	538.8
45°	508.0	509.6	510.1	507.4	510.1	509.6	508.0	506.9	505.3	504.8	504.2
47.5°	475.9	476.1	475.9	478.3	475.9	476.1	475.9	474.4	472.0	471.0	468.4
50°	453.4	452.2	453.4	452.2	453.4	452.2	453.4	450.6	449.0	446.3	444.2
52.5°	429.6	429.7	429.1	428.9	429.1	429.7	429.6	426.0	425.2	424.3	420.8
55°	392.2	393.3	392.7	392.7	392.7	393.3	392.2	390.0	389.6	386.3	383.0
57.5°	353.6	354.6	355.3	352.9	355.3	354.6	353.6	353.3	352.9	349.5	346.0
60°	326.8	329.5	328.9	327.8	328.9	329.5	326.8	327.3	325.7	323.5	321.3
62.5°	302.1	303.0	303.0	302.7	303.0	303.0	302.1	299.6	298.8	296.7	294.5
65°	264.0	265.1	263.4	265.1	263.4	265.1	264.0	262.4	258.6	257.5	255.4
67.5°	223.0	223.3	224.5	225.3	224.5	223.3	223.0	223.6	221.2	219.1	218.7
70°	197.5	196.9	198.5	200.2	198.5	196.9	197.5	196.4	194.8	193.1	190.9
72.5°	170.6	171.8	171.3	172.4	171.3	171.8	170.6	170.8	169.3	167.1	165.0
75°	131.4	133.1	132.6	134.2	132.6	133.1	131.4	132.6	131.4	129.3	127.1
77.5°	95.0	95.2	95.0	95.9	95.0	95.2	95.0	95.9	94.7	95.4	92.9
80°	72.5	71.4	70.4	72.5	70.4	71.4	72.5	72.5	70.8	72.5	70.8
82.5°	50.4	51.0	50.0	50.0	50.0	51.0	50.4	51.7	51.0	51.7	50.1
85°	23.2	22.7	21.6	21.6	21.6	22.7	23.2	23.2	24.9	23.8	23.8
87.5°	10.3	9.9	10.0	9.7	10.0	9.9	10.3	10.2	10.0	10.6	10.4
90°	29.8	30.2	30.8	31.3	30.8	30.2	29.8	29.3	28.4	27.1	25.8
92.5°	30.4	30.7	31.0	31.3	31.0	30.7	30.4	30.1	29.6	28.9	28.2
95°	50.6	50.4	50.1	49.9	50.1	50.4	50.6	50.9	50.4	49.1	47.8
97.5°	65.6	66.0	66.3	66.5	66.3	66.0	65.6	65.3	64.7	63.6	62.6
100°	76.1	76.6	77.2	77.7	77.2	76.6	76.1	75.7	74.4	72.3	70.2
102.5°	81.1	81.8	82.5	83.2	82.5	81.8	81.1	80.4	78.7	76.0	73.3
105°	85.0	86.1	87.1	88.1	87.1	86.1	85.0	84.0	82.1	79.2	76.4
107.5°	87.6	88.6	89.7	90.7	89.7	88.6	87.6	86.6	87.5	90.3	93.3
110°	88.5	89.5	90.6	91.6	90.6	89.5	88.5	87.5	99.9	125.6	151.4



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	90.1	90.9	91.7	92.5	91.7	90.9	90.1	89.2	135.8	229.8	323.8
115°	150.7	132.2	113.7	95.1	113.7	132.2	150.7	169.3	238.2	357.5	476.9
117.5°	571.1	510.1	449.1	388.2	449.1	510.1	571.1	632.1	677.0	705.9	734.7
120°	811.7	776.9	742.1	707.4	742.1	776.9	811.7	846.4	862.3	859.2	856.1
122.5°	902.9	896.2	889.4	882.6	889.4	896.2	902.9	909.6	912.1	910.3	908.4
125°	989.1	989.9	990.7	991.4	990.7	989.9	989.1	988.3	987.0	985.2	983.4
127.5°	1059.6	1059.7	1059.9	1060.1	1059.9	1059.7	1059.6	1059.5	1058.0	1055.4	1052.8
130°	1103.5	1103.3	1103.0	1102.7	1103.0	1103.3	1103.5	1103.8	1102.4	1099.7	1096.8
132.5°	1145.3	1145.0	1144.8	1144.4	1144.8	1145.0	1145.3	1145.5	1144.4	1142.0	1139.5
135°	1206.3	1205.8	1205.3	1204.8	1205.3	1205.8	1206.3	1206.8	1205.8	1203.2	1200.6
137.5°	1262.3	1261.5	1260.6	1259.7	1260.6	1261.5	1262.3	1263.2	1262.4	1259.9	1257.4
140°	1298.0	1296.7	1295.3	1294.0	1295.3	1296.7	1298.0	1299.2	1298.7	1296.4	1294.0
142.5°	1331.3	1330.0	1328.8	1327.5	1328.8	1330.0	1331.3	1332.6	1332.2	1330.1	1328.0
145°	1377.9	1376.6	1375.3	1374.1	1375.3	1376.6	1377.9	1379.2	1379.0	1377.1	1375.3
147.5°	1418.4	1417.3	1416.2	1415.1	1416.2	1417.3	1418.4	1419.4	1419.4	1418.0	1416.7
150°	1444.1	1442.8	1441.4	1440.1	1441.4	1442.8	1444.1	1445.3	1445.2	1443.7	1442.1
152.5°	1466.6	1464.9	1463.2	1461.5	1463.2	1464.9	1466.6	1468.3	1468.4	1466.8	1465.3
155°	1497.4	1495.3	1493.2	1491.2	1493.2	1495.3	1497.4	1499.4	1499.7	1498.1	1496.6
157.5°	1524.4	1522.3	1520.3	1518.3	1520.3	1522.3	1524.4	1526.3	1526.5	1524.7	1523.0
160°	1539.5	1537.7	1535.9	1534.1	1535.9	1537.7	1539.5	1541.3	1541.4	1539.9	1538.3
162.5°	1553.7	1551.5	1549.3	1547.1	1549.3	1551.5	1553.7	1555.9	1556.2	1554.4	1552.7
165°	1572.0	1570.2	1568.4	1566.5	1568.4	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2
167.5°	1585.8	1583.5	1581.2	1578.8	1581.2	1583.5	1585.8	1588.1	1588.4	1586.6	1584.8
170°	1593.3	1590.9	1588.6	1586.2	1588.6	1590.9	1593.3	1595.5	1595.8	1594.0	1592.2
172.5°	1598.8	1596.4	1594.2	1591.8	1594.2	1596.4	1598.8	1601.1	1601.3	1599.5	1597.7
175°	1604.4	1601.8	1599.3	1596.7	1599.3	1601.8	1604.4	1607.0	1607.4	1605.6	1603.8
177.5°	1605.2	1603.4	1601.6	1599.7	1601.6	1603.4	1605.2	1607.1	1607.4	1605.9	1604.4
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1352.7	1357.5	1364.8	1372.6	1377.4	1386.4	1389.0	1393.3	1397.3	1406.4	1415.8
5°	1274.6	1282.1	1300.0	1309.7	1323.2	1339.0	1349.2	1360.1	1372.0	1392.5	1411.4
7.5°	1190.8	1203.5	1225.6	1243.8	1263.1	1285.6	1301.9	1323.2	1341.0	1370.0	1397.7
10°	1135.0	1152.8	1172.9	1194.5	1221.6	1245.4	1268.1	1295.1	1316.8	1351.4	1383.9
12.5°	1084.8	1087.5	1116.1	1140.0	1177.0	1206.4	1232.6	1267.5	1288.7	1329.8	1363.9
15°	997.0	1013.3	1039.3	1058.2	1102.0	1139.3	1176.2	1212.4	1236.7	1287.5	1332.4
17.5°	923.2	938.1	964.7	995.7	1027.2	1064.4	1112.0	1150.1	1183.2	1241.4	1294.5
20°	876.4	894.8	921.9	953.7	981.4	1021.9	1063.1	1106.9	1142.6	1208.0	1270.2
22.5°	836.6	851.1	872.9	904.4	934.6	971.8	1016.8	1064.5	1101.9	1172.6	1235.6
25°	780.6	792.6	806.6	832.6	866.7	907.3	942.4	994.9	1049.5	1115.5	1191.8
27.5°	730.3	738.7	751.1	774.0	800.4	838.3	877.3	927.2	982.1	1053.8	1134.2
30°	699.5	704.9	717.4	736.3	762.2	792.0	831.5	879.1	935.4	1007.9	1087.9
32.5°	672.7	677.7	685.7	703.8	726.4	751.8	787.3	834.9	888.6	959.9	1048.6
35°	632.4	636.2	643.3	657.9	670.3	695.2	725.0	768.2	818.5	886.7	978.7
37.5°	592.3	597.5	601.8	608.0	623.9	640.3	666.2	702.7	752.1	820.9	908.6
40°	565.9	570.2	576.7	579.4	592.4	607.0	628.1	661.6	711.4	774.1	859.7
42.5°	539.1	543.4	547.2	550.4	561.7	574.5	593.5	622.2	666.4	727.4	812.0
45°	502.6	503.1	506.9	512.8	518.3	527.5	541.0	565.9	600.0	657.3	734.1
47.5°	465.5	466.2	466.8	469.4	475.4	483.7	492.8	513.0	543.5	589.2	664.0
50°	440.9	439.9	440.9	443.0	446.9	453.9	464.1	478.7	503.7	546.4	615.1
52.5°	417.1	416.9	416.2	417.1	420.0	424.9	432.1	444.6	466.8	506.1	566.6
55°	380.8	378.1	378.7	376.5	381.4	382.5	387.9	398.2	417.7	444.7	501.5
57.5°	342.3	340.0	337.6	337.0	336.5	339.4	343.7	351.9	366.8	390.4	436.6
60°	317.6	314.9	311.6	310.5	310.5	312.2	314.3	320.2	334.4	355.5	393.3
62.5°	292.4	289.3	287.4	284.5	283.7	285.4	287.5	291.7	301.9	321.6	354.3
65°	253.7	250.0	247.2	246.7	245.6	244.0	245.1	249.4	257.5	273.2	299.1
67.5°	214.9	211.3	210.7	207.5	206.0	206.2	206.0	209.7	214.6	228.1	247.4
70°	189.3	186.6	185.6	182.9	181.8	180.7	179.6	182.9	187.8	199.1	215.9
72.5°	163.4	161.1	158.7	156.5	156.7	155.6	155.4	157.4	161.3	171.8	184.7
75°	126.0	126.6	123.9	121.2	120.7	119.5	119.5	121.2	122.8	130.9	141.2
77.5°	91.4	91.0	88.7	87.9	87.3	86.1	87.3	88.4	89.3	94.7	102.2
80°	69.8	69.8	67.1	67.1	66.5	64.9	66.5	65.5	67.6	73.1	78.4
82.5°	49.9	49.0	48.9	48.0	47.9	46.7	47.5	48.6	49.4	53.2	56.3
85°	24.4	24.4	23.8	23.2	23.8	23.2	23.8	24.4	24.9	26.5	29.2
87.5°	10.1	10.3	10.3	10.3	9.9	9.9	9.9	9.7	10.0	9.9	9.8
90°	24.5	23.2	21.1	19.1	17.0	14.9	12.5	9.7	6.8	4.0	1.1
92.5°	27.6	26.9	25.8	24.9	23.8	22.7	22.4	22.7	22.9	23.2	23.4
95°	46.5	45.2	43.5	41.6	39.8	38.0	41.3	49.9	58.4	66.9	75.3
97.5°	61.6	60.5	56.3	52.2	48.0	43.9	53.7	77.7	101.7	125.6	149.6
100°	68.2	66.1	61.7	57.3	52.9	48.6	64.0	99.3	134.6	169.9	205.2
102.5°	70.6	67.9	104.6	141.2	177.9	214.5	236.6	244.0	251.5	259.0	266.4
105°	73.5	70.8	141.0	211.4	281.8	352.1	383.4	375.7	367.9	360.2	352.5
107.5°	96.1	99.1	183.4	267.7	352.1	436.5	475.6	469.3	463.1	456.8	450.6
110°	177.2	202.9	277.4	351.9	426.3	500.8	535.3	529.9	524.5	519.1	513.7



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	417.8	511.8	530.2	548.6	567.0	585.4	592.2	587.4	582.6	577.8	573.1
115°	596.1	715.4	709.0	702.5	696.1	689.7	684.3	679.9	675.5	671.2	666.8
117.5°	763.6	792.5	788.0	783.6	779.1	774.7	770.1	765.2	760.3	755.4	750.5
120°	853.0	849.9	845.3	840.7	836.0	831.4	827.1	823.3	819.4	815.5	811.7
122.5°	906.5	904.7	899.6	894.5	889.5	884.5	880.0	875.9	871.8	867.7	863.6
125°	981.6	979.8	974.9	970.0	965.2	960.3	956.1	952.8	949.4	946.1	942.7
127.5°	1050.2	1047.6	1043.9	1040.2	1036.6	1032.9	1029.2	1025.5	1021.8	1018.1	1014.4
130°	1094.0	1091.1	1088.3	1085.5	1082.6	1079.8	1076.4	1072.2	1068.0	1064.0	1059.8
132.5°	1137.2	1134.7	1131.9	1129.0	1126.3	1123.4	1120.2	1116.7	1113.2	1109.7	1106.2
135°	1198.1	1195.5	1193.2	1190.8	1188.5	1186.2	1183.0	1178.8	1174.8	1170.6	1166.5
137.5°	1254.8	1252.3	1249.7	1247.1	1244.4	1241.8	1239.0	1236.2	1233.3	1230.4	1227.5
140°	1291.8	1289.4	1286.6	1283.8	1280.9	1278.1	1275.6	1273.6	1271.5	1269.4	1267.4
142.5°	1325.8	1323.7	1320.5	1317.3	1314.0	1310.8	1308.2	1306.4	1304.5	1302.6	1300.8
145°	1373.5	1371.7	1367.3	1363.0	1358.6	1354.2	1352.2	1352.4	1352.7	1352.9	1353.2
147.5°	1415.3	1414.0	1409.7	1405.3	1400.9	1396.6	1395.0	1396.0	1396.9	1397.9	1398.9
150°	1440.6	1439.0	1434.8	1430.8	1426.6	1422.5	1421.3	1423.2	1425.0	1426.8	1428.6
152.5°	1463.7	1462.2	1458.2	1454.3	1450.4	1446.5	1445.6	1447.6	1449.6	1451.6	1453.6
155°	1495.0	1493.5	1490.4	1487.4	1484.3	1481.2	1480.7	1483.0	1485.4	1487.7	1490.0
157.5°	1521.3	1519.5	1517.3	1515.2	1513.0	1510.8	1510.7	1512.7	1514.7	1516.6	1518.6
160°	1536.8	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2
162.5°	1550.9	1549.2	1547.8	1546.5	1545.2	1543.8	1543.9	1545.5	1547.0	1548.6	1550.0
165°	1568.4	1566.5	1565.8	1565.0	1564.2	1563.5	1563.8	1565.4	1566.9	1568.5	1570.0
167.5°	1583.0	1581.2	1580.5	1579.7	1579.0	1578.3	1578.7	1580.2	1581.8	1583.3	1584.9
170°	1590.4	1588.6	1588.0	1587.6	1587.1	1586.5	1587.1	1588.6	1590.2	1591.7	1593.3
172.5°	1595.9	1594.2	1593.7	1593.1	1592.6	1592.1	1592.6	1594.2	1595.7	1597.3	1598.8
175°	1602.0	1600.2	1599.7	1599.1	1598.6	1598.1	1598.8	1600.6	1602.4	1604.2	1606.0
177.5°	1603.0	1601.6	1601.3	1601.2	1600.9	1600.8	1601.3	1602.8	1604.3	1605.7	1607.1
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1415.0	1417.2	1424.1	1431.0	1438.8	1441.0	1444.5	1441.4	1440.6	1448.8	1454.8
5°	1419.0	1428.7	1447.7	1465.0	1479.6	1489.9	1500.7	1505.0	1513.1	1524.5	1538.6
7.5°	1414.5	1433.4	1463.1	1488.4	1515.9	1535.6	1551.1	1564.3	1580.4	1601.9	1625.4
10°	1409.2	1434.7	1471.0	1501.8	1535.3	1560.7	1581.8	1602.4	1626.2	1656.0	1686.8
12.5°	1399.8	1430.0	1475.3	1511.7	1554.8	1579.8	1608.3	1652.6	1678.1	1719.6	1763.0
15°	1380.6	1414.1	1477.4	1522.3	1571.0	1618.6	1671.1	1713.4	1755.5	1779.9	1841.0
17.5°	1352.2	1401.4	1471.5	1523.9	1585.8	1660.8	1719.7	1767.5	1816.2	1855.7	1886.4
20°	1329.2	1382.7	1462.8	1525.6	1599.1	1679.8	1747.4	1796.1	1838.3	1871.3	1890.2
22.5°	1300.2	1367.6	1445.5	1519.1	1613.0	1692.7	1763.8	1802.1	1837.4	1853.5	1860.8
25°	1254.6	1335.7	1423.9	1513.7	1619.8	1704.1	1769.0	1792.3	1802.5	1786.9	1760.9
27.5°	1205.3	1295.8	1398.9	1503.5	1615.6	1696.7	1743.3	1739.6	1722.2	1671.4	1630.8
30°	1168.6	1268.1	1379.0	1493.1	1605.7	1684.7	1711.7	1684.7	1645.1	1588.4	1530.5
32.5°	1130.0	1233.1	1357.8	1478.4	1587.5	1656.9	1662.8	1616.2	1555.1	1490.5	1418.4
35°	1071.7	1183.2	1317.8	1445.5	1548.8	1592.7	1566.7	1484.5	1412.0	1323.8	1225.3
37.5°	1005.8	1128.9	1264.0	1397.3	1490.9	1502.4	1437.9	1351.4	1249.1	1145.5	1029.6
40°	956.5	1086.9	1225.9	1360.6	1443.3	1431.4	1349.2	1254.0	1132.3	1005.7	898.1
42.5°	912.3	1042.7	1184.3	1316.5	1382.7	1350.1	1254.0	1137.2	1006.3	887.1	788.6
45°	835.8	970.0	1115.0	1242.7	1280.5	1221.6	1094.5	964.6	835.8	736.3	658.4
47.5°	761.6	894.2	1037.8	1150.1	1163.4	1084.1	945.2	811.6	700.9	619.9	564.9
50°	707.1	840.2	982.4	1082.6	1078.2	982.4	839.6	712.5	620.0	554.5	517.7
52.5°	658.2	783.9	920.6	1011.5	988.6	884.2	747.9	635.0	559.0	507.8	474.4
55°	582.1	698.4	828.3	901.3	859.1	743.3	628.1	537.2	480.9	442.5	416.5
57.5°	506.5	615.6	726.8	771.8	725.1	618.2	522.2	456.2	413.9	385.5	368.6
60°	459.8	555.1	654.0	693.0	637.3	542.1	466.4	407.4	373.2	350.0	334.8
62.5°	413.1	498.4	591.7	612.9	562.0	481.5	414.4	365.4	337.4	316.7	302.4
65°	349.5	419.2	490.2	504.2	457.1	394.9	341.9	310.0	285.1	269.9	258.6
67.5°	286.6	342.7	392.9	404.2	363.0	319.8	281.5	253.7	236.8	224.3	214.7
70°	249.4	293.8	334.8	344.1	311.0	272.6	243.4	221.3	206.1	195.3	186.1
72.5°	210.0	247.0	281.2	287.4	260.4	231.1	207.1	189.6	176.3	169.3	160.5
75°	160.7	182.3	208.8	210.4	192.6	174.7	156.4	145.0	137.9	129.3	125.0
77.5°	113.4	130.4	145.5	148.5	137.9	125.7	115.4	106.5	100.5	96.5	92.5
80°	86.6	100.1	106.6	110.4	102.8	94.2	88.2	82.3	78.4	75.7	73.1
82.5°	61.9	70.2	76.3	79.2	75.1	69.9	63.9	60.6	57.6	55.4	54.5
85°	31.4	35.1	39.0	40.0	39.0	36.8	33.5	33.5	31.9	31.4	31.4
87.5°	11.7	13.9	14.5	16.4	16.0	16.4	16.8	16.8	16.8	16.6	16.4
90°	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5	25.8
92.5°	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6	28.2
95°	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5	47.8
97.5°	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6	62.6
100°	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2	70.2
102.5°	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6	73.3
105°	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5	76.4
107.5°	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1	93.3
110°	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2	151.4



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8	323.8
115°	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1	476.9
117.5°	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6	734.7
120°	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0	856.1
122.5°	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5	908.4
125°	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6	983.4
127.5°	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2	1052.8
130°	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0	1096.8
132.5°	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2	1139.5
135°	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1	1200.6
137.5°	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8	1257.4
140°	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8	1294.0
142.5°	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8	1328.0
145°	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5	1375.3
147.5°	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3	1416.7
150°	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6	1442.1
152.5°	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7	1465.3
155°	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0	1496.6
157.5°	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3	1523.0
160°	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8	1538.3
162.5°	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9	1552.7
165°	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4	1570.2
167.5°	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0	1584.8
170°	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4	1592.2
172.5°	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9	1597.7
175°	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0	1603.8
177.5°	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0	1604.4
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1460.0	1466.1	1466.1	1467.0	1473.9	1473.0	1472.6
5°	1553.7	1562.9	1564.0	1573.8	1580.2	1578.1	1572.1
7.5°	1642.1	1659.2	1672.2	1679.4	1688.0	1693.3	1690.9
10°	1712.2	1737.1	1752.2	1762.5	1775.0	1784.2	1780.9
12.5°	1775.9	1805.5	1826.3	1843.9	1845.5	1857.3	1849.3
15°	1875.1	1906.4	1909.7	1922.6	1933.0	1931.9	1932.4
17.5°	1907.9	1917.9	1919.9	1920.3	1920.4	1916.6	1908.4
20°	1896.1	1892.4	1883.2	1876.2	1863.7	1862.1	1851.3
22.5°	1840.8	1828.8	1805.7	1790.5	1771.1	1766.0	1763.0
25°	1731.7	1705.2	1668.4	1633.2	1623.5	1604.6	1610.0
27.5°	1582.1	1540.8	1500.9	1472.3	1446.5	1418.1	1426.3
30°	1476.9	1430.4	1374.1	1330.8	1303.3	1276.2	1271.3
32.5°	1351.4	1283.2	1220.5	1182.3	1140.1	1123.0	1104.2
35°	1135.0	1068.4	1006.2	952.7	921.9	898.1	876.4
37.5°	940.4	863.7	813.5	770.1	747.9	734.3	737.7
40°	819.6	752.5	715.8	682.7	662.2	652.4	654.6
42.5°	721.8	671.6	641.3	618.6	604.1	598.8	597.5
45°	610.7	582.6	557.7	544.8	537.8	531.8	528.0
47.5°	535.0	512.1	498.1	490.3	484.2	478.1	478.0
50°	489.6	474.4	464.7	456.6	451.8	447.4	451.2
52.5°	454.9	441.2	431.4	424.1	422.3	418.4	418.3
55°	403.6	392.7	385.7	379.2	376.0	373.8	371.1
57.5°	356.9	346.6	340.1	336.0	329.8	327.6	326.8
60°	323.5	315.4	308.9	303.5	300.8	296.4	296.4
62.5°	292.8	284.7	278.6	274.5	270.0	268.3	268.8
65°	248.3	241.8	235.9	231.5	230.5	227.2	228.3
67.5°	207.4	203.1	196.8	194.4	192.4	190.6	189.3
70°	180.2	175.9	172.6	169.3	167.7	167.7	167.7
72.5°	157.2	152.1	150.1	145.9	146.9	145.2	143.5
75°	121.7	118.5	116.8	115.2	112.5	112.5	112.5
77.5°	89.6	88.6	86.7	85.0	84.3	83.7	84.0
80°	69.2	68.7	67.6	67.6	66.5	66.0	64.9
82.5°	53.2	51.9	51.2	50.7	50.5	50.4	50.2
85°	30.3	29.2	29.2	29.8	28.7	28.7	29.2
87.5°	17.1	17.4	17.1	17.2	17.8	17.4	17.5
90°	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	125.6	99.9	87.5	88.5	89.5	90.6	91.6



TEST NUMBER: P331579-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)