

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331595-927

Luminaire Tested: **S122DIW-S1005D710U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331595-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5460.2 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.2
10°-20°	334.1	6.1
20°-30°	491.0	9.0
30°-40°	570.4	10.4
40°-50°	569.8	10.4
50°-60°	496.9	9.1
60°-70°	367.4	6.7
70°-80°	208.1	3.8
80°-90°	57.9	1.1
90°-100°	25.6	0.5
100°-110°	93.8	1.7
110°-120°	250.6	4.6
120°-130°	413.7	7.6
130°-140°	440.0	8.1
140°-150°	408.9	7.5
150°-160°	328.8	6.0
160°-170°	211.9	3.9
170°-180°	72.9	1.3
0°-30°	943.8	17.3
0°-40°	1514.2	27.7
0°-60°	2580.8	47.3
0°-90°	3214.1	58.9
90°-120°	369.9	6.8
90°-150°	1632.5	29.9
90°-180°	2246.0	41.1
0°-180°	5460.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	6	11	14	15	4
95°	36	19	22	24	24	44
105°	169	176	34	40	42	180
115°	319	329	342	97	46	314
125°	451	458	469	472	474	402
135°	558	567	572	577	576	431
145°	647	647	656	660	657	405
155°	713	708	714	717	713	328
165°	751	748	749	753	749	212
175°	768	764	765	769	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.4	17.3	17.1	17.0	16.7	16.6	16.3	16.1	15.8	15.3
90°	0.6	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7
92.5°	11.2	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2
95°	36.0	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3
97.5°	71.5	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5
100°	98.2	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6
102.5°	127.5	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7
105°	168.6	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2
107.5°	215.5	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9
110°	245.7	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.1	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9
115°	318.9	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1
117.5°	358.9	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2
120°	388.2	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0
122.5°	413.0	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6
125°	450.8	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4
127.5°	485.1	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2
130°	506.8	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2
132.5°	529.1	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8
135°	557.9	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0
137.5°	587.1	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2
140°	606.2	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8
142.5°	622.1	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1
145°	647.2	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0
147.5°	669.0	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9
150°	683.3	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0
152.5°	695.2	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1
155°	712.6	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0
157.5°	726.3	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5
160°	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0
162.5°	741.3	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7
165°	750.9	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1
167.5°	758.0	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1
170°	762.0	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7
172.5°	764.6	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3
175°	768.1	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2
177.5°	768.7	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	14.7	14.3	13.7	13.4	13.2	13.1	12.9	12.7
90°	12.4	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.5	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	22.9	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	29.9	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	33.6	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	35.1	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	36.5	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	44.6	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	72.4	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331595-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	154.9	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	228.1	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	351.4	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	409.5	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	434.4	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	470.3	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	503.5	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	524.6	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	545.0	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	574.3	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	601.3	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	618.9	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	635.1	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	657.7	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	677.6	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	689.7	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	700.8	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	715.7	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	728.4	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	735.7	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	742.6	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.0	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	761.5	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	764.1	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.1	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	767.4	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)