

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331555-930

Luminaire Tested: **S122DIW-S865D435U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331555-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4518.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																												
1	103	98	95	91	97	93	90	87	83	81	79	74	72	71	66	65	63	59																												
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	51																												
3	86	77	70	64	81	73	67	61	66	61	56	59	55	52	53	50	47	44																												
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38																												
5	73	62	54	48	69	59	51	46	53	47	43	48	43	39	43	39	36	34																												
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32	30																												
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27																												
8	59	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24																												
9	55	42	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22																												
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22727	22727	22727	22727
5°	25480	22875	20272	22875
10°	29198	22689	17544	22689
15°	32301	22272	15499	22272
20°	31809	21825	14129	21825
25°	28682	21232	13261	21232
30°	23702	20282	12629	20282
35°	17274	19291	12177	19291
40°	13797	18120	11927	18120
45°	12056	16762	11586	16762
50°	11333	15450	11359	15450
55°	10446	14117	11054	14117
60°	9571	12700	10585	12700
65°	8722	11427	10128	11427
70°	7917	10192	9451	10192
75°	7018	8808	8372	8808
80°	6034	7290	6741	7290
85°	5409	5409	4001	5409



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	3.0
10°-20°	389.7	8.6
20°-30°	565.6	12.5
30°-40°	596.9	13.2
40°-50°	528.5	11.7
50°-60°	421.7	9.3
60°-70°	286.7	6.3
70°-80°	147.0	3.3
80°-90°	36.6	0.8
90°-100°	16.1	0.4
100°-110°	58.9	1.3
110°-120°	157.5	3.5
120°-130°	259.9	5.8
130°-140°	276.4	6.1
140°-150°	256.9	5.7
150°-160°	206.6	4.6
160°-170°	133.1	2.9
170°-180°	45.8	1.0
0°-30°	1089.4	24.1
0°-40°	1686.3	37.3
0°-60°	2636.5	58.4
0°-90°	3106.7	68.8
90°-120°	232.4	5.1
90°-150°	1025.8	22.7
90°-180°	1411.0	31.2
0°-180°	4518.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1408	1408	1408	1408	1408	
5°	1572	1411	1251	1411	1572	157
15°	1932	1332	927	1332	1932	533
25°	1610	1192	744	1192	1610	728
35°	876	979	618	979	876	570
45°	528	734	507	734	528	415
55°	371	502	393	502	371	333
65°	228	299	265	299	228	227
75°	112	141	134	141	112	120
85°	29	29	22	29	29	32
90°	9	0	9	0	9	6
95°	15	23	15	23	15	14
105°	26	106	26	106	26	28
115°	28	200	28	200	28	72
125°	298	283	298	283	298	258
135°	362	351	362	351	362	279
145°	413	407	413	407	413	258
155°	448	448	448	448	448	207
165°	471	472	471	472	471	133
175°	480	483	480	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1472.6	1473.0	1473.9	1467.0	1466.1	1466.1	1460.0	1454.8	1448.8	1440.6	1441.4
5°	1572.1	1578.1	1580.2	1573.8	1564.0	1562.9	1553.7	1538.6	1524.5	1513.1	1505.0
7.5°	1690.9	1693.3	1688.0	1679.4	1672.2	1659.2	1642.1	1625.4	1601.9	1580.4	1564.3
10°	1780.9	1784.2	1775.0	1762.5	1752.2	1737.1	1712.2	1686.8	1656.0	1626.2	1602.4
12.5°	1849.3	1857.3	1845.5	1843.9	1826.3	1805.5	1775.9	1763.0	1719.6	1678.1	1652.6
15°	1932.4	1931.9	1933.0	1922.6	1909.7	1906.4	1875.1	1841.0	1779.9	1755.5	1713.4
17.5°	1908.4	1916.6	1920.4	1920.3	1919.9	1917.9	1907.9	1886.4	1855.7	1816.2	1767.5
20°	1851.3	1862.1	1863.7	1876.2	1883.2	1892.4	1896.1	1890.2	1871.3	1838.3	1796.1
22.5°	1763.0	1766.0	1771.1	1790.5	1805.7	1828.8	1840.8	1860.8	1853.5	1837.4	1802.1
25°	1610.0	1604.6	1623.5	1633.2	1668.4	1705.2	1731.7	1760.9	1786.9	1802.5	1792.3
27.5°	1426.3	1418.1	1446.5	1472.3	1500.9	1540.8	1582.1	1630.8	1671.4	1722.2	1739.6
30°	1271.3	1276.2	1303.3	1330.8	1374.1	1430.4	1476.9	1530.5	1588.4	1645.1	1684.7
32.5°	1104.2	1123.0	1140.1	1182.3	1220.5	1283.2	1351.4	1418.4	1490.5	1555.1	1616.2
35°	876.4	898.1	921.9	952.7	1006.2	1068.4	1135.0	1225.3	1323.8	1412.0	1484.5
37.5°	737.7	734.3	747.9	770.1	813.5	863.7	940.4	1029.6	1145.5	1249.1	1351.4
40°	654.6	652.4	662.2	682.7	715.8	752.5	819.6	898.1	1005.7	1132.3	1254.0
42.5°	597.5	598.8	604.1	618.6	641.3	671.6	721.8	788.6	887.1	1006.3	1137.2
45°	528.0	531.8	537.8	544.8	557.7	582.6	610.7	658.4	736.3	835.8	964.6
47.5°	478.0	478.1	484.2	490.3	498.1	512.1	535.0	564.9	619.9	700.9	811.6
50°	451.2	447.4	451.8	456.6	464.7	474.4	489.6	517.7	554.5	620.0	712.5
52.5°	418.3	418.4	422.3	424.1	431.4	441.2	454.9	474.4	507.8	559.0	635.0
55°	371.1	373.8	376.0	379.2	385.7	392.7	403.6	416.5	442.5	480.9	537.2
57.5°	326.8	327.6	329.8	336.0	340.1	346.6	356.9	368.6	385.5	413.9	456.2
60°	296.4	296.4	300.8	303.5	308.9	315.4	323.5	334.8	350.0	373.2	407.4
62.5°	268.8	268.3	270.0	274.5	278.6	284.7	292.8	302.4	316.7	337.4	365.4
65°	228.3	227.2	230.5	231.5	235.9	241.8	248.3	258.6	269.9	285.1	310.0
67.5°	189.3	190.6	192.4	194.4	196.8	203.1	207.4	214.7	224.3	236.8	253.7
70°	167.7	167.7	167.7	169.3	172.6	175.9	180.2	186.1	195.3	206.1	221.3
72.5°	143.5	145.2	146.9	145.9	150.1	152.1	157.2	160.5	169.3	176.3	189.6
75°	112.5	112.5	112.5	115.2	116.8	118.5	121.7	125.0	129.3	137.9	145.0
77.5°	84.0	83.7	84.3	85.0	86.7	88.6	89.6	92.5	96.5	100.5	106.5
80°	64.9	66.0	66.5	67.6	67.6	68.7	69.2	73.1	75.7	78.4	82.3
82.5°	50.2	50.4	50.5	50.7	51.2	51.9	53.2	54.5	55.4	57.6	60.6
85°	29.2	28.7	28.7	29.8	29.2	29.2	30.3	31.4	31.4	31.9	33.5
87.5°	13.1	13.1	13.5	13.0	13.0	13.4	13.3	12.8	13.1	13.5	13.9
90°	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7	7.3	6.9	6.4
92.5°	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5	8.3	8.1	7.7
95°	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3	13.9	13.6	13.0
97.5°	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8	18.5	18.2	17.0
100°	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1	20.5	19.9	18.5
102.5°	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0	21.2	20.4	31.5
105°	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0	22.1	21.3	42.4
107.5°	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0	28.9	29.8	55.1
110°	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5	53.2	61.0	83.3



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3	125.6	153.8	159.3
115°	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3	179.1	215.0	213.0
117.5°	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8	229.5	238.1	236.8
120°	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3	256.3	255.4	254.0
122.5°	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0	272.5	271.9	270.4
125°	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5	295.0	294.5	293.0
127.5°	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4	315.6	314.8	313.7
130°	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6	328.7	327.9	327.1
132.5°	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5	341.8	341.0	340.1
135°	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9	360.0	359.3	358.6
137.5°	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9	377.1	376.3	375.5
140°	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9	388.2	387.5	386.6
142.5°	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1	398.4	397.8	396.8
145°	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4	412.8	412.2	410.9
147.5°	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7	425.3	424.9	423.6
150°	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4	432.9	432.4	431.2
152.5°	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3	439.9	439.4	438.2
155°	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8	449.3	448.8	447.9
157.5°	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7	457.1	456.6	456.0
160°	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3	461.9	461.4	460.9
162.5°	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6	466.1	465.5	465.1
165°	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8	470.6
167.5°	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3	475.7	475.2	475.0
170°	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5	477.9	477.4	477.3
172.5°	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1	479.6	479.1	478.9
175°	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0	481.4	480.9	480.7
177.5°	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2	481.8	481.3	481.3
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1444.5	1441.0	1438.8	1431.0	1424.1	1417.2	1415.0	1415.8	1406.4	1397.3	1393.3
5°	1500.7	1489.9	1479.6	1465.0	1447.7	1428.7	1419.0	1411.4	1392.5	1372.0	1360.1
7.5°	1551.1	1535.6	1515.9	1488.4	1463.1	1433.4	1414.5	1397.7	1370.0	1341.0	1323.2
10°	1581.8	1560.7	1535.3	1501.8	1471.0	1434.7	1409.2	1383.9	1351.4	1316.8	1295.1
12.5°	1608.3	1579.8	1554.8	1511.7	1475.3	1430.0	1399.8	1363.9	1329.8	1288.7	1267.5
15°	1671.1	1618.6	1571.0	1522.3	1477.4	1414.1	1380.6	1332.4	1287.5	1236.7	1212.4
17.5°	1719.7	1660.8	1585.8	1523.9	1471.5	1401.4	1352.2	1294.5	1241.4	1183.2	1150.1
20°	1747.4	1679.8	1599.1	1525.6	1462.8	1382.7	1329.2	1270.2	1208.0	1142.6	1106.9
22.5°	1763.8	1692.7	1613.0	1519.1	1445.5	1367.6	1300.2	1235.6	1172.6	1101.9	1064.5
25°	1769.0	1704.1	1619.8	1513.7	1423.9	1335.7	1254.6	1191.8	1115.5	1049.5	994.9
27.5°	1743.3	1696.7	1615.6	1503.5	1398.9	1295.8	1205.3	1134.2	1053.8	982.1	927.2
30°	1711.7	1684.7	1605.7	1493.1	1379.0	1268.1	1168.6	1087.9	1007.9	935.4	879.1
32.5°	1662.8	1656.9	1587.5	1478.4	1357.8	1233.1	1130.0	1048.6	959.9	888.6	834.9
35°	1566.7	1592.7	1548.8	1445.5	1317.8	1183.2	1071.7	978.7	886.7	818.5	768.2
37.5°	1437.9	1502.4	1490.9	1397.3	1264.0	1128.9	1005.8	908.6	820.9	752.1	702.7
40°	1349.2	1431.4	1443.3	1360.6	1225.9	1086.9	956.5	859.7	774.1	711.4	661.6
42.5°	1254.0	1350.1	1382.7	1316.5	1184.3	1042.7	912.3	812.0	727.4	666.4	622.2
45°	1094.5	1221.6	1280.5	1242.7	1115.0	970.0	835.8	734.1	657.3	600.0	565.9
47.5°	945.2	1084.1	1163.4	1150.1	1037.8	894.2	761.6	664.0	589.2	543.5	513.0
50°	839.6	982.4	1078.2	1082.6	982.4	840.2	707.1	615.1	546.4	503.7	478.7
52.5°	747.9	884.2	988.6	1011.5	920.6	783.9	658.2	566.6	506.1	466.8	444.6
55°	628.1	743.3	859.1	901.3	828.3	698.4	582.1	501.5	444.7	417.7	398.2
57.5°	522.2	618.2	725.1	771.8	726.8	615.6	506.5	436.6	390.4	366.8	351.9
60°	466.4	542.1	637.3	693.0	654.0	555.1	459.8	393.3	355.5	334.4	320.2
62.5°	414.4	481.5	562.0	612.9	591.7	498.4	413.1	354.3	321.6	301.9	291.7
65°	341.9	394.9	457.1	504.2	490.2	419.2	349.5	299.1	273.2	257.5	249.4
67.5°	281.5	319.8	363.0	404.2	392.9	342.7	286.6	247.4	228.1	214.6	209.7
70°	243.4	272.6	311.0	344.1	334.8	293.8	249.4	215.9	199.1	187.8	182.9
72.5°	207.1	231.1	260.4	287.4	281.2	247.0	210.0	184.7	171.8	161.3	157.4
75°	156.4	174.7	192.6	210.4	208.8	182.3	160.7	141.2	130.9	122.8	121.2
77.5°	115.4	125.7	137.9	148.5	145.5	130.4	113.4	102.2	94.7	89.3	88.4
80°	88.2	94.2	102.8	110.4	106.6	100.1	86.6	78.4	73.1	67.6	65.5
82.5°	63.9	69.9	75.1	79.2	76.3	70.2	61.9	56.3	53.2	49.4	48.6
85°	33.5	36.8	39.0	40.0	39.0	35.1	31.4	29.2	26.5	24.9	24.4
87.5°	14.1	14.0	13.9	14.6	13.1	13.0	11.1	9.6	9.3	9.0	8.4
90°	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3	1.2	2.0	2.9
92.5°	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0	6.9	6.8	6.8
95°	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7	20.1	17.5	15.0
97.5°	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9	37.7	30.6	23.3
100°	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7	51.0	40.4	29.8
102.5°	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1	77.9	75.6	73.4
105°	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9	108.3	110.6	112.9
107.5°	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4	137.3	139.2	141.0
110°	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3	156.0	157.6	159.2



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2	173.7	175.1	176.5
115°	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4	201.7	203.0	204.3
117.5°	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5	227.0	228.4	229.9
120°	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9	245.1	246.2	247.4
122.5°	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5	260.7	262.0	263.2
125°	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3	284.3	285.4	286.3
127.5°	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8	306.0	307.0	308.2
130°	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5	319.8	321.0	322.2
132.5°	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5	333.5	334.5	335.6
135°	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6	351.8	353.0	354.2
137.5°	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9	369.7	370.6	371.5
140°	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9	381.5	382.1	382.7
142.5°	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9	391.5	392.0	392.6
145°	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7	406.6	406.5	406.4
147.5°	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4	420.1	419.8	419.6
150°	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3	428.8	428.2	427.7
152.5°	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8	436.3	435.6	435.0
155°	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8	447.1	446.4	445.7
157.5°	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3	455.8	455.2	454.6
160°	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	460.9	460.5	460.0
162.5°	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9	465.4	464.9	464.5
165°	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8	471.4	470.9	470.4
167.5°	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3	475.8	475.4	474.9
170°	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8	478.3	477.8	477.4
172.5°	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5	480.0	479.6	479.1
175°	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7	482.1	481.5	481.0
177.5°	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0	482.6	482.1	481.7
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1389.0	1386.4	1377.4	1372.6	1364.8	1357.5	1352.7	1354.9	1356.6	1355.7	1354.5
5°	1349.2	1339.0	1323.2	1309.7	1300.0	1282.1	1274.6	1270.8	1267.5	1263.7	1260.0
7.5°	1301.9	1285.6	1263.1	1243.8	1225.6	1203.5	1190.8	1183.2	1175.5	1166.9	1159.4
10°	1268.1	1245.4	1221.6	1194.5	1172.9	1152.8	1135.0	1123.1	1112.3	1102.0	1094.5
12.5°	1232.6	1206.4	1177.0	1140.0	1116.1	1087.5	1084.8	1063.8	1046.9	1040.6	1031.7
15°	1176.2	1139.3	1102.0	1058.2	1039.3	1013.3	997.0	980.8	966.2	955.9	953.2
17.5°	1112.0	1064.4	1027.2	995.7	964.7	938.1	923.2	910.2	898.1	884.4	882.6
20°	1063.1	1021.9	981.4	953.7	921.9	894.8	876.4	863.4	853.1	845.1	838.0
22.5°	1016.8	971.8	934.6	904.4	872.9	851.1	836.6	824.0	815.5	806.5	799.9
25°	942.4	907.3	866.7	832.6	806.6	792.6	780.6	769.8	764.4	758.5	750.9
27.5°	877.3	838.3	800.4	774.0	751.1	738.7	730.3	722.8	717.8	714.3	710.0
30°	831.5	792.0	762.2	736.3	717.4	704.9	699.5	695.2	689.3	687.1	684.9
32.5°	787.3	751.8	726.4	703.8	685.7	677.7	672.7	668.8	664.1	661.9	657.6
35°	725.0	695.2	670.3	657.9	643.3	636.2	632.4	627.0	622.6	620.5	620.0
37.5°	666.2	640.3	623.9	608.0	601.8	597.5	592.3	588.6	587.3	586.9	586.4
40°	628.1	607.0	592.4	579.4	576.7	570.2	565.9	562.6	562.6	563.2	562.6
42.5°	593.5	574.5	561.7	550.4	547.2	543.4	539.1	538.8	539.7	541.5	539.7
45°	541.0	527.5	518.3	512.8	506.9	503.1	502.6	504.2	504.8	505.3	506.9
47.5°	492.8	483.7	475.4	469.4	466.8	466.2	465.5	468.4	471.0	472.0	474.4
50°	464.1	453.9	446.9	443.0	440.9	439.9	440.9	444.2	446.3	449.0	450.6
52.5°	432.1	424.9	420.0	417.1	416.2	416.9	417.1	420.8	424.3	425.2	426.0
55°	387.9	382.5	381.4	376.5	378.7	378.1	380.8	383.0	386.3	389.6	390.0
57.5°	343.7	339.4	336.5	337.0	337.6	340.0	342.3	346.0	349.5	352.9	353.3
60°	314.3	312.2	310.5	310.5	311.6	314.9	317.6	321.3	323.5	325.7	327.3
62.5°	287.5	285.4	283.7	284.5	287.4	289.3	292.4	294.5	296.7	298.8	299.6
65°	245.1	244.0	245.6	246.7	247.2	250.0	253.7	255.4	257.5	258.6	262.4
67.5°	206.0	206.2	206.0	207.5	210.7	211.3	214.9	218.7	219.1	221.2	223.6
70°	179.6	180.7	181.8	182.9	185.6	186.6	189.3	190.9	193.1	194.8	196.4
72.5°	155.4	155.6	156.7	156.5	158.7	161.1	163.4	165.0	167.1	169.3	170.8
75°	119.5	119.5	120.7	121.2	123.9	126.6	126.0	127.1	129.3	131.4	132.6
77.5°	87.3	86.1	87.3	87.9	88.7	91.0	91.4	92.9	95.4	94.7	95.9
80°	66.5	64.9	66.5	67.1	67.1	69.8	69.8	70.8	72.5	70.8	72.5
82.5°	47.5	46.7	47.9	48.0	48.9	49.0	49.9	50.1	51.7	51.0	51.7
85°	23.8	23.2	23.8	23.2	23.8	24.4	24.4	23.8	23.8	24.9	23.2
87.5°	8.1	7.8	7.5	7.7	7.3	7.0	6.7	6.8	6.8	6.0	6.1
90°	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7	8.2	8.5	8.8
92.5°	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5	8.7	8.9	9.0
95°	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3	14.8	15.2	15.3
97.5°	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8	19.2	19.4	19.6
100°	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1	21.7	22.3	22.7
102.5°	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0	22.8	23.6	24.1
105°	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0	23.8	24.7	25.3
107.5°	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0	27.1	26.3	26.0
110°	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5	37.7	30.0	26.3



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3	69.1	40.8	26.8
115°	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3	107.5	71.6	50.9
117.5°	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8	212.1	203.4	190.0
120°	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3	258.2	259.2	254.4
122.5°	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0	273.5	274.1	273.4
125°	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5	296.1	296.6	297.0
127.5°	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4	317.2	318.0	318.4
130°	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6	330.4	331.3	331.7
132.5°	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5	343.2	343.9	344.2
135°	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9	361.6	362.4	362.6
137.5°	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9	378.6	379.4	379.6
140°	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9	389.6	390.3	390.4
142.5°	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1	399.7	400.4	400.5
145°	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4	413.8	414.4	414.5
147.5°	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7	426.2	426.6	426.6
150°	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4	433.8	434.3	434.4
152.5°	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3	440.8	441.3	441.2
155°	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8	450.2	450.7	450.6
157.5°	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7	458.2	458.8	458.7
160°	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3	462.8	463.3	463.2
162.5°	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6	467.2	467.7	467.6
165°	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9	472.4	473.0	473.0
167.5°	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3	476.8	477.4	477.3
170°	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5	479.1	479.6	479.5
172.5°	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1	480.7	481.3	481.2
175°	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0	482.5	483.1	483.0
177.5°	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2	482.6	483.1	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1350.1	1349.2	1349.2	1345.3	1349.2	1349.2	1350.1	1354.5	1355.7	1356.6	1354.9
5°	1252.4	1250.8	1248.1	1250.8	1248.1	1250.8	1252.4	1260.0	1263.7	1267.5	1270.8
7.5°	1155.8	1149.2	1148.3	1141.9	1148.3	1149.2	1155.8	1159.4	1166.9	1175.5	1183.2
10°	1085.2	1080.9	1080.4	1070.1	1080.4	1080.9	1085.2	1094.5	1102.0	1112.3	1123.1
12.5°	1031.6	1021.2	1023.2	1017.2	1023.2	1021.2	1031.6	1031.7	1040.6	1046.9	1063.8
15°	938.7	938.7	936.5	927.2	936.5	938.7	938.7	953.2	955.9	966.2	980.8
17.5°	871.9	870.7	865.6	868.2	865.6	870.7	871.9	882.6	884.4	898.1	910.2
20°	832.0	828.8	822.3	822.3	822.3	828.8	832.0	838.0	845.1	853.1	863.4
22.5°	794.4	794.2	787.3	789.4	787.3	794.2	794.4	799.9	806.5	815.5	824.0
25°	750.3	746.0	742.8	744.4	742.8	746.0	750.3	750.9	758.5	764.4	769.8
27.5°	708.6	706.2	706.0	701.6	706.0	706.2	708.6	710.0	714.3	717.8	722.8
30°	684.4	679.0	680.0	677.4	680.0	679.0	684.4	684.9	687.1	689.3	695.2
32.5°	656.6	654.7	653.6	651.3	653.6	654.7	656.6	657.6	661.9	664.1	668.8
35°	618.9	619.5	616.7	617.8	616.7	619.5	618.9	620.0	620.5	622.6	627.0
37.5°	585.9	587.6	586.4	586.7	586.4	587.6	585.9	586.4	586.9	587.3	588.6
40°	564.3	564.3	564.3	565.9	564.3	564.3	564.3	562.6	563.2	562.6	562.6
42.5°	543.5	542.6	541.8	541.6	541.8	542.6	543.5	539.7	541.5	539.7	538.8
45°	508.0	509.6	510.1	507.4	510.1	509.6	508.0	506.9	505.3	504.8	504.2
47.5°	475.9	476.1	475.9	478.3	475.9	476.1	475.9	474.4	472.0	471.0	468.4
50°	453.4	452.2	453.4	452.2	453.4	452.2	453.4	450.6	449.0	446.3	444.2
52.5°	429.6	429.7	429.1	428.9	429.1	429.7	429.6	426.0	425.2	424.3	420.8
55°	392.2	393.3	392.7	392.7	392.7	393.3	392.2	390.0	389.6	386.3	383.0
57.5°	353.6	354.6	355.3	352.9	355.3	354.6	353.6	353.3	352.9	349.5	346.0
60°	326.8	329.5	328.9	327.8	328.9	329.5	326.8	327.3	325.7	323.5	321.3
62.5°	302.1	303.0	303.0	302.7	303.0	303.0	302.1	299.6	298.8	296.7	294.5
65°	264.0	265.1	263.4	265.1	263.4	265.1	264.0	262.4	258.6	257.5	255.4
67.5°	223.0	223.3	224.5	225.3	224.5	223.3	223.0	223.6	221.2	219.1	218.7
70°	197.5	196.9	198.5	200.2	198.5	196.9	197.5	196.4	194.8	193.1	190.9
72.5°	170.6	171.8	171.3	172.4	171.3	171.8	170.6	170.8	169.3	167.1	165.0
75°	131.4	133.1	132.6	134.2	132.6	133.1	131.4	132.6	131.4	129.3	127.1
77.5°	95.0	95.2	95.0	95.9	95.0	95.2	95.0	95.9	94.7	95.4	92.9
80°	72.5	71.4	70.4	72.5	70.4	71.4	72.5	72.5	70.8	72.5	70.8
82.5°	50.4	51.0	50.0	50.0	50.0	51.0	50.4	51.7	51.0	51.7	50.1
85°	23.2	22.7	21.6	21.6	21.6	22.7	23.2	23.2	24.9	23.8	23.8
87.5°	6.1	5.7	5.7	5.4	5.7	5.7	6.1	6.1	6.0	6.8	6.8
90°	9.0	9.1	9.3	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7
92.5°	9.1	9.2	9.3	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5
95°	15.2	15.2	15.1	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3
97.5°	19.7	19.8	19.9	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8
100°	22.9	23.1	23.2	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1
102.5°	24.4	24.6	24.8	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0
105°	25.5	25.8	26.2	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0
107.5°	26.3	26.7	26.9	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0
110°	26.6	26.9	27.2	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	27.1	27.3	27.6	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3
115°	45.3	39.7	34.2	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3
117.5°	171.6	153.3	135.0	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8
120°	243.9	233.5	223.0	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3
122.5°	271.3	269.3	267.3	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0
125°	297.3	297.5	297.7	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5
127.5°	318.5	318.5	318.5	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4
130°	331.7	331.6	331.5	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6
132.5°	344.1	344.1	344.1	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5
135°	362.6	362.4	362.2	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9
137.5°	379.4	379.1	378.9	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9
140°	390.0	389.6	389.3	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9
142.5°	400.1	399.7	399.3	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1
145°	414.1	413.7	413.4	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4
147.5°	426.2	425.9	425.6	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7
150°	434.0	433.6	433.2	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4
152.5°	440.8	440.3	439.7	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3
155°	450.0	449.4	448.7	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8
157.5°	458.1	457.5	456.9	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7
160°	462.7	462.1	461.5	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3
162.5°	466.9	466.3	465.6	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6
165°	472.4	471.9	471.3	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9
167.5°	476.5	475.9	475.2	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3
170°	478.8	478.1	477.4	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5
172.5°	480.5	479.8	479.1	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1
175°	482.2	481.4	480.6	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0
177.5°	482.4	481.8	481.3	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1352.7	1357.5	1364.8	1372.6	1377.4	1386.4	1389.0	1393.3	1397.3	1406.4	1415.8
5°	1274.6	1282.1	1300.0	1309.7	1323.2	1339.0	1349.2	1360.1	1372.0	1392.5	1411.4
7.5°	1190.8	1203.5	1225.6	1243.8	1263.1	1285.6	1301.9	1323.2	1341.0	1370.0	1397.7
10°	1135.0	1152.8	1172.9	1194.5	1221.6	1245.4	1268.1	1295.1	1316.8	1351.4	1383.9
12.5°	1084.8	1087.5	1116.1	1140.0	1177.0	1206.4	1232.6	1267.5	1288.7	1329.8	1363.9
15°	997.0	1013.3	1039.3	1058.2	1102.0	1139.3	1176.2	1212.4	1236.7	1287.5	1332.4
17.5°	923.2	938.1	964.7	995.7	1027.2	1064.4	1112.0	1150.1	1183.2	1241.4	1294.5
20°	876.4	894.8	921.9	953.7	981.4	1021.9	1063.1	1106.9	1142.6	1208.0	1270.2
22.5°	836.6	851.1	872.9	904.4	934.6	971.8	1016.8	1064.5	1101.9	1172.6	1235.6
25°	780.6	792.6	806.6	832.6	866.7	907.3	942.4	994.9	1049.5	1115.5	1191.8
27.5°	730.3	738.7	751.1	774.0	800.4	838.3	877.3	927.2	982.1	1053.8	1134.2
30°	699.5	704.9	717.4	736.3	762.2	792.0	831.5	879.1	935.4	1007.9	1087.9
32.5°	672.7	677.7	685.7	703.8	726.4	751.8	787.3	834.9	888.6	959.9	1048.6
35°	632.4	636.2	643.3	657.9	670.3	695.2	725.0	768.2	818.5	886.7	978.7
37.5°	592.3	597.5	601.8	608.0	623.9	640.3	666.2	702.7	752.1	820.9	908.6
40°	565.9	570.2	576.7	579.4	592.4	607.0	628.1	661.6	711.4	774.1	859.7
42.5°	539.1	543.4	547.2	550.4	561.7	574.5	593.5	622.2	666.4	727.4	812.0
45°	502.6	503.1	506.9	512.8	518.3	527.5	541.0	565.9	600.0	657.3	734.1
47.5°	465.5	466.2	466.8	469.4	475.4	483.7	492.8	513.0	543.5	589.2	664.0
50°	440.9	439.9	440.9	443.0	446.9	453.9	464.1	478.7	503.7	546.4	615.1
52.5°	417.1	416.9	416.2	417.1	420.0	424.9	432.1	444.6	466.8	506.1	566.6
55°	380.8	378.1	378.7	376.5	381.4	382.5	387.9	398.2	417.7	444.7	501.5
57.5°	342.3	340.0	337.6	337.0	336.5	339.4	343.7	351.9	366.8	390.4	436.6
60°	317.6	314.9	311.6	310.5	310.5	312.2	314.3	320.2	334.4	355.5	393.3
62.5°	292.4	289.3	287.4	284.5	283.7	285.4	287.5	291.7	301.9	321.6	354.3
65°	253.7	250.0	247.2	246.7	245.6	244.0	245.1	249.4	257.5	273.2	299.1
67.5°	214.9	211.3	210.7	207.5	206.0	206.2	206.0	209.7	214.6	228.1	247.4
70°	189.3	186.6	185.6	182.9	181.8	180.7	179.6	182.9	187.8	199.1	215.9
72.5°	163.4	161.1	158.7	156.5	156.7	155.6	155.4	157.4	161.3	171.8	184.7
75°	126.0	126.6	123.9	121.2	120.7	119.5	119.5	121.2	122.8	130.9	141.2
77.5°	91.4	91.0	88.7	87.9	87.3	86.1	87.3	88.4	89.3	94.7	102.2
80°	69.8	69.8	67.1	67.1	66.5	64.9	66.5	65.5	67.6	73.1	78.4
82.5°	49.9	49.0	48.9	48.0	47.9	46.7	47.5	48.6	49.4	53.2	56.3
85°	24.4	24.4	23.8	23.2	23.8	23.2	23.8	24.4	24.9	26.5	29.2
87.5°	6.7	7.0	7.3	7.7	7.5	7.8	8.1	8.4	9.0	9.3	9.6
90°	7.3	6.9	6.4	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3
92.5°	8.3	8.1	7.7	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0
95°	13.9	13.6	13.0	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7
97.5°	18.5	18.2	17.0	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9
100°	20.5	19.9	18.5	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7
102.5°	21.2	20.4	31.5	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1
105°	22.1	21.3	42.4	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9
107.5°	28.9	29.8	55.1	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4
110°	53.2	61.0	83.3	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.6	153.8	159.3	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2
115°	179.1	215.0	213.0	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4
117.5°	229.5	238.1	236.8	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5
120°	256.3	255.4	254.0	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9
122.5°	272.5	271.9	270.4	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5
125°	295.0	294.5	293.0	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3
127.5°	315.6	314.8	313.7	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8
130°	328.7	327.9	327.1	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5
132.5°	341.8	341.0	340.1	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5
135°	360.0	359.3	358.6	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6
137.5°	377.1	376.3	375.5	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9
140°	388.2	387.5	386.6	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9
142.5°	398.4	397.8	396.8	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9
145°	412.8	412.2	410.9	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7
147.5°	425.3	424.9	423.6	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4
150°	432.9	432.4	431.2	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3
152.5°	439.9	439.4	438.2	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8
155°	449.3	448.8	447.9	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8
157.5°	457.1	456.6	456.0	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3
160°	461.9	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4
162.5°	466.1	465.5	465.1	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9
165°	471.3	470.8	470.6	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8
167.5°	475.7	475.2	475.0	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3
170°	477.9	477.4	477.3	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8
172.5°	479.6	479.1	478.9	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5
175°	481.4	480.9	480.7	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7
177.5°	481.8	481.3	481.3	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1415.0	1417.2	1424.1	1431.0	1438.8	1441.0	1444.5	1441.4	1440.6	1448.8	1454.8
5°	1419.0	1428.7	1447.7	1465.0	1479.6	1489.9	1500.7	1505.0	1513.1	1524.5	1538.6
7.5°	1414.5	1433.4	1463.1	1488.4	1515.9	1535.6	1551.1	1564.3	1580.4	1601.9	1625.4
10°	1409.2	1434.7	1471.0	1501.8	1535.3	1560.7	1581.8	1602.4	1626.2	1656.0	1686.8
12.5°	1399.8	1430.0	1475.3	1511.7	1554.8	1579.8	1608.3	1652.6	1678.1	1719.6	1763.0
15°	1380.6	1414.1	1477.4	1522.3	1571.0	1618.6	1671.1	1713.4	1755.5	1779.9	1841.0
17.5°	1352.2	1401.4	1471.5	1523.9	1585.8	1660.8	1719.7	1767.5	1816.2	1855.7	1886.4
20°	1329.2	1382.7	1462.8	1525.6	1599.1	1679.8	1747.4	1796.1	1838.3	1871.3	1890.2
22.5°	1300.2	1367.6	1445.5	1519.1	1613.0	1692.7	1763.8	1802.1	1837.4	1853.5	1860.8
25°	1254.6	1335.7	1423.9	1513.7	1619.8	1704.1	1769.0	1792.3	1802.5	1786.9	1760.9
27.5°	1205.3	1295.8	1398.9	1503.5	1615.6	1696.7	1743.3	1739.6	1722.2	1671.4	1630.8
30°	1168.6	1268.1	1379.0	1493.1	1605.7	1684.7	1711.7	1684.7	1645.1	1588.4	1530.5
32.5°	1130.0	1233.1	1357.8	1478.4	1587.5	1656.9	1662.8	1616.2	1555.1	1490.5	1418.4
35°	1071.7	1183.2	1317.8	1445.5	1548.8	1592.7	1566.7	1484.5	1412.0	1323.8	1225.3
37.5°	1005.8	1128.9	1264.0	1397.3	1490.9	1502.4	1437.9	1351.4	1249.1	1145.5	1029.6
40°	956.5	1086.9	1225.9	1360.6	1443.3	1431.4	1349.2	1254.0	1132.3	1005.7	898.1
42.5°	912.3	1042.7	1184.3	1316.5	1382.7	1350.1	1254.0	1137.2	1006.3	887.1	788.6
45°	835.8	970.0	1115.0	1242.7	1280.5	1221.6	1094.5	964.6	835.8	736.3	658.4
47.5°	761.6	894.2	1037.8	1150.1	1163.4	1084.1	945.2	811.6	700.9	619.9	564.9
50°	707.1	840.2	982.4	1082.6	1078.2	982.4	839.6	712.5	620.0	554.5	517.7
52.5°	658.2	783.9	920.6	1011.5	988.6	884.2	747.9	635.0	559.0	507.8	474.4
55°	582.1	698.4	828.3	901.3	859.1	743.3	628.1	537.2	480.9	442.5	416.5
57.5°	506.5	615.6	726.8	771.8	725.1	618.2	522.2	456.2	413.9	385.5	368.6
60°	459.8	555.1	654.0	693.0	637.3	542.1	466.4	407.4	373.2	350.0	334.8
62.5°	413.1	498.4	591.7	612.9	562.0	481.5	414.4	365.4	337.4	316.7	302.4
65°	349.5	419.2	490.2	504.2	457.1	394.9	341.9	310.0	285.1	269.9	258.6
67.5°	286.6	342.7	392.9	404.2	363.0	319.8	281.5	253.7	236.8	224.3	214.7
70°	249.4	293.8	334.8	344.1	311.0	272.6	243.4	221.3	206.1	195.3	186.1
72.5°	210.0	247.0	281.2	287.4	260.4	231.1	207.1	189.6	176.3	169.3	160.5
75°	160.7	182.3	208.8	210.4	192.6	174.7	156.4	145.0	137.9	129.3	125.0
77.5°	113.4	130.4	145.5	148.5	137.9	125.7	115.4	106.5	100.5	96.5	92.5
80°	86.6	100.1	106.6	110.4	102.8	94.2	88.2	82.3	78.4	75.7	73.1
82.5°	61.9	70.2	76.3	79.2	75.1	69.9	63.9	60.6	57.6	55.4	54.5
85°	31.4	35.1	39.0	40.0	39.0	36.8	33.5	33.5	31.9	31.4	31.4
87.5°	11.1	13.0	13.1	14.6	13.9	14.0	14.1	13.9	13.5	13.1	12.8
90°	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7
92.5°	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5
95°	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3
97.5°	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8
100°	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1
102.5°	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0
105°	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0
107.5°	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0
110°	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3
115°	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3
117.5°	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8
120°	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3
122.5°	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0
125°	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5
127.5°	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4
130°	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6
132.5°	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5
135°	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9
137.5°	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9
140°	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9
142.5°	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1
145°	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4
147.5°	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7
150°	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4
152.5°	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3
155°	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8
157.5°	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7
160°	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3
162.5°	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6
165°	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9
167.5°	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3
170°	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5
172.5°	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1
175°	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0
177.5°	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1460.0	1466.1	1466.1	1467.0	1473.9	1473.0	1472.6
5°	1553.7	1562.9	1564.0	1573.8	1580.2	1578.1	1572.1
7.5°	1642.1	1659.2	1672.2	1679.4	1688.0	1693.3	1690.9
10°	1712.2	1737.1	1752.2	1762.5	1775.0	1784.2	1780.9
12.5°	1775.9	1805.5	1826.3	1843.9	1845.5	1857.3	1849.3
15°	1875.1	1906.4	1909.7	1922.6	1933.0	1931.9	1932.4
17.5°	1907.9	1917.9	1919.9	1920.3	1920.4	1916.6	1908.4
20°	1896.1	1892.4	1883.2	1876.2	1863.7	1862.1	1851.3
22.5°	1840.8	1828.8	1805.7	1790.5	1771.1	1766.0	1763.0
25°	1731.7	1705.2	1668.4	1633.2	1623.5	1604.6	1610.0
27.5°	1582.1	1540.8	1500.9	1472.3	1446.5	1418.1	1426.3
30°	1476.9	1430.4	1374.1	1330.8	1303.3	1276.2	1271.3
32.5°	1351.4	1283.2	1220.5	1182.3	1140.1	1123.0	1104.2
35°	1135.0	1068.4	1006.2	952.7	921.9	898.1	876.4
37.5°	940.4	863.7	813.5	770.1	747.9	734.3	737.7
40°	819.6	752.5	715.8	682.7	662.2	652.4	654.6
42.5°	721.8	671.6	641.3	618.6	604.1	598.8	597.5
45°	610.7	582.6	557.7	544.8	537.8	531.8	528.0
47.5°	535.0	512.1	498.1	490.3	484.2	478.1	478.0
50°	489.6	474.4	464.7	456.6	451.8	447.4	451.2
52.5°	454.9	441.2	431.4	424.1	422.3	418.4	418.3
55°	403.6	392.7	385.7	379.2	376.0	373.8	371.1
57.5°	356.9	346.6	340.1	336.0	329.8	327.6	326.8
60°	323.5	315.4	308.9	303.5	300.8	296.4	296.4
62.5°	292.8	284.7	278.6	274.5	270.0	268.3	268.8
65°	248.3	241.8	235.9	231.5	230.5	227.2	228.3
67.5°	207.4	203.1	196.8	194.4	192.4	190.6	189.3
70°	180.2	175.9	172.6	169.3	167.7	167.7	167.7
72.5°	157.2	152.1	150.1	145.9	146.9	145.2	143.5
75°	121.7	118.5	116.8	115.2	112.5	112.5	112.5
77.5°	89.6	88.6	86.7	85.0	84.3	83.7	84.0
80°	69.2	68.7	67.6	67.6	66.5	66.0	64.9
82.5°	53.2	51.9	51.2	50.7	50.5	50.4	50.2
85°	30.3	29.2	29.2	29.8	28.7	28.7	29.2
87.5°	13.3	13.4	13.0	13.0	13.5	13.1	13.1
90°	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331555-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)