

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331597-927

Luminaire Tested: **S122DIW-S1005D970U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331597-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6553.3 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	2.3
10°-20°	437.4	6.7
20°-30°	634.7	9.7
30°-40°	669.8	10.2
40°-50°	593.0	9.0
50°-60°	473.3	7.2
60°-70°	321.7	4.9
70°-80°	164.9	2.5
80°-90°	42.3	0.6
90°-100°	34.9	0.5
100°-110°	128.0	2.0
110°-120°	342.1	5.2
120°-130°	564.7	8.6
130°-140°	600.5	9.2
140°-150°	558.1	8.5
150°-160°	448.7	6.8
160°-170°	289.2	4.4
170°-180°	99.5	1.5
0°-30°	1222.5	18.7
0°-40°	1892.3	28.9
0°-60°	2958.6	45.1
0°-90°	3487.6	53.2
90°-120°	504.9	7.7
90°-150°	2228.2	34.0
90°-180°	3066.0	46.8
0°-180°	6553.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	36
90°	20	1	20	1	20	11
95°	33	49	33	49	33	30
105°	58	230	58	230	58	60
115°	62	435	62	435	62	155
125°	647	615	647	615	647	560
135°	786	762	786	762	786	606
145°	897	883	897	883	897	561
155°	973	973	973	973	973	449
165°	1023	1025	1023	1025	1023	289
175°	1042	1048	1042	1048	1042	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	16.7	16.6	17.0	16.5	16.5	16.8	16.6	16.0	16.3	16.6	16.9
90°	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8	16.0	15.1	13.8
92.5°	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5	18.0	17.6	16.9
95°	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2	30.3	29.5	28.4
97.5°	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9	40.2	39.5	36.8
100°	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9	44.5	43.2	40.3
102.5°	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8	46.1	44.4	68.3
105°	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9	48.0	46.2	92.1
107.5°	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8	62.7	64.6	119.7
110°	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8	115.7	132.5	181.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4	272.7	334.1	346.1
115°	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2	389.1	467.1	462.9
117.5°	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6	498.4	517.3	514.4
120°	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9	556.9	554.8	551.8
122.5°	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0	591.8	590.6	587.2
125°	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0	640.8	639.6	636.4
127.5°	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3	685.6	683.8	681.4
130°	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0	714.2	712.3	710.4
132.5°	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9	742.4	740.8	738.9
135°	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8	782.1	780.5	778.9
137.5°	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8	819.2	817.5	815.8
140°	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8	843.3	841.8	839.9
142.5°	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9	865.5	864.1	862.1
145°	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9	896.7	895.5	892.6
147.5°	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8	923.9	923.1	920.2
150°	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4	940.4	939.4	936.7
152.5°	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6	955.5	954.5	952.0
155°	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0	976.0	974.9	973.0
157.5°	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2	993.1	991.9	990.5
160°	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2	1003.2	1002.2	1001.2
162.5°	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6	1012.4	1011.3	1010.4
165°	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6	1022.2
167.5°	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5	1033.3	1032.2	1031.7
170°	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4	1038.2	1037.0	1036.7
172.5°	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0	1041.9	1040.7	1040.3
175°	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9	1045.8	1044.6	1044.3
177.5°	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4	1046.5	1045.5	1045.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	17.0	16.8	16.6	17.2	15.4	15.0	12.7	10.9	10.7	10.6	10.0
90°	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3	15.1	15.0	14.8
95°	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2	43.6	38.1	32.6
97.5°	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7	82.0	66.4	50.7
100°	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0	110.9	87.9	64.9
102.5°	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0	169.1	164.2	159.3
105°	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1	235.2	240.2	245.3
107.5°	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1	298.3	302.3	306.3
110°	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3	338.9	342.4	345.9



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1	377.2	380.3	383.5
115°	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2	438.1	441.0	443.9
117.5°	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9	493.1	496.3	499.5
120°	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9	532.4	534.9	537.4
122.5°	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8	566.4	569.1	571.7
125°	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4	617.6	619.8	621.9
127.5°	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2	664.6	667.0	669.5
130°	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9	694.6	697.3	699.9
132.5°	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2	724.5	726.7	729.0
135°	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5	764.2	766.9	769.6
137.5°	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3	803.2	805.1	807.0
140°	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4	828.7	830.0	831.4
142.5°	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1	850.3	851.6	852.8
145°	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4	883.2	883.0	882.9
147.5°	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2	912.5	911.9	911.2
150°	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6	931.4	930.2	929.1
152.5°	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0	947.6	946.3	945.0
155°	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7	971.1	969.6	968.1
157.5°	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3	990.1	988.7	987.5
160°	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1001.2	1000.2	999.2
162.5°	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9	1010.9	1009.9	1008.8
165°	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9	1023.9	1022.9	1021.9
167.5°	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6	1033.6	1032.6	1031.6
170°	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1	1039.0	1038.1	1037.0
172.5°	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7	1042.7	1041.6	1040.7
175°	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4	1047.2	1046.0	1044.9
177.5°	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2	1048.2	1047.3	1046.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	9.9	9.7	9.5	9.7	9.6	9.3	9.0	9.2	9.3	8.6	8.7
90°	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8	17.7	18.5	19.1
92.5°	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5	18.9	19.3	19.6
95°	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2	32.1	32.9	33.2
97.5°	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9	41.5	42.2	42.6
100°	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9	47.2	48.6	49.4
102.5°	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8	49.6	51.3	52.4
105°	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9	51.7	53.6	54.8
107.5°	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8	59.0	57.1	56.5
110°	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8	82.0	65.2	57.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4	150.0	88.6	58.2
115°	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2	233.4	155.5	110.5
117.5°	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6	460.8	442.0	412.6
120°	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9	560.9	562.9	552.5
122.5°	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0	594.2	595.4	593.8
125°	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0	643.2	644.4	645.2
127.5°	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3	689.0	690.7	691.6
130°	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0	717.9	719.7	720.6
132.5°	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9	745.5	747.1	747.8
135°	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8	785.4	787.1	787.8
137.5°	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8	822.4	824.1	824.7
140°	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8	846.3	847.8	848.1
142.5°	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9	868.3	869.7	869.9
145°	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9	899.0	900.2	900.4
147.5°	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8	925.7	926.5	926.6
150°	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4	942.4	943.4	943.5
152.5°	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6	957.5	958.5	958.5
155°	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0	977.9	979.0	978.8
157.5°	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2	995.4	996.5	996.4
160°	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2	1005.2	1006.2	1006.2
162.5°	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6	1014.7	1015.9	1015.7
165°	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4
167.5°	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5	1035.7	1036.9	1036.7
170°	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4	1040.5	1041.7	1041.6
172.5°	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0	1044.2	1045.4	1045.2
175°	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9	1048.1	1049.3	1049.1
177.5°	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4	1048.3	1049.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	8.7	8.3	8.4	8.0	8.4	8.3	8.7	8.7	8.6	9.3	9.2
90°	19.4	19.7	20.1	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8
92.5°	19.8	20.0	20.2	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5
95°	33.0	32.9	32.7	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2
97.5°	42.9	43.0	43.3	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9
100°	49.7	50.1	50.4	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9
102.5°	52.9	53.4	53.9	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8
105°	55.5	56.2	56.9	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9
107.5°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8
110°	57.8	58.5	59.1	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	58.8	59.3	59.9	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4
115°	98.4	86.3	74.1	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2
117.5°	372.8	333.0	293.3	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6
120°	529.9	507.2	484.4	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9
122.5°	589.4	585.0	580.6	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0
125°	645.7	646.2	646.7	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0
127.5°	691.7	691.8	691.9	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3
130°	720.3	720.2	720.0	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0
132.5°	747.6	747.4	747.3	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9
135°	787.5	787.1	786.8	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8
137.5°	824.1	823.5	822.9	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8
140°	847.3	846.4	845.6	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8
142.5°	869.1	868.2	867.4	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9
145°	899.5	898.7	897.9	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9
147.5°	925.9	925.2	924.5	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8
150°	942.7	941.8	941.0	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4
152.5°	957.4	956.3	955.2	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6
155°	977.5	976.1	974.8	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0
157.5°	995.1	993.8	992.4	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2
160°	1005.0	1003.8	1002.7	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2
162.5°	1014.2	1012.8	1011.4	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6
165°	1026.2	1025.0	1023.8	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0
167.5°	1035.2	1033.7	1032.2	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5
170°	1040.1	1038.6	1037.0	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4
172.5°	1043.7	1042.2	1040.7	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0
175°	1047.3	1045.7	1044.0	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9
177.5°	1047.9	1046.7	1045.5	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	9.0	9.3	9.6	9.7	9.5	9.7	9.9	10.0	10.6	10.7	10.9
90°	16.0	15.1	13.8	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8
92.5°	18.0	17.6	16.9	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3
95°	30.3	29.5	28.4	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2
97.5°	40.2	39.5	36.8	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7
100°	44.5	43.2	40.3	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0
102.5°	46.1	44.4	68.3	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0
105°	48.0	46.2	92.1	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1
107.5°	62.7	64.6	119.7	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1
110°	115.7	132.5	181.1	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.7	334.1	346.1	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1
115°	389.1	467.1	462.9	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2
117.5°	498.4	517.3	514.4	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9
120°	556.9	554.8	551.8	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9
122.5°	591.8	590.6	587.2	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8
125°	640.8	639.6	636.4	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4
127.5°	685.6	683.8	681.4	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2
130°	714.2	712.3	710.4	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9
132.5°	742.4	740.8	738.9	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2
135°	782.1	780.5	778.9	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5
137.5°	819.2	817.5	815.8	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3
140°	843.3	841.8	839.9	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4
142.5°	865.5	864.1	862.1	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1
145°	896.7	895.5	892.6	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4
147.5°	923.9	923.1	920.2	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2
150°	940.4	939.4	936.7	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6
152.5°	955.5	954.5	952.0	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0
155°	976.0	974.9	973.0	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7
157.5°	993.1	991.9	990.5	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3
160°	1003.2	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2
162.5°	1012.4	1011.3	1010.4	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9
165°	1023.8	1022.6	1022.2	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9
167.5°	1033.3	1032.2	1031.7	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6
170°	1038.2	1037.0	1036.7	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1
172.5°	1041.9	1040.7	1040.3	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7
175°	1045.8	1044.6	1044.3	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4
177.5°	1046.5	1045.5	1045.4	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.7	15.0	15.4	17.2	16.6	16.8	17.0	16.9	16.6	16.3	16.0
90°	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8
92.5°	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5
95°	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2
97.5°	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9
100°	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9
102.5°	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8
105°	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9
107.5°	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8
110°	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4
115°	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2
117.5°	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6
120°	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9
122.5°	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0
125°	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0
127.5°	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3
130°	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0
132.5°	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9
135°	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8
137.5°	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8
140°	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8
142.5°	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9
145°	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9
147.5°	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8
150°	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4
152.5°	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6
155°	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0
157.5°	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2
160°	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2
162.5°	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6
165°	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0
167.5°	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5
170°	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4
172.5°	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0
175°	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9
177.5°	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	16.6	16.8	16.5	16.5	17.0	16.6	16.7
90°	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331597-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)