

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331601-927

Luminaire Tested: **S122DIW-S1005D970U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331601-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6280.5 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	1.9
10°-20°	334.1	5.3
20°-30°	491.0	7.8
30°-40°	570.4	9.1
40°-50°	569.8	9.1
50°-60°	496.9	7.9
60°-70°	367.4	5.8
70°-80°	208.1	3.3
80°-90°	58.5	0.9
90°-100°	34.9	0.6
100°-110°	128.0	2.0
110°-120°	342.1	5.4
120°-130°	564.7	9.0
130°-140°	600.5	9.6
140°-150°	558.1	8.9
150°-160°	448.7	7.1
160°-170°	289.2	4.6
170°-180°	99.5	1.6
0°-30°	943.8	15.0
0°-40°	1514.2	24.1
0°-60°	2580.8	41.1
0°-90°	3214.8	51.2
90°-120°	504.9	8.0
90°-150°	2228.2	35.5
90°-180°	3066.0	48.8
0°-180°	6280.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	9	15	19	20	5
95°	49	26	30	33	33	60
105°	230	240	46	54	58	246
115°	435	448	467	133	62	428
125°	615	626	640	645	647	549
135°	762	773	780	787	786	588
145°	883	883	896	900	897	552
155°	973	967	975	979	973	448
165°	1025	1021	1023	1027	1023	289
175°	1048	1043	1045	1049	1042	100
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.7	17.6	17.5	17.4	17.3	17.3	17.1	17.0	16.8	16.6	16.2
90°	0.8	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0
92.5°	15.3	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0
95°	49.2	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3
97.5°	97.7	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2
100°	134.0	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5
102.5°	174.0	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1
105°	230.1	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0
107.5°	294.1	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7
110°	335.3	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.1	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7
115°	435.2	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1
117.5°	489.9	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4
120°	529.9	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9
122.5°	563.8	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8
125°	615.4	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8
127.5°	662.2	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6
130°	691.9	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2
132.5°	722.2	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4
135°	761.5	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1
137.5°	801.3	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2
140°	827.4	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3
142.5°	849.1	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5
145°	883.4	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7
147.5°	913.2	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9
150°	932.6	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4
152.5°	949.0	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5
155°	972.7	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0
157.5°	991.3	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1
160°	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2
162.5°	1011.9	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4
165°	1024.9	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8
167.5°	1034.6	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3
170°	1040.1	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2
172.5°	1043.7	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9
175°	1048.4	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8
177.5°	1049.2	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	15.7	15.2	14.7	14.4	14.3	14.1	13.9	13.8
90°	16.8	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.5	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	31.2	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	40.9	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	45.9	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	47.8	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	49.9	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	60.8	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	98.8	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331601-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	211.4	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	311.2	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	479.6	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	558.9	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	593.0	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	642.0	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	687.3	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	716.0	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	743.9	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	783.8	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	820.8	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	844.8	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	866.9	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	897.9	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	924.8	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	941.4	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	956.6	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.0	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	994.2	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1004.2	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1013.6	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1034.5	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1039.4	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1043.0	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1046.9	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1047.4	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)