

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331863-930

Luminaire Tested: **S122RDIW-S1005D1440U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331863-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7539.8 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18				
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.7
10°-20°	354.8	4.7
20°-30°	498.3	6.6
30°-40°	543.4	7.2
40°-50°	499.6	6.6
50°-60°	392.4	5.2
60°-70°	255.8	3.4
70°-80°	131.9	1.7
80°-90°	38.2	0.5
90°-100°	53.5	0.7
100°-110°	196.0	2.6
110°-120°	524.0	6.9
120°-130°	865.0	11.5
130°-140°	919.9	12.2
140°-150°	855.0	11.3
150°-160°	687.4	9.1
160°-170°	443.0	5.9
170°-180°	152.5	2.0
0°-30°	982.4	13.0
0°-40°	1525.7	20.2
0°-60°	2417.7	32.1
0°-90°	2843.6	37.7
90°-120°	773.5	10.3
90°-150°	3413.3	45.3
90°-180°	4696.0	62.3
0°-180°	7539.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	14	23	29	31	6
95°	75	40	45	51	50	92
105°	352	368	71	83	88	377
115°	667	687	715	204	95	656
125°	943	958	980	988	991	840
135°	1166	1185	1196	1206	1205	901
145°	1353	1353	1372	1379	1374	846
155°	1490	1481	1494	1500	1491	686
165°	1570	1564	1566	1574	1566	443
175°	1606	1598	1600	1607	1597	153
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.2	15.0	13.8	12.6	11.4	11.0	11.4	11.8	12.2	12.6	12.6
90°	1.1	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5
92.5°	23.4	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6
95°	75.3	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5
97.5°	149.6	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6
100°	205.2	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2
102.5°	266.4	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6
105°	352.5	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5
107.5°	450.6	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1
110°	513.7	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	573.1	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8
115°	666.8	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1
117.5°	750.5	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6
120°	811.7	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0
122.5°	863.6	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5
125°	942.7	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6
127.5°	1014.4	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2
130°	1059.8	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0
132.5°	1106.2	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2
135°	1166.5	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1
137.5°	1227.5	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8
140°	1267.4	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8
142.5°	1300.8	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8
145°	1353.2	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5
147.5°	1398.9	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3
150°	1428.6	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6
152.5°	1453.6	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7
155°	1490.0	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0
157.5°	1518.6	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3
160°	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8
162.5°	1550.0	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9
165°	1570.0	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4
167.5°	1584.9	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0
170°	1593.3	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4
172.5°	1598.8	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9
175°	1606.0	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0
177.5°	1607.1	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	12.7	12.7	12.8	12.9	13.0	13.0	13.1	13.3
90°	25.8	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.2	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	47.8	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	62.6	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	70.2	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	73.3	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	76.4	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	93.3	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	151.4	125.6	99.9	87.5	88.5	89.5	90.6	91.6



TEST NUMBER: P331863-930

CATALOG NUMBER: S122RDIW-S1005D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	323.8	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	476.9	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	734.7	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	856.1	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	908.4	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	983.4	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1052.8	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1096.8	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1139.5	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1200.6	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1257.4	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1294.0	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1328.0	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1375.3	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1416.7	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1442.1	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1465.3	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1496.6	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1523.0	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1538.3	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1552.7	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1584.8	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1592.2	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1597.7	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1603.8	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1604.4	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)