

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331483-927

Luminaire Tested: **S122DIW-S290D1240U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331483-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4961.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	50	46	42	39	33	30	28	21	20	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	0.9
10°-20°	129.6	2.6
20°-30°	188.1	3.8
30°-40°	198.5	4.0
40°-50°	175.8	3.5
50°-60°	140.3	2.8
60°-70°	95.4	1.9
70°-80°	48.9	1.0
80°-90°	15.1	0.3
90°-100°	44.7	0.9
100°-110°	163.8	3.3
110°-120°	437.9	8.8
120°-130°	722.9	14.6
130°-140°	768.8	15.5
140°-150°	714.5	14.4
150°-160°	574.5	11.6
160°-170°	370.2	7.5
170°-180°	127.4	2.6
0°-30°	362.4	7.3
0°-40°	560.9	11.3
0°-60°	877.0	17.7
0°-90°	1036.3	20.9
90°-120°	646.4	13.0
90°-150°	2852.5	57.5
90°-180°	3925.0	79.1
0°-180°	4961.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	26	1	26	1	26	12
95°	42	63	42	63	42	39
105°	74	295	74	295	74	77
115°	80	557	80	557	80	199
125°	828	788	828	788	828	717
135°	1007	975	1007	975	1007	776
145°	1148	1131	1148	1131	1148	718
155°	1246	1245	1246	1245	1246	575
165°	1309	1312	1309	1312	1309	370
175°	1334	1342	1334	1342	1334	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	9.0	8.9	9.0	8.7	8.6	8.6	8.4	8.1	8.0	7.9	7.7
90°	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5	20.4	19.4	17.7
92.5°	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6	23.1	22.5	21.6
95°	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9	38.9	37.8	36.3
97.5°	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3	51.4	50.6	47.1
100°	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7	57.0	55.2	51.6
102.5°	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2	59.0	56.8	87.4
105°	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8	61.5	59.1	117.9
107.5°	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0	80.3	82.8	153.3
110°	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5	148.1	169.6	231.8



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6	349.2	427.7	443.1
115°	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5	498.2	597.9	592.6
117.5°	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0	638.1	662.3	658.5
120°	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5	712.9	710.3	706.5
122.5°	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1	757.6	756.1	751.9
125°	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9	820.4	818.9	814.8
127.5°	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8	877.7	875.4	872.4
130°	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6	914.3	911.9	909.5
132.5°	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4	950.3	948.3	945.9
135°	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4	1001.2	999.1	997.1
137.5°	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8	1048.7	1046.6	1044.3
140°	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5	1079.5	1077.6	1075.2
142.5°	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8	1108.0	1106.3	1103.5
145°	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4	1147.9	1146.4	1142.7
147.5°	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9	1182.8	1181.6	1178.1
150°	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1	1203.9	1202.6	1199.1
152.5°	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6	1223.3	1221.9	1218.7
155°	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7	1249.4	1248.2	1245.5
157.5°	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8	1271.3	1269.9	1268.0
160°	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6	1284.3	1283.0	1281.8
162.5°	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6	1296.1	1294.7	1293.6
165°	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2	1308.5
167.5°	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4	1322.9	1321.4	1320.8
170°	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6	1329.1	1327.6	1327.1
172.5°	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2	1333.7	1332.2	1331.8
175°	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3	1338.8	1337.3	1336.9
177.5°	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8	1339.7	1338.5	1338.2
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	7.5	7.1	6.8	6.7	5.8	5.3	4.3	3.3	3.7	4.0	4.2
90°	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6	19.3	19.2	18.9
95°	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0	55.8	48.8	41.7
97.5°	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0	105.0	84.9	65.0
100°	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5	142.0	112.5	83.0
102.5°	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7	216.4	210.2	204.0
105°	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6	301.0	307.5	313.9
107.5°	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6	381.8	387.0	392.2
110°	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3	433.8	438.3	442.8



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9	482.9	486.9	490.9
115°	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2	560.9	564.5	568.2
117.5°	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2	631.3	635.3	639.4
120°	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3	681.6	684.8	688.0
122.5°	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8	725.2	728.6	732.0
125°	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8	790.6	793.4	796.2
127.5°	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7	850.8	853.9	857.1
130°	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7	889.1	892.6	896.0
132.5°	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5	927.4	930.3	933.3
135°	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9	978.3	981.8	985.2
137.5°	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8	1028.3	1030.6	1033.1
140°	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1	1060.9	1062.6	1064.3
142.5°	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1	1088.6	1090.2	1091.7
145°	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8	1130.7	1130.4	1130.2
147.5°	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0	1168.2	1167.4	1166.6
150°	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9	1192.4	1190.9	1189.3
152.5°	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8	1213.1	1211.4	1209.7
155°	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2	1243.3	1241.3	1239.4
157.5°	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1	1267.4	1265.7	1264.2
160°	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1281.8	1280.4	1279.1
162.5°	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5	1294.1	1292.8	1291.6
165°	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1	1310.8	1309.5	1308.2
167.5°	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5	1323.2	1321.9	1320.6
170°	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5	1330.2	1328.9	1327.6
172.5°	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1	1334.8	1333.6	1332.2
175°	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1	1340.6	1339.1	1337.6
177.5°	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1	1341.9	1340.7	1339.5
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.5	4.8	5.0	5.3	5.5	5.8	5.8	6.0	6.3	6.2	6.3
90°	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5	22.6	23.7	24.5
92.5°	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6	24.2	24.7	25.1
95°	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9	41.0	42.1	42.5
97.5°	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3	53.2	54.0	54.6
100°	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7	60.4	62.1	63.2
102.5°	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2	63.5	65.8	67.2
105°	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8	66.2	68.6	70.2
107.5°	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0	75.5	73.1	72.3
110°	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5	105.0	83.4	73.1



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6	192.1	113.5	74.5
115°	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5	298.8	199.1	141.5
117.5°	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0	589.9	565.8	528.2
120°	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5	718.0	720.6	707.4
122.5°	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1	760.7	762.2	760.2
125°	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9	823.4	824.9	825.9
127.5°	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8	882.0	884.2	885.4
130°	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6	919.0	921.3	922.4
132.5°	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4	954.3	956.4	957.3
135°	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4	1005.5	1007.7	1008.5
137.5°	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8	1052.9	1055.0	1055.7
140°	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5	1083.4	1085.4	1085.8
142.5°	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8	1111.6	1113.3	1113.6
145°	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4	1150.9	1152.4	1152.6
147.5°	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9	1185.0	1186.1	1186.2
150°	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1	1206.5	1207.8	1207.8
152.5°	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6	1225.8	1227.2	1227.1
155°	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7	1252.0	1253.3	1253.1
157.5°	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8	1274.2	1275.7	1275.6
160°	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6	1286.9	1288.2	1288.1
162.5°	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6	1299.0	1300.5	1300.3
165°	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2
167.5°	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4	1325.9	1327.4	1327.2
170°	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6	1332.1	1333.6	1333.4
172.5°	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2	1336.7	1338.2	1338.1
175°	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3	1341.8	1343.3	1343.0
177.5°	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8	1342.0	1343.3	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	6.4	6.3	6.4	6.4	6.4	6.3	6.4	6.3	6.2	6.3	6.0
90°	24.9	25.3	25.7	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5
92.5°	25.3	25.7	25.9	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6
95°	42.3	42.1	41.9	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9
97.5°	54.8	55.1	55.4	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3
100°	63.6	64.1	64.5	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7
102.5°	67.7	68.4	69.0	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2
105°	71.1	71.9	72.8	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8
107.5°	73.2	74.1	74.9	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0
110°	74.0	74.9	75.7	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	75.3	76.0	76.6	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6
115°	126.0	110.5	95.0	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5
117.5°	477.3	426.4	375.4	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0
120°	678.3	649.3	620.2	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5
122.5°	754.6	748.9	743.3	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1
125°	826.6	827.3	827.9	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9
127.5°	885.5	885.7	885.7	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8
130°	922.2	922.0	921.8	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6
132.5°	957.1	956.9	956.6	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4
135°	1008.1	1007.7	1007.3	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4
137.5°	1054.9	1054.2	1053.5	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8
140°	1084.7	1083.6	1082.5	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5
142.5°	1112.6	1111.5	1110.4	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8
145°	1151.5	1150.5	1149.4	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4
147.5°	1185.3	1184.4	1183.5	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9
150°	1206.8	1205.7	1204.6	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1
152.5°	1225.7	1224.2	1222.8	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6
155°	1251.3	1249.7	1247.9	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7
157.5°	1273.9	1272.2	1270.6	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8
160°	1286.6	1285.1	1283.6	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6
162.5°	1298.5	1296.6	1294.7	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6
165°	1313.7	1312.2	1310.7	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2
167.5°	1325.2	1323.3	1321.4	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4
170°	1331.5	1329.5	1327.6	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6
172.5°	1336.1	1334.2	1332.2	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2
175°	1340.8	1338.7	1336.5	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3
177.5°	1341.6	1340.0	1338.5	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	5.8	5.8	5.5	5.3	5.0	4.8	4.5	4.2	4.0	3.7	3.3
90°	20.4	19.4	17.7	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0
92.5°	23.1	22.5	21.6	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6
95°	38.9	37.8	36.3	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0
97.5°	51.4	50.6	47.1	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0
100°	57.0	55.2	51.6	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5
102.5°	59.0	56.8	87.4	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7
105°	61.5	59.1	117.9	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6
107.5°	80.3	82.8	153.3	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6
110°	148.1	169.6	231.8	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.2	427.7	443.1	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9
115°	498.2	597.9	592.6	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2
117.5°	638.1	662.3	658.5	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2
120°	712.9	710.3	706.5	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3
122.5°	757.6	756.1	751.9	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8
125°	820.4	818.9	814.8	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8
127.5°	877.7	875.4	872.4	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7
130°	914.3	911.9	909.5	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7
132.5°	950.3	948.3	945.9	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5
135°	1001.2	999.1	997.1	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9
137.5°	1048.7	1046.6	1044.3	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8
140°	1079.5	1077.6	1075.2	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1
142.5°	1108.0	1106.3	1103.5	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1
145°	1147.9	1146.4	1142.7	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8
147.5°	1182.8	1181.6	1178.1	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0
150°	1203.9	1202.6	1199.1	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9
152.5°	1223.3	1221.9	1218.7	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8
155°	1249.4	1248.2	1245.5	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2
157.5°	1271.3	1269.9	1268.0	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1
160°	1284.3	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0
162.5°	1296.1	1294.7	1293.6	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5
165°	1310.7	1309.2	1308.5	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1
167.5°	1322.9	1321.4	1320.8	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5
170°	1329.1	1327.6	1327.1	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5
172.5°	1333.7	1332.2	1331.8	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1
175°	1338.8	1337.3	1336.9	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1
177.5°	1339.7	1338.5	1338.2	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.3	5.3	5.8	6.7	6.8	7.1	7.5	7.7	7.9	8.0	8.1
90°	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5
92.5°	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6
95°	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9
97.5°	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3
100°	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7
102.5°	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2
105°	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8
107.5°	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0
110°	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6
115°	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5
117.5°	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0
120°	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5
122.5°	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1
125°	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9
127.5°	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8
130°	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6
132.5°	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4
135°	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4
137.5°	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8
140°	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5
142.5°	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8
145°	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4
147.5°	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9
150°	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1
152.5°	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6
155°	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7
157.5°	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8
160°	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6
162.5°	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6
165°	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2
167.5°	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4
170°	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6
172.5°	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2
175°	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3
177.5°	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	8.4	8.6	8.6	8.7	9.0	8.9	9.0
90°	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331483-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)