

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331494-927

Luminaire Tested: **S122DIW-S290D1440U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331494-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4915.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	47	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	31	29	27	19	18	17	12
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	14	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	46	39	33	51	41	35	30	32	27	24	22	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10	7
8	49	38	30	25	43	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	0.7
10°-20°	99.0	2.0
20°-30°	145.6	3.0
30°-40°	169.1	3.4
40°-50°	168.9	3.4
50°-60°	147.3	3.0
60°-70°	108.9	2.2
70°-80°	61.7	1.3
80°-90°	22.2	0.5
90°-100°	89.7	1.8
100°-110°	278.5	5.7
110°-120°	476.1	9.7
120°-130°	626.1	12.7
130°-140°	702.7	14.3
140°-150°	689.0	14.0
150°-160°	577.9	11.8
160°-170°	383.3	7.8
170°-180°	134.0	2.7
0°-30°	279.8	5.7
0°-40°	448.8	9.1
0°-60°	765.0	15.6
0°-90°	957.8	19.5
90°-120°	844.3	17.2
90°-150°	2862.0	58.2
90°-180°	3957.0	80.5
0°-180°	4915.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	16	42	40	41	4
95°	62	74	76	76	74	71
105°	257	260	263	265	265	271
115°	478	484	482	481	478	472
125°	695	705	702	699	697	621
135°	899	912	915	914	910	694
145°	1092	1100	1107	1108	1104	682
155°	1248	1252	1255	1261	1258	574
165°	1358	1357	1357	1364	1359	383
175°	1413	1409	1407	1414	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.4	5.9	6.4	7.0	7.4	8.2	9.3	10.3	11.3	12.4	12.1
90°	1.2	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3
92.5°	21.2	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1
95°	62.1	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4
97.5°	113.4	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5
100°	151.7	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8
102.5°	191.8	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2
105°	256.7	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2
107.5°	322.2	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6
110°	364.2	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.1	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7
115°	477.7	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2
117.5°	545.1	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3
120°	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9
122.5°	631.1	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2
125°	695.1	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4
127.5°	757.4	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7
130°	796.5	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2
132.5°	840.5	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5
135°	899.3	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6
137.5°	961.2	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8
140°	998.4	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1
142.5°	1036.6	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6
145°	1091.5	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3
147.5°	1140.5	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0
150°	1173.9	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7
152.5°	1203.6	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5
155°	1248.0	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5
157.5°	1285.9	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3
160°	1308.9	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1
162.5°	1329.9	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4
165°	1357.9	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5
167.5°	1381.2	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3
170°	1393.7	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8
172.5°	1402.3	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4
175°	1412.8	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7
177.5°	1417.1	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	11.8	11.5	11.2	11.0	11.0	11.0	11.0	11.0
90°	40.7	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.2	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.4	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	263.8	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	327.9	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331494-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.0	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	482.0	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.7	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	634.5	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	700.6	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	764.8	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.7	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	851.4	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.3	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.5	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1051.9	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.6	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1156.5	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1257.8	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1294.1	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1315.7	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1335.2	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1360.4	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1381.2	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1392.7	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1401.2	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1410.6	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)