

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331779-930

Luminaire Tested: **S122RDIW-S290D1240U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331779-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1240U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4884.3 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11
4	69	59	52	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	42	35	30	32	27	24	22	19	17	14	12	11	7
7	54	42	35	29	47	37	31	27	29	24	21	20	17	15	12	11	10	7
8	50	38	31	26	44	34	28	23	26	21	18	18	16	13	11	10	9	6
9	46	35	28	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5
10	43	32	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	0.8
10°-20°	105.2	2.2
20°-30°	147.7	3.0
30°-40°	161.1	3.3
40°-50°	148.1	3.0
50°-60°	116.3	2.4
60°-70°	75.8	1.6
70°-80°	39.1	0.8
80°-90°	13.5	0.3
90°-100°	46.0	0.9
100°-110°	168.6	3.5
110°-120°	450.7	9.2
120°-130°	744.0	15.2
130°-140°	791.2	16.2
140°-150°	735.4	15.1
150°-160°	591.2	12.1
160°-170°	381.0	7.8
170°-180°	131.1	2.7
0°-30°	291.2	6.0
0°-40°	452.3	9.3
0°-60°	716.7	14.7
0°-90°	845.1	17.3
90°-120°	665.3	13.6
90°-150°	2935.8	60.1
90°-180°	4039.0	82.7
0°-180°	4884.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	12	20	25	27	4
95°	65	34	39	44	43	79
105°	303	316	61	71	76	324
115°	574	591	615	175	82	564
125°	811	824	843	850	853	723
135°	1003	1019	1028	1038	1036	775
145°	1164	1164	1180	1186	1182	728
155°	1282	1274	1285	1290	1282	590
165°	1350	1345	1347	1354	1347	381
175°	1381	1375	1376	1382	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	5.0	4.9	4.9	4.8	4.8	5.0	5.3	5.6	6.0	6.4	6.5
90°	1.0	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0
92.5°	20.1	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7
95°	64.8	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0
97.5°	128.7	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9
100°	176.5	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6
102.5°	229.2	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7
105°	303.2	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3
107.5°	387.6	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7
110°	441.8	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.8	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4
115°	573.5	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7
117.5°	645.5	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7
120°	698.1	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7
122.5°	742.8	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7
125°	810.8	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3
127.5°	872.5	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3
130°	911.6	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9
132.5°	951.5	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0
135°	1003.3	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5
137.5°	1055.7	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3
140°	1090.1	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0
142.5°	1118.8	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4
145°	1163.8	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4
147.5°	1203.1	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3
150°	1228.7	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0
152.5°	1250.3	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0
155°	1281.6	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9
157.5°	1306.1	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4
160°	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8
162.5°	1333.3	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9
165°	1350.4	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9
167.5°	1363.2	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5
170°	1370.4	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9
172.5°	1375.1	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6
175°	1381.3	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9
177.5°	1382.3	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	6.7	6.8	7.0	7.1	7.2	7.3	7.3	7.4
90°	22.2	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.3	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	41.1	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	53.8	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	60.4	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	63.0	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	65.7	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	80.2	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	130.2	108.0	85.9	75.3	76.1	77.0	77.9	78.8



TEST NUMBER: P331779-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.5	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	410.1	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	631.9	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	736.4	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	781.3	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	845.9	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	905.5	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	943.4	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	980.2	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1032.7	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1081.4	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1113.0	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1142.2	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1182.9	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1218.5	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1240.3	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1260.3	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1287.2	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1309.9	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1323.1	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1335.5	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1363.0	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1369.5	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1374.2	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1379.4	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1380.0	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)